

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332821-840

Luminaire Tested: **S124DIW-S1020D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332821-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8707.1 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51														
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	43	43	43														
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36	36	36	36	36	36	36														
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	31	31	31														
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	26	26	26														
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23	23	23	23	23														
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20	20	20	20	20	20	20														
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18	18	18	18	18	18	18														
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	16	16	16														
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	14	14	14														
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	1.9
10°-20°	462.4	5.3
20°-30°	680.5	7.8
30°-40°	791.1	9.1
40°-50°	791.2	9.1
50°-60°	692.1	7.9
60°-70°	514.0	5.9
70°-80°	292.0	3.4
80°-90°	88.2	1.0
90°-100°	46.8	0.5
100°-110°	298.3	3.4
110°-120°	570.7	6.6
120°-130°	724.4	8.3
130°-140°	775.1	8.9
140°-150°	724.8	8.3
150°-160°	584.5	6.7
160°-170°	377.0	4.3
170°-180°	129.9	1.5
0°-30°	1307.0	15.0
0°-40°	2098.1	24.1
0°-60°	3581.3	41.1
0°-90°	4475.5	51.4
90°-120°	915.8	10.5
90°-150°	3140.1	36.1
90°-180°	4232.0	48.6
0°-180°	8707.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	3	14	22	28	31	7
95°	56	23	22	28	30	72
105°	308	314	319	326	292	322
115°	575	578	577	579	579	566
125°	808	812	810	813	814	721
135°	1003	1002	1006	1008	1010	772
145°	1156	1159	1159	1160	1162	722
155°	1268	1268	1266	1269	1267	584
165°	1337	1332	1332	1339	1331	378
175°	1368	1362	1363	1371	1360	130
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.7	29.9	30.2	30.4	30.7	30.8	31.0	31.1	31.2	31.3	31.6
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	12.9	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0
95°	56.2	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8
97.5°	119.5	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2
100°	167.8	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2
102.5°	221.9	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2
105°	308.0	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2
107.5°	388.0	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0
110°	442.0	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	494.4	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7
115°	575.0	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5
117.5°	647.6	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9
120°	696.8	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3
122.5°	742.7	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8
125°	808.3	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0
127.5°	870.5	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2
130°	910.6	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9
132.5°	947.5	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4
135°	1002.7	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2
137.5°	1051.6	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0
140°	1083.6	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3
142.5°	1112.2	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6
145°	1156.2	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5
147.5°	1191.1	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1
150°	1216.6	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6
152.5°	1237.8	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6
155°	1267.7	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6
157.5°	1292.9	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0
160°	1307.6	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8
162.5°	1320.7	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2
165°	1337.3	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0
167.5°	1350.4	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5
170°	1357.8	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4
172.5°	1362.6	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4
175°	1368.0	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9
177.5°	1370.4	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	31.8	32.1	32.4	32.6	32.7	32.7	32.8	32.9
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	24.4	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	25.2	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.3	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	37.3	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	133.5	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	323.4	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	400.0	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.1	452.6	453.0	453.6	454.3	454.9	455.7	456.4



TEST NUMBER: P332821-840

CATALOG NUMBER: S124DIW-S1020D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	502.6	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	577.9	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.1	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	811.7	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	876.0	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.1	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.6	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1006.7	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1057.5	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.0	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.1	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.7	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.3	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.0	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1267.5	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1318.5	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1335.8	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1348.5	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1356.2	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1361.2	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1367.0	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1369.3	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)