

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332755-930

Luminaire Tested: **S124DIW-S575D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332755-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D770U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4537.0 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45					45			
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38					38			
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32					32			
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27					27			
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23					23			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20					20			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17					17			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16					16			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14					14			
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13					13			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11					11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	1.6
10°-20°	210.1	4.6
20°-30°	309.2	6.8
30°-40°	359.5	7.9
40°-50°	359.5	7.9
50°-60°	314.5	6.9
60°-70°	233.5	5.1
70°-80°	132.7	2.9
80°-90°	40.6	0.9
90°-100°	27.7	0.6
100°-110°	176.5	3.9
110°-120°	337.5	7.4
120°-130°	428.5	9.4
130°-140°	458.5	10.1
140°-150°	428.7	9.4
150°-160°	345.7	7.6
160°-170°	223.0	4.9
170°-180°	76.9	1.7
0°-30°	593.9	13.1
0°-40°	953.4	21.0
0°-60°	1627.3	35.9
0°-90°	2034.1	44.8
90°-120°	541.7	11.9
90°-150°	1857.3	40.9
90°-180°	2503.0	55.2
0°-180°	4537.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	2	8	13	17	18	3
95°	33	14	13	17	18	43
105°	182	186	189	193	172	191
115°	340	342	341	342	342	335
125°	478	480	479	481	482	427
135°	593	593	595	596	597	457
145°	684	686	686	686	688	427
155°	750	750	749	751	749	346
165°	791	788	788	792	787	223
175°	809	806	806	811	804	77
180°	809	809	809	809	809	



TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.5	13.8	13.9	14.1	14.3	14.4	14.5	14.7	14.8	14.8	15.0
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	7.7	7.7	7.8	7.8	7.9	8.6	9.6	10.7	11.7	12.8	13.6
95°	33.3	28.7	24.1	19.6	15.0	12.8	12.9	13.0	13.2	13.3	14.1
97.5°	70.7	73.5	76.4	79.2	82.1	76.0	61.0	46.0	31.0	16.0	16.1
100°	99.2	101.7	104.1	106.5	108.9	100.9	82.3	63.8	45.2	26.7	24.4
102.5°	131.2	133.0	134.8	136.6	138.3	137.9	135.6	133.1	130.7	128.3	103.6
105°	182.1	183.0	183.8	184.6	185.4	186.1	186.8	187.4	188.2	188.8	190.0
107.5°	229.5	229.9	230.3	230.7	231.1	231.8	232.7	233.6	234.5	235.4	236.0
110°	261.5	261.9	262.3	262.7	263.0	263.7	264.5	265.3	266.1	266.8	267.2



TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.4	293.2	293.9	294.6	295.3	295.9	296.3	296.6	297.0	297.4	297.3
115°	340.1	340.6	341.0	341.3	341.7	341.9	341.7	341.6	341.4	341.3	341.6
117.5°	383.1	383.6	384.2	384.7	385.2	385.6	386.0	386.2	386.5	386.9	386.8
120°	412.1	412.7	413.2	413.8	414.3	414.5	414.3	414.3	414.1	413.9	414.3
122.5°	439.3	439.5	439.9	440.2	440.5	440.8	441.0	441.2	441.3	441.6	441.7
125°	478.1	478.7	479.2	479.7	480.2	480.4	480.1	479.9	479.6	479.3	479.7
127.5°	514.9	515.0	515.2	515.3	515.4	515.8	516.4	517.1	517.6	518.3	518.2
130°	538.6	538.7	538.9	539.0	539.2	539.4	539.8	540.2	540.6	541.0	541.2
132.5°	560.4	560.7	560.9	561.1	561.3	561.7	562.2	562.8	563.3	563.8	563.9
135°	593.0	593.0	592.8	592.6	592.6	592.7	593.3	593.8	594.4	594.9	595.2
137.5°	622.0	622.1	622.2	622.2	622.2	622.6	623.1	623.7	624.4	624.9	625.2
140°	640.9	641.2	641.4	641.7	642.0	642.2	642.5	642.8	643.0	643.4	643.7
142.5°	657.9	658.4	658.8	659.3	659.7	660.1	660.2	660.4	660.6	660.7	661.0
145°	683.9	684.3	684.7	685.1	685.5	685.7	685.7	685.7	685.7	685.7	685.8
147.5°	704.6	705.3	706.0	706.8	707.6	707.8	707.8	707.6	707.4	707.4	707.4
150°	719.6	720.1	720.6	721.2	721.7	721.9	721.8	721.6	721.5	721.4	721.4
152.5°	732.1	732.5	733.0	733.4	733.9	733.9	733.7	733.5	733.3	733.0	733.2
155°	749.8	750.0	750.1	750.2	750.4	750.2	749.8	749.4	749.0	748.6	749.2
157.5°	764.8	764.7	764.6	764.5	764.4	764.1	763.7	763.2	762.7	762.3	763.0
160°	773.4	773.0	772.7	772.3	771.8	771.5	771.4	771.3	771.1	771.0	771.8
162.5°	781.1	780.6	780.2	779.7	779.1	778.8	778.7	778.5	778.4	778.3	779.1
165°	791.0	790.3	789.6	789.0	788.3	788.0	788.0	788.0	788.0	788.0	789.0
167.5°	798.7	798.0	797.4	796.6	795.9	795.6	795.5	795.4	795.3	795.2	796.4
170°	803.1	802.3	801.4	800.6	799.9	799.5	799.6	799.8	799.9	800.1	801.1
172.5°	806.0	805.2	804.4	803.6	802.7	802.4	802.6	802.7	802.8	803.0	804.0
175°	809.1	808.3	807.6	806.7	805.9	805.6	805.7	805.8	806.0	806.1	807.3
177.5°	810.6	809.8	809.1	808.3	807.6	807.3	807.6	807.7	808.0	808.1	809.0
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1



TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	15.2	15.3	15.5	15.6	15.7	15.7	15.7	15.8
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	14.4	15.2	16.1	16.5	16.6	16.6	16.6	16.7
95°	14.9	15.7	16.6	17.0	17.1	17.3	17.4	17.5
97.5°	16.1	16.2	16.3	16.4	16.6	16.7	16.8	17.0
100°	22.1	19.7	17.4	16.4	16.6	16.7	16.8	17.0
102.5°	79.0	54.3	29.7	17.3	17.4	17.4	17.4	17.4
105°	191.3	192.4	193.6	191.8	187.0	182.1	177.3	172.5
107.5°	236.6	237.2	237.8	238.3	238.9	239.4	239.9	240.4
110°	267.4	267.7	268.0	268.3	268.7	269.1	269.5	269.9





TEST NUMBER: P332755-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.3	297.3	297.2	297.4	297.9	298.4	299.0	299.5
115°	341.9	342.1	342.4	342.5	342.5	342.5	342.5	342.5
117.5°	386.7	386.7	386.6	386.5	386.5	386.5	386.4	386.4
120°	414.5	414.7	415.0	415.0	414.7	414.5	414.3	413.9
122.5°	441.9	442.1	442.2	442.1	441.9	441.6	441.3	441.1
125°	480.1	480.5	480.9	481.2	481.4	481.4	481.6	481.8
127.5°	518.1	518.0	518.0	517.9	517.8	517.6	517.6	517.5
130°	541.3	541.4	541.6	541.6	541.6	541.6	541.6	541.6
132.5°	564.0	564.2	564.4	564.4	564.3	564.1	564.0	563.9
135°	595.4	595.7	596.0	596.2	596.5	596.8	597.0	597.3
137.5°	625.5	625.8	626.1	626.2	626.1	626.1	626.0	625.9
140°	644.1	644.5	644.9	645.2	645.3	645.5	645.6	645.7
142.5°	661.4	661.6	661.9	662.1	662.1	662.1	662.2	662.2
145°	685.9	686.1	686.2	686.4	686.6	687.0	687.2	687.5
147.5°	707.5	707.7	707.8	707.9	708.0	708.2	708.3	708.4
150°	721.4	721.4	721.4	721.5	721.6	721.7	721.9	721.9
152.5°	733.4	733.6	733.9	733.9	733.9	733.8	733.7	733.6
155°	749.7	750.2	750.7	750.8	750.4	750.0	749.6	749.3
157.5°	763.7	764.4	765.1	765.1	764.4	763.7	763.0	762.3
160°	772.7	773.4	774.2	774.2	773.4	772.7	771.8	771.0
162.5°	779.9	780.6	781.5	781.5	780.6	779.6	778.7	777.8
165°	790.1	791.2	792.2	792.2	791.0	789.8	788.6	787.3
167.5°	797.6	798.7	800.0	799.9	798.5	797.2	795.8	794.5
170°	802.2	803.3	804.4	804.2	802.9	801.5	800.2	798.8
172.5°	805.1	806.2	807.2	807.1	805.6	804.2	802.7	801.3
175°	808.5	809.8	811.0	810.7	809.1	807.6	805.9	804.3
177.5°	809.9	810.7	811.6	811.4	810.1	808.8	807.6	806.2
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1

(END OF REPORT)