

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332756-930

Luminaire Tested: **S124DIW-S575D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332756-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D770U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4204.8 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.8
10°-20°	210.1	5.0
20°-30°	309.2	7.4
30°-40°	359.5	8.5
40°-50°	359.5	8.5
50°-60°	314.5	7.5
60°-70°	233.5	5.6
70°-80°	132.7	3.2
80°-90°	40.6	1.0
90°-100°	51.6	1.2
100°-110°	152.9	3.6
110°-120°	259.5	6.2
120°-130°	342.1	8.1
130°-140°	384.2	9.1
140°-150°	377.6	9.0
150°-160°	317.6	7.6
160°-170°	211.3	5.0
170°-180°	74.0	1.8
0°-30°	593.9	14.1
0°-40°	953.4	22.7
0°-60°	1627.3	38.7
0°-90°	2034.1	48.4
90°-120°	463.9	11.0
90°-150°	1567.9	37.3
90°-180°	2171.0	51.6
0°-180°	4204.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	2	8	13	17	18	4
95°	36	42	46	48	48	40
105°	141	142	144	146	148	150
115°	264	264	263	262	261	260
125°	384	384	384	382	381	342
135°	496	499	499	498	496	383
145°	602	604	605	604	603	377
155°	690	690	689	691	689	317
165°	751	749	748	751	749	212
175°	781	778	778	781	778	74
180°	782	782	782	782	782	



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.5	13.8	13.9	14.1	14.3	14.4	14.5	14.7	14.8	14.8	15.0
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	13.0	14.7	16.3	18.0	19.7	21.0	21.7	22.4	23.2	24.0	24.5
95°	36.3	37.5	38.7	39.9	41.2	42.2	43.1	44.1	45.1	46.0	46.4
97.5°	63.4	64.4	65.4	66.3	67.3	68.3	69.5	70.5	71.7	72.7	73.2
100°	84.7	85.3	85.8	86.3	86.8	87.7	88.9	90.2	91.4	92.6	92.9
102.5°	107.0	107.2	107.4	107.6	107.9	108.5	109.6	110.7	111.8	112.9	113.3
105°	141.0	141.1	141.3	141.4	141.5	141.9	142.4	142.9	143.5	144.0	144.4
107.5°	176.7	176.8	177.0	177.2	177.3	177.5	177.6	177.7	177.7	177.8	178.1
110°	200.9	201.1	201.5	201.7	201.9	202.0	201.9	201.8	201.6	201.5	201.2



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.1	226.2	226.2	226.2	226.2	225.9	225.7	225.4	225.2	225.2
115°	263.8	263.8	263.8	263.8	263.8	263.7	263.4	263.2	262.9	262.6	262.4
117.5°	299.4	299.5	299.6	299.7	299.9	299.8	299.6	299.5	299.2	299.1	298.6
120°	323.1	323.7	324.2	324.7	325.3	325.3	325.0	324.6	324.2	323.8	323.0
122.5°	347.8	348.1	348.2	348.5	348.7	348.7	348.5	348.3	348.1	348.0	347.5
125°	384.3	384.3	384.3	384.3	384.3	384.2	384.0	383.9	383.8	383.6	383.4
127.5°	417.3	417.7	418.1	418.5	418.9	419.0	418.7	418.6	418.3	418.2	417.8
130°	440.5	440.9	441.3	441.7	442.1	442.3	442.3	442.3	442.3	442.3	442.1
132.5°	464.2	464.6	464.8	465.1	465.5	465.5	465.4	465.3	465.2	465.0	464.8
135°	495.6	496.4	497.2	498.0	498.8	499.2	499.2	499.2	499.2	499.2	499.0
137.5°	529.7	530.1	530.4	530.8	531.2	531.5	531.7	531.9	532.1	532.4	532.0
140°	552.4	552.7	553.0	553.3	553.5	553.7	553.7	553.7	553.7	553.7	553.5
142.5°	573.2	573.6	573.8	574.1	574.4	574.5	574.3	574.2	574.1	574.0	574.0
145°	602.1	602.6	603.2	603.7	604.2	604.5	604.7	604.9	605.0	605.1	605.0
147.5°	630.6	631.3	631.9	632.6	633.2	633.5	633.4	633.2	633.2	633.1	632.9
150°	648.1	648.6	649.1	649.7	650.2	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	664.6	664.9	665.2	665.5	665.9	666.0	666.1	666.3	666.3	666.4	666.8
155°	689.8	689.8	689.8	689.8	689.8	689.7	689.6	689.5	689.3	689.3	689.7
157.5°	711.1	710.9	710.6	710.4	710.1	710.0	710.0	710.0	710.0	709.9	710.3
160°	723.7	723.6	723.4	723.3	723.2	723.0	722.9	722.8	722.6	722.5	722.9
162.5°	735.3	735.0	734.6	734.3	733.9	733.7	733.5	733.4	733.3	733.1	733.9
165°	751.0	750.6	750.2	749.7	749.3	749.0	748.7	748.4	748.2	747.9	748.7
167.5°	762.9	762.4	761.8	761.2	760.7	760.3	760.4	760.4	760.4	760.5	761.3
170°	769.7	769.0	768.3	767.7	767.0	766.7	766.9	767.0	767.1	767.3	768.1
172.5°	774.5	774.0	773.4	772.8	772.3	772.0	772.0	772.1	772.1	772.1	773.1
175°	781.2	780.5	779.8	779.2	778.5	778.1	778.0	777.8	777.7	777.6	778.5
177.5°	783.3	782.9	782.3	781.8	781.2	781.0	781.0	781.0	781.0	781.0	781.7
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	15.2	15.3	15.5	15.6	15.7	15.7	15.7	15.8
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	24.9	25.4	25.9	26.3	26.4	26.6	26.7	26.9
95°	46.8	47.2	47.6	47.8	47.8	47.8	47.8	47.8
97.5°	73.7	74.2	74.7	74.9	74.9	74.9	74.9	74.9
100°	93.1	93.4	93.7	93.8	93.8	93.8	93.8	93.8
102.5°	113.7	114.1	114.4	114.6	114.8	114.9	115.0	115.1
105°	144.8	145.2	145.6	146.0	146.4	146.8	147.2	147.7
107.5°	178.6	178.9	179.3	179.4	179.4	179.4	179.4	179.4
110°	201.0	200.7	200.4	200.5	200.9	201.3	201.7	202.1



TEST NUMBER: P332756-930

CATALOG NUMBER: S124DIW-S575D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.1	225.0	225.0	225.0	225.1	225.2	225.3	225.3
115°	262.4	262.2	262.0	262.0	261.8	261.7	261.5	261.4
117.5°	298.2	297.7	297.2	296.9	296.6	296.3	296.0	295.8
120°	322.4	321.7	321.1	320.8	321.1	321.4	321.6	321.9
122.5°	347.0	346.6	346.1	345.6	345.1	344.6	344.2	343.7
125°	383.1	382.9	382.5	382.3	382.0	381.7	381.5	381.2
127.5°	417.6	417.4	417.0	416.8	416.6	416.4	416.1	416.0
130°	441.8	441.5	441.2	440.8	440.3	439.8	439.2	438.7
132.5°	464.6	464.3	464.0	463.7	463.6	463.3	463.1	462.9
135°	498.6	498.4	498.1	497.8	497.4	497.0	496.6	496.2
137.5°	531.7	531.3	531.0	530.8	530.9	531.0	531.1	531.2
140°	553.4	553.3	553.1	553.0	552.9	552.7	552.6	552.4
142.5°	574.0	573.9	573.9	573.9	573.8	573.8	573.8	573.7
145°	604.9	604.7	604.5	604.3	603.9	603.5	603.1	602.7
147.5°	632.8	632.8	632.6	632.5	632.3	632.3	632.1	631.9
150°	650.5	650.5	650.5	650.4	650.3	650.1	650.0	649.9
152.5°	667.1	667.4	667.7	667.7	667.4	667.1	666.7	666.3
155°	690.3	690.8	691.4	691.4	690.8	690.3	689.7	689.3
157.5°	710.7	711.1	711.5	711.5	711.0	710.6	710.1	709.6
160°	723.3	723.7	724.1	724.0	723.3	722.6	721.9	721.3
162.5°	734.6	735.3	736.1	736.1	735.4	734.7	734.1	733.4
165°	749.5	750.3	751.1	751.3	750.7	750.2	749.7	749.1
167.5°	762.1	762.9	763.7	763.7	762.9	762.1	761.2	760.3
170°	768.9	769.7	770.5	770.5	769.5	768.6	767.6	766.7
172.5°	774.0	774.9	775.8	775.8	774.8	773.9	772.9	772.0
175°	779.4	780.4	781.3	781.3	780.4	779.4	778.5	777.6
177.5°	782.4	783.2	784.0	783.9	783.0	782.2	781.3	780.5
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4

(END OF REPORT)