

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332799-930

Luminaire Tested: **S124DIW-S795D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332799-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1560U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7977.6 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332799-930  
CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37				31	
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31				26	
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	29	27				22	
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23				19	
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20				17	
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18				15	
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16				13	
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14				12	
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13				11	
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12				10	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8451	8451	8451	8451
5°	9951	8473	7478	8473
10°	11914	8435	6733	8435
15°	14098	8350	6182	8350
20°	15698	8262	5692	8262
25°	15952	8134	5353	8134
30°	13573	8011	5246	8011
35°	10435	7811	5248	7811
40°	8134	7576	5347	7576
45°	6782	7223	5436	7223
50°	5968	6791	5620	6791
55°	5468	6273	5847	6273
60°	5125	5811	6119	5811
65°	4770	5291	6346	5291
70°	4360	4780	6489	4780
75°	3896	4208	6410	4208
80°	3268	3445	6206	3445
85°	2408	2492	5947	2492



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.0	1.3
10°-20°	314.3	3.9
20°-30°	498.4	6.2
30°-40°	554.7	7.0
40°-50°	504.9	6.3
50°-60°	412.6	5.2
60°-70°	294.6	3.7
70°-80°	162.2	2.0
80°-90°	49.0	0.6
90°-100°	56.2	0.7
100°-110°	358.5	4.5
110°-120°	685.8	8.6
120°-130°	870.5	10.9
130°-140°	931.4	11.7
140°-150°	871.0	10.9
150°-160°	702.4	8.8
160°-170°	453.0	5.7
170°-180°	156.1	2.0
0°-30°	914.7	11.5
0°-40°	1469.4	18.4
0°-60°	2386.9	29.9
0°-90°	2892.7	36.3
90°-120°	1100.5	13.8
90°-150°	3773.4	47.3
90°-180°	5085.0	63.7
0°-180°	7977.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1047	1047	1047	1047	1047	
5°	1228	1046	923	1046	1228	125
15°	1687	999	740	999	1687	477
25°	1791	913	601	913	1791	789
35°	1059	793	532	793	1059	672
45°	594	633	476	633	594	468
55°	388	446	415	446	388	351
65°	250	277	332	277	250	247
75°	125	135	206	135	125	133
85°	26	27	64	27	26	33
90°	37	4	37	4	37	17
95°	36	68	36	68	36	28
105°	350	370	350	370	350	306
115°	696	691	696	691	696	689
125°	979	971	979	971	979	872
135°	1214	1205	1214	1205	1214	934
145°	1397	1389	1397	1389	1397	873
155°	1522	1523	1522	1523	1522	702
165°	1600	1607	1600	1607	1600	452
175°	1634	1644	1634	1644	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1114.0	1113.7	1110.2	1109.5	1107.1	1104.0	1103.3	1097.7	1086.6	1081.4	1080.0
5°	1228.0	1236.6	1225.4	1223.2	1221.9	1207.6	1200.2	1191.6	1171.6	1159.9	1150.8
7.5°	1364.0	1365.0	1360.1	1356.1	1345.1	1332.5	1313.9	1293.9	1270.2	1245.4	1226.8
10°	1453.4	1456.9	1451.3	1450.4	1428.3	1414.5	1386.7	1363.3	1336.4	1306.4	1279.1
12.5°	1547.8	1543.0	1540.1	1521.5	1517.4	1492.2	1459.9	1435.7	1394.3	1359.9	1323.6
15°	1686.8	1677.2	1671.1	1645.5	1633.0	1597.8	1563.6	1537.2	1482.9	1431.3	1392.3
17.5°	1768.2	1777.8	1763.7	1753.2	1720.7	1696.1	1661.1	1605.6	1563.2	1499.1	1449.8
20°	1827.2	1828.1	1820.3	1809.5	1783.9	1752.6	1714.5	1653.8	1603.0	1539.3	1471.7
22.5°	1843.1	1843.4	1840.0	1829.9	1810.5	1785.3	1746.8	1696.1	1634.6	1565.3	1497.7
25°	1790.8	1789.1	1793.0	1804.3	1796.8	1789.1	1766.9	1729.2	1672.0	1598.7	1525.8
27.5°	1596.2	1608.2	1630.2	1657.9	1684.7	1705.0	1710.7	1703.0	1667.5	1607.3	1531.0
30°	1456.0	1470.8	1487.3	1515.0	1568.8	1599.6	1633.4	1659.0	1644.7	1596.5	1525.4
32.5°	1302.0	1305.7	1330.2	1361.7	1411.0	1470.2	1523.8	1575.7	1593.0	1567.7	1508.5
35°	1058.8	1064.9	1091.4	1122.6	1182.9	1255.3	1335.9	1407.9	1467.3	1491.2	1460.9
37.5°	864.1	881.5	900.2	933.8	986.8	1052.0	1135.8	1228.9	1317.4	1376.8	1386.8
40°	771.8	782.7	796.1	821.7	866.7	931.0	1002.9	1109.6	1203.7	1288.7	1316.5
42.5°	699.0	705.3	713.5	736.7	771.0	834.9	900.6	994.4	1088.9	1190.5	1237.0
45°	594.0	600.5	614.4	627.9	653.9	698.1	759.2	836.4	931.4	1029.4	1115.2
47.5°	518.3	522.4	530.7	545.0	567.1	596.3	646.0	710.5	798.5	893.6	985.1
50°	475.2	478.7	485.2	498.2	515.1	541.1	581.9	642.2	711.1	807.0	896.7
52.5°	441.2	442.6	447.4	456.2	469.7	491.5	525.0	574.9	639.0	724.4	813.8
55°	388.5	390.3	394.6	401.1	412.8	426.6	452.2	489.5	545.5	619.6	697.2
57.5°	345.1	346.3	350.0	352.5	362.2	373.4	393.1	419.7	462.1	525.0	594.3
60°	317.4	316.5	320.9	323.0	329.5	339.1	354.2	379.8	416.7	467.4	531.2
62.5°	290.3	289.1	292.8	295.6	299.4	307.5	319.9	340.0	369.9	415.7	470.8
65°	249.7	248.0	250.2	253.6	257.1	261.5	270.6	288.4	312.2	345.1	387.2
67.5°	209.0	210.8	211.2	212.9	214.9	220.8	227.1	239.6	256.4	282.8	318.5
70°	184.7	185.2	186.9	186.9	188.2	193.4	198.6	205.9	222.4	246.7	275.7
72.5°	160.5	162.2	161.6	163.0	163.9	167.4	171.2	178.2	192.2	210.3	234.8
75°	124.9	126.2	126.2	126.6	127.9	129.2	132.2	137.5	147.4	160.9	177.8
77.5°	91.1	91.2	91.8	93.4	93.4	95.5	97.8	101.9	106.8	116.0	126.4
80°	70.3	71.1	70.7	71.6	71.6	73.3	74.1	79.3	81.5	87.6	95.8
82.5°	51.5	52.3	52.3	53.5	54.2	54.5	55.8	57.8	60.0	65.4	68.7
85°	26.0	26.9	26.0	26.9	28.2	28.6	29.9	30.3	32.1	33.4	36.4
87.5°	15.0	16.0	15.8	16.1	16.6	16.8	16.8	16.1	17.2	17.2	18.2
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4	27.7	26.1	23.9
95°	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3	28.7	27.1	26.7
97.5°	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8	32.6	32.4	62.9
100°	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8	49.5	54.1	91.8
102.5°	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5	210.5	260.7	265.5
105°	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5	386.0	383.6	382.2
107.5°	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7	479.5	478.3	476.4
110°	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3	542.7	542.2	540.5



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0	604.1	604.2	603.4
115°	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6	694.0	693.4	693.7
117.5°	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7	785.8	785.9	785.3
120°	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0	841.2
122.5°	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7	897.4	897.1	896.7
125°	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4	974.6	973.8	974.3
127.5°	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6	1052.8	1053.0	1051.7
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8	1099.4	1099.2	1098.4
132.5°	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0	1145.7	1145.4	1144.4
135°	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7	1209.2	1208.6	1207.5
137.5°	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8	1270.2	1269.6	1268.4
140°	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6	1307.8	1306.9	1306.4
142.5°	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6	1343.0	1342.4	1342.1
145°	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6	1393.3	1393.0	1393.0
147.5°	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5	1437.3	1437.0	1437.3
150°	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6	1465.6	1465.6	1465.8
152.5°	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0	1489.6	1489.1	1489.6
155°	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1	1522.0	1520.9	1521.8
157.5°	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7	1549.6
160°	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4	1566.7
162.5°	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5	1582.7	1581.1	1581.4
165°	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2	1603.0	1600.8	1600.8
167.5°	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4	1618.0	1615.6	1615.8
170°	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8	1627.6	1625.4	1625.1
172.5°	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7	1633.5	1631.3	1631.0
175°	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6	1640.1	1637.7	1637.4
177.5°	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4	1643.6	1641.8	1641.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1080.4	1075.5	1072.0	1069.3	1061.7	1057.1	1053.7	1048.8	1043.3	1037.4	1030.0
5°	1141.7	1126.9	1116.1	1099.6	1084.0	1071.0	1057.6	1045.5	1030.7	1014.6	1002.9
7.5°	1206.2	1184.2	1156.1	1131.7	1104.3	1080.4	1059.2	1037.3	1014.6	992.5	972.3
10°	1247.1	1218.9	1187.6	1150.8	1116.1	1085.3	1056.7	1029.0	1002.1	975.2	952.2
12.5°	1291.1	1256.0	1209.8	1166.8	1127.9	1086.7	1052.2	1018.2	985.8	957.5	930.7
15°	1350.2	1299.5	1246.2	1188.5	1137.3	1089.2	1042.0	999.1	962.6	925.3	899.3
17.5°	1386.6	1323.8	1262.8	1202.6	1140.7	1079.9	1029.0	979.4	933.8	896.7	864.0
20°	1410.5	1348.1	1272.2	1211.9	1138.2	1075.8	1016.8	961.7	914.0	874.6	840.7
22.5°	1431.3	1359.2	1283.3	1204.0	1130.6	1064.4	999.8	944.4	895.7	854.1	821.7
25°	1442.6	1359.8	1277.4	1198.5	1115.2	1036.7	978.2	913.2	861.1	817.3	782.7
27.5°	1443.8	1355.3	1262.1	1174.4	1088.4	1015.4	941.4	883.4	829.3	783.0	749.7
30°	1440.0	1347.7	1247.5	1152.5	1066.2	986.9	922.8	859.4	804.4	758.4	723.7
32.5°	1427.8	1331.7	1228.7	1128.2	1038.9	961.2	895.0	834.8	781.1	735.8	699.4
35°	1392.8	1297.8	1188.1	1083.6	992.1	913.6	853.8	792.6	738.9	695.9	660.8
37.5°	1337.8	1252.0	1140.4	1032.3	942.5	863.6	804.4	749.1	700.6	657.0	621.0
40°	1290.0	1214.6	1102.7	997.3	900.2	825.2	769.6	718.9	670.8	629.6	595.3
42.5°	1234.9	1169.1	1065.9	954.3	860.6	785.3	731.2	685.6	640.3	602.2	567.9
45°	1136.4	1093.2	996.0	892.8	795.2	724.1	672.5	632.7	594.5	557.2	528.6
47.5°	1023.4	1001.9	920.1	822.1	729.5	659.4	614.7	577.8	544.4	512.8	487.5
50°	947.5	937.0	866.3	771.8	683.4	617.4	572.3	540.7	512.1	484.4	460.5
52.5°	872.5	872.1	808.5	721.9	640.0	576.5	531.7	502.2	477.4	454.9	433.4
55°	758.0	770.1	720.2	643.0	569.7	512.5	472.2	445.7	428.4	409.8	393.7
57.5°	652.7	672.9	631.8	563.8	502.6	449.9	414.8	394.9	376.4	365.2	353.5
60°	584.1	603.2	571.0	513.8	456.2	411.1	377.6	359.9	343.8	336.1	327.8
62.5°	523.0	540.1	516.2	463.2	413.1	369.8	341.6	324.5	313.6	305.2	299.7
65°	435.8	450.0	429.7	391.1	348.2	313.5	290.5	277.0	266.7	263.2	257.1
67.5°	352.3	365.3	354.2	321.5	287.1	260.7	242.8	229.9	223.7	220.7	216.4
70°	302.6	315.7	303.9	275.3	248.9	226.8	209.9	202.5	196.0	194.7	188.6
72.5°	260.7	269.5	257.8	235.5	212.8	194.2	181.1	173.3	170.0	167.6	164.4
75°	195.6	203.3	195.6	178.2	162.2	149.2	137.9	134.9	130.9	129.6	127.5
77.5°	138.4	145.2	139.2	128.3	116.3	106.3	100.3	96.4	95.5	93.2	94.2
80°	105.8	110.1	104.5	97.1	87.6	80.6	76.3	74.1	71.6	70.7	72.4
82.5°	76.0	77.9	75.0	70.0	62.9	58.5	55.5	53.0	52.5	52.7	52.7
85°	39.5	39.1	38.6	34.2	32.1	29.0	27.3	26.9	26.4	27.3	28.2
87.5°	17.7	17.6	16.9	14.9	13.3	11.7	10.7	9.8	10.7	11.7	12.6
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5	15.7	15.8	16.0
95°	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6	58.3	49.1	39.8
97.5°	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6	149.4	155.2	161.0
100°	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6	206.6	211.5	216.4
102.5°	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5	270.2	273.8	277.4
105°	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1	371.7	373.3	375.0
107.5°	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2	467.1	467.9	468.7
110°	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2	532.0	532.8	533.6





TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1	595.6	597.0	598.5
115°	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0	691.8	692.6	693.4
117.5°	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3	779.3	780.5	781.5
120°	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3	838.4	839.5	840.6
122.5°	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3	893.0	893.6	894.3
125°	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3	972.4	973.5	974.6
127.5°	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0	1046.4	1046.6	1046.8
130°	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3	1094.5	1094.8	1095.1
132.5°	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5	1139.0	1139.5	1140.0
135°	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9	1204.6	1204.4	1204.1
137.5°	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7	1263.8	1263.9	1264.0
140°	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0	1302.6	1303.2	1303.7
142.5°	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5
145°	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4	1390.2	1391.0	1391.8
147.5°	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4	1432.9	1434.4	1436.0
150°	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9	1463.0	1464.0	1465.2
152.5°	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4	1488.3	1489.2	1490.0
155°	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4	1523.6	1523.9	1524.2
157.5°	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6	1553.5	1553.3	1553.1
160°	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3	1570.5	1569.7	1568.9
162.5°	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1	1586.0	1584.9	1584.0
165°	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0	1605.6	1604.3	1602.9
167.5°	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7	1621.3	1619.8	1618.5
170°	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6	1629.9	1628.2	1626.6
172.5°	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4	1635.8	1634.2	1632.6
175°	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8	1642.2	1640.5	1638.9
177.5°	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8	1645.3	1643.7	1642.2
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1026.6	1023.5	1019.0	1012.8	1007.5	1002.0	1000.6	998.5	1002.7	999.2	998.2
5°	993.0	983.8	972.2	958.7	950.9	939.6	937.4	933.1	928.8	928.4	924.0
7.5°	957.3	944.0	928.6	914.9	902.2	889.9	881.9	880.1	873.8	870.0	865.7
10°	934.4	917.9	900.2	887.1	872.5	859.4	850.3	845.1	840.7	836.0	831.7
12.5°	907.3	889.8	875.2	861.1	843.6	833.7	818.7	809.8	808.9	808.9	797.7
15°	875.9	858.5	836.0	816.0	806.5	787.4	779.2	768.7	762.3	755.8	750.6
17.5°	839.9	818.3	800.7	777.8	759.6	744.4	733.6	727.3	717.5	708.3	701.6
20°	817.3	794.3	775.8	751.5	731.5	712.8	703.8	695.0	687.7	679.9	672.5
22.5°	794.4	770.5	747.6	724.1	705.5	685.8	677.0	665.2	658.2	653.9	646.5
25°	758.4	732.4	706.4	683.8	664.7	647.3	635.7	626.6	618.7	615.3	610.5
27.5°	719.2	693.3	668.2	642.6	620.9	608.4	599.0	592.2	587.6	583.0	580.9
30°	694.2	667.3	640.4	616.6	596.6	584.1	575.4	570.6	567.1	565.0	562.8
32.5°	668.9	642.4	614.1	592.3	574.5	563.3	556.7	551.9	550.2	549.3	548.6
35°	628.3	601.4	575.4	555.9	539.0	534.7	529.0	526.4	525.5	528.6	529.9
37.5°	589.0	564.0	540.1	521.2	510.1	503.8	501.8	502.0	505.1	507.8	510.9
40°	563.7	539.4	516.9	500.3	490.0	486.1	485.2	487.4	490.8	493.9	497.3
42.5°	539.1	515.1	494.6	479.2	472.0	468.4	468.9	471.1	475.9	479.6	484.9
45°	500.8	480.9	460.9	448.3	442.3	443.1	443.1	447.0	451.8	457.5	463.1
47.5°	464.8	444.7	428.3	417.8	414.6	413.8	416.3	421.3	428.2	435.2	443.0
50°	440.5	421.4	407.2	397.6	394.1	395.4	398.9	403.7	411.9	420.6	428.8
52.5°	415.9	398.6	385.3	376.4	374.1	376.3	379.8	387.3	394.6	404.0	413.9
55°	377.6	362.9	352.5	346.0	345.1	346.4	350.3	358.6	369.0	380.7	390.3
57.5°	339.6	327.3	317.7	313.2	313.6	314.9	321.3	331.1	342.2	354.7	367.0
60°	314.0	302.6	294.9	291.4	291.8	294.4	302.2	311.4	325.2	337.4	350.3
62.5°	289.7	279.7	272.3	269.2	268.6	274.3	281.8	291.2	305.1	318.6	332.6
65°	250.6	242.8	236.8	235.1	236.4	240.7	250.2	262.8	274.5	288.8	303.5
67.5°	212.5	206.0	201.9	202.7	204.2	210.7	218.7	229.4	242.7	257.6	272.1
70°	188.2	182.1	178.6	179.0	181.6	189.5	196.4	207.2	221.6	236.8	248.9
72.5°	163.2	159.2	156.1	157.9	160.5	165.9	174.6	185.4	198.0	212.1	224.9
75°	125.3	125.3	123.6	124.9	128.8	134.0	140.5	151.7	164.4	175.6	186.1
77.5°	92.9	92.0	93.1	94.7	96.9	103.1	110.6	118.6	128.1	139.3	148.0
80°	71.1	71.6	73.7	76.3	77.2	81.9	89.8	97.1	104.5	114.1	122.3
82.5°	53.4	53.9	55.0	58.3	59.1	64.2	69.3	76.6	83.3	89.8	96.6
85°	29.0	29.0	31.2	32.5	34.7	38.2	41.2	45.5	51.6	55.9	62.5
87.5°	14.3	14.8	16.6	17.7	19.2	21.4	22.4	26.5	28.2	30.3	33.7
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4	31.0	32.6	33.5
95°	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3	32.0	33.6	34.6
97.5°	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8	32.9	33.1	33.3
100°	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8	40.2	35.5	33.3
102.5°	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5	110.3	60.3	35.2
105°	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5	391.0	393.5	389.7
107.5°	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7	481.9	483.1	484.2
110°	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3	543.9	544.4	545.1



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0	603.8	603.7	604.2
115°	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6	695.0	695.6	695.9
117.5°	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7	785.5	785.5	785.4
120°	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0	842.6	843.2	843.2
122.5°	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7	898.1	898.4	898.2
125°	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4	976.2	977.1	977.6
127.5°	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6	1052.5	1052.3	1052.1
130°	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8	1100.0	1100.2	1100.4
132.5°	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0	1146.2	1146.5	1146.6
135°	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7	1210.2	1210.8	1211.4
137.5°	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8	1271.4	1272.0	1272.2
140°	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6	1309.5	1310.3	1310.8
142.5°	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6	1344.2	1344.8	1345.1
145°	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6	1393.8	1394.1	1394.6
147.5°	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5	1437.7	1437.9	1438.2
150°	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6	1465.6	1465.6	1465.7
152.5°	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0	1490.4	1490.9	1491.0
155°	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1	1524.2	1525.3	1525.4
157.5°	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4
160°	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0
162.5°	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5	1586.1	1587.7	1587.6
165°	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2	1607.4	1609.6	1609.4
167.5°	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4	1622.8	1625.2	1625.1
170°	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8	1632.0	1634.2	1633.9
172.5°	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7	1637.9	1640.1	1639.6
175°	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6	1645.1	1647.6	1647.1
177.5°	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4	1647.1	1648.9	1648.5
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	997.4	996.8	994.3	994.0	994.3	996.8	997.4	998.2	999.2	1002.7	998.5
5°	921.5	919.2	917.9	922.8	917.9	919.2	921.5	924.0	928.4	928.8	933.1
7.5°	864.1	862.3	858.5	857.4	858.5	862.3	864.1	865.7	870.0	873.8	880.1
10°	827.3	825.6	822.1	821.3	822.1	825.6	827.3	831.7	836.0	840.7	845.1
12.5°	791.9	788.5	787.7	788.6	787.7	788.5	791.9	797.7	808.9	808.9	809.8
15°	744.9	743.2	738.4	739.7	738.4	743.2	744.9	750.6	755.8	762.3	768.7
17.5°	698.6	696.5	690.7	695.9	690.7	696.5	698.6	701.6	708.3	717.5	727.3
20°	669.5	666.0	663.0	662.5	663.0	666.0	669.5	672.5	679.9	687.7	695.0
22.5°	641.7	638.6	638.4	635.5	638.4	638.6	641.7	646.5	653.9	658.2	665.2
25°	607.1	604.1	603.2	601.0	603.2	604.1	607.1	610.5	615.3	618.7	626.6
27.5°	580.4	578.9	577.4	578.0	577.4	578.9	580.4	580.9	583.0	587.6	592.2
30°	564.1	563.7	562.8	562.8	562.8	563.7	564.1	562.8	565.0	567.1	570.6
32.5°	550.6	550.5	551.1	551.1	551.1	550.5	550.6	548.6	549.3	550.2	551.9
35°	531.6	532.9	533.8	532.5	533.8	532.9	531.6	529.9	528.6	525.5	526.4
37.5°	514.5	515.8	517.0	518.4	517.0	515.8	514.5	510.9	507.8	505.1	502.0
40°	501.2	504.3	505.2	507.4	505.2	504.3	501.2	497.3	493.9	490.8	487.4
42.5°	488.8	492.1	494.4	494.8	494.4	492.1	488.8	484.9	479.6	475.9	471.1
45°	469.6	473.0	476.1	476.1	476.1	473.0	469.6	463.1	457.5	451.8	447.0
47.5°	449.7	454.8	457.8	458.6	457.8	454.8	449.7	443.0	435.2	428.2	421.3
50°	436.2	442.3	445.3	447.5	445.3	442.3	436.2	428.8	420.6	411.9	403.7
52.5°	423.1	429.1	433.2	434.3	433.2	429.1	423.1	413.9	404.0	394.6	387.3
55°	400.2	408.9	413.7	415.4	413.7	408.9	400.2	390.3	380.7	369.0	358.6
57.5°	378.7	386.7	392.2	393.5	392.2	386.7	378.7	367.0	354.7	342.2	331.1
60°	362.1	370.7	377.6	379.0	377.6	370.7	362.1	350.3	337.4	325.2	311.4
62.5°	345.0	354.1	360.4	363.7	360.4	354.1	345.0	332.6	318.6	305.1	291.2
65°	315.7	324.7	330.8	332.2	330.8	324.7	315.7	303.5	288.8	274.5	262.8
67.5°	283.6	292.7	296.7	299.2	296.7	292.7	283.6	272.1	257.6	242.7	229.4
70°	261.1	268.4	272.7	274.9	272.7	268.4	261.1	248.9	236.8	221.6	207.2
72.5°	235.4	243.0	248.1	248.5	248.1	243.0	235.4	224.9	212.1	198.0	185.4
75°	196.0	202.9	205.5	205.5	205.5	202.9	196.0	186.1	175.6	164.4	151.7
77.5°	155.2	158.7	162.0	162.7	162.0	158.7	155.2	148.0	139.3	128.1	118.6
80°	128.8	130.9	133.5	133.5	133.5	130.9	128.8	122.3	114.1	104.5	97.1
82.5°	101.7	103.5	106.2	105.8	106.2	103.5	101.7	96.6	89.8	83.3	76.6
85°	61.6	65.5	65.1	64.2	65.1	65.5	61.6	62.5	55.9	51.6	45.5
87.5°	34.8	35.2	36.4	37.2	36.4	35.2	34.8	33.7	30.3	28.2	26.5
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	33.6	33.8	33.8	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4
95°	34.8	35.1	35.4	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3
97.5°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8
100°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8
102.5°	35.2	35.3	35.4	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5
105°	379.9	370.1	360.3	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5
107.5°	485.3	486.2	487.3	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7
110°	545.9	546.7	547.6	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	605.3	606.3	607.3	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0
115°	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6
117.5°	785.2	785.1	785.1	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7
120°	842.6	842.0	841.6	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0
122.5°	897.7	897.2	896.6	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7
125°	977.9	978.1	978.4	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4
127.5°	1051.9	1051.7	1051.4	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8
132.5°	1146.3	1146.1	1145.9	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0
135°	1211.9	1212.4	1213.0	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7
137.5°	1272.0	1271.9	1271.7	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8
140°	1311.1	1311.3	1311.6	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6
142.5°	1345.2	1345.2	1345.2	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6
145°	1395.1	1395.6	1396.2	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6
147.5°	1438.4	1438.7	1439.0	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5
150°	1466.0	1466.2	1466.6	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6
152.5°	1490.9	1490.7	1490.5	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0
155°	1524.6	1523.8	1523.0	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1
157.5°	1553.0	1551.5	1550.1	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5
160°	1571.3	1569.7	1568.1	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7
162.5°	1585.8	1583.9	1582.0	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5
165°	1607.0	1604.5	1602.1	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2
167.5°	1622.3	1619.6	1616.8	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4
170°	1631.2	1628.4	1625.7	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8
172.5°	1636.7	1633.8	1630.8	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7
175°	1643.8	1640.5	1637.3	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6
177.5°	1645.8	1643.2	1640.5	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1000.6	1002.0	1007.5	1012.8	1019.0	1023.5	1026.6	1030.0	1037.4	1043.3	1048.8
5°	937.4	939.6	950.9	958.7	972.2	983.8	993.0	1002.9	1014.6	1030.7	1045.5
7.5°	881.9	889.9	902.2	914.9	928.6	944.0	957.3	972.3	992.5	1014.6	1037.3
10°	850.3	859.4	872.5	887.1	900.2	917.9	934.4	952.2	975.2	1002.1	1029.0
12.5°	818.7	833.7	843.6	861.1	875.2	889.8	907.3	930.7	957.5	985.8	1018.2
15°	779.2	787.4	806.5	816.0	836.0	858.5	875.9	899.3	925.3	962.6	999.1
17.5°	733.6	744.4	759.6	777.8	800.7	818.3	839.9	864.0	896.7	933.8	979.4
20°	703.8	712.8	731.5	751.5	775.8	794.3	817.3	840.7	874.6	914.0	961.7
22.5°	677.0	685.8	705.5	724.1	747.6	770.5	794.4	821.7	854.1	895.7	944.4
25°	635.7	647.3	664.7	683.8	706.4	732.4	758.4	782.7	817.3	861.1	913.2
27.5°	599.0	608.4	620.9	642.6	668.2	693.3	719.2	749.7	783.0	829.3	883.4
30°	575.4	584.1	596.6	616.6	640.4	667.3	694.2	723.7	758.4	804.4	859.4
32.5°	556.7	563.3	574.5	592.3	614.1	642.4	668.9	699.4	735.8	781.1	834.8
35°	529.0	534.7	539.0	555.9	575.4	601.4	628.3	660.8	695.9	738.9	792.6
37.5°	501.8	503.8	510.1	521.2	540.1	564.0	589.0	621.0	657.0	700.6	749.1
40°	485.2	486.1	490.0	500.3	516.9	539.4	563.7	595.3	629.6	670.8	718.9
42.5°	468.9	468.4	472.0	479.2	494.6	515.1	539.1	567.9	602.2	640.3	685.6
45°	443.1	443.1	442.3	448.3	460.9	480.9	500.8	528.6	557.2	594.5	632.7
47.5°	416.3	413.8	414.6	417.8	428.3	444.7	464.8	487.5	512.8	544.4	577.8
50°	398.9	395.4	394.1	397.6	407.2	421.4	440.5	460.5	484.4	512.1	540.7
52.5°	379.8	376.3	374.1	376.4	385.3	398.6	415.9	433.4	454.9	477.4	502.2
55°	350.3	346.4	345.1	346.0	352.5	362.9	377.6	393.7	409.8	428.4	445.7
57.5°	321.3	314.9	313.6	313.2	317.7	327.3	339.6	353.5	365.2	376.4	394.9
60°	302.2	294.4	291.8	291.4	294.9	302.6	314.0	327.8	336.1	343.8	359.9
62.5°	281.8	274.3	268.6	269.2	272.3	279.7	289.7	299.7	305.2	313.6	324.5
65°	250.2	240.7	236.4	235.1	236.8	242.8	250.6	257.1	263.2	266.7	277.0
67.5°	218.7	210.7	204.2	202.7	201.9	206.0	212.5	216.4	220.7	223.7	229.9
70°	196.4	189.5	181.6	179.0	178.6	182.1	188.2	188.6	194.7	196.0	202.5
72.5°	174.6	165.9	160.5	157.9	156.1	159.2	163.2	164.4	167.6	170.0	173.3
75°	140.5	134.0	128.8	124.9	123.6	125.3	125.3	127.5	129.6	130.9	134.9
77.5°	110.6	103.1	96.9	94.7	93.1	92.0	92.9	94.2	93.2	95.5	96.4
80°	89.8	81.9	77.2	76.3	73.7	71.6	71.1	72.4	70.7	71.6	74.1
82.5°	69.3	64.2	59.1	58.3	55.0	53.9	53.4	52.7	52.7	52.5	53.0
85°	41.2	38.2	34.7	32.5	31.2	29.0	29.0	28.2	27.3	26.4	26.9
87.5°	22.4	21.4	19.2	17.7	16.6	14.8	14.3	12.6	11.7	10.7	9.8
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	27.7	26.1	23.9	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5
95°	28.7	27.1	26.7	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6
97.5°	32.6	32.4	62.9	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6
100°	49.5	54.1	91.8	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6
102.5°	210.5	260.7	265.5	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5
105°	386.0	383.6	382.2	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1
107.5°	479.5	478.3	476.4	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2
110°	542.7	542.2	540.5	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2



TEST NUMBER: P332799-930  
 CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	604.1	604.2	603.4	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1
115°	694.0	693.4	693.7	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0
117.5°	785.8	785.9	785.3	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3
120°	841.6	841.0	841.2	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3
122.5°	897.4	897.1	896.7	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3
125°	974.6	973.8	974.3	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3
127.5°	1052.8	1053.0	1051.7	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0
130°	1099.4	1099.2	1098.4	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3
132.5°	1145.7	1145.4	1144.4	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5
135°	1209.2	1208.6	1207.5	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9
137.5°	1270.2	1269.6	1268.4	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7
140°	1307.8	1306.9	1306.4	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0
142.5°	1343.0	1342.4	1342.1	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4
145°	1393.3	1393.0	1393.0	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4
147.5°	1437.3	1437.0	1437.3	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4
150°	1465.6	1465.6	1465.8	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9
152.5°	1489.6	1489.1	1489.6	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4
155°	1522.0	1520.9	1521.8	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4
157.5°	1550.1	1548.7	1549.6	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6
160°	1568.1	1566.4	1566.7	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3
162.5°	1582.7	1581.1	1581.4	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1
165°	1603.0	1600.8	1600.8	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0
167.5°	1618.0	1615.6	1615.8	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7
170°	1627.6	1625.4	1625.1	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6
172.5°	1633.5	1631.3	1631.0	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4
175°	1640.1	1637.7	1637.4	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8
177.5°	1643.6	1641.8	1641.4	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1053.7	1057.1	1061.7	1069.3	1072.0	1075.5	1080.4	1080.0	1081.4	1086.6	1097.7
5°	1057.6	1071.0	1084.0	1099.6	1116.1	1126.9	1141.7	1150.8	1159.9	1171.6	1191.6
7.5°	1059.2	1080.4	1104.3	1131.7	1156.1	1184.2	1206.2	1226.8	1245.4	1270.2	1293.9
10°	1056.7	1085.3	1116.1	1150.8	1187.6	1218.9	1247.1	1279.1	1306.4	1336.4	1363.3
12.5°	1052.2	1086.7	1127.9	1166.8	1209.8	1256.0	1291.1	1323.6	1359.9	1394.3	1435.7
15°	1042.0	1089.2	1137.3	1188.5	1246.2	1299.5	1350.2	1392.3	1431.3	1482.9	1537.2
17.5°	1029.0	1079.9	1140.7	1202.6	1262.8	1323.8	1386.6	1449.8	1499.1	1563.2	1605.6
20°	1016.8	1075.8	1138.2	1211.9	1272.2	1348.1	1410.5	1471.7	1539.3	1603.0	1653.8
22.5°	999.8	1064.4	1130.6	1204.0	1283.3	1359.2	1431.3	1497.7	1565.3	1634.6	1696.1
25°	978.2	1036.7	1115.2	1198.5	1277.4	1359.8	1442.6	1525.8	1598.7	1672.0	1729.2
27.5°	941.4	1015.4	1088.4	1174.4	1262.1	1355.3	1443.8	1531.0	1607.3	1667.5	1703.0
30°	922.8	986.9	1066.2	1152.5	1247.5	1347.7	1440.0	1525.4	1596.5	1644.7	1659.0
32.5°	895.0	961.2	1038.9	1128.2	1228.7	1331.7	1427.8	1508.5	1567.7	1593.0	1575.7
35°	853.8	913.6	992.1	1083.6	1188.1	1297.8	1392.8	1460.9	1491.2	1467.3	1407.9
37.5°	804.4	863.6	942.5	1032.3	1140.4	1252.0	1337.8	1386.8	1376.8	1317.4	1228.9
40°	769.6	825.2	900.2	997.3	1102.7	1214.6	1290.0	1316.5	1288.7	1203.7	1109.6
42.5°	731.2	785.3	860.6	954.3	1065.9	1169.1	1234.9	1237.0	1190.5	1088.9	994.4
45°	672.5	724.1	795.2	892.8	996.0	1093.2	1136.4	1115.2	1029.4	931.4	836.4
47.5°	614.7	659.4	729.5	822.1	920.1	1001.9	1023.4	985.1	893.6	798.5	710.5
50°	572.3	617.4	683.4	771.8	866.3	937.0	947.5	896.7	807.0	711.1	642.2
52.5°	531.7	576.5	640.0	721.9	808.5	872.1	872.5	813.8	724.4	639.0	574.9
55°	472.2	512.5	569.7	643.0	720.2	770.1	758.0	697.2	619.6	545.5	489.5
57.5°	414.8	449.9	502.6	563.8	631.8	672.9	652.7	594.3	525.0	462.1	419.7
60°	377.6	411.1	456.2	513.8	571.0	603.2	584.1	531.2	467.4	416.7	379.8
62.5°	341.6	369.8	413.1	463.2	516.2	540.1	523.0	470.8	415.7	369.9	340.0
65°	290.5	313.5	348.2	391.1	429.7	450.0	435.8	387.2	345.1	312.2	288.4
67.5°	242.8	260.7	287.1	321.5	354.2	365.3	352.3	318.5	282.8	256.4	239.6
70°	209.9	226.8	248.9	275.3	303.9	315.7	302.6	275.7	246.7	222.4	205.9
72.5°	181.1	194.2	212.8	235.5	257.8	269.5	260.7	234.8	210.3	192.2	178.2
75°	137.9	149.2	162.2	178.2	195.6	203.3	195.6	177.8	160.9	147.4	137.5
77.5°	100.3	106.3	116.3	128.3	139.2	145.2	138.4	126.4	116.0	106.8	101.9
80°	76.3	80.6	87.6	97.1	104.5	110.1	105.8	95.8	87.6	81.5	79.3
82.5°	55.5	58.5	62.9	70.0	75.0	77.9	76.0	68.7	65.4	60.0	57.8
85°	27.3	29.0	32.1	34.2	38.6	39.1	39.5	36.4	33.4	32.1	30.3
87.5°	10.7	11.7	13.3	14.9	16.9	17.6	17.7	18.2	17.2	17.2	16.1
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4
95°	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3
97.5°	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8
100°	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8
102.5°	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5
105°	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5
107.5°	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7
110°	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3





TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0
115°	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6
117.5°	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7
120°	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0
122.5°	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7
125°	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4
127.5°	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6
130°	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8
132.5°	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0
135°	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7
137.5°	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8
140°	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6
142.5°	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6
145°	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6
147.5°	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5
150°	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6
152.5°	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0
155°	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1
157.5°	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5
160°	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7
162.5°	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5
165°	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2
167.5°	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4
170°	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8
172.5°	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7
175°	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6
177.5°	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1103.3	1104.0	1107.1	1109.5	1110.2	1113.7	1114.0
5°	1200.2	1207.6	1221.9	1223.2	1225.4	1236.6	1228.0
7.5°	1313.9	1332.5	1345.1	1356.1	1360.1	1365.0	1364.0
10°	1386.7	1414.5	1428.3	1450.4	1451.3	1456.9	1453.4
12.5°	1459.9	1492.2	1517.4	1521.5	1540.1	1543.0	1547.8
15°	1563.6	1597.8	1633.0	1645.5	1671.1	1677.2	1686.8
17.5°	1661.1	1696.1	1720.7	1753.2	1763.7	1777.8	1768.2
20°	1714.5	1752.6	1783.9	1809.5	1820.3	1828.1	1827.2
22.5°	1746.8	1785.3	1810.5	1829.9	1840.0	1843.4	1843.1
25°	1766.9	1789.1	1796.8	1804.3	1793.0	1789.1	1790.8
27.5°	1710.7	1705.0	1684.7	1657.9	1630.2	1608.2	1596.2
30°	1633.4	1599.6	1568.8	1515.0	1487.3	1470.8	1456.0
32.5°	1523.8	1470.2	1411.0	1361.7	1330.2	1305.7	1302.0
35°	1335.9	1255.3	1182.9	1122.6	1091.4	1064.9	1058.8
37.5°	1135.8	1052.0	986.8	933.8	900.2	881.5	864.1
40°	1002.9	931.0	866.7	821.7	796.1	782.7	771.8
42.5°	900.6	834.9	771.0	736.7	713.5	705.3	699.0
45°	759.2	698.1	653.9	627.9	614.4	600.5	594.0
47.5°	646.0	596.3	567.1	545.0	530.7	522.4	518.3
50°	581.9	541.1	515.1	498.2	485.2	478.7	475.2
52.5°	525.0	491.5	469.7	456.2	447.4	442.6	441.2
55°	452.2	426.6	412.8	401.1	394.6	390.3	388.5
57.5°	393.1	373.4	362.2	352.5	350.0	346.3	345.1
60°	354.2	339.1	329.5	323.0	320.9	316.5	317.4
62.5°	319.9	307.5	299.4	295.6	292.8	289.1	290.3
65°	270.6	261.5	257.1	253.6	250.2	248.0	249.7
67.5°	227.1	220.8	214.9	212.9	211.2	210.8	209.0
70°	198.6	193.4	188.2	186.9	186.9	185.2	184.7
72.5°	171.2	167.4	163.9	163.0	161.6	162.2	160.5
75°	132.2	129.2	127.9	126.6	126.2	126.2	124.9
77.5°	97.8	95.5	93.4	93.4	91.8	91.2	91.1
80°	74.1	73.3	71.6	71.6	70.7	71.1	70.3
82.5°	55.8	54.5	54.2	53.5	52.3	52.3	51.5
85°	29.9	28.6	28.2	26.9	26.0	26.9	26.0
87.5°	16.8	16.8	16.6	16.1	15.8	16.0	15.0
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332799-930

CATALOG NUMBER: S124DIW-S795D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)