

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332833-840

Luminaire Tested: **S124DIW-S1020D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332833-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D1560U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10775.8 lumens  
Efficiency: N/A  
Efficacy: 140.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.1	1.5
10°-20°	462.4	4.3
20°-30°	680.5	6.3
30°-40°	791.1	7.3
40°-50°	791.2	7.3
50°-60°	692.1	6.4
60°-70°	514.0	4.8
70°-80°	292.0	2.7
80°-90°	90.1	0.8
90°-100°	69.6	0.6
100°-110°	444.0	4.1
110°-120°	849.4	7.9
120°-130°	1078.3	10.0
130°-140°	1153.7	10.7
140°-150°	1078.8	10.0
150°-160°	870.0	8.1
160°-170°	561.1	5.2
170°-180°	193.4	1.8
0°-30°	1307.0	12.1
0°-40°	2098.1	19.5
0°-60°	3581.3	33.2
0°-90°	4477.4	41.6
90°-120°	1363.1	12.6
90°-150°	4673.9	43.4
90°-180°	6298.0	58.4
0°-180°	10775.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	4	21	34	42	46	8
95°	84	35	34	42	44	108
105°	458	468	475	485	434	480
115°	856	860	859	862	862	842
125°	1203	1209	1206	1211	1212	1074
135°	1492	1491	1497	1500	1503	1149
145°	1721	1725	1726	1727	1730	1075
155°	1887	1888	1884	1889	1885	870
165°	1990	1983	1983	1994	1981	562
175°	2036	2028	2028	2040	2024	194
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	30.0	30.5	30.9	31.4	31.9	32.3	32.6	32.9	33.2	33.5	33.9
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	19.2	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3
95°	83.7	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5
97.5°	177.8	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4
100°	249.7	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3
102.5°	330.1	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7
105°	458.4	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2
107.5°	577.4	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9
110°	657.9	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3



TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	735.9	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2
115°	855.9	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6
117.5°	964.0	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3
120°	1037.1	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4
122.5°	1105.3	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6
125°	1203.2	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2
127.5°	1295.7	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0
130°	1355.4	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8
132.5°	1410.2	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1
135°	1492.5	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7
137.5°	1565.3	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3
140°	1612.8	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9
142.5°	1655.4	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4
145°	1720.9	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8
147.5°	1773.0	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3
150°	1810.8	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3
152.5°	1842.4	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1
155°	1886.9	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2
157.5°	1924.4	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1
160°	1946.3	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3
162.5°	1965.8	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5
165°	1990.4	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5
167.5°	2009.9	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1
170°	2020.9	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0
172.5°	2028.2	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3
175°	2036.1	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5
177.5°	2039.8	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	34.3	34.7	35.1	35.4	35.5	35.6	35.9	36.0
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	36.4	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	37.6	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.6	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	55.5	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	198.7	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	481.2	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	595.4	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.0	673.7	674.3	675.2	676.2	677.2	678.2	679.2





TEST NUMBER: P332833-840

CATALOG NUMBER: S124DIW-S1020D1560U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.1	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.3	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.2	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.0	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1208.2	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.8	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.2	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.5	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1498.3	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.1	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1620.9	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1664.3	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.2	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.5	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1845.6	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1886.5	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1962.6	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1988.2	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2007.1	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2018.7	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2026.0	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2034.6	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2038.0	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)