

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332810-840

Luminaire Tested: **S124DIW-S1020D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332810-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D470U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6114.9 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.7
10°-20°	462.4	7.6
20°-30°	680.5	11.1
30°-40°	791.1	12.9
40°-50°	791.2	12.9
50°-60°	692.1	11.3
60°-70°	514.0	8.4
70°-80°	292.0	4.8
80°-90°	86.0	1.4
90°-100°	39.0	0.6
100°-110°	115.6	1.9
110°-120°	196.2	3.2
120°-130°	258.7	4.2
130°-140°	290.6	4.8
140°-150°	285.5	4.7
150°-160°	240.2	3.9
160°-170°	159.8	2.6
170°-180°	56.0	0.9
0°-30°	1307.0	21.4
0°-40°	2098.1	34.3
0°-60°	3581.3	58.6
0°-90°	4473.3	73.2
90°-120°	350.9	5.7
90°-150°	1185.7	19.4
90°-180°	1642.0	26.9
0°-180°	6114.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	1	6	10	13	14	6
95°	28	32	35	36	36	31
105°	107	107	109	110	112	113
115°	200	199	199	198	198	197
125°	290	290	290	289	288	259
135°	375	377	378	377	375	290
145°	455	457	458	457	456	285
155°	522	522	521	523	521	240
165°	568	566	566	568	566	160
175°	591	589	588	591	588	56
180°	592	592	592	592	592	



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.3	29.3	29.3	29.3	29.2	29.2	29.1	29.0	28.9	28.8	29.0
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	9.8	11.1	12.3	13.6	14.9	15.9	16.5	17.0	17.6	18.1	18.5
95°	27.5	28.4	29.3	30.2	31.1	31.9	32.6	33.3	34.0	34.7	35.0
97.5°	48.0	48.7	49.4	50.2	50.9	51.7	52.5	53.3	54.1	55.0	55.3
100°	64.0	64.4	64.8	65.2	65.7	66.3	67.3	68.2	69.1	70.0	70.2
102.5°	80.9	81.1	81.2	81.4	81.6	82.1	82.9	83.7	84.5	85.4	85.6
105°	106.6	106.7	106.8	106.9	107.0	107.2	107.7	108.1	108.5	108.9	109.2
107.5°	133.6	133.7	133.9	134.0	134.1	134.2	134.3	134.3	134.4	134.4	134.7
110°	151.9	152.1	152.3	152.5	152.7	152.8	152.7	152.6	152.5	152.4	152.2



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.0	171.0	171.1	171.1	171.2	171.1	170.9	170.7	170.5	170.4	170.3
115°	199.5	199.5	199.5	199.5	199.5	199.4	199.2	199.0	198.8	198.6	198.5
117.5°	226.4	226.5	226.6	226.7	226.7	226.7	226.6	226.4	226.3	226.1	225.8
120°	244.4	244.8	245.2	245.6	246.0	246.0	245.7	245.4	245.1	244.8	244.3
122.5°	263.1	263.2	263.4	263.5	263.7	263.7	263.6	263.4	263.3	263.2	262.8
125°	290.5	290.5	290.5	290.5	290.5	290.5	290.4	290.3	290.2	290.1	289.9
127.5°	315.6	315.9	316.2	316.5	316.8	316.9	316.7	316.5	316.4	316.2	316.0
130°	333.2	333.5	333.8	334.1	334.4	334.5	334.5	334.5	334.5	334.5	334.3
132.5°	351.0	351.3	351.5	351.7	351.9	352.0	351.9	351.8	351.8	351.7	351.5
135°	374.8	375.4	376.0	376.6	377.2	377.5	377.5	377.5	377.5	377.5	377.3
137.5°	400.6	400.9	401.1	401.4	401.7	401.9	402.1	402.3	402.4	402.6	402.3
140°	417.8	418.0	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7	418.6
142.5°	433.5	433.7	433.9	434.1	434.3	434.4	434.3	434.2	434.1	434.0	434.0
145°	455.3	455.8	456.2	456.6	457.0	457.2	457.3	457.4	457.5	457.6	457.5
147.5°	477.0	477.4	477.9	478.4	478.9	479.1	479.0	478.9	478.9	478.8	478.7
150°	490.1	490.5	490.9	491.3	491.7	491.9	491.9	491.9	491.9	491.9	491.9
152.5°	502.5	502.8	503.0	503.3	503.5	503.7	503.7	503.8	503.9	504.0	504.2
155°	521.7	521.7	521.7	521.7	521.7	521.6	521.5	521.4	521.3	521.2	521.6
157.5°	537.8	537.6	537.5	537.2	537.0	536.9	536.9	536.9	536.8	536.8	537.1
160°	547.3	547.2	547.1	547.0	546.9	546.8	546.7	546.6	546.5	546.4	546.7
162.5°	556.1	555.8	555.5	555.3	555.0	554.8	554.7	554.6	554.5	554.4	555.0
165°	567.8	567.5	567.2	566.9	566.6	566.4	566.2	566.0	565.8	565.6	566.2
167.5°	576.9	576.5	576.1	575.7	575.2	575.0	575.0	575.1	575.1	575.1	575.7
170°	582.1	581.6	581.1	580.6	580.1	579.9	580.0	580.1	580.2	580.3	580.9
172.5°	585.7	585.3	584.9	584.5	584.0	583.8	583.8	583.9	583.9	583.9	584.6
175°	590.8	590.3	589.8	589.3	588.8	588.4	588.3	588.2	588.1	588.0	588.8
177.5°	592.4	592.0	591.6	591.2	590.8	590.6	590.6	590.6	590.6	590.6	591.2
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	29.1	29.2	29.3	29.4	29.4	29.5	29.5	29.6
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	18.9	19.2	19.6	19.8	20.0	20.1	20.2	20.3
95°	35.3	35.6	36.0	36.2	36.2	36.2	36.2	36.2
97.5°	55.7	56.1	56.5	56.7	56.7	56.7	56.7	56.7
100°	70.4	70.6	70.8	70.9	70.9	70.9	70.9	70.9
102.5°	85.9	86.2	86.5	86.7	86.7	86.8	86.9	87.1
105°	109.6	109.9	110.2	110.5	110.8	111.1	111.4	111.7
107.5°	135.0	135.3	135.6	135.7	135.7	135.7	135.6	135.6
110°	152.0	151.8	151.6	151.6	151.9	152.2	152.5	152.8



TEST NUMBER: P332810-840

CATALOG NUMBER: S124DIW-S1020D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.3	170.2	170.2	170.2	170.3	170.3	170.4	170.4
115°	198.4	198.3	198.2	198.1	198.0	197.9	197.8	197.7
117.5°	225.5	225.1	224.8	224.5	224.3	224.1	223.9	223.7
120°	243.8	243.3	242.8	242.7	242.9	243.1	243.3	243.5
122.5°	262.5	262.1	261.8	261.4	261.1	260.6	260.2	259.9
125°	289.7	289.5	289.3	289.1	288.9	288.7	288.5	288.3
127.5°	315.8	315.6	315.4	315.2	315.1	314.9	314.8	314.6
130°	334.1	333.9	333.7	333.4	333.0	332.5	332.1	331.7
132.5°	351.3	351.1	350.9	350.7	350.5	350.4	350.2	350.1
135°	377.1	376.9	376.7	376.5	376.2	375.9	375.6	375.3
137.5°	402.0	401.8	401.5	401.4	401.5	401.5	401.6	401.7
140°	418.5	418.4	418.3	418.2	418.1	418.0	417.9	417.8
142.5°	434.0	434.0	434.0	433.9	433.9	433.9	433.9	433.9
145°	457.4	457.3	457.2	457.0	456.7	456.4	456.1	455.8
147.5°	478.6	478.5	478.5	478.4	478.3	478.2	478.1	478.0
150°	491.9	491.9	491.9	491.9	491.8	491.7	491.6	491.5
152.5°	504.5	504.7	505.0	504.9	504.7	504.4	504.2	503.9
155°	522.0	522.4	522.8	522.8	522.4	522.0	521.6	521.2
157.5°	537.5	537.8	538.1	538.1	537.8	537.3	537.0	536.6
160°	547.0	547.3	547.6	547.5	547.0	546.5	545.9	545.4
162.5°	555.5	556.1	556.6	556.6	556.1	555.6	555.1	554.6
165°	566.8	567.4	568.0	568.2	567.7	567.3	566.9	566.5
167.5°	576.3	576.9	577.5	577.5	576.9	576.3	575.6	575.0
170°	581.5	582.1	582.7	582.6	581.9	581.2	580.5	579.8
172.5°	585.3	586.0	586.6	586.6	585.9	585.2	584.5	583.8
175°	589.5	590.2	590.9	590.9	590.2	589.5	588.8	588.0
177.5°	591.8	592.3	592.9	592.8	592.2	591.6	590.9	590.3
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7

(END OF REPORT)