

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332811-840

Luminaire Tested: **S124DIW-S1020D770U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332811-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7752.8 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	83	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13605	13605	13605	13605
5°	16022	13639	12039	13639
10°	19184	13581	10839	13581
15°	22697	13443	9954	13443
20°	25274	13302	9164	13302
25°	25683	13097	8620	13097
30°	21853	12899	8447	12899
35°	16802	12577	8449	12577
40°	13095	12198	8608	12198
45°	10919	11628	8752	11628
50°	9610	10934	9048	10934
55°	8804	10101	9413	10101
60°	8251	9357	9852	9357
65°	7681	8521	10214	8521
70°	7020	7695	10447	7695
75°	6273	6772	10321	6772
80°	5258	5551	9995	5551
85°	3881	4011	9568	4011



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	2.1
10°-20°	506.1	6.5
20°-30°	802.5	10.4
30°-40°	893.1	11.5
40°-50°	812.9	10.5
50°-60°	664.3	8.6
60°-70°	474.2	6.1
70°-80°	261.1	3.4
80°-90°	74.2	1.0
90°-100°	34.3	0.4
100°-110°	218.6	2.8
110°-120°	418.1	5.4
120°-130°	530.7	6.8
130°-140°	567.9	7.3
140°-150°	531.0	6.8
150°-160°	428.2	5.5
160°-170°	276.2	3.6
170°-180°	95.2	1.2
0°-30°	1472.7	19.0
0°-40°	2365.8	30.5
0°-60°	3843.0	49.6
0°-90°	4652.6	60.0
90°-120°	670.9	8.7
90°-150°	2300.6	29.7
90°-180°	3100.0	40.0
0°-180°	7752.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1685	1685	1685	1685	1685	
5°	1977	1683	1486	1683	1977	201
15°	2716	1608	1191	1608	2716	767
25°	2883	1470	968	1470	2883	1271
35°	1705	1276	857	1276	1705	1082
45°	956	1018	767	1018	956	753
55°	626	718	669	718	626	565
65°	402	446	535	446	402	398
75°	201	217	331	217	201	214
85°	42	43	103	43	42	52
90°	22	2	22	2	22	11
95°	22	41	22	41	22	17
105°	214	226	214	226	214	186
115°	424	421	424	421	424	420
125°	597	592	597	592	597	531
135°	740	735	740	735	740	569
145°	852	847	852	847	852	532
155°	928	929	928	929	928	428
165°	975	980	975	980	975	275
175°	996	1002	996	1002	996	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1793.6	1793.1	1787.5	1786.4	1782.4	1777.5	1776.4	1767.4	1749.5	1741.1	1738.9
5°	1977.1	1991.0	1972.9	1969.4	1967.3	1944.3	1932.4	1918.4	1886.3	1867.4	1852.8
7.5°	2196.1	2197.7	2189.8	2183.3	2165.6	2145.5	2115.4	2083.3	2045.0	2005.2	1975.1
10°	2340.2	2345.7	2336.6	2335.2	2299.7	2277.2	2232.6	2194.9	2151.6	2103.4	2059.5
12.5°	2492.0	2484.2	2479.6	2449.7	2443.2	2402.4	2350.5	2311.7	2244.9	2189.5	2130.9
15°	2715.7	2700.4	2690.6	2649.4	2629.2	2572.6	2517.4	2474.9	2387.6	2304.5	2241.7
17.5°	2846.9	2862.4	2839.7	2822.8	2770.5	2730.8	2674.4	2585.1	2516.8	2413.6	2334.3
20°	2941.9	2943.3	2930.7	2913.3	2872.1	2821.9	2760.4	2662.6	2581.0	2478.3	2369.4
22.5°	2967.6	2967.9	2962.5	2946.2	2915.1	2874.3	2812.4	2730.8	2631.8	2520.2	2411.4
25°	2883.3	2880.4	2886.8	2904.9	2893.1	2880.4	2844.9	2784.1	2692.0	2573.9	2456.7
27.5°	2569.9	2589.2	2624.6	2669.4	2712.4	2745.2	2754.4	2742.0	2684.8	2587.8	2465.0
30°	2344.3	2368.0	2394.6	2439.2	2525.8	2575.4	2629.9	2671.0	2648.0	2570.5	2456.0
32.5°	2096.4	2102.2	2141.6	2192.4	2271.7	2367.0	2453.4	2537.0	2564.8	2524.2	2428.6
35°	1704.9	1714.5	1757.2	1807.5	1904.5	2021.0	2150.9	2266.8	2362.5	2400.9	2352.0
37.5°	1391.2	1419.3	1449.4	1503.4	1588.8	1693.7	1828.7	1978.6	2121.2	2216.7	2232.9
40°	1242.6	1260.1	1281.7	1322.9	1395.5	1498.8	1614.8	1786.6	1938.0	2074.9	2119.5
42.5°	1125.4	1135.6	1148.8	1186.1	1241.4	1344.1	1450.0	1601.0	1753.1	1916.7	1991.7
45°	956.4	966.9	989.3	1010.9	1052.8	1124.0	1222.4	1346.7	1499.5	1657.4	1795.5
47.5°	834.4	841.1	854.3	877.6	913.1	960.1	1040.2	1144.0	1285.7	1438.9	1586.1
50°	765.2	770.7	781.2	802.1	829.4	871.2	936.9	1033.9	1144.9	1299.2	1443.7
52.5°	710.4	712.7	720.3	734.6	756.2	791.4	845.3	925.5	1028.7	1166.3	1310.2
55°	625.5	628.3	635.3	645.8	664.6	686.9	728.1	788.2	878.3	997.6	1122.6
57.5°	555.7	557.6	563.5	567.5	583.1	601.3	632.9	675.8	744.1	845.3	956.8
60°	511.0	509.7	516.6	520.1	530.6	545.9	570.4	611.6	670.9	752.6	855.2
62.5°	467.5	465.5	471.4	475.9	482.0	495.1	515.0	547.3	595.5	669.3	758.0
65°	402.1	399.3	402.8	408.4	413.9	421.0	435.7	464.2	502.6	555.7	623.4
67.5°	336.5	339.4	340.0	342.7	346.0	355.5	365.6	385.8	412.8	455.3	512.7
70°	297.4	298.1	300.9	300.9	303.0	311.3	319.7	331.6	358.1	397.3	444.0
72.5°	258.3	261.3	260.1	262.4	263.9	269.4	275.6	286.9	309.5	338.6	378.1
75°	201.1	203.2	203.2	203.9	205.9	208.0	212.9	221.3	237.3	259.0	286.2
77.5°	146.6	146.9	147.8	150.4	150.4	153.7	157.3	164.1	172.0	186.8	203.4
80°	113.1	114.5	113.8	115.2	115.2	118.0	119.4	127.7	131.3	141.0	154.3
82.5°	82.9	84.3	84.2	86.1	87.3	87.9	89.8	93.1	96.6	105.2	110.7
85°	41.9	43.3	41.9	43.3	45.3	46.0	48.2	48.9	51.7	53.7	58.7
87.5°	16.8	18.4	18.3	18.8	19.9	20.3	20.7	19.9	21.9	22.3	24.2
90°	22.5	22.1	21.8	21.5	21.1	20.5	19.5	18.5	17.5	16.5	15.1
92.5°	20.7	20.6	20.6	20.5	20.4	19.9	18.9	17.9	16.9	15.9	14.5
95°	21.7	21.6	21.4	21.2	21.1	20.5	19.5	18.5	17.5	16.5	16.4
97.5°	21.0	20.8	20.7	20.5	20.3	20.2	20.1	20.0	19.9	19.8	38.4
100°	21.0	20.8	20.7	20.5	20.3	21.6	24.4	27.4	30.2	33.0	55.9
102.5°	21.6	21.5	21.5	21.5	21.4	36.8	67.3	97.9	128.4	159.0	161.9
105°	213.7	219.6	225.6	231.7	237.6	239.8	238.3	236.9	235.4	233.9	233.1
107.5°	297.7	297.1	296.5	295.9	295.2	294.6	293.8	293.1	292.4	291.5	290.4
110°	334.4	333.9	333.4	332.9	332.3	331.9	331.5	331.2	330.9	330.5	329.6



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	370.9	370.3	369.6	369.0	368.4	368.1	368.2	368.2	368.3	368.4	367.9
115°	424.2	424.2	424.2	424.2	424.2	424.1	423.7	423.4	423.1	422.7	422.9
117.5°	478.6	478.6	478.7	478.8	478.8	478.9	479.0	479.0	479.1	479.2	478.8
120°	512.7	513.1	513.4	513.7	514.0	514.0	513.7	513.4	513.1	512.7	512.9
122.5°	546.3	546.6	546.9	547.3	547.6	547.8	547.5	547.3	547.1	546.9	546.6
125°	596.7	596.5	596.3	596.2	596.0	595.7	595.2	594.7	594.2	593.7	594.0
127.5°	641.0	641.1	641.2	641.4	641.5	641.6	641.7	641.8	641.9	642.0	641.2
130°	670.9	670.9	670.9	670.9	670.9	670.9	670.7	670.4	670.3	670.1	669.6
132.5°	698.5	698.6	698.7	698.9	699.0	699.0	698.8	698.6	698.5	698.3	697.7
135°	739.8	739.5	739.2	738.8	738.5	738.2	737.9	737.5	737.2	736.9	736.2
137.5°	775.3	775.4	775.5	775.6	775.7	775.5	775.2	774.8	774.4	774.1	773.4
140°	799.8	799.7	799.5	799.3	799.2	798.8	798.3	797.8	797.3	796.9	796.5
142.5°	820.2	820.2	820.1	820.1	820.1	819.9	819.5	819.2	818.8	818.4	818.2
145°	851.5	851.2	850.9	850.5	850.2	850.0	849.8	849.6	849.5	849.3	849.3
147.5°	877.5	877.4	877.2	877.0	876.9	876.7	876.6	876.4	876.3	876.2	876.3
150°	894.2	894.1	893.9	893.8	893.6	893.5	893.5	893.5	893.5	893.5	893.7
152.5°	908.7	908.8	908.9	909.0	909.1	909.0	908.7	908.5	908.2	908.0	908.3
155°	928.1	928.5	929.0	929.5	930.0	929.9	929.3	928.6	928.0	927.3	927.8
157.5°	944.2	945.0	945.9	946.8	947.7	947.7	946.8	945.9	945.0	944.2	944.7
160°	955.0	956.0	957.0	958.0	959.0	959.0	958.0	957.0	956.0	955.0	955.1
162.5°	963.4	964.5	965.6	966.8	968.0	968.0	966.9	966.0	965.0	964.0	964.1
165°	975.2	976.7	978.3	979.8	981.3	981.3	980.0	978.7	977.3	976.0	976.0
167.5°	984.1	985.7	987.4	989.1	990.8	990.9	989.4	988.0	986.4	985.0	985.1
170°	989.5	991.2	992.8	994.5	996.1	996.3	995.0	993.6	992.3	991.0	990.8
172.5°	992.5	994.3	996.1	997.8	999.7	999.9	998.6	997.2	995.9	994.6	994.4
175°	996.2	998.3	1000.3	1002.2	1004.2	1004.5	1003.0	1001.5	1000.0	998.5	998.4
177.5°	998.7	1000.3	1001.8	1003.4	1005.0	1005.3	1004.2	1003.2	1002.1	1001.0	1000.8
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1739.5	1731.6	1726.1	1721.6	1709.3	1702.0	1696.5	1688.6	1679.7	1670.2	1658.5
5°	1838.2	1814.4	1797.0	1770.5	1745.3	1724.3	1702.7	1683.1	1659.4	1633.7	1614.8
7.5°	1941.9	1906.6	1861.4	1822.1	1778.0	1739.6	1705.3	1670.0	1633.5	1598.0	1565.5
10°	2007.8	1962.5	1912.2	1852.8	1797.0	1747.4	1701.3	1656.7	1613.4	1570.0	1533.1
12.5°	2078.7	2022.2	1947.9	1878.6	1815.9	1749.7	1694.0	1639.3	1587.1	1541.6	1498.4
15°	2173.9	2092.2	2006.4	1913.6	1831.2	1753.7	1677.6	1608.5	1549.8	1489.8	1447.9
17.5°	2232.5	2131.4	2033.3	1936.2	1836.4	1738.8	1656.7	1576.9	1503.5	1443.9	1391.1
20°	2271.0	2170.5	2048.3	1951.3	1832.6	1732.0	1637.1	1548.4	1471.7	1408.2	1353.6
22.5°	2304.5	2188.4	2066.2	1938.4	1820.3	1713.6	1609.7	1520.6	1442.1	1375.1	1322.9
25°	2322.7	2189.3	2056.7	1929.7	1795.5	1669.2	1575.0	1470.3	1386.4	1316.0	1260.1
27.5°	2324.6	2182.0	2031.9	1890.8	1752.4	1634.8	1515.8	1422.2	1335.2	1260.7	1207.1
30°	2318.4	2169.8	2008.5	1855.6	1716.7	1588.9	1485.6	1383.7	1295.1	1221.0	1165.2
32.5°	2299.0	2144.0	1978.3	1816.5	1672.5	1547.6	1441.0	1344.0	1257.6	1184.7	1126.1
35°	2242.4	2089.5	1912.9	1744.6	1597.3	1471.0	1374.6	1276.2	1189.6	1120.4	1064.0
37.5°	2154.0	2015.8	1836.2	1662.1	1517.4	1390.5	1295.1	1206.1	1128.0	1057.8	999.9
40°	2076.9	1955.4	1775.3	1605.7	1449.4	1328.6	1239.2	1157.5	1080.1	1013.7	958.6
42.5°	1988.1	1882.3	1716.2	1536.4	1385.6	1264.4	1177.2	1103.9	1030.9	969.6	914.4
45°	1829.8	1760.0	1603.6	1437.4	1280.4	1165.9	1082.8	1018.5	957.2	897.1	851.0
47.5°	1647.7	1613.1	1481.5	1323.6	1174.6	1061.7	989.7	930.3	876.5	825.6	785.0
50°	1525.4	1508.6	1394.8	1242.6	1100.2	994.1	921.5	870.6	824.5	779.8	741.4
52.5°	1404.7	1404.2	1301.6	1162.3	1030.5	928.3	856.2	808.6	768.6	732.4	697.8
55°	1220.3	1239.9	1159.6	1035.3	917.4	825.2	760.2	717.7	689.7	659.7	633.9
57.5°	1051.0	1083.4	1017.1	907.7	809.3	724.4	667.8	635.8	606.1	587.9	569.2
60°	940.4	971.1	919.5	827.3	734.5	661.9	608.0	579.5	553.6	541.1	527.8
62.5°	842.1	869.5	831.2	745.8	665.2	595.3	550.0	522.5	505.0	491.3	482.5
65°	701.7	724.7	691.9	629.8	560.6	504.7	467.8	446.1	429.4	423.7	413.9
67.5°	567.1	588.1	570.4	517.6	462.1	419.9	390.9	370.1	360.2	355.4	348.4
70°	487.3	508.3	489.4	443.3	400.7	365.2	337.9	326.0	315.6	313.5	303.7
72.5°	419.7	433.9	415.2	379.1	342.6	312.7	291.5	279.1	273.7	269.9	264.6
75°	314.9	327.4	314.9	286.9	261.1	240.1	222.0	217.1	210.9	208.7	205.2
77.5°	222.9	233.7	224.1	206.6	187.3	171.2	161.4	155.1	153.7	150.1	151.8
80°	170.4	177.3	168.2	156.4	141.0	129.9	122.9	119.4	115.2	113.8	116.5
82.5°	122.3	125.4	120.8	112.8	101.4	94.1	89.4	85.3	84.4	84.7	84.7
85°	63.5	62.8	62.1	55.1	51.7	46.8	44.0	43.3	42.6	44.0	45.3
87.5°	24.0	24.2	23.4	20.9	18.9	16.9	15.9	14.9	15.9	16.9	17.8
90°	13.8	12.5	11.2	9.6	7.8	6.0	4.0	2.2	4.0	6.0	7.8
92.5°	13.2	11.9	10.6	9.8	9.7	9.7	9.6	9.5	9.6	9.7	9.7
95°	16.2	16.0	15.9	18.6	24.2	29.9	35.5	41.2	35.5	29.9	24.2
97.5°	57.0	75.5	94.1	101.7	98.2	94.6	91.1	87.6	91.1	94.6	98.2
100°	79.0	102.0	124.9	134.9	131.9	129.0	125.9	122.9	125.9	129.0	131.9
102.5°	164.9	167.9	170.9	171.3	169.2	166.9	164.7	162.5	164.7	166.9	169.2
105°	232.2	231.4	230.6	229.6	228.6	227.6	226.6	225.6	226.6	227.6	228.6
107.5°	289.3	288.2	287.1	286.3	285.8	285.3	284.8	284.3	284.8	285.3	285.8
110°	328.6	327.6	326.6	325.8	325.4	324.9	324.4	323.9	324.4	324.9	325.4



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	367.4	367.0	366.5	365.8	364.9	364.1	363.1	362.2	363.1	364.1	364.9
115°	423.1	423.2	423.4	423.2	422.7	422.3	421.8	421.3	421.8	422.3	422.7
117.5°	478.4	478.1	477.7	477.2	476.5	475.8	475.1	474.5	475.1	475.8	476.5
120°	513.1	513.2	513.4	513.1	512.5	511.8	511.2	510.5	511.2	511.8	512.5
122.5°	546.4	546.2	545.9	545.6	545.2	544.8	544.4	544.1	544.4	544.8	545.2
125°	594.4	594.7	595.0	594.8	594.2	593.5	592.9	592.2	592.9	593.5	594.2
127.5°	640.5	639.6	638.9	638.4	638.2	638.1	637.9	637.7	637.9	638.1	638.2
130°	669.1	668.6	668.1	667.8	667.6	667.5	667.3	667.1	667.3	667.5	667.6
132.5°	697.1	696.4	695.8	695.3	695.0	694.8	694.5	694.2	694.5	694.8	695.0
135°	735.5	734.9	734.2	734.0	734.1	734.3	734.5	734.6	734.5	734.3	734.1
137.5°	772.5	771.8	771.1	770.7	770.6	770.6	770.5	770.4	770.5	770.6	770.6
140°	796.2	795.9	795.5	795.2	794.9	794.5	794.2	793.9	794.2	794.5	794.9
142.5°	818.0	817.8	817.6	817.2	816.6	816.1	815.5	814.9	815.5	816.1	816.6
145°	849.3	849.3	849.3	849.1	848.6	848.1	847.6	847.1	847.6	848.1	848.6
147.5°	876.5	876.7	876.8	876.5	875.5	874.5	873.6	872.7	873.6	874.5	875.5
150°	893.8	894.0	894.2	893.9	893.3	892.6	891.9	891.3	891.9	892.6	893.3
152.5°	908.6	908.8	909.1	909.0	908.5	908.0	907.4	906.9	907.4	908.0	908.5
155°	928.3	928.8	929.3	929.5	929.3	929.1	929.0	928.8	929.0	929.1	929.3
157.5°	945.3	945.9	946.4	946.8	947.0	947.1	947.2	947.3	947.2	947.1	947.0
160°	955.3	955.5	955.6	956.0	956.5	957.0	957.5	958.0	957.5	957.0	956.5
162.5°	964.3	964.5	964.6	965.0	965.7	966.3	966.9	967.6	966.9	966.3	965.7
165°	976.0	976.0	976.0	976.4	977.2	978.1	978.9	979.8	978.9	978.1	977.2
167.5°	985.2	985.3	985.4	985.8	986.7	987.6	988.5	989.4	988.5	987.6	986.7
170°	990.7	990.5	990.3	990.8	991.7	992.7	993.7	994.7	993.7	992.7	991.7
172.5°	994.2	994.1	993.9	994.3	995.3	996.3	997.3	998.4	997.3	996.3	995.3
175°	998.2	997.9	997.8	998.3	999.3	1000.3	1001.2	1002.2	1001.2	1000.3	999.3
177.5°	1000.5	1000.3	1000.0	1000.3	1001.2	1002.2	1003.1	1004.0	1003.1	1002.2	1001.2
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1652.8	1647.9	1640.6	1630.5	1622.1	1613.3	1611.0	1607.6	1614.4	1608.7	1607.1
5°	1598.7	1584.1	1565.2	1543.6	1531.0	1512.9	1509.3	1502.4	1495.4	1494.7	1487.7
7.5°	1541.4	1519.8	1495.1	1473.1	1452.7	1432.8	1419.9	1417.0	1406.7	1400.7	1393.7
10°	1504.5	1477.9	1449.4	1428.4	1404.6	1383.7	1369.1	1360.7	1353.6	1345.9	1339.0
12.5°	1460.9	1432.7	1409.1	1386.4	1358.3	1342.3	1318.2	1303.6	1302.3	1302.4	1284.2
15°	1410.2	1382.3	1345.9	1313.8	1298.5	1267.8	1254.6	1237.8	1227.3	1216.8	1208.5
17.5°	1352.3	1317.5	1289.2	1252.3	1222.9	1198.5	1181.1	1171.0	1155.3	1140.4	1129.7
20°	1316.0	1279.0	1248.9	1209.8	1177.7	1147.7	1133.1	1119.1	1107.2	1094.7	1082.8
22.5°	1279.1	1240.4	1203.7	1165.7	1135.9	1104.2	1090.0	1071.1	1059.8	1052.8	1040.9
25°	1221.0	1179.1	1137.2	1101.0	1070.3	1042.3	1023.5	1008.8	996.2	990.7	983.0
27.5°	1157.9	1116.3	1075.8	1034.6	999.8	979.5	964.4	953.3	946.1	938.7	935.2
30°	1117.7	1074.4	1031.2	992.7	960.6	940.4	926.5	918.8	913.1	909.7	906.2
32.5°	1076.9	1034.2	988.7	953.6	924.8	906.9	896.3	888.6	885.8	884.5	883.2
35°	1011.6	968.3	926.5	895.0	867.8	860.8	851.7	847.5	846.2	851.0	853.1
37.5°	948.4	908.2	869.6	839.1	821.3	811.1	808.0	808.2	813.1	817.5	822.5
40°	907.6	868.5	832.1	805.7	788.9	782.6	781.2	784.7	790.3	795.2	800.7
42.5°	867.9	829.4	796.4	771.5	759.8	754.1	755.0	758.4	766.3	772.2	780.6
45°	806.4	774.3	742.1	721.9	712.1	713.5	713.5	719.7	727.4	736.5	745.6
47.5°	748.4	716.0	689.6	672.6	667.5	666.3	670.2	678.4	689.4	700.6	713.4
50°	709.3	678.5	655.5	640.2	634.6	636.7	642.3	649.9	663.2	677.2	690.4
52.5°	669.6	641.7	620.4	606.1	602.2	606.0	611.6	623.7	635.3	650.4	666.4
55°	608.0	584.3	567.5	557.1	555.7	557.8	564.1	577.3	594.1	613.0	628.3
57.5°	546.7	526.9	511.6	504.3	505.0	507.0	517.4	533.1	551.0	571.1	590.9
60°	505.4	487.3	474.7	469.2	469.8	474.0	486.6	501.3	523.6	543.1	564.1
62.5°	466.4	450.4	438.4	433.4	432.4	441.6	453.6	468.9	491.2	513.0	535.6
65°	403.5	390.9	381.2	378.4	380.5	387.5	402.8	423.0	441.9	464.9	488.7
67.5°	342.0	331.7	325.1	326.3	328.8	339.1	352.0	369.4	390.8	414.7	438.2
70°	303.0	293.2	287.6	288.3	292.6	305.1	316.3	333.7	356.8	381.2	400.7
72.5°	262.8	256.3	251.4	254.3	258.4	267.1	281.0	298.5	318.8	341.5	362.1
75°	201.8	201.8	198.9	201.1	207.3	215.7	226.2	244.4	264.6	282.8	299.5
77.5°	149.7	148.1	150.0	152.5	156.1	166.0	178.0	191.0	206.2	224.4	238.2
80°	114.5	115.2	118.7	122.9	124.3	132.0	144.5	156.4	168.2	183.6	196.8
82.5°	86.0	86.7	88.6	93.8	95.2	103.5	111.6	123.4	134.2	144.5	155.5
85°	46.8	46.8	50.3	52.3	55.8	61.4	66.3	73.3	83.1	90.1	100.5
87.5°	19.8	20.1	22.6	24.0	26.0	29.0	30.3	36.7	39.1	42.1	47.3
90°	9.6	11.2	12.5	13.8	15.1	16.5	17.5	18.5	19.5	20.5	21.1
92.5°	9.8	10.6	11.9	13.2	14.5	15.9	16.9	17.9	18.9	19.9	20.4
95°	18.6	15.9	16.0	16.2	16.4	16.5	17.5	18.5	19.5	20.5	21.1
97.5°	101.7	94.1	75.5	57.0	38.4	19.8	19.9	20.0	20.1	20.2	20.3
100°	134.9	124.9	102.0	79.0	55.9	33.0	30.2	27.4	24.4	21.6	20.3
102.5°	171.3	170.9	167.9	164.9	161.9	159.0	128.4	97.9	67.3	36.8	21.4
105°	229.6	230.6	231.4	232.2	233.1	233.9	235.4	236.9	238.3	239.8	237.6
107.5°	286.3	287.1	288.2	289.3	290.4	291.5	292.4	293.1	293.8	294.6	295.2
110°	325.8	326.6	327.6	328.6	329.6	330.5	330.9	331.2	331.5	331.9	332.3



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.8	366.5	367.0	367.4	367.9	368.4	368.3	368.2	368.2	368.1	368.4
115°	423.2	423.4	423.2	423.1	422.9	422.7	423.1	423.4	423.7	424.1	424.2
117.5°	477.2	477.7	478.1	478.4	478.8	479.2	479.1	479.0	479.0	478.9	478.8
120°	513.1	513.4	513.2	513.1	512.9	512.7	513.1	513.4	513.7	514.0	514.0
122.5°	545.6	545.9	546.2	546.4	546.6	546.9	547.1	547.3	547.5	547.8	547.6
125°	594.8	595.0	594.7	594.4	594.0	593.7	594.2	594.7	595.2	595.7	596.0
127.5°	638.4	638.9	639.6	640.5	641.2	642.0	641.9	641.8	641.7	641.6	641.5
130°	667.8	668.1	668.6	669.1	669.6	670.1	670.3	670.4	670.7	670.9	670.9
132.5°	695.3	695.8	696.4	697.1	697.7	698.3	698.5	698.6	698.8	699.0	699.0
135°	734.0	734.2	734.9	735.5	736.2	736.9	737.2	737.5	737.9	738.2	738.5
137.5°	770.7	771.1	771.8	772.5	773.4	774.1	774.4	774.8	775.2	775.5	775.7
140°	795.2	795.5	795.9	796.2	796.5	796.9	797.3	797.8	798.3	798.8	799.2
142.5°	817.2	817.6	817.8	818.0	818.2	818.4	818.8	819.2	819.5	819.9	820.1
145°	849.1	849.3	849.3	849.3	849.3	849.3	849.5	849.6	849.8	850.0	850.2
147.5°	876.5	876.8	876.7	876.5	876.3	876.2	876.3	876.4	876.6	876.7	876.9
150°	893.9	894.2	894.0	893.8	893.7	893.5	893.5	893.5	893.5	893.5	893.6
152.5°	909.0	909.1	908.8	908.6	908.3	908.0	908.2	908.5	908.7	909.0	909.1
155°	929.5	929.3	928.8	928.3	927.8	927.3	928.0	928.6	929.3	929.9	930.0
157.5°	946.8	946.4	945.9	945.3	944.7	944.2	945.0	945.9	946.8	947.7	947.7
160°	956.0	955.6	955.5	955.3	955.1	955.0	956.0	957.0	958.0	959.0	959.0
162.5°	965.0	964.6	964.5	964.3	964.1	964.0	965.0	966.0	966.9	968.0	968.0
165°	976.4	976.0	976.0	976.0	976.0	976.0	977.3	978.7	980.0	981.3	981.3
167.5°	985.8	985.4	985.3	985.2	985.1	985.0	986.4	988.0	989.4	990.9	990.8
170°	990.8	990.3	990.5	990.7	990.8	991.0	992.3	993.6	995.0	996.3	996.1
172.5°	994.3	993.9	994.1	994.2	994.4	994.6	995.9	997.2	998.6	999.9	999.7
175°	998.3	997.8	997.9	998.2	998.4	998.5	1000.0	1001.5	1003.0	1004.5	1004.2
177.5°	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1	1003.2	1004.2	1005.3	1005.0
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1606.0	1604.9	1600.9	1600.4	1600.9	1604.9	1606.0	1607.1	1608.7	1614.4	1607.6
5°	1483.5	1480.1	1477.9	1485.6	1477.9	1480.1	1483.5	1487.7	1494.7	1495.4	1502.4
7.5°	1391.2	1388.5	1382.3	1380.4	1382.3	1388.5	1391.2	1393.7	1400.7	1406.7	1417.0
10°	1332.0	1329.2	1323.6	1322.2	1323.6	1329.2	1332.0	1339.0	1345.9	1353.6	1360.7
12.5°	1275.1	1269.5	1268.4	1269.7	1268.4	1269.5	1275.1	1284.2	1302.4	1302.3	1303.6
15°	1199.4	1196.6	1188.9	1191.0	1188.9	1196.6	1199.4	1208.5	1216.8	1227.3	1237.8
17.5°	1124.8	1121.5	1112.2	1120.3	1112.2	1121.5	1124.8	1129.7	1140.4	1155.3	1171.0
20°	1077.9	1072.3	1067.4	1066.7	1067.4	1072.3	1077.9	1082.8	1094.7	1107.2	1119.1
22.5°	1033.2	1028.2	1027.7	1023.2	1027.7	1028.2	1033.2	1040.9	1052.8	1059.8	1071.1
25°	977.3	972.5	971.1	967.7	971.1	972.5	977.3	983.0	990.7	996.2	1008.8
27.5°	934.5	932.1	929.6	930.7	929.6	932.1	934.5	935.2	938.7	946.1	953.3
30°	908.3	907.6	906.2	906.2	906.2	907.6	908.3	906.2	909.7	913.1	918.8
32.5°	886.5	886.4	887.2	887.2	887.2	886.4	886.5	883.2	884.5	885.8	888.6
35°	855.9	858.0	859.4	857.3	859.4	858.0	855.9	853.1	851.0	846.2	847.5
37.5°	828.3	830.3	832.3	834.7	832.3	830.3	828.3	822.5	817.5	813.1	808.2
40°	807.0	811.9	813.3	816.8	813.3	811.9	807.0	800.7	795.2	790.3	784.7
42.5°	786.9	792.3	796.0	796.7	796.0	792.3	786.9	780.6	772.2	766.3	758.4
45°	756.1	761.6	766.6	766.6	766.6	761.6	756.1	745.6	736.5	727.4	719.7
47.5°	724.1	732.2	737.1	738.3	737.1	732.2	724.1	713.4	700.6	689.4	678.4
50°	702.4	712.1	717.0	720.4	717.0	712.1	702.4	690.4	677.2	663.2	649.9
52.5°	681.1	690.8	697.4	699.2	697.4	690.8	681.1	666.4	650.4	635.3	623.7
55°	644.4	658.3	666.0	668.8	666.0	658.3	644.4	628.3	613.0	594.1	577.3
57.5°	609.8	622.6	631.6	633.6	631.6	622.6	609.8	590.9	571.1	551.0	533.1
60°	582.9	596.9	608.0	610.2	608.0	596.9	582.9	564.1	543.1	523.6	501.3
62.5°	555.5	570.1	580.2	585.6	580.2	570.1	555.5	535.6	513.0	491.2	468.9
65°	508.3	522.9	532.7	534.7	532.7	522.9	508.3	488.7	464.9	441.9	423.0
67.5°	456.6	471.2	477.7	481.7	477.7	471.2	456.6	438.2	414.7	390.8	369.4
70°	420.3	432.1	439.1	442.6	439.1	432.1	420.3	400.7	381.2	356.8	333.7
72.5°	378.9	391.3	399.5	400.2	399.5	391.3	378.9	362.1	341.5	318.8	298.5
75°	315.6	326.7	330.9	330.9	330.9	326.7	315.6	299.5	282.8	264.6	244.4
77.5°	249.7	255.5	260.8	262.0	260.8	255.5	249.7	238.2	224.4	206.2	191.0
80°	207.3	210.9	215.0	215.0	215.0	210.9	207.3	196.8	183.6	168.2	156.4
82.5°	163.8	166.7	170.9	170.4	170.9	166.7	163.8	155.5	144.5	134.2	123.4
85°	99.2	105.4	104.7	103.3	104.7	105.4	99.2	100.5	90.1	83.1	73.3
87.5°	49.0	49.6	51.3	52.5	51.3	49.6	49.0	47.3	42.1	39.1	36.7
90°	21.5	21.8	22.1	22.5	22.1	21.8	21.5	21.1	20.5	19.5	18.5
92.5°	20.5	20.6	20.6	20.7	20.6	20.6	20.5	20.4	19.9	18.9	17.9
95°	21.2	21.4	21.6	21.7	21.6	21.4	21.2	21.1	20.5	19.5	18.5
97.5°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	20.2	20.1	20.0
100°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	21.6	24.4	27.4
102.5°	21.5	21.5	21.5	21.6	21.5	21.5	21.5	21.4	36.8	67.3	97.9
105°	231.7	225.6	219.6	213.7	219.6	225.6	231.7	237.6	239.8	238.3	236.9
107.5°	295.9	296.5	297.1	297.7	297.1	296.5	295.9	295.2	294.6	293.8	293.1
110°	332.9	333.4	333.9	334.4	333.9	333.4	332.9	332.3	331.9	331.5	331.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	369.0	369.6	370.3	370.9	370.3	369.6	369.0	368.4	368.1	368.2	368.2
115°	424.2	424.2	424.2	424.2	424.2	424.2	424.2	424.2	424.1	423.7	423.4
117.5°	478.8	478.7	478.6	478.6	478.6	478.7	478.8	478.8	478.9	479.0	479.0
120°	513.7	513.4	513.1	512.7	513.1	513.4	513.7	514.0	514.0	513.7	513.4
122.5°	547.3	546.9	546.6	546.3	546.6	546.9	547.3	547.6	547.8	547.5	547.3
125°	596.2	596.3	596.5	596.7	596.5	596.3	596.2	596.0	595.7	595.2	594.7
127.5°	641.4	641.2	641.1	641.0	641.1	641.2	641.4	641.5	641.6	641.7	641.8
130°	670.9	670.9	670.9	670.9	670.9	670.9	670.9	670.9	670.9	670.7	670.4
132.5°	698.9	698.7	698.6	698.5	698.6	698.7	698.9	699.0	699.0	698.8	698.6
135°	738.8	739.2	739.5	739.8	739.5	739.2	738.8	738.5	738.2	737.9	737.5
137.5°	775.6	775.5	775.4	775.3	775.4	775.5	775.6	775.7	775.5	775.2	774.8
140°	799.3	799.5	799.7	799.8	799.7	799.5	799.3	799.2	798.8	798.3	797.8
142.5°	820.1	820.1	820.2	820.2	820.2	820.1	820.1	820.1	819.9	819.5	819.2
145°	850.5	850.9	851.2	851.5	851.2	850.9	850.5	850.2	850.0	849.8	849.6
147.5°	877.0	877.2	877.4	877.5	877.4	877.2	877.0	876.9	876.7	876.6	876.4
150°	893.8	893.9	894.1	894.2	894.1	893.9	893.8	893.6	893.5	893.5	893.5
152.5°	909.0	908.9	908.8	908.7	908.8	908.9	909.0	909.1	909.0	908.7	908.5
155°	929.5	929.0	928.5	928.1	928.5	929.0	929.5	930.0	929.9	929.3	928.6
157.5°	946.8	945.9	945.0	944.2	945.0	945.9	946.8	947.7	947.7	946.8	945.9
160°	958.0	957.0	956.0	955.0	956.0	957.0	958.0	959.0	959.0	958.0	957.0
162.5°	966.8	965.6	964.5	963.4	964.5	965.6	966.8	968.0	968.0	966.9	966.0
165°	979.8	978.3	976.7	975.2	976.7	978.3	979.8	981.3	981.3	980.0	978.7
167.5°	989.1	987.4	985.7	984.1	985.7	987.4	989.1	990.8	990.9	989.4	988.0
170°	994.5	992.8	991.2	989.5	991.2	992.8	994.5	996.1	996.3	995.0	993.6
172.5°	997.8	996.1	994.3	992.5	994.3	996.1	997.8	999.7	999.9	998.6	997.2
175°	1002.2	1000.3	998.3	996.2	998.3	1000.3	1002.2	1004.2	1004.5	1003.0	1001.5
177.5°	1003.4	1001.8	1000.3	998.7	1000.3	1001.8	1003.4	1005.0	1005.3	1004.2	1003.2
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1611.0	1613.3	1622.1	1630.5	1640.6	1647.9	1652.8	1658.5	1670.2	1679.7	1688.6
5°	1509.3	1512.9	1531.0	1543.6	1565.2	1584.1	1598.7	1614.8	1633.7	1659.4	1683.1
7.5°	1419.9	1432.8	1452.7	1473.1	1495.1	1519.8	1541.4	1565.5	1598.0	1633.5	1670.0
10°	1369.1	1383.7	1404.6	1428.4	1449.4	1477.9	1504.5	1533.1	1570.0	1613.4	1656.7
12.5°	1318.2	1342.3	1358.3	1386.4	1409.1	1432.7	1460.9	1498.4	1541.6	1587.1	1639.3
15°	1254.6	1267.8	1298.5	1313.8	1345.9	1382.3	1410.2	1447.9	1489.8	1549.8	1608.5
17.5°	1181.1	1198.5	1222.9	1252.3	1289.2	1317.5	1352.3	1391.1	1443.9	1503.5	1576.9
20°	1133.1	1147.7	1177.7	1209.8	1248.9	1279.0	1316.0	1353.6	1408.2	1471.7	1548.4
22.5°	1090.0	1104.2	1135.9	1165.7	1203.7	1240.4	1279.1	1322.9	1375.1	1442.1	1520.6
25°	1023.5	1042.3	1070.3	1101.0	1137.2	1179.1	1221.0	1260.1	1316.0	1386.4	1470.3
27.5°	964.4	979.5	999.8	1034.6	1075.8	1116.3	1157.9	1207.1	1260.7	1335.2	1422.2
30°	926.5	940.4	960.6	992.7	1031.2	1074.4	1117.7	1165.2	1221.0	1295.1	1383.7
32.5°	896.3	906.9	924.8	953.6	988.7	1034.2	1076.9	1126.1	1184.7	1257.6	1344.0
35°	851.7	860.8	867.8	895.0	926.5	968.3	1011.6	1064.0	1120.4	1189.6	1276.2
37.5°	808.0	811.1	821.3	839.1	869.6	908.2	948.4	999.9	1057.8	1128.0	1206.1
40°	781.2	782.6	788.9	805.7	832.1	868.5	907.6	958.6	1013.7	1080.1	1157.5
42.5°	755.0	754.1	759.8	771.5	796.4	829.4	867.9	914.4	969.6	1030.9	1103.9
45°	713.5	713.5	712.1	721.9	742.1	774.3	806.4	851.0	897.1	957.2	1018.5
47.5°	670.2	666.3	667.5	672.6	689.6	716.0	748.4	785.0	825.6	876.5	930.3
50°	642.3	636.7	634.6	640.2	655.5	678.5	709.3	741.4	779.8	824.5	870.6
52.5°	611.6	606.0	602.2	606.1	620.4	641.7	669.6	697.8	732.4	768.6	808.6
55°	564.1	557.8	555.7	557.1	567.5	584.3	608.0	633.9	659.7	689.7	717.7
57.5°	517.4	507.0	505.0	504.3	511.6	526.9	546.7	569.2	587.9	606.1	635.8
60°	486.6	474.0	469.8	469.2	474.7	487.3	505.4	527.8	541.1	553.6	579.5
62.5°	453.6	441.6	432.4	433.4	438.4	450.4	466.4	482.5	491.3	505.0	522.5
65°	402.8	387.5	380.5	378.4	381.2	390.9	403.5	413.9	423.7	429.4	446.1
67.5°	352.0	339.1	328.8	326.3	325.1	331.7	342.0	348.4	355.4	360.2	370.1
70°	316.3	305.1	292.6	288.3	287.6	293.2	303.0	303.7	313.5	315.6	326.0
72.5°	281.0	267.1	258.4	254.3	251.4	256.3	262.8	264.6	269.9	273.7	279.1
75°	226.2	215.7	207.3	201.1	198.9	201.8	201.8	205.2	208.7	210.9	217.1
77.5°	178.0	166.0	156.1	152.5	150.0	148.1	149.7	151.8	150.1	153.7	155.1
80°	144.5	132.0	124.3	122.9	118.7	115.2	114.5	116.5	113.8	115.2	119.4
82.5°	111.6	103.5	95.2	93.8	88.6	86.7	86.0	84.7	84.7	84.4	85.3
85°	66.3	61.4	55.8	52.3	50.3	46.8	46.8	45.3	44.0	42.6	43.3
87.5°	30.3	29.0	26.0	24.0	22.6	20.1	19.8	17.8	16.9	15.9	14.9
90°	17.5	16.5	15.1	13.8	12.5	11.2	9.6	7.8	6.0	4.0	2.2
92.5°	16.9	15.9	14.5	13.2	11.9	10.6	9.8	9.7	9.7	9.6	9.5
95°	17.5	16.5	16.4	16.2	16.0	15.9	18.6	24.2	29.9	35.5	41.2
97.5°	19.9	19.8	38.4	57.0	75.5	94.1	101.7	98.2	94.6	91.1	87.6
100°	30.2	33.0	55.9	79.0	102.0	124.9	134.9	131.9	129.0	125.9	122.9
102.5°	128.4	159.0	161.9	164.9	167.9	170.9	171.3	169.2	166.9	164.7	162.5
105°	235.4	233.9	233.1	232.2	231.4	230.6	229.6	228.6	227.6	226.6	225.6
107.5°	292.4	291.5	290.4	289.3	288.2	287.1	286.3	285.8	285.3	284.8	284.3
110°	330.9	330.5	329.6	328.6	327.6	326.6	325.8	325.4	324.9	324.4	323.9



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	368.3	368.4	367.9	367.4	367.0	366.5	365.8	364.9	364.1	363.1	362.2
115°	423.1	422.7	422.9	423.1	423.2	423.4	423.2	422.7	422.3	421.8	421.3
117.5°	479.1	479.2	478.8	478.4	478.1	477.7	477.2	476.5	475.8	475.1	474.5
120°	513.1	512.7	512.9	513.1	513.2	513.4	513.1	512.5	511.8	511.2	510.5
122.5°	547.1	546.9	546.6	546.4	546.2	545.9	545.6	545.2	544.8	544.4	544.1
125°	594.2	593.7	594.0	594.4	594.7	595.0	594.8	594.2	593.5	592.9	592.2
127.5°	641.9	642.0	641.2	640.5	639.6	638.9	638.4	638.2	638.1	637.9	637.7
130°	670.3	670.1	669.6	669.1	668.6	668.1	667.8	667.6	667.5	667.3	667.1
132.5°	698.5	698.3	697.7	697.1	696.4	695.8	695.3	695.0	694.8	694.5	694.2
135°	737.2	736.9	736.2	735.5	734.9	734.2	734.0	734.1	734.3	734.5	734.6
137.5°	774.4	774.1	773.4	772.5	771.8	771.1	770.7	770.6	770.6	770.5	770.4
140°	797.3	796.9	796.5	796.2	795.9	795.5	795.2	794.9	794.5	794.2	793.9
142.5°	818.8	818.4	818.2	818.0	817.8	817.6	817.2	816.6	816.1	815.5	814.9
145°	849.5	849.3	849.3	849.3	849.3	849.3	849.1	848.6	848.1	847.6	847.1
147.5°	876.3	876.2	876.3	876.5	876.7	876.8	876.5	875.5	874.5	873.6	872.7
150°	893.5	893.5	893.7	893.8	894.0	894.2	893.9	893.3	892.6	891.9	891.3
152.5°	908.2	908.0	908.3	908.6	908.8	909.1	909.0	908.5	908.0	907.4	906.9
155°	928.0	927.3	927.8	928.3	928.8	929.3	929.5	929.3	929.1	929.0	928.8
157.5°	945.0	944.2	944.7	945.3	945.9	946.4	946.8	947.0	947.1	947.2	947.3
160°	956.0	955.0	955.1	955.3	955.5	955.6	956.0	956.5	957.0	957.5	958.0
162.5°	965.0	964.0	964.1	964.3	964.5	964.6	965.0	965.7	966.3	966.9	967.6
165°	977.3	976.0	976.0	976.0	976.0	976.0	976.4	977.2	978.1	978.9	979.8
167.5°	986.4	985.0	985.1	985.2	985.3	985.4	985.8	986.7	987.6	988.5	989.4
170°	992.3	991.0	990.8	990.7	990.5	990.3	990.8	991.7	992.7	993.7	994.7
172.5°	995.9	994.6	994.4	994.2	994.1	993.9	994.3	995.3	996.3	997.3	998.4
175°	1000.0	998.5	998.4	998.2	997.9	997.8	998.3	999.3	1000.3	1001.2	1002.2
177.5°	1002.1	1001.0	1000.8	1000.5	1000.3	1000.0	1000.3	1001.2	1002.2	1003.1	1004.0
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1696.5	1702.0	1709.3	1721.6	1726.1	1731.6	1739.5	1738.9	1741.1	1749.5	1767.4
5°	1702.7	1724.3	1745.3	1770.5	1797.0	1814.4	1838.2	1852.8	1867.4	1886.3	1918.4
7.5°	1705.3	1739.6	1778.0	1822.1	1861.4	1906.6	1941.9	1975.1	2005.2	2045.0	2083.3
10°	1701.3	1747.4	1797.0	1852.8	1912.2	1962.5	2007.8	2059.5	2103.4	2151.6	2194.9
12.5°	1694.0	1749.7	1815.9	1878.6	1947.9	2022.2	2078.7	2130.9	2189.5	2244.9	2311.7
15°	1677.6	1753.7	1831.2	1913.6	2006.4	2092.2	2173.9	2241.7	2304.5	2387.6	2474.9
17.5°	1656.7	1738.8	1836.4	1936.2	2033.3	2131.4	2232.5	2334.3	2413.6	2516.8	2585.1
20°	1637.1	1732.0	1832.6	1951.3	2048.3	2170.5	2271.0	2369.4	2478.3	2581.0	2662.6
22.5°	1609.7	1713.6	1820.3	1938.4	2066.2	2188.4	2304.5	2411.4	2520.2	2631.8	2730.8
25°	1575.0	1669.2	1795.5	1929.7	2056.7	2189.3	2322.7	2456.7	2573.9	2692.0	2784.1
27.5°	1515.8	1634.8	1752.4	1890.8	2031.9	2182.0	2324.6	2465.0	2587.8	2684.8	2742.0
30°	1485.6	1588.9	1716.7	1855.6	2008.5	2169.8	2318.4	2456.0	2570.5	2648.0	2671.0
32.5°	1441.0	1547.6	1672.5	1816.5	1978.3	2144.0	2299.0	2428.6	2524.2	2564.8	2537.0
35°	1374.6	1471.0	1597.3	1744.6	1912.9	2089.5	2242.4	2352.0	2400.9	2362.5	2266.8
37.5°	1295.1	1390.5	1517.4	1662.1	1836.2	2015.8	2154.0	2232.9	2216.7	2121.2	1978.6
40°	1239.2	1328.6	1449.4	1605.7	1775.3	1955.4	2076.9	2119.5	2074.9	1938.0	1786.6
42.5°	1177.2	1264.4	1385.6	1536.4	1716.2	1882.3	1988.1	1991.7	1916.7	1753.1	1601.0
45°	1082.8	1165.9	1280.4	1437.4	1603.6	1760.0	1829.8	1795.5	1657.4	1499.5	1346.7
47.5°	989.7	1061.7	1174.6	1323.6	1481.5	1613.1	1647.7	1586.1	1438.9	1285.7	1144.0
50°	921.5	994.1	1100.2	1242.6	1394.8	1508.6	1525.4	1443.7	1299.2	1144.9	1033.9
52.5°	856.2	928.3	1030.5	1162.3	1301.6	1404.2	1404.7	1310.2	1166.3	1028.7	925.5
55°	760.2	825.2	917.4	1035.3	1159.6	1239.9	1220.3	1122.6	997.6	878.3	788.2
57.5°	667.8	724.4	809.3	907.7	1017.1	1083.4	1051.0	956.8	845.3	744.1	675.8
60°	608.0	661.9	734.5	827.3	919.5	971.1	940.4	855.2	752.6	670.9	611.6
62.5°	550.0	595.3	665.2	745.8	831.2	869.5	842.1	758.0	669.3	595.5	547.3
65°	467.8	504.7	560.6	629.8	691.9	724.7	701.7	623.4	555.7	502.6	464.2
67.5°	390.9	419.9	462.1	517.6	570.4	588.1	567.1	512.7	455.3	412.8	385.8
70°	337.9	365.2	400.7	443.3	489.4	508.3	487.3	444.0	397.3	358.1	331.6
72.5°	291.5	312.7	342.6	379.1	415.2	433.9	419.7	378.1	338.6	309.5	286.9
75°	222.0	240.1	261.1	286.9	314.9	327.4	314.9	286.2	259.0	237.3	221.3
77.5°	161.4	171.2	187.3	206.6	224.1	233.7	222.9	203.4	186.8	172.0	164.1
80°	122.9	129.9	141.0	156.4	168.2	177.3	170.4	154.3	141.0	131.3	127.7
82.5°	89.4	94.1	101.4	112.8	120.8	125.4	122.3	110.7	105.2	96.6	93.1
85°	44.0	46.8	51.7	55.1	62.1	62.8	63.5	58.7	53.7	51.7	48.9
87.5°	15.9	16.9	18.9	20.9	23.4	24.2	24.0	24.2	22.3	21.9	19.9
90°	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5	18.5
92.5°	9.6	9.7	9.7	9.8	10.6	11.9	13.2	14.5	15.9	16.9	17.9
95°	35.5	29.9	24.2	18.6	15.9	16.0	16.2	16.4	16.5	17.5	18.5
97.5°	91.1	94.6	98.2	101.7	94.1	75.5	57.0	38.4	19.8	19.9	20.0
100°	125.9	129.0	131.9	134.9	124.9	102.0	79.0	55.9	33.0	30.2	27.4
102.5°	164.7	166.9	169.2	171.3	170.9	167.9	164.9	161.9	159.0	128.4	97.9
105°	226.6	227.6	228.6	229.6	230.6	231.4	232.2	233.1	233.9	235.4	236.9
107.5°	284.8	285.3	285.8	286.3	287.1	288.2	289.3	290.4	291.5	292.4	293.1
110°	324.4	324.9	325.4	325.8	326.6	327.6	328.6	329.6	330.5	330.9	331.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	363.1	364.1	364.9	365.8	366.5	367.0	367.4	367.9	368.4	368.3	368.2
115°	421.8	422.3	422.7	423.2	423.4	423.2	423.1	422.9	422.7	423.1	423.4
117.5°	475.1	475.8	476.5	477.2	477.7	478.1	478.4	478.8	479.2	479.1	479.0
120°	511.2	511.8	512.5	513.1	513.4	513.2	513.1	512.9	512.7	513.1	513.4
122.5°	544.4	544.8	545.2	545.6	545.9	546.2	546.4	546.6	546.9	547.1	547.3
125°	592.9	593.5	594.2	594.8	595.0	594.7	594.4	594.0	593.7	594.2	594.7
127.5°	637.9	638.1	638.2	638.4	638.9	639.6	640.5	641.2	642.0	641.9	641.8
130°	667.3	667.5	667.6	667.8	668.1	668.6	669.1	669.6	670.1	670.3	670.4
132.5°	694.5	694.8	695.0	695.3	695.8	696.4	697.1	697.7	698.3	698.5	698.6
135°	734.5	734.3	734.1	734.0	734.2	734.9	735.5	736.2	736.9	737.2	737.5
137.5°	770.5	770.6	770.6	770.7	771.1	771.8	772.5	773.4	774.1	774.4	774.8
140°	794.2	794.5	794.9	795.2	795.5	795.9	796.2	796.5	796.9	797.3	797.8
142.5°	815.5	816.1	816.6	817.2	817.6	817.8	818.0	818.2	818.4	818.8	819.2
145°	847.6	848.1	848.6	849.1	849.3	849.3	849.3	849.3	849.3	849.5	849.6
147.5°	873.6	874.5	875.5	876.5	876.8	876.7	876.5	876.3	876.2	876.3	876.4
150°	891.9	892.6	893.3	893.9	894.2	894.0	893.8	893.7	893.5	893.5	893.5
152.5°	907.4	908.0	908.5	909.0	909.1	908.8	908.6	908.3	908.0	908.2	908.5
155°	929.0	929.1	929.3	929.5	929.3	928.8	928.3	927.8	927.3	928.0	928.6
157.5°	947.2	947.1	947.0	946.8	946.4	945.9	945.3	944.7	944.2	945.0	945.9
160°	957.5	957.0	956.5	956.0	955.6	955.5	955.3	955.1	955.0	956.0	957.0
162.5°	966.9	966.3	965.7	965.0	964.6	964.5	964.3	964.1	964.0	965.0	966.0
165°	978.9	978.1	977.2	976.4	976.0	976.0	976.0	976.0	976.0	977.3	978.7
167.5°	988.5	987.6	986.7	985.8	985.4	985.3	985.2	985.1	985.0	986.4	988.0
170°	993.7	992.7	991.7	990.8	990.3	990.5	990.7	990.8	991.0	992.3	993.6
172.5°	997.3	996.3	995.3	994.3	993.9	994.1	994.2	994.4	994.6	995.9	997.2
175°	1001.2	1000.3	999.3	998.3	997.8	997.9	998.2	998.4	998.5	1000.0	1001.5
177.5°	1003.1	1002.2	1001.2	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1	1003.2
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3	1685.3
2.5°	1776.4	1777.5	1782.4	1786.4	1787.5	1793.1	1793.6
5°	1932.4	1944.3	1967.3	1969.4	1972.9	1991.0	1977.1
7.5°	2115.4	2145.5	2165.6	2183.3	2189.8	2197.7	2196.1
10°	2232.6	2277.2	2299.7	2335.2	2336.6	2345.7	2340.2
12.5°	2350.5	2402.4	2443.2	2449.7	2479.6	2484.2	2492.0
15°	2517.4	2572.6	2629.2	2649.4	2690.6	2700.4	2715.7
17.5°	2674.4	2730.8	2770.5	2822.8	2839.7	2862.4	2846.9
20°	2760.4	2821.9	2872.1	2913.3	2930.7	2943.3	2941.9
22.5°	2812.4	2874.3	2915.1	2946.2	2962.5	2967.9	2967.6
25°	2844.9	2880.4	2893.1	2904.9	2886.8	2880.4	2883.3
27.5°	2754.4	2745.2	2712.4	2669.4	2624.6	2589.2	2569.9
30°	2629.9	2575.4	2525.8	2439.2	2394.6	2368.0	2344.3
32.5°	2453.4	2367.0	2271.7	2192.4	2141.6	2102.2	2096.4
35°	2150.9	2021.0	1904.5	1807.5	1757.2	1714.5	1704.9
37.5°	1828.7	1693.7	1588.8	1503.4	1449.4	1419.3	1391.2
40°	1614.8	1498.8	1395.5	1322.9	1281.7	1260.1	1242.6
42.5°	1450.0	1344.1	1241.4	1186.1	1148.8	1135.6	1125.4
45°	1222.4	1124.0	1052.8	1010.9	989.3	966.9	956.4
47.5°	1040.2	960.1	913.1	877.6	854.3	841.1	834.4
50°	936.9	871.2	829.4	802.1	781.2	770.7	765.2
52.5°	845.3	791.4	756.2	734.6	720.3	712.7	710.4
55°	728.1	686.9	664.6	645.8	635.3	628.3	625.5
57.5°	632.9	601.3	583.1	567.5	563.5	557.6	555.7
60°	570.4	545.9	530.6	520.1	516.6	509.7	511.0
62.5°	515.0	495.1	482.0	475.9	471.4	465.5	467.5
65°	435.7	421.0	413.9	408.4	402.8	399.3	402.1
67.5°	365.6	355.5	346.0	342.7	340.0	339.4	336.5
70°	319.7	311.3	303.0	300.9	300.9	298.1	297.4
72.5°	275.6	269.4	263.9	262.4	260.1	261.3	258.3
75°	212.9	208.0	205.9	203.9	203.2	203.2	201.1
77.5°	157.3	153.7	150.4	150.4	147.8	146.9	146.6
80°	119.4	118.0	115.2	115.2	113.8	114.5	113.1
82.5°	89.8	87.9	87.3	86.1	84.2	84.3	82.9
85°	48.2	46.0	45.3	43.3	41.9	43.3	41.9
87.5°	20.7	20.3	19.9	18.8	18.3	18.4	16.8
90°	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	18.9	19.9	20.4	20.5	20.6	20.6	20.7
95°	19.5	20.5	21.1	21.2	21.4	21.6	21.7
97.5°	20.1	20.2	20.3	20.5	20.7	20.8	21.0
100°	24.4	21.6	20.3	20.5	20.7	20.8	21.0
102.5°	67.3	36.8	21.4	21.5	21.5	21.5	21.6
105°	238.3	239.8	237.6	231.7	225.6	219.6	213.7
107.5°	293.8	294.6	295.2	295.9	296.5	297.1	297.7
110°	331.5	331.9	332.3	332.9	333.4	333.9	334.4



TEST NUMBER: P332811-840

CATALOG NUMBER: S124DIW-S1020D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	368.2	368.1	368.4	369.0	369.6	370.3	370.9
115°	423.7	424.1	424.2	424.2	424.2	424.2	424.2
117.5°	479.0	478.9	478.8	478.8	478.7	478.6	478.6
120°	513.7	514.0	514.0	513.7	513.4	513.1	512.7
122.5°	547.5	547.8	547.6	547.3	546.9	546.6	546.3
125°	595.2	595.7	596.0	596.2	596.3	596.5	596.7
127.5°	641.7	641.6	641.5	641.4	641.2	641.1	641.0
130°	670.7	670.9	670.9	670.9	670.9	670.9	670.9
132.5°	698.8	699.0	699.0	698.9	698.7	698.6	698.5
135°	737.9	738.2	738.5	738.8	739.2	739.5	739.8
137.5°	775.2	775.5	775.7	775.6	775.5	775.4	775.3
140°	798.3	798.8	799.2	799.3	799.5	799.7	799.8
142.5°	819.5	819.9	820.1	820.1	820.1	820.2	820.2
145°	849.8	850.0	850.2	850.5	850.9	851.2	851.5
147.5°	876.6	876.7	876.9	877.0	877.2	877.4	877.5
150°	893.5	893.5	893.6	893.8	893.9	894.1	894.2
152.5°	908.7	909.0	909.1	909.0	908.9	908.8	908.7
155°	929.3	929.9	930.0	929.5	929.0	928.5	928.1
157.5°	946.8	947.7	947.7	946.8	945.9	945.0	944.2
160°	958.0	959.0	959.0	958.0	957.0	956.0	955.0
162.5°	966.9	968.0	968.0	966.8	965.6	964.5	963.4
165°	980.0	981.3	981.3	979.8	978.3	976.7	975.2
167.5°	989.4	990.9	990.8	989.1	987.4	985.7	984.1
170°	995.0	996.3	996.1	994.5	992.8	991.2	989.5
172.5°	998.6	999.9	999.7	997.8	996.1	994.3	992.5
175°	1003.0	1004.5	1004.2	1002.2	1000.3	998.3	996.2
177.5°	1004.2	1005.3	1005.0	1003.4	1001.8	1000.3	998.7
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2

(END OF REPORT)