

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333092-930

Luminaire Tested: **S124RDIW-S1020D1560U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333092-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7950.9 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11293	11293	11293	11293
5°	13100	11327	10011	11327
10°	15497	11278	8936	11278
15°	17901	11173	7678	11173
20°	19930	11030	6943	11030
25°	20574	10889	6446	10889
30°	18011	10718	6147	10718
35°	14020	10464	5966	10464
40°	10513	10175	5868	10175
45°	8301	9710	5817	9710
50°	7008	9173	5649	9173
55°	6108	8583	5346	8583
60°	5496	7971	4732	7971
65°	4844	7310	4069	7310
70°	4362	6626	3673	6626
75°	3656	5873	3132	5873
80°	3092	5002	2934	5002
85°	2612	3909	2612	3909



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	1.7
10°-20°	408.9	5.1
20°-30°	639.5	8.0
30°-40°	710.9	8.9
40°-50°	630.7	7.9
50°-60°	491.5	6.2
60°-70°	321.8	4.0
70°-80°	158.2	2.0
80°-90°	43.8	0.6
90°-100°	104.8	1.3
100°-110°	310.6	3.9
110°-120°	527.1	6.6
120°-130°	695.1	8.7
130°-140°	780.6	9.8
140°-150°	767.1	9.6
150°-160°	645.2	8.1
160°-170°	429.2	5.4
170°-180°	150.3	1.9
0°-30°	1183.9	14.9
0°-40°	1894.8	23.8
0°-60°	3017.0	37.9
0°-90°	3540.8	44.5
90°-120°	942.5	11.9
90°-150°	3185.3	40.1
90°-180°	4410.0	55.5
0°-180°	7950.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1399	1399	1399	1399	1399	
5°	1616	1398	1235	1398	1616	164
15°	2142	1337	919	1337	2142	609
25°	2310	1222	724	1222	2310	1025
35°	1423	1062	605	1062	1423	892
45°	727	850	510	850	727	576
55°	434	610	380	610	434	395
65°	254	383	213	383	254	255
75°	117	188	100	188	117	129
85°	28	42	28	42	28	33
90°	37	4	37	4	37	20
95°	97	74	97	74	97	101
105°	300	286	300	286	300	316
115°	531	536	531	536	531	525
125°	774	781	774	781	774	691
135°	1008	1007	1008	1007	1008	778
145°	1224	1223	1224	1223	1224	766
155°	1400	1401	1400	1401	1400	645
165°	1522	1526	1522	1526	1522	429
175°	1580	1587	1580	1587	1580	150
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1475.5	1479.6	1475.5	1475.1	1470.6	1469.3	1467.5	1461.6	1450.7	1444.5	1445.8
5°	1616.5	1630.5	1622.7	1621.5	1609.2	1596.8	1588.9	1570.8	1551.7	1538.7	1528.0
7.5°	1779.5	1787.5	1782.7	1774.7	1754.7	1743.3	1725.0	1701.2	1666.9	1640.5	1616.6
10°	1890.4	1897.1	1894.9	1880.2	1865.6	1835.7	1818.8	1785.6	1742.1	1707.8	1675.6
12.5°	1999.5	2006.7	1986.9	1987.5	1959.8	1936.3	1909.4	1867.6	1817.5	1773.1	1732.9
15°	2141.8	2132.7	2132.7	2121.5	2090.4	2057.8	2030.2	1986.2	1923.0	1870.1	1814.3
17.5°	2253.2	2256.3	2251.7	2225.0	2200.7	2166.9	2116.3	2065.0	2006.4	1935.3	1878.2
20°	2319.9	2319.9	2314.8	2296.8	2265.2	2229.1	2174.5	2118.6	2044.3	1972.7	1908.5
22.5°	2346.9	2348.7	2342.8	2327.8	2299.5	2264.2	2217.7	2161.0	2084.4	2003.8	1924.2
25°	2309.7	2320.4	2321.6	2317.6	2309.2	2287.7	2247.7	2189.6	2120.9	2033.5	1947.8
27.5°	2120.6	2134.1	2145.9	2165.4	2191.4	2204.9	2206.7	2177.2	2117.2	2033.1	1946.9
30°	1932.1	1943.3	1980.0	2027.9	2065.1	2098.9	2128.3	2136.1	2102.3	2026.8	1936.0
32.5°	1722.9	1738.2	1774.8	1826.4	1888.3	1945.6	2011.4	2045.0	2044.1	1998.8	1914.8
35°	1422.6	1433.9	1467.7	1521.8	1596.2	1681.3	1785.6	1866.7	1921.9	1918.0	1866.7
37.5°	1147.3	1160.0	1194.2	1239.1	1311.2	1416.6	1517.5	1629.3	1731.5	1788.8	1771.6
40°	997.6	998.2	1031.4	1077.7	1145.3	1237.1	1347.0	1471.0	1584.9	1677.9	1695.9
42.5°	879.5	879.5	901.6	951.4	1000.1	1086.5	1191.5	1314.6	1447.8	1555.3	1603.0
45°	727.1	732.1	750.2	780.1	818.4	891.6	975.6	1090.1	1239.4	1366.8	1446.3
47.5°	615.7	623.1	634.6	659.0	689.5	738.3	807.8	910.6	1032.1	1172.2	1285.3
50°	558.0	559.1	573.7	587.3	613.8	652.6	713.5	799.2	910.8	1045.5	1171.2
52.5°	508.4	508.2	517.0	534.1	555.6	586.0	635.1	713.1	812.0	932.8	1062.5
55°	434.0	436.8	443.6	457.1	473.4	494.9	533.8	592.4	670.2	773.3	891.1
57.5°	377.4	378.9	384.2	389.9	404.9	420.4	449.6	490.3	556.0	640.4	750.2
60°	340.4	341.0	342.7	351.1	363.0	377.6	397.4	431.7	487.0	564.2	651.0
62.5°	304.4	305.3	307.9	314.1	323.3	333.5	354.1	381.7	427.5	493.4	571.6
65°	253.6	254.2	258.1	260.4	267.7	276.7	292.0	310.5	342.1	397.4	456.6
67.5°	211.9	211.9	212.1	215.2	220.3	226.2	235.4	250.2	274.0	307.9	360.1
70°	184.8	184.8	186.0	187.7	190.5	195.6	200.6	211.9	229.4	257.0	297.0
72.5°	159.6	160.0	161.2	161.5	163.0	167.1	170.9	178.1	191.1	211.9	244.3
75°	117.2	119.0	121.7	124.0	126.8	126.3	130.2	134.7	138.7	151.1	169.7
77.5°	87.2	86.3	86.7	88.6	88.9	89.5	92.3	95.8	98.7	104.6	111.3
80°	66.5	66.5	68.2	68.7	68.2	68.7	71.6	73.3	74.4	76.6	82.8
82.5°	50.3	51.2	50.6	51.2	51.5	52.1	54.5	54.8	55.9	56.8	59.4
85°	28.2	28.8	29.3	28.2	28.2	28.2	29.3	29.8	31.0	30.4	31.6
87.5°	17.3	16.7	17.0	17.0	17.3	16.6	16.8	17.4	16.1	16.2	15.8
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	54.5	54.2	53.9	53.6	53.2	52.6	51.6	50.6	49.7	48.7	47.1
95°	97.1	97.1	97.1	97.1	97.1	96.7	95.9	95.1	94.2	93.4	91.6
97.5°	152.2	152.2	152.2	152.2	152.2	151.7	150.7	149.8	148.7	147.7	145.5
100°	190.5	190.5	190.5	190.5	190.5	190.3	189.7	189.1	188.7	188.1	185.6
102.5°	233.8	233.6	233.4	233.2	232.9	232.4	231.7	230.9	230.2	229.4	227.1
105°	299.9	299.1	298.3	297.5	296.7	295.9	295.1	294.2	293.4	292.6	291.5
107.5°	364.4	364.4	364.5	364.5	364.6	364.3	363.5	362.7	361.9	361.2	361.0
110°	410.6	409.8	409.0	408.1	407.3	407.2	407.7	408.3	408.8	409.4	409.6



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.8	457.6	457.5	457.3	457.1	457.1	457.2	457.3	457.5	457.5	458.0
115°	531.1	531.3	531.7	531.9	532.1	532.5	532.7	533.0	533.3	533.5	534.1
117.5°	600.9	601.4	602.0	602.5	603.1	603.8	604.8	605.7	606.6	607.6	607.9
120°	654.0	653.5	652.9	652.4	651.8	652.2	653.6	654.9	656.3	657.7	658.5
122.5°	698.3	699.3	700.3	701.2	702.2	703.2	704.1	705.0	706.0	706.9	707.3
125°	774.5	775.0	775.6	776.1	776.7	777.2	777.8	778.3	778.9	779.4	779.7
127.5°	845.1	845.5	846.0	846.4	846.8	847.3	847.8	848.4	848.9	849.5	849.9
130°	891.3	892.3	893.5	894.5	895.6	896.4	897.0	897.6	898.1	898.6	898.6
132.5°	940.4	940.9	941.3	941.8	942.2	942.6	943.2	943.8	944.4	944.9	945.1
135°	1008.0	1008.9	1009.7	1010.5	1011.3	1012.0	1012.6	1013.1	1013.7	1014.2	1014.2
137.5°	1079.1	1079.0	1078.8	1078.6	1078.5	1078.7	1079.5	1080.2	1080.8	1081.6	1081.2
140°	1122.4	1122.7	1122.9	1123.2	1123.5	1123.7	1124.1	1124.3	1124.5	1124.9	1124.9
142.5°	1165.6	1165.7	1165.8	1165.8	1165.9	1166.0	1166.0	1166.0	1166.1	1166.1	1166.4
145°	1224.4	1225.2	1226.0	1226.9	1227.7	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1283.9	1284.2	1284.5	1284.7	1285.0	1285.2	1285.5	1285.7	1285.9	1286.1	1286.4
150°	1320.3	1320.6	1320.9	1321.1	1321.4	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1353.7	1354.5	1355.2	1355.8	1356.6	1356.6	1355.9	1355.3	1354.6	1354.0	1353.8
155°	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2	1400.5
157.5°	1441.8	1442.7	1443.7	1444.5	1445.4	1445.5	1444.7	1443.9	1443.1	1442.3	1442.3
160°	1465.3	1466.7	1468.1	1469.5	1470.8	1471.1	1470.3	1469.5	1468.7	1467.9	1468.1
162.5°	1490.0	1491.3	1492.7	1494.0	1495.4	1495.3	1493.9	1492.4	1490.9	1489.5	1489.7
165°	1521.9	1523.0	1524.1	1525.2	1526.3	1526.0	1524.4	1522.7	1521.1	1519.5	1520.0
167.5°	1544.7	1546.5	1548.2	1549.9	1551.6	1551.6	1550.0	1548.3	1546.7	1545.1	1545.0
170°	1557.5	1559.5	1561.4	1563.3	1565.2	1565.4	1563.7	1562.1	1560.4	1558.8	1558.5
172.5°	1568.4	1570.3	1572.2	1574.1	1576.1	1576.1	1574.2	1572.4	1570.5	1568.6	1568.6
175°	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7	1580.0
177.5°	1585.6	1587.4	1589.1	1590.8	1592.6	1592.7	1591.1	1589.7	1588.1	1586.6	1586.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1441.3	1435.0	1431.8	1424.6	1416.0	1411.5	1407.5	1401.6	1393.9	1385.8	1380.0
5°	1514.4	1500.9	1484.0	1463.7	1445.7	1428.2	1413.0	1397.7	1380.3	1362.3	1344.3
7.5°	1589.5	1562.9	1534.1	1500.9	1468.6	1439.2	1412.1	1386.2	1356.8	1330.6	1306.7
10°	1641.8	1605.7	1565.7	1523.5	1481.2	1444.5	1408.5	1375.8	1339.7	1307.6	1280.5
12.5°	1684.2	1641.8	1593.7	1541.1	1490.2	1445.9	1404.4	1361.8	1320.8	1286.0	1249.9
15°	1754.5	1696.5	1631.7	1568.6	1502.6	1442.3	1386.5	1336.9	1290.1	1241.1	1206.7
17.5°	1802.9	1734.1	1655.2	1579.4	1501.5	1430.4	1366.0	1306.9	1253.0	1202.9	1162.0
20°	1831.7	1755.7	1668.3	1582.1	1494.7	1418.6	1349.3	1283.9	1228.2	1174.0	1131.7
22.5°	1848.0	1763.8	1668.3	1578.0	1487.5	1405.1	1329.0	1260.9	1200.2	1146.1	1099.3
25°	1853.2	1763.0	1665.5	1561.8	1462.6	1375.2	1296.3	1222.5	1154.9	1100.7	1051.2
27.5°	1846.0	1739.8	1639.9	1533.5	1431.2	1339.0	1256.2	1178.7	1110.9	1052.9	1002.0
30°	1835.2	1721.3	1614.2	1503.7	1400.0	1311.6	1224.2	1149.8	1079.3	1019.0	967.8
32.5°	1811.7	1698.8	1583.6	1470.4	1365.3	1274.1	1191.2	1116.4	1047.3	985.7	931.2
35°	1765.3	1650.8	1525.8	1409.7	1306.4	1211.8	1134.0	1061.8	995.9	930.0	872.5
37.5°	1704.1	1587.1	1462.7	1335.5	1232.3	1142.9	1071.5	1003.8	939.5	879.2	815.5
40°	1646.3	1539.8	1411.3	1285.1	1179.1	1092.8	1027.0	965.5	900.7	840.9	777.2
42.5°	1576.5	1485.7	1355.8	1229.1	1124.5	1041.5	980.0	919.9	861.0	803.1	736.6
45°	1459.8	1391.0	1269.3	1147.5	1042.1	959.9	903.5	850.5	798.7	743.4	680.9
47.5°	1326.1	1279.5	1174.4	1049.8	952.3	878.2	823.8	780.5	736.6	681.4	626.6
50°	1233.2	1203.3	1101.9	988.1	895.0	826.8	771.0	730.4	693.8	640.8	591.8
52.5°	1134.0	1118.1	1032.4	923.6	833.7	766.9	719.2	682.7	645.6	601.6	555.7
55°	982.9	991.4	918.7	824.6	740.0	683.7	640.3	609.8	578.3	541.1	505.6
57.5°	828.5	859.4	810.6	728.0	648.7	596.6	563.9	538.3	511.8	481.0	450.7
60°	736.1	762.0	734.4	661.7	592.4	543.9	513.5	493.7	467.2	439.0	416.0
62.5°	645.9	673.6	657.3	598.6	534.2	492.5	465.7	447.3	427.5	403.0	379.0
65°	532.6	550.7	542.7	502.2	456.6	421.0	396.2	382.7	364.7	346.7	325.2
67.5°	408.0	442.8	438.1	416.6	377.2	349.4	333.2	321.2	304.8	291.4	276.9
70°	335.3	367.5	366.9	349.4	328.0	302.1	290.8	280.7	266.0	253.1	241.2
72.5°	274.5	303.9	308.3	294.9	280.2	260.7	249.8	242.8	228.6	219.7	210.1
75°	192.2	213.6	219.2	219.2	212.5	202.4	192.7	188.3	178.1	170.2	164.6
77.5°	126.0	139.6	148.4	150.3	151.4	148.0	140.1	137.0	129.1	126.4	121.0
80°	89.0	98.1	108.2	111.6	114.4	113.3	109.9	107.6	100.4	97.5	95.2
82.5°	61.6	66.5	74.8	82.3	81.5	84.5	81.5	79.7	74.2	73.1	70.9
85°	32.1	32.7	33.8	38.9	41.7	42.8	43.4	42.2	40.6	40.6	36.6
87.5°	15.3	14.4	14.9	14.4	14.3	15.5	16.2	16.1	15.3	14.6	13.8
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	45.7	44.1	42.6	40.1	36.6	33.2	29.8	26.3	29.8	33.2	36.6
95°	89.6	87.7	85.8	83.6	81.1	78.7	76.2	73.8	76.2	78.7	81.1
97.5°	143.2	141.0	138.8	136.7	134.8	132.7	130.8	128.8	130.8	132.7	134.8
100°	183.2	180.8	178.2	176.5	175.4	174.3	173.2	172.1	173.2	174.3	175.4
102.5°	224.9	222.7	220.5	219.1	218.7	218.3	217.8	217.4	217.8	218.3	218.7
105°	290.4	289.3	288.2	287.6	287.2	287.0	286.7	286.4	286.7	287.0	287.2
107.5°	360.9	360.7	360.5	360.3	360.0	359.6	359.3	359.0	359.3	359.6	360.0
110°	409.9	410.2	410.5	410.3	409.8	409.2	408.7	408.1	408.7	409.2	409.8



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	459.0	459.5	459.7	459.6	459.5	459.4	459.3	459.4	459.5	459.6
115°	534.6	535.2	535.7	536.0	536.0	536.0	536.0	536.0	536.0	536.0	536.0
117.5°	608.3	608.7	609.1	609.2	608.9	608.7	608.5	608.3	608.5	608.7	608.9
120°	659.3	660.1	661.0	660.8	659.7	658.7	657.5	656.5	657.5	658.7	659.7
122.5°	707.6	708.0	708.4	708.3	707.9	707.5	707.0	706.6	707.0	707.5	707.9
125°	779.9	780.2	780.5	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
127.5°	850.4	850.8	851.3	851.0	850.2	849.4	848.6	847.7	848.6	849.4	850.2
130°	898.6	898.6	898.6	898.2	897.4	896.6	895.8	895.0	895.8	896.6	897.4
132.5°	945.3	945.5	945.7	945.6	944.9	944.4	943.8	943.1	943.8	944.4	944.9
135°	1014.2	1014.2	1014.2	1013.4	1011.8	1010.1	1008.4	1006.8	1008.4	1010.1	1011.8
137.5°	1080.7	1080.3	1079.9	1079.2	1078.5	1077.7	1076.9	1076.2	1076.9	1077.7	1078.5
140°	1124.9	1124.9	1124.9	1124.5	1124.1	1123.5	1122.9	1122.4	1122.9	1123.5	1124.1
142.5°	1166.6	1166.8	1167.0	1166.9	1166.3	1165.8	1165.2	1164.7	1165.2	1165.8	1166.3
145°	1228.8	1228.5	1228.2	1227.6	1226.5	1225.4	1224.3	1223.2	1224.3	1225.4	1226.5
147.5°	1286.5	1286.8	1287.0	1286.5	1285.2	1283.9	1282.5	1281.2	1282.5	1283.9	1285.2
150°	1321.5	1321.5	1321.5	1321.0	1319.9	1318.8	1317.7	1316.6	1317.7	1318.8	1319.9
152.5°	1353.6	1353.3	1353.2	1352.7	1352.0	1351.4	1350.7	1350.1	1350.7	1351.4	1352.0
155°	1400.8	1401.0	1401.3	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4
157.5°	1442.3	1442.4	1442.5	1442.8	1443.2	1443.7	1444.2	1444.7	1444.2	1443.7	1443.2
160°	1468.4	1468.7	1468.9	1469.2	1469.5	1469.7	1470.0	1470.3	1470.0	1469.7	1469.5
162.5°	1490.0	1490.3	1490.5	1491.0	1491.8	1492.5	1493.2	1493.9	1493.2	1492.5	1491.8
165°	1520.5	1521.1	1521.7	1522.3	1523.1	1524.0	1524.8	1525.6	1524.8	1524.0	1523.1
167.5°	1544.9	1544.9	1544.8	1545.4	1546.5	1547.7	1548.8	1550.0	1548.8	1547.7	1546.5
170°	1558.3	1558.0	1557.7	1558.3	1559.6	1561.0	1562.4	1563.7	1562.4	1561.0	1559.6
172.5°	1568.6	1568.5	1568.4	1569.0	1570.1	1571.2	1572.4	1573.5	1572.4	1571.2	1570.1
175°	1580.2	1580.5	1580.8	1581.6	1583.0	1584.4	1585.7	1587.1	1585.7	1584.4	1583.0
177.5°	1586.6	1586.6	1586.6	1587.1	1588.2	1589.3	1590.4	1591.5	1590.4	1589.3	1588.2
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1373.6	1369.1	1363.3	1356.5	1348.4	1341.2	1338.1	1340.8	1342.1	1338.5	1338.1
5°	1331.9	1317.8	1306.4	1289.6	1276.0	1264.8	1256.9	1253.5	1254.6	1245.6	1243.3
7.5°	1284.8	1268.1	1249.7	1229.6	1210.9	1194.3	1185.6	1180.9	1171.3	1167.3	1160.4
10°	1254.6	1232.1	1214.1	1190.3	1169.0	1149.2	1139.6	1131.7	1122.2	1117.7	1108.1
12.5°	1223.5	1197.3	1177.5	1152.9	1131.1	1107.3	1098.1	1083.5	1068.5	1059.1	1046.8
15°	1179.7	1148.1	1123.9	1094.5	1068.6	1041.5	1017.3	990.3	980.2	958.7	946.3
17.5°	1128.4	1096.3	1066.3	1027.0	987.0	953.4	927.6	901.6	886.1	872.5	866.2
20°	1094.5	1065.3	1023.5	977.9	933.4	896.2	875.3	858.4	841.5	831.9	825.2
22.5°	1062.5	1025.1	976.6	927.4	882.9	853.8	836.1	818.7	804.9	795.8	786.8
25°	1008.9	959.9	908.6	852.2	821.7	796.4	777.2	763.1	754.7	742.8	738.3
27.5°	953.7	894.4	837.8	799.9	768.2	745.0	728.3	717.7	707.0	699.4	693.6
30°	911.3	851.1	800.4	764.3	732.1	713.0	699.4	687.1	678.6	672.4	667.9
32.5°	869.4	809.1	766.5	727.7	702.4	683.7	669.3	660.0	653.4	645.3	642.6
35°	808.8	755.2	718.0	683.1	657.2	640.3	629.0	619.4	613.8	611.6	609.8
37.5°	750.5	706.7	666.7	638.1	614.9	601.6	588.3	583.6	579.8	575.7	577.5
40°	713.5	672.4	636.9	606.4	587.8	573.2	565.3	559.7	556.3	556.3	556.3
42.5°	681.5	641.3	606.7	579.4	560.8	548.4	539.6	534.8	533.8	533.3	536.0
45°	631.9	594.6	559.7	537.1	521.4	508.9	503.9	499.9	499.9	502.2	502.7
47.5°	582.5	547.7	519.7	494.4	480.0	472.2	467.8	465.8	466.0	468.2	470.8
50°	552.4	518.0	490.3	467.8	454.3	446.9	443.0	441.9	443.0	443.0	446.9
52.5°	519.4	488.7	461.5	442.5	427.2	420.4	418.2	416.6	417.3	419.1	420.8
55°	471.2	443.6	417.7	399.6	388.3	383.8	378.8	379.3	378.2	379.3	379.3
57.5°	422.8	398.0	373.9	359.6	349.7	343.2	337.6	339.2	337.5	337.3	336.4
60°	391.8	364.7	345.5	332.6	321.2	315.6	310.5	311.7	310.0	308.8	306.6
62.5°	357.9	335.3	317.1	304.6	295.5	289.0	284.0	282.8	278.9	275.1	270.1
65°	308.8	290.2	273.9	262.1	253.6	248.6	244.6	241.2	232.8	223.7	219.2
67.5°	261.2	247.8	232.5	222.5	215.6	209.0	201.5	195.7	187.8	182.9	180.0
70°	230.5	217.5	204.6	195.0	187.7	181.5	173.0	169.1	163.5	161.2	158.4
72.5°	201.2	189.1	177.1	168.4	160.6	155.8	149.1	145.2	142.7	141.8	139.0
75°	156.7	147.1	138.1	130.2	124.0	120.6	117.8	115.0	113.8	108.8	106.0
77.5°	114.3	108.0	102.3	96.7	92.3	90.1	84.6	81.4	79.5	77.1	76.6
80°	89.0	84.5	78.9	75.5	69.3	67.1	64.8	64.2	63.7	63.1	62.5
82.5°	66.9	62.5	56.8	54.8	53.1	51.8	50.4	49.8	49.2	49.6	49.5
85°	33.8	31.6	31.6	31.0	30.4	29.8	29.3	29.3	28.8	29.3	28.8
87.5°	14.4	14.5	14.9	14.4	15.3	15.8	15.7	16.0	16.8	16.2	16.4
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	40.1	42.6	44.1	45.7	47.1	48.7	49.7	50.6	51.6	52.6	53.2
95°	83.6	85.8	87.7	89.6	91.6	93.4	94.2	95.1	95.9	96.7	97.1
97.5°	136.7	138.8	141.0	143.2	145.5	147.7	148.7	149.8	150.7	151.7	152.2
100°	176.5	178.2	180.8	183.2	185.6	188.1	188.7	189.1	189.7	190.3	190.5
102.5°	219.1	220.5	222.7	224.9	227.1	229.4	230.2	230.9	231.7	232.4	232.9
105°	287.6	288.2	289.3	290.4	291.5	292.6	293.4	294.2	295.1	295.9	296.7
107.5°	360.3	360.5	360.7	360.9	361.0	361.2	361.9	362.7	363.5	364.3	364.6
110°	410.3	410.5	410.2	409.9	409.6	409.4	408.8	408.3	407.7	407.2	407.3



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	459.7	459.5	459.0	458.5	458.0	457.5	457.5	457.3	457.2	457.1	457.1
115°	536.0	535.7	535.2	534.6	534.1	533.5	533.3	533.0	532.7	532.5	532.1
117.5°	609.2	609.1	608.7	608.3	607.9	607.6	606.6	605.7	604.8	603.8	603.1
120°	660.8	661.0	660.1	659.3	658.5	657.7	656.3	654.9	653.6	652.2	651.8
122.5°	708.3	708.4	708.0	707.6	707.3	706.9	706.0	705.0	704.1	703.2	702.2
125°	780.6	780.5	780.2	779.9	779.7	779.4	778.9	778.3	777.8	777.2	776.7
127.5°	851.0	851.3	850.8	850.4	849.9	849.5	848.9	848.4	847.8	847.3	846.8
130°	898.2	898.6	898.6	898.6	898.6	898.6	898.1	897.6	897.0	896.4	895.6
132.5°	945.6	945.7	945.5	945.3	945.1	944.9	944.4	943.8	943.2	942.6	942.2
135°	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7	1013.1	1012.6	1012.0	1011.3
137.5°	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8	1080.2	1079.5	1078.7	1078.5
140°	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.3	1124.1	1123.7	1123.5
142.5°	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1	1166.0	1166.0	1166.0	1165.9
145°	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1	1228.8	1228.5	1228.2	1227.7
147.5°	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9	1285.7	1285.5	1285.2	1285.0
150°	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.4
152.5°	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6	1355.3	1355.9	1356.6	1356.6
155°	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6
157.5°	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1	1443.9	1444.7	1445.5	1445.4
160°	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7	1469.5	1470.3	1471.1	1470.8
162.5°	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9	1492.4	1493.9	1495.3	1495.4
165°	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1	1522.7	1524.4	1526.0	1526.3
167.5°	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7	1548.3	1550.0	1551.6	1551.6
170°	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4	1562.1	1563.7	1565.4	1565.2
172.5°	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5	1572.4	1574.2	1576.1	1576.1
175°	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4
177.5°	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1	1589.7	1591.1	1592.7	1592.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1335.3	1336.2	1333.1	1332.2	1333.1	1336.2	1335.3	1338.1	1338.5	1342.1	1340.8
5°	1238.8	1237.7	1234.9	1235.4	1234.9	1237.7	1238.8	1243.3	1245.6	1254.6	1253.5
7.5°	1156.3	1151.9	1153.2	1148.7	1153.2	1151.9	1156.3	1160.4	1167.3	1171.3	1180.9
10°	1105.8	1099.6	1094.5	1090.1	1094.5	1099.6	1105.8	1108.1	1117.7	1122.2	1131.7
12.5°	1036.8	1031.5	1024.7	1026.1	1024.7	1031.5	1036.8	1046.8	1059.1	1068.5	1083.5
15°	939.0	930.5	917.0	918.7	917.0	930.5	939.0	946.3	958.7	980.2	990.3
17.5°	856.1	856.2	850.0	851.5	850.0	856.2	856.1	866.2	872.5	886.1	901.6
20°	813.3	809.3	809.9	808.2	809.9	809.3	813.3	825.2	831.9	841.5	858.4
22.5°	783.6	778.7	774.8	771.3	774.8	778.7	783.6	786.8	795.8	804.9	818.7
25°	733.3	729.9	724.8	723.7	724.8	729.9	733.3	738.3	742.8	754.7	763.1
27.5°	689.1	688.4	686.4	683.8	686.4	688.4	689.1	693.6	699.4	707.0	717.7
30°	663.4	662.3	661.1	659.4	661.1	662.3	663.4	667.9	672.4	678.6	687.1
32.5°	640.4	639.7	638.5	638.7	638.5	639.7	640.4	642.6	645.3	653.4	660.0
35°	607.6	607.0	605.9	605.4	605.9	607.0	607.6	609.8	611.6	613.8	619.4
37.5°	576.9	578.4	577.7	577.6	577.7	578.4	576.9	577.5	575.7	579.8	583.6
40°	555.7	556.3	557.4	556.8	557.4	556.3	555.7	556.3	556.3	556.3	559.7
42.5°	538.2	538.3	539.8	537.9	539.8	538.3	538.2	536.0	533.3	533.8	534.8
45°	506.7	510.1	509.5	509.5	509.5	510.1	506.7	502.7	502.2	499.9	499.9
47.5°	472.3	475.2	476.1	475.9	476.1	475.2	472.3	470.8	468.2	466.0	465.8
50°	449.8	448.7	450.4	449.8	450.4	448.7	449.8	446.9	443.0	443.0	441.9
52.5°	422.2	422.5	422.4	421.8	422.4	422.5	422.2	420.8	419.1	417.3	416.6
55°	379.8	380.4	379.3	379.8	379.3	380.4	379.8	379.3	379.3	378.2	379.3
57.5°	333.9	331.2	332.3	330.9	332.3	331.2	333.9	336.4	337.3	337.5	339.2
60°	301.0	296.4	295.3	293.1	295.3	296.4	301.0	306.6	308.8	310.0	311.7
62.5°	264.0	260.8	257.0	258.8	257.0	260.8	264.0	270.1	275.1	278.9	282.8
65°	214.7	212.5	210.8	213.0	210.8	212.5	214.7	219.2	223.7	232.8	241.2
67.5°	177.7	176.5	176.5	175.4	176.5	176.5	177.7	180.0	182.9	187.8	195.7
70°	158.4	156.7	156.7	155.6	156.7	156.7	158.4	158.4	161.2	163.5	169.1
72.5°	138.5	136.8	137.3	136.6	137.3	136.8	138.5	139.0	141.8	142.7	145.2
75°	102.6	99.8	99.8	100.4	99.8	99.8	102.6	106.0	108.8	113.8	115.0
77.5°	76.6	76.0	76.8	75.7	76.8	76.0	76.6	76.6	77.1	79.5	81.4
80°	62.5	62.0	61.5	63.1	61.5	62.0	62.5	62.5	63.1	63.7	64.2
82.5°	48.6	48.5	48.3	50.5	48.3	48.5	48.6	49.5	49.6	49.2	49.8
85°	29.3	28.2	29.3	28.2	29.3	28.2	29.3	28.8	29.3	28.8	29.3
87.5°	17.4	17.0	16.7	17.3	16.7	17.0	17.4	16.4	16.2	16.8	16.0
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	53.6	53.9	54.2	54.5	54.2	53.9	53.6	53.2	52.6	51.6	50.6
95°	97.1	97.1	97.1	97.1	97.1	97.1	97.1	97.1	96.7	95.9	95.1
97.5°	152.2	152.2	152.2	152.2	152.2	152.2	152.2	152.2	151.7	150.7	149.8
100°	190.5	190.5	190.5	190.5	190.5	190.5	190.5	190.5	190.3	189.7	189.1
102.5°	233.2	233.4	233.6	233.8	233.6	233.4	233.2	232.9	232.4	231.7	230.9
105°	297.5	298.3	299.1	299.9	299.1	298.3	297.5	296.7	295.9	295.1	294.2
107.5°	364.5	364.5	364.4	364.4	364.4	364.5	364.5	364.6	364.3	363.5	362.7
110°	408.1	409.0	409.8	410.6	409.8	409.0	408.1	407.3	407.2	407.7	408.3



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	457.3	457.5	457.6	457.8	457.6	457.5	457.3	457.1	457.1	457.2	457.3
115°	531.9	531.7	531.3	531.1	531.3	531.7	531.9	532.1	532.5	532.7	533.0
117.5°	602.5	602.0	601.4	600.9	601.4	602.0	602.5	603.1	603.8	604.8	605.7
120°	652.4	652.9	653.5	654.0	653.5	652.9	652.4	651.8	652.2	653.6	654.9
122.5°	701.2	700.3	699.3	698.3	699.3	700.3	701.2	702.2	703.2	704.1	705.0
125°	776.1	775.6	775.0	774.5	775.0	775.6	776.1	776.7	777.2	777.8	778.3
127.5°	846.4	846.0	845.5	845.1	845.5	846.0	846.4	846.8	847.3	847.8	848.4
130°	894.5	893.5	892.3	891.3	892.3	893.5	894.5	895.6	896.4	897.0	897.6
132.5°	941.8	941.3	940.9	940.4	940.9	941.3	941.8	942.2	942.6	943.2	943.8
135°	1010.5	1009.7	1008.9	1008.0	1008.9	1009.7	1010.5	1011.3	1012.0	1012.6	1013.1
137.5°	1078.6	1078.8	1079.0	1079.1	1079.0	1078.8	1078.6	1078.5	1078.7	1079.5	1080.2
140°	1123.2	1122.9	1122.7	1122.4	1122.7	1122.9	1123.2	1123.5	1123.7	1124.1	1124.3
142.5°	1165.8	1165.8	1165.7	1165.6	1165.7	1165.8	1165.8	1165.9	1166.0	1166.0	1166.0
145°	1226.9	1226.0	1225.2	1224.4	1225.2	1226.0	1226.9	1227.7	1228.2	1228.5	1228.8
147.5°	1284.7	1284.5	1284.2	1283.9	1284.2	1284.5	1284.7	1285.0	1285.2	1285.5	1285.7
150°	1321.1	1320.9	1320.6	1320.3	1320.6	1320.9	1321.1	1321.4	1321.5	1321.5	1321.5
152.5°	1355.8	1355.2	1354.5	1353.7	1354.5	1355.2	1355.8	1356.6	1356.6	1355.9	1355.3
155°	1403.5	1402.4	1401.3	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4
157.5°	1444.5	1443.7	1442.7	1441.8	1442.7	1443.7	1444.5	1445.4	1445.5	1444.7	1443.9
160°	1469.5	1468.1	1466.7	1465.3	1466.7	1468.1	1469.5	1470.8	1471.1	1470.3	1469.5
162.5°	1494.0	1492.7	1491.3	1490.0	1491.3	1492.7	1494.0	1495.4	1495.3	1493.9	1492.4
165°	1525.2	1524.1	1523.0	1521.9	1523.0	1524.1	1525.2	1526.3	1526.0	1524.4	1522.7
167.5°	1549.9	1548.2	1546.5	1544.7	1546.5	1548.2	1549.9	1551.6	1551.6	1550.0	1548.3
170°	1563.3	1561.4	1559.5	1557.5	1559.5	1561.4	1563.3	1565.2	1565.4	1563.7	1562.1
172.5°	1574.1	1572.2	1570.3	1568.4	1570.3	1572.2	1574.1	1576.1	1576.1	1574.2	1572.4
175°	1585.4	1583.6	1581.6	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6
177.5°	1590.8	1589.1	1587.4	1585.6	1587.4	1589.1	1590.8	1592.6	1592.7	1591.1	1589.7
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1338.1	1341.2	1348.4	1356.5	1363.3	1369.1	1373.6	1380.0	1385.8	1393.9	1401.6
5°	1256.9	1264.8	1276.0	1289.6	1306.4	1317.8	1331.9	1344.3	1362.3	1380.3	1397.7
7.5°	1185.6	1194.3	1210.9	1229.6	1249.7	1268.1	1284.8	1306.7	1330.6	1356.8	1386.2
10°	1139.6	1149.2	1169.0	1190.3	1214.1	1232.1	1254.6	1280.5	1307.6	1339.7	1375.8
12.5°	1098.1	1107.3	1131.1	1152.9	1177.5	1197.3	1223.5	1249.9	1286.0	1320.8	1361.8
15°	1017.3	1041.5	1068.6	1094.5	1123.9	1148.1	1179.7	1206.7	1241.1	1290.1	1336.9
17.5°	927.6	953.4	987.0	1027.0	1066.3	1096.3	1128.4	1162.0	1202.9	1253.0	1306.9
20°	875.3	896.2	933.4	977.9	1023.5	1065.3	1094.5	1131.7	1174.0	1228.2	1283.9
22.5°	836.1	853.8	882.9	927.4	976.6	1025.1	1062.5	1099.3	1146.1	1200.2	1260.9
25°	777.2	796.4	821.7	852.2	908.6	959.9	1008.9	1051.2	1100.7	1154.9	1222.5
27.5°	728.3	745.0	768.2	799.9	837.8	894.4	953.7	1002.0	1052.9	1110.9	1178.7
30°	699.4	713.0	732.1	764.3	800.4	851.1	911.3	967.8	1019.0	1079.3	1149.8
32.5°	669.3	683.7	702.4	727.7	766.5	809.1	869.4	931.2	985.7	1047.3	1116.4
35°	629.0	640.3	657.2	683.1	718.0	755.2	808.8	872.5	930.0	995.9	1061.8
37.5°	588.3	601.6	614.9	638.1	666.7	706.7	750.5	815.5	879.2	939.5	1003.8
40°	565.3	573.2	587.8	606.4	636.9	672.4	713.5	777.2	840.9	900.7	965.5
42.5°	539.6	548.4	560.8	579.4	606.7	641.3	681.5	736.6	803.1	861.0	919.9
45°	503.9	508.9	521.4	537.1	559.7	594.6	631.9	680.9	743.4	798.7	850.5
47.5°	467.8	472.2	480.0	494.4	519.7	547.7	582.5	626.6	681.4	736.6	780.5
50°	443.0	446.9	454.3	467.8	490.3	518.0	552.4	591.8	640.8	693.8	730.4
52.5°	418.2	420.4	427.2	442.5	461.5	488.7	519.4	555.7	601.6	645.6	682.7
55°	378.8	383.8	388.3	399.6	417.7	443.6	471.2	505.6	541.1	578.3	609.8
57.5°	337.6	343.2	349.7	359.6	373.9	398.0	422.8	450.7	481.0	511.8	538.3
60°	310.5	315.6	321.2	332.6	345.5	364.7	391.8	416.0	439.0	467.2	493.7
62.5°	284.0	289.0	295.5	304.6	317.1	335.3	357.9	379.0	403.0	427.5	447.3
65°	244.6	248.6	253.6	262.1	273.9	290.2	308.8	325.2	346.7	364.7	382.7
67.5°	201.5	209.0	215.6	222.5	232.5	247.8	261.2	276.9	291.4	304.8	321.2
70°	173.0	181.5	187.7	195.0	204.6	217.5	230.5	241.2	253.1	266.0	280.7
72.5°	149.1	155.8	160.6	168.4	177.1	189.1	201.2	210.1	219.7	228.6	242.8
75°	117.8	120.6	124.0	130.2	138.1	147.1	156.7	164.6	170.2	178.1	188.3
77.5°	84.6	90.1	92.3	96.7	102.3	108.0	114.3	121.0	126.4	129.1	137.0
80°	64.8	67.1	69.3	75.5	78.9	84.5	89.0	95.2	97.5	100.4	107.6
82.5°	50.4	51.8	53.1	54.8	56.8	62.5	66.9	70.9	73.1	74.2	79.7
85°	29.3	29.8	30.4	31.0	31.6	31.6	33.8	36.6	40.6	40.6	42.2
87.5°	15.7	15.8	15.3	14.4	14.9	14.5	14.4	13.8	14.6	15.3	16.1
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	49.7	48.7	47.1	45.7	44.1	42.6	40.1	36.6	33.2	29.8	26.3
95°	94.2	93.4	91.6	89.6	87.7	85.8	83.6	81.1	78.7	76.2	73.8
97.5°	148.7	147.7	145.5	143.2	141.0	138.8	136.7	134.8	132.7	130.8	128.8
100°	188.7	188.1	185.6	183.2	180.8	178.2	176.5	175.4	174.3	173.2	172.1
102.5°	230.2	229.4	227.1	224.9	222.7	220.5	219.1	218.7	218.3	217.8	217.4
105°	293.4	292.6	291.5	290.4	289.3	288.2	287.6	287.2	287.0	286.7	286.4
107.5°	361.9	361.2	361.0	360.9	360.7	360.5	360.3	360.0	359.6	359.3	359.0
110°	408.8	409.4	409.6	409.9	410.2	410.5	410.3	409.8	409.2	408.7	408.1



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.5	457.5	458.0	458.5	459.0	459.5	459.7	459.6	459.5	459.4	459.3
115°	533.3	533.5	534.1	534.6	535.2	535.7	536.0	536.0	536.0	536.0	536.0
117.5°	606.6	607.6	607.9	608.3	608.7	609.1	609.2	608.9	608.7	608.5	608.3
120°	656.3	657.7	658.5	659.3	660.1	661.0	660.8	659.7	658.7	657.5	656.5
122.5°	706.0	706.9	707.3	707.6	708.0	708.4	708.3	707.9	707.5	707.0	706.6
125°	778.9	779.4	779.7	779.9	780.2	780.5	780.6	780.6	780.6	780.6	780.6
127.5°	848.9	849.5	849.9	850.4	850.8	851.3	851.0	850.2	849.4	848.6	847.7
130°	898.1	898.6	898.6	898.6	898.6	898.6	898.2	897.4	896.6	895.8	895.0
132.5°	944.4	944.9	945.1	945.3	945.5	945.7	945.6	944.9	944.4	943.8	943.1
135°	1013.7	1014.2	1014.2	1014.2	1014.2	1014.2	1013.4	1011.8	1010.1	1008.4	1006.8
137.5°	1080.8	1081.6	1081.2	1080.7	1080.3	1079.9	1079.2	1078.5	1077.7	1076.9	1076.2
140°	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.1	1123.5	1122.9	1122.4
142.5°	1166.1	1166.1	1166.4	1166.6	1166.8	1167.0	1166.9	1166.3	1165.8	1165.2	1164.7
145°	1229.1	1229.3	1229.1	1228.8	1228.5	1228.2	1227.6	1226.5	1225.4	1224.3	1223.2
147.5°	1285.9	1286.1	1286.4	1286.5	1286.8	1287.0	1286.5	1285.2	1283.9	1282.5	1281.2
150°	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.0	1319.9	1318.8	1317.7	1316.6
152.5°	1354.6	1354.0	1353.8	1353.6	1353.3	1353.2	1352.7	1352.0	1351.4	1350.7	1350.1
155°	1401.3	1400.2	1400.5	1400.8	1401.0	1401.3	1401.4	1401.4	1401.4	1401.4	1401.4
157.5°	1443.1	1442.3	1442.3	1442.3	1442.4	1442.5	1442.8	1443.2	1443.7	1444.2	1444.7
160°	1468.7	1467.9	1468.1	1468.4	1468.7	1468.9	1469.2	1469.5	1469.7	1470.0	1470.3
162.5°	1490.9	1489.5	1489.7	1490.0	1490.3	1490.5	1491.0	1491.8	1492.5	1493.2	1493.9
165°	1521.1	1519.5	1520.0	1520.5	1521.1	1521.7	1522.3	1523.1	1524.0	1524.8	1525.6
167.5°	1546.7	1545.1	1545.0	1544.9	1544.9	1544.8	1545.4	1546.5	1547.7	1548.8	1550.0
170°	1560.4	1558.8	1558.5	1558.3	1558.0	1557.7	1558.3	1559.6	1561.0	1562.4	1563.7
172.5°	1570.5	1568.6	1568.6	1568.6	1568.5	1568.4	1569.0	1570.1	1571.2	1572.4	1573.5
175°	1581.6	1579.7	1580.0	1580.2	1580.5	1580.8	1581.6	1583.0	1584.4	1585.7	1587.1
177.5°	1588.1	1586.6	1586.6	1586.6	1586.6	1586.6	1587.1	1588.2	1589.3	1590.4	1591.5
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1407.5	1411.5	1416.0	1424.6	1431.8	1435.0	1441.3	1445.8	1444.5	1450.7	1461.6
5°	1413.0	1428.2	1445.7	1463.7	1484.0	1500.9	1514.4	1528.0	1538.7	1551.7	1570.8
7.5°	1412.1	1439.2	1468.6	1500.9	1534.1	1562.9	1589.5	1616.6	1640.5	1666.9	1701.2
10°	1408.5	1444.5	1481.2	1523.5	1565.7	1605.7	1641.8	1675.6	1707.8	1742.1	1785.6
12.5°	1404.4	1445.9	1490.2	1541.1	1593.7	1641.8	1684.2	1732.9	1773.1	1817.5	1867.6
15°	1386.5	1442.3	1502.6	1568.6	1631.7	1696.5	1754.5	1814.3	1870.1	1923.0	1986.2
17.5°	1366.0	1430.4	1501.5	1579.4	1655.2	1734.1	1802.9	1878.2	1935.3	2006.4	2065.0
20°	1349.3	1418.6	1494.7	1582.1	1668.3	1755.7	1831.7	1908.5	1972.7	2044.3	2118.6
22.5°	1329.0	1405.1	1487.5	1578.0	1668.3	1763.8	1848.0	1924.2	2003.8	2084.4	2161.0
25°	1296.3	1375.2	1462.6	1561.8	1665.5	1763.0	1853.2	1947.8	2033.5	2120.9	2189.6
27.5°	1256.2	1339.0	1431.2	1533.5	1639.9	1739.8	1846.0	1946.9	2033.1	2117.2	2177.2
30°	1224.2	1311.6	1400.0	1503.7	1614.2	1721.3	1835.2	1936.0	2026.8	2102.3	2136.1
32.5°	1191.2	1274.1	1365.3	1470.4	1583.6	1698.8	1811.7	1914.8	1998.8	2044.1	2045.0
35°	1134.0	1211.8	1306.4	1409.7	1525.8	1650.8	1765.3	1866.7	1918.0	1921.9	1866.7
37.5°	1071.5	1142.9	1232.3	1335.5	1462.7	1587.1	1704.1	1771.6	1788.8	1731.5	1629.3
40°	1027.0	1092.8	1179.1	1285.1	1411.3	1539.8	1646.3	1695.9	1677.9	1584.9	1471.0
42.5°	980.0	1041.5	1124.5	1229.1	1355.8	1485.7	1576.5	1603.0	1555.3	1447.8	1314.6
45°	903.5	959.9	1042.1	1147.5	1269.3	1391.0	1459.8	1446.3	1366.8	1239.4	1090.1
47.5°	823.8	878.2	952.3	1049.8	1174.4	1279.5	1326.1	1285.3	1172.2	1032.1	910.6
50°	771.0	826.8	895.0	988.1	1101.9	1203.3	1233.2	1171.2	1045.5	910.8	799.2
52.5°	719.2	766.9	833.7	923.6	1032.4	1118.1	1134.0	1062.5	932.8	812.0	713.1
55°	640.3	683.7	740.0	824.6	918.7	991.4	982.9	891.1	773.3	670.2	592.4
57.5°	563.9	596.6	648.7	728.0	810.6	859.4	828.5	750.2	640.4	556.0	490.3
60°	513.5	543.9	592.4	661.7	734.4	762.0	736.1	651.0	564.2	487.0	431.7
62.5°	465.7	492.5	534.2	598.6	657.3	673.6	645.9	571.6	493.4	427.5	381.7
65°	396.2	421.0	456.6	502.2	542.7	550.7	532.6	456.6	397.4	342.1	310.5
67.5°	333.2	349.4	377.2	416.6	438.1	442.8	408.0	360.1	307.9	274.0	250.2
70°	290.8	302.1	328.0	349.4	366.9	367.5	335.3	297.0	257.0	229.4	211.9
72.5°	249.8	260.7	280.2	294.9	308.3	303.9	274.5	244.3	211.9	191.1	178.1
75°	192.7	202.4	212.5	219.2	219.2	213.6	192.2	169.7	151.1	138.7	134.7
77.5°	140.1	148.0	151.4	150.3	148.4	139.6	126.0	111.3	104.6	98.7	95.8
80°	109.9	113.3	114.4	111.6	108.2	98.1	89.0	82.8	76.6	74.4	73.3
82.5°	81.5	84.5	81.5	82.3	74.8	66.5	61.6	59.4	56.8	55.9	54.8
85°	43.4	42.8	41.7	38.9	33.8	32.7	32.1	31.6	30.4	31.0	29.8
87.5°	16.2	15.5	14.3	14.4	14.9	14.4	15.3	15.8	16.2	16.1	17.4
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7	50.6
95°	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2	95.1
97.5°	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7	149.8
100°	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7	189.1
102.5°	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2	230.9
105°	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4	294.2
107.5°	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9	362.7
110°	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8	408.3



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5	457.3
115°	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3	533.0
117.5°	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6	605.7
120°	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3	654.9
122.5°	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0	705.0
125°	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9	778.3
127.5°	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9	848.4
130°	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1	897.6
132.5°	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4	943.8
135°	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7	1013.1
137.5°	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8	1080.2
140°	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.3
142.5°	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1	1166.0
145°	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1	1228.8
147.5°	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9	1285.7
150°	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6	1355.3
155°	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3	1402.4
157.5°	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1	1443.9
160°	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7	1469.5
162.5°	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9	1492.4
165°	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1	1522.7
167.5°	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7	1548.3
170°	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4	1562.1
172.5°	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5	1572.4
175°	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6	1583.6
177.5°	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1	1589.7
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1467.5	1469.3	1470.6	1475.1	1475.5	1479.6	1475.5
5°	1588.9	1596.8	1609.2	1621.5	1622.7	1630.5	1616.5
7.5°	1725.0	1743.3	1754.7	1774.7	1782.7	1787.5	1779.5
10°	1818.8	1835.7	1865.6	1880.2	1894.9	1897.1	1890.4
12.5°	1909.4	1936.3	1959.8	1987.5	1986.9	2006.7	1999.5
15°	2030.2	2057.8	2090.4	2121.5	2132.7	2132.7	2141.8
17.5°	2116.3	2166.9	2200.7	2225.0	2251.7	2256.3	2253.2
20°	2174.5	2229.1	2265.2	2296.8	2314.8	2319.9	2319.9
22.5°	2217.7	2264.2	2299.5	2327.8	2342.8	2348.7	2346.9
25°	2247.7	2287.7	2309.2	2317.6	2321.6	2320.4	2309.7
27.5°	2206.7	2204.9	2191.4	2165.4	2145.9	2134.1	2120.6
30°	2128.3	2098.9	2065.1	2027.9	1980.0	1943.3	1932.1
32.5°	2011.4	1945.6	1888.3	1826.4	1774.8	1738.2	1722.9
35°	1785.6	1681.3	1596.2	1521.8	1467.7	1433.9	1422.6
37.5°	1517.5	1416.6	1311.2	1239.1	1194.2	1160.0	1147.3
40°	1347.0	1237.1	1145.3	1077.7	1031.4	998.2	997.6
42.5°	1191.5	1086.5	1000.1	951.4	901.6	879.5	879.5
45°	975.6	891.6	818.4	780.1	750.2	732.1	727.1
47.5°	807.8	738.3	689.5	659.0	634.6	623.1	615.7
50°	713.5	652.6	613.8	587.3	573.7	559.1	558.0
52.5°	635.1	586.0	555.6	534.1	517.0	508.2	508.4
55°	533.8	494.9	473.4	457.1	443.6	436.8	434.0
57.5°	449.6	420.4	404.9	389.9	384.2	378.9	377.4
60°	397.4	377.6	363.0	351.1	342.7	341.0	340.4
62.5°	354.1	333.5	323.3	314.1	307.9	305.3	304.4
65°	292.0	276.7	267.7	260.4	258.1	254.2	253.6
67.5°	235.4	226.2	220.3	215.2	212.1	211.9	211.9
70°	200.6	195.6	190.5	187.7	186.0	184.8	184.8
72.5°	170.9	167.1	163.0	161.5	161.2	160.0	159.6
75°	130.2	126.3	126.8	124.0	121.7	119.0	117.2
77.5°	92.3	89.5	88.9	88.6	86.7	86.3	87.2
80°	71.6	68.7	68.2	68.7	68.2	66.5	66.5
82.5°	54.5	52.1	51.5	51.2	50.6	51.2	50.3
85°	29.3	28.2	28.2	28.2	29.3	28.8	28.2
87.5°	16.8	16.6	17.3	17.0	17.0	16.7	17.3
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P333092-930

CATALOG NUMBER: S124RDIW-S1020D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)