

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332852-840

Luminaire Tested: **S124DIW-S1195D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332852-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1050U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8838.2 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41
3	83	73	66	60	77	68	62	57	60	55	50	52	48	44	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.1
10°-20°	534.0	6.0
20°-30°	786.0	8.9
30°-40°	913.7	10.3
40°-50°	913.7	10.3
50°-60°	799.3	9.0
60°-70°	593.6	6.7
70°-80°	337.2	3.8
80°-90°	101.3	1.1
90°-100°	87.2	1.0
100°-110°	258.4	2.9
110°-120°	438.7	5.0
120°-130°	578.4	6.5
130°-140°	649.6	7.4
140°-150°	638.4	7.2
150°-160°	536.9	6.1
160°-170°	357.2	4.0
170°-180°	125.1	1.4
0°-30°	1509.5	17.1
0°-40°	2423.2	27.4
0°-60°	4136.2	46.8
0°-90°	5168.3	58.5
90°-120°	784.3	8.9
90°-150°	2650.7	30.0
90°-180°	3670.0	41.5
0°-180°	8838.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	3	14	22	28	31	8
95°	61	70	78	81	81	68
105°	238	240	244	247	250	253
115°	446	446	444	443	442	440
125°	650	650	649	647	644	579
135°	838	844	844	842	839	648
145°	1018	1022	1023	1022	1019	637
155°	1166	1166	1165	1169	1165	536
165°	1270	1267	1264	1270	1266	358
175°	1321	1316	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.1	34.3	34.5	34.8	35.0	35.1	35.2	35.3	35.3	35.4	35.7
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	21.9	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3
95°	61.4	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5
97.5°	107.2	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8
100°	143.2	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9
102.5°	180.9	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6
105°	238.3	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2
107.5°	298.7	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2
110°	339.6	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.2	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7
115°	446.1	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7
117.5°	506.2	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8
120°	546.3	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2
122.5°	588.0	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4
125°	649.6	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1
127.5°	705.5	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5
130°	744.8	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4
132.5°	784.9	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9
135°	837.9	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5
137.5°	895.5	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5
140°	934.0	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8
142.5°	969.3	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4
145°	1017.9	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1066.2	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2
150°	1095.7	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1123.5	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3
155°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2
157.5°	1202.2	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9
160°	1223.6	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1
162.5°	1243.1	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7
165°	1269.6	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9
167.5°	1289.8	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1
170°	1301.3	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6
172.5°	1309.5	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0
175°	1320.7	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2
177.5°	1324.4	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	36.1	36.3	36.6	36.8	36.9	37.0	37.0	37.1
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.1	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.1	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	124.6	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.4	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.2	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	244.9	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	301.8	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.7	339.3	338.8	339.0	339.6	340.3	341.0	341.7



TEST NUMBER: P332852-840

CATALOG NUMBER: S124DIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.6	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.5	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	504.0	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	545.0	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	586.7	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.7	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	706.0	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.9	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.4	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	843.1	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.9	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.6	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.4	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.6	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1070.0	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1127.8	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1201.6	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1222.8	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1241.9	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1267.2	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1288.5	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1299.9	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1308.5	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1322.9	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)