

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333081-930

Luminaire Tested: **S124RDIW-S1020D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333081-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5906.6 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333081-930
CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58																			
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49																			
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42																			
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36																			
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31																			
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27																			
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24																			
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21																			
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19																			
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17																			
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.3
10°-20°	385.6	6.5
20°-30°	556.9	9.4
30°-40°	631.2	10.7
40°-50°	609.5	10.3
50°-60°	506.9	8.6
60°-70°	350.0	5.9
70°-80°	177.4	3.0
80°-90°	47.8	0.8
90°-100°	27.7	0.5
100°-110°	176.5	3.0
110°-120°	337.5	5.7
120°-130°	428.5	7.3
130°-140°	458.5	7.8
140°-150°	428.7	7.3
150°-160°	345.7	5.9
160°-170°	223.0	3.8
170°-180°	76.9	1.3
0°-30°	1080.8	18.3
0°-40°	1712.0	29.0
0°-60°	2828.4	47.9
0°-90°	3403.6	57.6
90°-120°	541.7	9.2
90°-150°	1857.3	31.4
90°-180°	2503.0	42.4
0°-180°	5906.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	69
90°	2	8	13	17	18	4
95°	33	14	13	17	18	43
105°	182	186	189	193	172	191
115°	340	342	341	342	342	335
125°	478	480	479	481	482	427
135°	593	593	595	596	597	457
145°	684	686	686	686	688	427
155°	750	750	749	751	749	346
165°	791	788	788	792	787	223
175°	809	806	806	811	804	77
180°	809	809	809	809	809	



TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.1	19.8	18.5	17.2	15.9	15.2	15.2	15.2	15.2	15.3	15.2
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	7.7	7.7	7.8	7.8	7.9	8.6	9.6	10.7	11.7	12.8	13.6
95°	33.3	28.7	24.1	19.6	15.0	12.8	12.9	13.0	13.2	13.3	14.1
97.5°	70.7	73.5	76.4	79.2	82.1	76.0	61.0	46.0	31.0	16.0	16.1
100°	99.2	101.7	104.1	106.5	108.9	100.9	82.3	63.8	45.2	26.7	24.4
102.5°	131.2	133.0	134.8	136.6	138.3	137.9	135.6	133.1	130.7	128.3	103.6
105°	182.1	183.0	183.8	184.6	185.4	186.1	186.8	187.4	188.2	188.8	190.0
107.5°	229.5	229.9	230.3	230.7	231.1	231.8	232.7	233.6	234.5	235.4	236.0
110°	261.5	261.9	262.3	262.7	263.0	263.7	264.5	265.3	266.1	266.8	267.2



TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.4	293.2	293.9	294.6	295.3	295.9	296.3	296.6	297.0	297.4	297.3
115°	340.1	340.6	341.0	341.3	341.7	341.9	341.7	341.6	341.4	341.3	341.6
117.5°	383.1	383.6	384.2	384.7	385.2	385.6	386.0	386.2	386.5	386.9	386.8
120°	412.1	412.7	413.2	413.8	414.3	414.5	414.3	414.3	414.1	413.9	414.3
122.5°	439.3	439.5	439.9	440.2	440.5	440.8	441.0	441.2	441.3	441.6	441.7
125°	478.1	478.7	479.2	479.7	480.2	480.4	480.1	479.9	479.6	479.3	479.7
127.5°	514.9	515.0	515.2	515.3	515.4	515.8	516.4	517.1	517.6	518.3	518.2
130°	538.6	538.7	538.9	539.0	539.2	539.4	539.8	540.2	540.6	541.0	541.2
132.5°	560.4	560.7	560.9	561.1	561.3	561.7	562.2	562.8	563.3	563.8	563.9
135°	593.0	593.0	592.8	592.6	592.6	592.7	593.3	593.8	594.4	594.9	595.2
137.5°	622.0	622.1	622.2	622.2	622.2	622.6	623.1	623.7	624.4	624.9	625.2
140°	640.9	641.2	641.4	641.7	642.0	642.2	642.5	642.8	643.0	643.4	643.7
142.5°	657.9	658.4	658.8	659.3	659.7	660.1	660.2	660.4	660.6	660.7	661.0
145°	683.9	684.3	684.7	685.1	685.5	685.7	685.7	685.7	685.7	685.7	685.8
147.5°	704.6	705.3	706.0	706.8	707.6	707.8	707.8	707.6	707.4	707.4	707.4
150°	719.6	720.1	720.6	721.2	721.7	721.9	721.8	721.6	721.5	721.4	721.4
152.5°	732.1	732.5	733.0	733.4	733.9	733.9	733.7	733.5	733.3	733.0	733.2
155°	749.8	750.0	750.1	750.2	750.4	750.2	749.8	749.4	749.0	748.6	749.2
157.5°	764.8	764.7	764.6	764.5	764.4	764.1	763.7	763.2	762.7	762.3	763.0
160°	773.4	773.0	772.7	772.3	771.8	771.5	771.4	771.3	771.1	771.0	771.8
162.5°	781.1	780.6	780.2	779.7	779.1	778.8	778.7	778.5	778.4	778.3	779.1
165°	791.0	790.3	789.6	789.0	788.3	788.0	788.0	788.0	788.0	788.0	789.0
167.5°	798.7	798.0	797.4	796.6	795.9	795.6	795.5	795.4	795.3	795.2	796.4
170°	803.1	802.3	801.4	800.6	799.9	799.5	799.6	799.8	799.9	800.1	801.1
172.5°	806.0	805.2	804.4	803.6	802.7	802.4	802.6	802.7	802.8	803.0	804.0
175°	809.1	808.3	807.6	806.7	805.9	805.6	805.7	805.8	806.0	806.1	807.3
177.5°	810.6	809.8	809.1	808.3	807.6	807.3	807.6	807.7	808.0	808.1	809.0
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1



TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	15.2	15.2	15.2	15.2	15.5	15.7	16.0	16.2
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	14.4	15.2	16.1	16.5	16.6	16.6	16.6	16.7
95°	14.9	15.7	16.6	17.0	17.1	17.3	17.4	17.5
97.5°	16.1	16.2	16.3	16.4	16.6	16.7	16.8	17.0
100°	22.1	19.7	17.4	16.4	16.6	16.7	16.8	17.0
102.5°	79.0	54.3	29.7	17.3	17.4	17.4	17.4	17.4
105°	191.3	192.4	193.6	191.8	187.0	182.1	177.3	172.5
107.5°	236.6	237.2	237.8	238.3	238.9	239.4	239.9	240.4
110°	267.4	267.7	268.0	268.3	268.7	269.1	269.5	269.9



TEST NUMBER: P333081-930

CATALOG NUMBER: S124RDIW-S1020D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.3	297.3	297.2	297.4	297.9	298.4	299.0	299.5
115°	341.9	342.1	342.4	342.5	342.5	342.5	342.5	342.5
117.5°	386.7	386.7	386.6	386.5	386.5	386.5	386.4	386.4
120°	414.5	414.7	415.0	415.0	414.7	414.5	414.3	413.9
122.5°	441.9	442.1	442.2	442.1	441.9	441.6	441.3	441.1
125°	480.1	480.5	480.9	481.2	481.4	481.4	481.6	481.8
127.5°	518.1	518.0	518.0	517.9	517.8	517.6	517.6	517.5
130°	541.3	541.4	541.6	541.6	541.6	541.6	541.6	541.6
132.5°	564.0	564.2	564.4	564.4	564.3	564.1	564.0	563.9
135°	595.4	595.7	596.0	596.2	596.5	596.8	597.0	597.3
137.5°	625.5	625.8	626.1	626.2	626.1	626.1	626.0	625.9
140°	644.1	644.5	644.9	645.2	645.3	645.5	645.6	645.7
142.5°	661.4	661.6	661.9	662.1	662.1	662.1	662.2	662.2
145°	685.9	686.1	686.2	686.4	686.6	687.0	687.2	687.5
147.5°	707.5	707.7	707.8	707.9	708.0	708.2	708.3	708.4
150°	721.4	721.4	721.4	721.5	721.6	721.7	721.9	721.9
152.5°	733.4	733.6	733.9	733.9	733.9	733.8	733.7	733.6
155°	749.7	750.2	750.7	750.8	750.4	750.0	749.6	749.3
157.5°	763.7	764.4	765.1	765.1	764.4	763.7	763.0	762.3
160°	772.7	773.4	774.2	774.2	773.4	772.7	771.8	771.0
162.5°	779.9	780.6	781.5	781.5	780.6	779.6	778.7	777.8
165°	790.1	791.2	792.2	792.2	791.0	789.8	788.6	787.3
167.5°	797.6	798.7	800.0	799.9	798.5	797.2	795.8	794.5
170°	802.2	803.3	804.4	804.2	802.9	801.5	800.2	798.8
172.5°	805.1	806.2	807.2	807.1	805.6	804.2	802.7	801.3
175°	808.5	809.8	811.0	810.7	809.1	807.6	805.9	804.3
177.5°	809.9	810.7	811.6	811.4	810.1	808.8	807.6	806.2
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1

(END OF REPORT)