

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332857-840

Luminaire Tested: **S124DIW-S1195D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332857-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10586.6 lumens  
Efficiency: N/A  
Efficacy: 138.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49																				
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41																				
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34																				
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29																				
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25																				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22																				
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19																				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17																				
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15																				
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16	14																				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	1.8
10°-20°	534.0	5.0
20°-30°	786.0	7.4
30°-40°	913.7	8.6
40°-50°	913.7	8.6
50°-60°	799.3	7.5
60°-70°	593.6	5.6
70°-80°	337.2	3.2
80°-90°	102.4	1.0
90°-100°	59.9	0.6
100°-110°	381.9	3.6
110°-120°	730.6	6.9
120°-130°	927.4	8.8
130°-140°	992.3	9.4
140°-150°	927.9	8.8
150°-160°	748.3	7.1
160°-170°	482.6	4.6
170°-180°	166.3	1.6
0°-30°	1509.5	14.3
0°-40°	2423.2	22.9
0°-60°	4136.2	39.1
0°-90°	5169.4	48.8
90°-120°	1172.4	11.1
90°-150°	4020.0	38.0
90°-180°	5417.0	51.2
0°-180°	10586.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	4	18	29	36	39	8
95°	72	30	29	36	38	93
105°	394	402	409	417	373	413
115°	736	740	739	741	741	724
125°	1035	1040	1037	1041	1043	924
135°	1284	1283	1288	1290	1293	989
145°	1480	1484	1484	1485	1488	925
155°	1623	1624	1620	1625	1622	748
165°	1712	1706	1706	1715	1704	484
175°	1751	1744	1745	1755	1741	167
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.3	34.6	35.0	35.3	35.7	36.1	36.2	36.4	36.6	36.8	37.1
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	16.5	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5
95°	72.0	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6
97.5°	153.0	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7
100°	214.8	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7
102.5°	284.0	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3
105°	394.3	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3
107.5°	496.7	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8
110°	565.8	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2



TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	632.9	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6
115°	736.1	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3
117.5°	829.1	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2
120°	892.0	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6
122.5°	950.7	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0
125°	1034.8	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2
127.5°	1114.4	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6
130°	1165.8	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3
132.5°	1212.9	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5
135°	1283.6	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2
137.5°	1346.3	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2
140°	1387.2	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2
142.5°	1423.8	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8
145°	1480.2	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4
147.5°	1524.9	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2
150°	1557.4	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4
152.5°	1584.7	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0
155°	1623.0	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4
157.5°	1655.2	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4
160°	1674.0	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5
162.5°	1690.7	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2
165°	1712.0	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8
167.5°	1728.8	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7
170°	1738.2	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9
172.5°	1744.4	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2
175°	1751.3	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4
177.5°	1754.4	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	37.5	37.8	38.1	38.4	38.5	38.6	38.7	38.8
90°	32.3	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	31.3	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	32.3	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	34.9	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	47.8	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	171.0	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	413.9	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	512.1	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	578.9	579.4	580.0	580.7	581.6	582.5	583.3	584.2





TEST NUMBER: P332857-840

CATALOG NUMBER: S124DIW-S1195D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.4	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	739.9	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	837.0	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.3	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1039.2	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.5	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.5	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1220.8	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1288.8	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1353.8	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1394.1	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1431.4	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.6	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.5	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.4	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1622.7	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1688.0	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1710.1	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1726.3	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1736.3	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1742.5	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1750.0	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1752.9	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)