

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333110-930

Luminaire Tested: **S124RDIW-S1195D1340U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333110-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7725.4 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69		62	60	59		51	50	49	43
2	90	82	76	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49		49	45	42		40	38	35	31
4	75	64	57	51	69	60	53	48	51	46	42		43	39	36		36	33	31	27
5	69	58	50	44	64	54	46	41	46	41	36		39	35	32		33	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		30	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28		32	28	25		27	24	21	19
8	55	43	35	30	51	40	33	28	34	29	25		30	25	22		25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22		27	23	20		23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20		25	21	18		21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.1
10°-20°	445.4	5.8
20°-30°	643.1	8.3
30°-40°	729.0	9.4
40°-50°	704.0	9.1
50°-60°	585.4	7.6
60°-70°	404.2	5.2
70°-80°	204.9	2.7
80°-90°	56.6	0.7
90°-100°	90.2	1.2
100°-110°	267.1	3.5
110°-120°	453.4	5.9
120°-130°	597.8	7.7
130°-140°	671.4	8.7
140°-150°	659.8	8.5
150°-160°	554.9	7.2
160°-170°	369.2	4.8
170°-180°	129.3	1.7
0°-30°	1248.2	16.2
0°-40°	1977.3	25.6
0°-60°	3266.6	42.3
0°-90°	3932.4	50.9
90°-120°	810.7	10.5
90°-150°	2739.7	35.5
90°-180°	3793.0	49.1
0°-180°	7725.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	3	15	23	29	32	7
95°	63	73	80	83	84	71
105°	246	248	252	255	258	261
115°	461	461	459	458	457	454
125°	671	671	670	668	666	598
135°	866	872	872	870	867	670
145°	1052	1056	1057	1056	1053	658
155°	1205	1205	1204	1208	1204	554
165°	1312	1309	1307	1313	1309	370
175°	1365	1360	1359	1365	1359	130
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.6	23.2	21.9	20.5	19.2	18.7	18.8	18.9	19.1	19.2	19.3
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	22.7	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7
95°	63.4	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0
97.5°	110.8	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9
100°	148.1	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2
102.5°	186.9	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0
105°	246.4	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3
107.5°	308.8	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3
110°	351.1	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.0	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5
115°	461.0	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7
117.5°	523.2	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7
120°	564.6	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5
122.5°	607.7	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2
125°	671.4	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8
127.5°	729.1	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2
130°	769.7	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4
132.5°	811.2	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2
135°	865.9	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9
137.5°	925.6	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6
140°	965.4	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3
142.5°	1001.8	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0
145°	1052.1	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1102.0	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0
150°	1132.5	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.1	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3
157.5°	1242.6	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2
160°	1264.6	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1
162.5°	1284.9	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4
165°	1312.1	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3
167.5°	1333.1	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3
170°	1344.9	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1
172.5°	1353.4	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8
175°	1365.1	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3
177.5°	1368.8	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	19.3	19.4	19.4	19.6	20.0	20.3	20.6	21.0
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	43.5	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	81.8	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	128.8	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	162.7	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	198.6	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.1	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	311.9	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	351.1	350.7	350.3	350.3	351.1	351.7	352.5	353.2



TEST NUMBER: P333110-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	393.4	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.4	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	521.0	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	563.4	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	606.3	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.4	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.7	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	772.0	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.7	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	871.4	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	929.0	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	967.0	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.9	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.8	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1165.7	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1241.9	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1263.9	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1283.6	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1309.7	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1331.7	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1343.5	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1352.3	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1367.3	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)