

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863-840

Luminaire Tested: **S124DIW-S1195D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11468.6 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	1.7
10°-20°	534.0	4.7
20°-30°	786.0	6.9
30°-40°	913.7	8.0
40°-50°	913.7	8.0
50°-60°	799.3	7.0
60°-70°	593.6	5.2
70°-80°	337.2	2.9
80°-90°	103.2	0.9
90°-100°	69.6	0.6
100°-110°	444.0	3.9
110°-120°	849.4	7.4
120°-130°	1078.3	9.4
130°-140°	1153.7	10.1
140°-150°	1078.8	9.4
150°-160°	870.0	7.6
160°-170°	561.1	4.9
170°-180°	193.4	1.7
0°-30°	1509.5	13.2
0°-40°	2423.2	21.1
0°-60°	4136.2	36.1
0°-90°	5170.2	45.1
90°-120°	1363.1	11.9
90°-150°	4673.9	40.8
90°-180°	6298.0	54.9
0°-180°	11468.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	4	21	34	42	46	9
95°	84	35	34	42	44	108
105°	458	468	475	485	434	480
115°	856	860	859	862	862	842
125°	1203	1209	1206	1211	1212	1074
135°	1492	1491	1497	1500	1503	1149
145°	1721	1725	1726	1727	1730	1075
155°	1887	1888	1884	1889	1885	870
165°	1990	1983	1983	1994	1981	562
175°	2036	2028	2028	2040	2024	194
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.4	34.9	35.3	35.9	36.3	36.7	36.9	37.2	37.4	37.7	38.1
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	19.2	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3
95°	83.7	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5
97.5°	177.8	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4
100°	249.7	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3
102.5°	330.1	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7
105°	458.4	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2
107.5°	577.4	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9
110°	657.9	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	735.9	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2
115°	855.9	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6
117.5°	964.0	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3
120°	1037.1	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4
122.5°	1105.3	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6
125°	1203.2	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2
127.5°	1295.7	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0
130°	1355.4	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8
132.5°	1410.2	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1
135°	1492.5	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7
137.5°	1565.3	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3
140°	1612.8	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9
142.5°	1655.4	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4
145°	1720.9	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8
147.5°	1773.0	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3
150°	1810.8	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3
152.5°	1842.4	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1
155°	1886.9	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2
157.5°	1924.4	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1
160°	1946.3	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3
162.5°	1965.8	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5
165°	1990.4	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5
167.5°	2009.9	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1
170°	2020.9	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0
172.5°	2028.2	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3
175°	2036.1	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5
177.5°	2039.8	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	38.5	38.9	39.3	39.6	39.7	39.8	40.0	40.1
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	36.4	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	37.6	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.6	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	55.5	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	198.7	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	481.2	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	595.4	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.0	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P332863-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.1	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.3	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.2	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.0	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1208.2	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.8	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.2	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.5	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1498.3	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.1	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1620.9	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1664.3	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.2	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.5	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1845.6	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1886.5	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1962.6	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1988.2	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2007.1	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2018.7	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2026.0	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2034.6	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2038.0	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)