

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332864-840

Luminaire Tested: **S124DIW-S1195D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332864-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10632.7 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	1.8
10°-20°	534.0	5.0
20°-30°	786.0	7.4
30°-40°	913.7	8.6
40°-50°	913.7	8.6
50°-60°	799.3	7.5
60°-70°	593.6	5.6
70°-80°	337.2	3.2
80°-90°	103.2	1.0
90°-100°	129.9	1.2
100°-110°	384.7	3.6
110°-120°	652.9	6.1
120°-130°	861.0	8.1
130°-140°	966.9	9.1
140°-150°	950.1	8.9
150°-160°	799.1	7.5
160°-170°	531.7	5.0
170°-180°	186.2	1.8
0°-30°	1509.5	14.2
0°-40°	2423.2	22.8
0°-60°	4136.2	38.9
0°-90°	5170.2	48.6
90°-120°	1167.5	11.0
90°-150°	3945.5	37.1
90°-180°	5463.0	51.4
0°-180°	10632.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	4	21	34	42	46	10
95°	91	105	116	120	120	102
105°	355	357	362	367	372	376
115°	664	664	661	659	658	654
125°	967	967	965	962	959	861
135°	1247	1256	1256	1253	1249	964
145°	1515	1521	1523	1521	1517	948
155°	1736	1736	1734	1740	1734	798
165°	1890	1885	1882	1890	1885	532
175°	1966	1958	1957	1966	1957	187
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.4	34.9	35.3	35.9	36.3	36.7	36.9	37.2	37.4	37.7	38.1
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	32.6	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5
95°	91.4	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7
97.5°	159.6	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2
100°	213.2	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7
102.5°	269.2	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1
105°	354.8	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5
107.5°	444.6	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3
110°	505.5	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	568.9	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6
115°	663.9	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6
117.5°	753.5	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3
120°	813.1	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9
122.5°	875.3	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4
125°	966.9	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7
127.5°	1050.1	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5
130°	1108.5	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5
132.5°	1168.2	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7
135°	1247.1	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6
137.5°	1333.0	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8
140°	1390.3	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9
142.5°	1442.6	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4
145°	1515.1	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1587.0	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8
150°	1630.8	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1672.2	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9
155°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8
157.5°	1789.5	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5
160°	1821.2	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2
162.5°	1850.4	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7
165°	1889.7	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1
167.5°	1919.9	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8
170°	1936.9	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8
172.5°	1949.0	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3
175°	1965.8	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0
177.5°	1971.3	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	38.5	38.9	39.3	39.6	39.7	39.8	40.0	40.1
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	62.7	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	117.8	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	185.5	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	234.3	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	286.0	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	364.5	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	449.3	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.7	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P332864-840

CATALOG NUMBER: S124DIW-S1195D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	566.4	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	660.1	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	750.2	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	811.2	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	873.2	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	964.0	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.9	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.8	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1169.0	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.9	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1338.0	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.6	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.3	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1522.1	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.6	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1678.7	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1788.5	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1820.2	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1848.6	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1886.1	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1917.8	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1934.9	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1947.6	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1969.0	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)