

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333111-930

Luminaire Tested: **S124RDIW-S1195D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333111-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1560U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9173.6 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13043	13043	13043	13043
5°	15129	13083	11563	13083
10°	17898	13025	10320	13025
15°	20674	12904	8868	12904
20°	23018	12740	8019	12740
25°	23762	12577	7445	12577
30°	20801	12379	7100	12379
35°	16192	12086	6890	12086
40°	12142	11751	6777	11751
45°	9587	11215	6719	11215
50°	8093	10595	6523	10595
55°	7054	9913	6175	9913
60°	6347	9206	5465	9206
65°	5595	8443	4701	8443
70°	5039	7652	4242	7652
75°	4223	6781	3615	6781
80°	3570	5779	3389	5779
85°	3010	4520	3010	4520



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.5	1.7
10°-20°	472.2	5.1
20°-30°	738.6	8.1
30°-40°	821.0	9.0
40°-50°	728.5	7.9
50°-60°	567.6	6.2
60°-70°	371.6	4.1
70°-80°	182.8	2.0
80°-90°	49.8	0.5
90°-100°	56.2	0.6
100°-110°	358.5	3.9
110°-120°	685.8	7.5
120°-130°	870.5	9.5
130°-140°	931.4	10.2
140°-150°	871.0	9.5
150°-160°	702.4	7.7
160°-170°	453.0	4.9
170°-180°	156.1	1.7
0°-30°	1367.3	14.9
0°-40°	2188.4	23.9
0°-60°	3484.5	38.0
0°-90°	4088.7	44.6
90°-120°	1100.5	12.0
90°-150°	3773.4	41.1
90°-180°	5085.0	55.4
0°-180°	9173.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1867	1614	1427	1614	1867	189
15°	2474	1544	1061	1544	2474	703
25°	2668	1412	836	1412	2668	1183
35°	1643	1226	699	1226	1643	1030
45°	840	982	588	982	840	665
55°	501	704	439	704	501	456
65°	293	442	246	442	293	295
75°	135	217	116	217	135	149
85°	32	49	32	49	32	38
90°	37	4	37	4	37	17
95°	36	68	36	68	36	28
105°	350	370	350	370	350	306
115°	696	691	696	691	696	689
125°	979	971	979	971	979	872
135°	1214	1205	1214	1205	1214	934
145°	1397	1389	1397	1389	1397	873
155°	1522	1523	1522	1523	1522	702
165°	1600	1607	1600	1607	1600	452
175°	1634	1644	1634	1644	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1704.1	1708.9	1704.1	1703.6	1698.4	1696.9	1694.8	1688.0	1675.5	1668.3	1669.8
5°	1866.9	1883.2	1874.0	1872.7	1858.5	1844.1	1835.0	1814.2	1792.0	1777.1	1764.7
7.5°	2055.1	2064.5	2058.8	2049.7	2026.5	2013.4	1992.3	1964.8	1925.1	1894.8	1867.0
10°	2183.3	2191.0	2188.5	2171.5	2154.6	2120.1	2100.6	2062.2	2012.1	1972.4	1935.3
12.5°	2309.3	2317.7	2294.7	2295.5	2263.4	2236.3	2205.3	2157.0	2099.1	2047.9	2001.4
15°	2473.6	2463.2	2463.2	2450.1	2414.3	2376.6	2344.7	2293.9	2221.0	2159.8	2095.4
17.5°	2602.2	2605.9	2600.5	2569.8	2541.7	2502.6	2444.2	2384.9	2317.2	2235.1	2169.2
20°	2679.3	2679.3	2673.4	2652.6	2616.1	2574.5	2511.4	2446.9	2360.9	2278.3	2204.1
22.5°	2710.5	2712.6	2705.7	2688.5	2655.8	2615.1	2561.3	2495.9	2407.3	2314.2	2222.3
25°	2667.6	2680.0	2681.2	2676.7	2666.9	2642.1	2596.0	2528.9	2449.5	2348.6	2249.7
27.5°	2449.1	2464.7	2478.4	2500.9	2530.9	2546.5	2548.5	2514.5	2445.2	2348.1	2248.5
30°	2231.4	2244.4	2286.8	2342.1	2385.1	2424.1	2458.0	2467.1	2428.0	2340.8	2236.0
32.5°	1989.8	2007.5	2049.8	2109.3	2180.9	2247.0	2323.1	2361.8	2360.9	2308.5	2211.5
35°	1643.0	1656.0	1695.1	1757.5	1843.5	1941.8	2062.2	2155.9	2219.7	2215.2	2155.9
37.5°	1325.0	1339.8	1379.2	1431.0	1514.3	1636.1	1752.6	1881.7	1999.7	2066.0	2046.2
40°	1152.2	1152.8	1191.2	1244.6	1322.7	1428.8	1555.8	1698.9	1830.4	1937.9	1958.7
42.5°	1015.7	1015.9	1041.2	1098.8	1155.0	1254.9	1376.1	1518.3	1672.2	1796.2	1851.4
45°	839.7	845.5	866.4	900.9	945.2	1029.8	1126.7	1258.9	1431.4	1578.5	1670.3
47.5°	711.1	719.7	733.0	761.1	796.4	852.7	932.9	1051.7	1192.0	1353.8	1484.4
50°	644.4	645.7	662.7	678.2	708.9	753.8	824.1	923.0	1051.9	1207.5	1352.7
52.5°	587.2	586.9	597.0	616.9	641.7	676.7	733.4	823.5	937.8	1077.3	1227.2
55°	501.2	504.5	512.3	527.9	546.8	571.5	616.4	684.1	774.0	893.1	1029.2
57.5°	435.9	437.6	443.7	450.3	467.7	485.6	519.3	566.3	642.1	739.6	866.4
60°	393.1	393.8	395.7	405.5	419.2	436.1	458.9	498.6	562.4	651.6	751.9
62.5°	351.5	352.7	355.7	362.8	373.4	385.1	409.0	440.8	493.7	569.8	660.1
65°	292.9	293.6	298.2	300.8	309.2	319.6	337.2	358.7	395.1	458.9	527.3
67.5°	244.8	244.8	245.0	248.5	254.4	261.3	271.8	289.0	316.5	355.7	416.0
70°	213.5	213.5	214.8	216.8	220.0	225.8	231.7	244.8	265.0	296.9	343.1
72.5°	184.3	184.8	186.1	186.5	188.3	193.1	197.4	205.7	220.7	244.8	282.1
75°	135.4	137.4	140.6	143.2	146.4	145.8	150.3	155.6	160.1	174.5	195.9
77.5°	100.8	99.7	100.1	102.3	102.7	103.4	106.6	110.6	114.1	120.8	128.5
80°	76.8	76.8	78.8	79.4	78.8	79.4	82.7	84.6	85.9	88.5	95.7
82.5°	58.0	59.1	58.5	59.1	59.5	60.2	62.9	63.3	64.6	65.6	68.6
85°	32.5	33.2	33.8	32.5	32.5	32.5	33.8	34.5	35.8	35.1	36.4
87.5°	18.8	18.2	18.6	18.5	18.9	18.2	18.3	19.1	17.7	17.9	17.4
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4	27.7	26.1	23.9
95°	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3	28.7	27.1	26.7
97.5°	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8	32.6	32.4	62.9
100°	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8	49.5	54.1	91.8
102.5°	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5	210.5	260.7	265.5
105°	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5	386.0	383.6	382.2
107.5°	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7	479.5	478.3	476.4
110°	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3	542.7	542.2	540.5



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0	604.1	604.2	603.4
115°	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6	694.0	693.4	693.7
117.5°	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7	785.8	785.9	785.3
120°	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0	841.2
122.5°	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7	897.4	897.1	896.7
125°	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4	974.6	973.8	974.3
127.5°	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6	1052.8	1053.0	1051.7
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8	1099.4	1099.2	1098.4
132.5°	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0	1145.7	1145.4	1144.4
135°	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7	1209.2	1208.6	1207.5
137.5°	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8	1270.2	1269.6	1268.4
140°	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6	1307.8	1306.9	1306.4
142.5°	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6	1343.0	1342.4	1342.1
145°	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6	1393.3	1393.0	1393.0
147.5°	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5	1437.3	1437.0	1437.3
150°	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6	1465.6	1465.6	1465.8
152.5°	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0	1489.6	1489.1	1489.6
155°	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1	1522.0	1520.9	1521.8
157.5°	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7	1549.6
160°	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4	1566.7
162.5°	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5	1582.7	1581.1	1581.4
165°	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2	1603.0	1600.8	1600.8
167.5°	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4	1618.0	1615.6	1615.8
170°	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8	1627.6	1625.4	1625.1
172.5°	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7	1633.5	1631.3	1631.0
175°	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6	1640.1	1637.7	1637.4
177.5°	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4	1643.6	1641.8	1641.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1664.6	1657.3	1653.7	1645.4	1635.4	1630.2	1625.5	1618.8	1609.9	1600.5	1593.7
5°	1749.1	1733.5	1713.9	1690.5	1669.7	1649.5	1631.9	1614.4	1594.2	1573.4	1552.5
7.5°	1835.8	1805.1	1771.9	1733.5	1696.1	1662.2	1630.8	1600.9	1567.1	1536.8	1509.1
10°	1896.2	1854.6	1808.3	1759.5	1710.7	1668.3	1626.7	1588.9	1547.3	1510.2	1479.0
12.5°	1945.1	1896.2	1840.6	1779.8	1721.1	1669.9	1622.0	1572.8	1525.4	1485.2	1443.6
15°	2026.3	1959.3	1884.5	1811.6	1735.4	1665.7	1601.3	1544.0	1490.0	1433.4	1393.7
17.5°	2082.3	2002.7	1911.7	1824.1	1734.1	1652.0	1577.6	1509.4	1447.1	1389.3	1342.0
20°	2115.5	2027.6	1926.8	1827.2	1726.3	1638.4	1558.4	1482.9	1418.4	1355.9	1307.1
22.5°	2134.3	2037.0	1926.8	1822.5	1718.0	1622.8	1534.9	1456.3	1386.1	1323.6	1269.6
25°	2140.3	2036.1	1923.5	1803.8	1689.2	1588.3	1497.1	1411.9	1333.7	1271.3	1214.0
27.5°	2132.0	2009.3	1894.0	1771.1	1652.9	1546.5	1450.8	1361.2	1283.0	1215.9	1157.2
30°	2119.5	1987.9	1864.3	1736.8	1616.9	1514.7	1413.8	1328.0	1246.6	1176.9	1117.7
32.5°	2092.4	1961.9	1828.9	1698.2	1576.9	1471.5	1375.8	1289.4	1209.6	1138.4	1075.5
35°	2038.7	1906.6	1762.1	1628.0	1508.9	1399.5	1309.7	1226.4	1150.2	1074.1	1007.6
37.5°	1968.1	1833.0	1689.3	1542.5	1423.2	1320.0	1237.5	1159.4	1085.0	1015.5	941.9
40°	1901.4	1778.4	1629.9	1484.2	1361.8	1262.2	1186.0	1115.1	1040.2	971.2	897.6
42.5°	1820.7	1715.9	1565.9	1419.6	1298.8	1202.8	1131.9	1062.5	994.4	927.5	850.8
45°	1686.0	1606.5	1465.9	1325.4	1203.6	1108.6	1043.5	982.3	922.3	858.6	786.4
47.5°	1531.5	1477.7	1356.4	1212.4	1099.8	1014.3	951.5	901.4	850.8	787.0	723.6
50°	1424.2	1389.8	1272.6	1141.1	1033.7	955.0	890.5	843.6	801.3	740.1	683.5
52.5°	1309.7	1291.4	1192.4	1066.7	962.9	885.7	830.6	788.4	745.6	694.8	641.8
55°	1135.2	1145.0	1061.0	952.4	854.7	789.6	739.5	704.3	667.9	624.9	583.9
57.5°	956.9	992.5	936.2	840.7	749.3	689.1	651.3	621.7	591.2	555.5	520.5
60°	850.1	880.0	848.2	764.2	684.1	628.2	593.0	570.2	539.6	507.1	480.4
62.5°	746.0	778.0	759.1	691.3	616.9	568.8	537.8	516.6	493.8	465.5	437.7
65°	615.1	635.9	626.9	580.0	527.3	486.2	457.6	442.0	421.2	400.3	375.6
67.5°	471.2	511.4	506.1	481.2	435.6	403.6	384.8	371.0	352.0	336.6	319.8
70°	387.3	424.4	423.8	403.6	378.9	348.9	335.9	324.2	307.2	292.3	278.6
72.5°	317.0	351.0	356.0	340.6	323.7	301.0	288.5	280.5	264.0	253.7	242.6
75°	222.0	246.7	253.2	253.2	245.4	233.7	222.7	217.4	205.7	196.6	190.0
77.5°	145.5	161.2	171.3	173.7	174.9	171.0	161.8	158.2	149.2	145.9	139.7
80°	102.8	113.2	125.0	128.9	132.2	130.9	126.9	124.3	115.9	112.6	110.0
82.5°	71.1	76.8	86.4	95.1	94.1	97.5	94.1	92.0	85.7	84.5	81.9
85°	37.1	37.7	39.1	44.9	48.2	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	17.0	16.1	16.7	16.1	16.1	17.5	18.5	18.4	17.4	16.6	15.6
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5	15.7	15.8	16.0
95°	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6	58.3	49.1	39.8
97.5°	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6	149.4	155.2	161.0
100°	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6	206.6	211.5	216.4
102.5°	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5	270.2	273.8	277.4
105°	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1	371.7	373.3	375.0
107.5°	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2	467.1	467.9	468.7
110°	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2	532.0	532.8	533.6





TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1	595.6	597.0	598.5
115°	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0	691.8	692.6	693.4
117.5°	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3	779.3	780.5	781.5
120°	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3	838.4	839.5	840.6
122.5°	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3	893.0	893.6	894.3
125°	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3	972.4	973.5	974.6
127.5°	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0	1046.4	1046.6	1046.8
130°	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3	1094.5	1094.8	1095.1
132.5°	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5	1139.0	1139.5	1140.0
135°	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9	1204.6	1204.4	1204.1
137.5°	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7	1263.8	1263.9	1264.0
140°	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0	1302.6	1303.2	1303.7
142.5°	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5
145°	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4	1390.2	1391.0	1391.8
147.5°	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4	1432.9	1434.4	1436.0
150°	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9	1463.0	1464.0	1465.2
152.5°	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4	1488.3	1489.2	1490.0
155°	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4	1523.6	1523.9	1524.2
157.5°	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6	1553.5	1553.3	1553.1
160°	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3	1570.5	1569.7	1568.9
162.5°	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1	1586.0	1584.9	1584.0
165°	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0	1605.6	1604.3	1602.9
167.5°	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7	1621.3	1619.8	1618.5
170°	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6	1629.9	1628.2	1626.6
172.5°	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4	1635.8	1634.2	1632.6
175°	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8	1642.2	1640.5	1638.9
177.5°	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8	1645.3	1643.7	1642.2
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1586.5	1581.3	1574.5	1566.7	1557.3	1549.0	1545.3	1548.5	1550.0	1545.9	1545.3
5°	1538.1	1521.9	1508.9	1489.4	1473.7	1460.7	1451.6	1447.7	1449.0	1438.6	1436.0
7.5°	1483.9	1464.6	1443.2	1420.1	1398.5	1379.3	1369.3	1363.8	1352.8	1348.1	1340.2
10°	1449.0	1422.9	1402.2	1374.8	1350.1	1327.3	1316.2	1307.1	1296.0	1290.8	1279.8
12.5°	1413.1	1382.8	1359.9	1331.5	1306.3	1278.9	1268.3	1251.4	1234.0	1223.1	1208.9
15°	1362.4	1326.0	1298.0	1264.1	1234.2	1203.0	1174.9	1143.7	1132.0	1107.3	1092.9
17.5°	1303.2	1266.2	1231.6	1186.2	1140.0	1101.1	1071.3	1041.4	1023.4	1007.6	1000.4
20°	1264.1	1230.3	1182.1	1129.4	1078.0	1035.0	1010.9	991.4	971.8	960.8	953.0
22.5°	1227.2	1183.9	1128.0	1071.1	1019.6	986.0	965.6	945.6	929.7	919.2	908.7
25°	1165.2	1108.6	1049.3	984.2	949.1	919.8	897.6	881.3	871.6	857.9	852.7
27.5°	1101.6	1032.9	967.6	923.8	887.2	860.4	841.1	828.9	816.5	807.8	801.0
30°	1052.6	982.9	924.3	882.6	845.5	823.5	807.8	793.5	783.7	776.6	771.4
32.5°	1004.1	934.5	885.3	840.5	811.2	789.6	772.9	762.2	754.6	745.3	742.2
35°	934.1	872.3	829.3	789.0	759.0	739.5	726.4	715.4	708.9	706.3	704.3
37.5°	866.8	816.1	770.0	736.9	710.2	694.8	679.5	674.0	669.5	664.9	667.0
40°	824.1	776.6	735.6	700.4	678.9	662.0	652.9	646.4	642.5	642.5	642.5
42.5°	787.1	740.6	700.7	669.2	647.7	633.4	623.2	617.8	616.4	616.0	619.1
45°	729.7	686.7	646.4	620.4	602.1	587.8	582.0	577.4	577.4	580.0	580.7
47.5°	672.8	632.6	600.1	571.0	554.3	545.4	540.3	537.9	538.2	540.8	543.8
50°	637.9	598.2	566.3	540.3	524.6	516.2	511.6	510.4	511.6	511.6	516.2
52.5°	599.9	564.4	533.0	511.1	493.4	485.5	483.0	481.2	481.9	484.0	486.0
55°	544.2	512.3	482.3	461.5	448.5	443.3	437.4	438.1	436.8	438.1	438.1
57.5°	488.4	459.7	431.9	415.3	403.8	396.3	389.9	391.8	389.8	389.6	388.5
60°	452.4	421.2	399.0	384.1	371.0	364.5	358.7	360.0	358.0	356.7	354.1
62.5°	413.4	387.3	366.2	351.8	341.4	333.8	327.9	326.6	322.1	317.6	311.9
65°	356.7	335.3	316.3	302.7	292.9	287.1	282.5	278.6	268.8	258.4	253.2
67.5°	301.7	286.2	268.6	257.0	249.1	241.4	232.7	226.0	216.9	211.2	207.9
70°	266.2	251.3	236.3	225.2	216.8	209.6	199.8	195.3	188.7	186.1	183.0
72.5°	232.4	218.4	204.6	194.5	185.5	179.9	172.3	167.7	164.9	163.8	160.5
75°	181.0	169.9	159.5	150.3	143.2	139.3	136.1	132.8	131.5	125.6	122.4
77.5°	132.0	124.7	118.2	111.7	106.6	104.0	97.8	94.0	91.8	89.0	88.4
80°	102.8	97.7	91.2	87.2	80.1	77.5	74.8	74.2	73.5	72.9	72.2
82.5°	77.4	72.2	65.6	63.3	61.3	59.8	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.4	36.4	35.8	35.1	34.5	33.8	33.8	33.2	33.8	33.2
87.5°	16.1	16.1	16.6	16.0	17.0	17.4	17.2	17.5	18.3	17.7	17.9
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4	31.0	32.6	33.5
95°	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3	32.0	33.6	34.6
97.5°	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8	32.9	33.1	33.3
100°	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8	40.2	35.5	33.3
102.5°	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5	110.3	60.3	35.2
105°	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5	391.0	393.5	389.7
107.5°	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7	481.9	483.1	484.2
110°	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3	543.9	544.4	545.1



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0	603.8	603.7	604.2
115°	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6	695.0	695.6	695.9
117.5°	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7	785.5	785.5	785.4
120°	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0	842.6	843.2	843.2
122.5°	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7	898.1	898.4	898.2
125°	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4	976.2	977.1	977.6
127.5°	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6	1052.5	1052.3	1052.1
130°	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8	1100.0	1100.2	1100.4
132.5°	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0	1146.2	1146.5	1146.6
135°	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7	1210.2	1210.8	1211.4
137.5°	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8	1271.4	1272.0	1272.2
140°	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6	1309.5	1310.3	1310.8
142.5°	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6	1344.2	1344.8	1345.1
145°	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6	1393.8	1394.1	1394.6
147.5°	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5	1437.7	1437.9	1438.2
150°	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6	1465.6	1465.6	1465.7
152.5°	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0	1490.4	1490.9	1491.0
155°	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1	1524.2	1525.3	1525.4
157.5°	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4
160°	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0
162.5°	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5	1586.1	1587.7	1587.6
165°	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2	1607.4	1609.6	1609.4
167.5°	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4	1622.8	1625.2	1625.1
170°	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8	1632.0	1634.2	1633.9
172.5°	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7	1637.9	1640.1	1639.6
175°	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6	1645.1	1647.6	1647.1
177.5°	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4	1647.1	1648.9	1648.5
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1542.2	1543.3	1539.6	1538.6	1539.6	1543.3	1542.2	1545.3	1545.9	1550.0	1548.5
5°	1430.8	1429.5	1426.2	1426.9	1426.2	1429.5	1430.8	1436.0	1438.6	1449.0	1447.7
7.5°	1335.5	1330.4	1331.8	1326.7	1331.8	1330.4	1335.5	1340.2	1348.1	1352.8	1363.8
10°	1277.2	1270.0	1264.1	1258.9	1264.1	1270.0	1277.2	1279.8	1290.8	1296.0	1307.1
12.5°	1197.5	1191.3	1183.4	1185.0	1183.4	1191.3	1197.5	1208.9	1223.1	1234.0	1251.4
15°	1084.4	1074.7	1059.1	1061.0	1059.1	1074.7	1084.4	1092.9	1107.3	1132.0	1143.7
17.5°	988.8	988.9	981.8	983.4	981.8	988.9	988.8	1000.4	1007.6	1023.4	1041.4
20°	939.3	934.7	935.4	933.4	935.4	934.7	939.3	953.0	960.8	971.8	991.4
22.5°	904.9	899.4	894.8	890.7	894.8	899.4	904.9	908.7	919.2	929.7	945.6
25°	846.9	842.9	837.1	835.8	837.1	842.9	846.9	852.7	857.9	871.6	881.3
27.5°	795.8	795.1	792.7	789.7	792.7	795.1	795.8	801.0	807.8	816.5	828.9
30°	766.1	764.8	763.5	761.6	763.5	764.8	766.1	771.4	776.6	783.7	793.5
32.5°	739.6	738.8	737.5	737.7	737.5	738.8	739.6	742.2	745.3	754.6	762.2
35°	701.7	701.1	699.8	699.1	699.8	701.1	701.7	704.3	706.3	708.9	715.4
37.5°	666.3	668.0	667.2	667.1	667.2	668.0	666.3	667.0	664.9	669.5	674.0
40°	641.8	642.5	643.8	643.1	643.8	642.5	641.8	642.5	642.5	642.5	646.4
42.5°	621.5	621.7	623.5	621.3	623.5	621.7	621.5	619.1	616.0	616.4	617.8
45°	585.2	589.1	588.5	588.5	588.5	589.1	585.2	580.7	580.0	577.4	577.4
47.5°	545.5	548.9	549.8	549.7	549.8	548.9	545.5	543.8	540.8	538.2	537.9
50°	519.4	518.1	520.1	519.4	520.1	518.1	519.4	516.2	511.6	511.6	510.4
52.5°	487.7	488.0	487.8	487.1	487.8	488.0	487.7	486.0	484.0	481.9	481.2
55°	438.7	439.4	438.1	438.7	438.1	439.4	438.7	438.1	438.1	436.8	438.1
57.5°	385.6	382.5	383.8	382.2	383.8	382.5	385.6	388.5	389.6	389.8	391.8
60°	347.6	342.4	341.1	338.5	341.1	342.4	347.6	354.1	356.7	358.0	360.0
62.5°	304.9	301.3	296.9	298.9	296.9	301.3	304.9	311.9	317.6	322.1	326.6
65°	248.0	245.4	243.4	246.1	243.4	245.4	248.0	253.2	258.4	268.8	278.6
67.5°	205.3	203.9	203.9	202.6	203.9	203.9	205.3	207.9	211.2	216.9	226.0
70°	183.0	181.0	181.0	179.7	181.0	181.0	183.0	183.0	186.1	188.7	195.3
72.5°	160.0	158.1	158.6	157.8	158.6	158.1	160.0	160.5	163.8	164.9	167.7
75°	118.5	115.2	115.2	115.9	115.2	115.2	118.5	122.4	125.6	131.5	132.8
77.5°	88.4	87.7	88.6	87.5	88.6	87.7	88.4	88.4	89.0	91.8	94.0
80°	72.2	71.6	70.9	72.9	70.9	71.6	72.2	72.2	72.9	73.5	74.2
82.5°	56.1	56.0	55.8	58.3	55.8	56.0	56.1	57.2	57.3	56.9	57.6
85°	33.8	32.5	33.8	32.5	33.8	32.5	33.8	33.2	33.8	33.2	33.8
87.5°	19.0	18.6	18.2	18.8	18.2	18.6	19.0	17.9	17.7	18.3	17.5
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	33.6	33.8	33.8	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4
95°	34.8	35.1	35.4	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3
97.5°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8
100°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8
102.5°	35.2	35.3	35.4	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5
105°	379.9	370.1	360.3	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5
107.5°	485.3	486.2	487.3	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7
110°	545.9	546.7	547.6	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	605.3	606.3	607.3	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0
115°	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6
117.5°	785.2	785.1	785.1	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7
120°	842.6	842.0	841.6	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0
122.5°	897.7	897.2	896.6	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7
125°	977.9	978.1	978.4	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4
127.5°	1051.9	1051.7	1051.4	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8
132.5°	1146.3	1146.1	1145.9	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0
135°	1211.9	1212.4	1213.0	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7
137.5°	1272.0	1271.9	1271.7	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8
140°	1311.1	1311.3	1311.6	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6
142.5°	1345.2	1345.2	1345.2	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6
145°	1395.1	1395.6	1396.2	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6
147.5°	1438.4	1438.7	1439.0	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5
150°	1466.0	1466.2	1466.6	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6
152.5°	1490.9	1490.7	1490.5	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0
155°	1524.6	1523.8	1523.0	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1
157.5°	1553.0	1551.5	1550.1	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5
160°	1571.3	1569.7	1568.1	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7
162.5°	1585.8	1583.9	1582.0	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5
165°	1607.0	1604.5	1602.1	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2
167.5°	1622.3	1619.6	1616.8	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4
170°	1631.2	1628.4	1625.7	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8
172.5°	1636.7	1633.8	1630.8	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7
175°	1643.8	1640.5	1637.3	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6
177.5°	1645.8	1643.2	1640.5	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1545.3	1549.0	1557.3	1566.7	1574.5	1581.3	1586.5	1593.7	1600.5	1609.9	1618.8
5°	1451.6	1460.7	1473.7	1489.4	1508.9	1521.9	1538.1	1552.5	1573.4	1594.2	1614.4
7.5°	1369.3	1379.3	1398.5	1420.1	1443.2	1464.6	1483.9	1509.1	1536.8	1567.1	1600.9
10°	1316.2	1327.3	1350.1	1374.8	1402.2	1422.9	1449.0	1479.0	1510.2	1547.3	1588.9
12.5°	1268.3	1278.9	1306.3	1331.5	1359.9	1382.8	1413.1	1443.6	1485.2	1525.4	1572.8
15°	1174.9	1203.0	1234.2	1264.1	1298.0	1326.0	1362.4	1393.7	1433.4	1490.0	1544.0
17.5°	1071.3	1101.1	1140.0	1186.2	1231.6	1266.2	1303.2	1342.0	1389.3	1447.1	1509.4
20°	1010.9	1035.0	1078.0	1129.4	1182.1	1230.3	1264.1	1307.1	1355.9	1418.4	1482.9
22.5°	965.6	986.0	1019.6	1071.1	1128.0	1183.9	1227.2	1269.6	1323.6	1386.1	1456.3
25°	897.6	919.8	949.1	984.2	1049.3	1108.6	1165.2	1214.0	1271.3	1333.7	1411.9
27.5°	841.1	860.4	887.2	923.8	967.6	1032.9	1101.6	1157.2	1215.9	1283.0	1361.2
30°	807.8	823.5	845.5	882.6	924.3	982.9	1052.6	1117.7	1176.9	1246.6	1328.0
32.5°	772.9	789.6	811.2	840.5	885.3	934.5	1004.1	1075.5	1138.4	1209.6	1289.4
35°	726.4	739.5	759.0	789.0	829.3	872.3	934.1	1007.6	1074.1	1150.2	1226.4
37.5°	679.5	694.8	710.2	736.9	770.0	816.1	866.8	941.9	1015.5	1085.0	1159.4
40°	652.9	662.0	678.9	700.4	735.6	776.6	824.1	897.6	971.2	1040.2	1115.1
42.5°	623.2	633.4	647.7	669.2	700.7	740.6	787.1	850.8	927.5	994.4	1062.5
45°	582.0	587.8	602.1	620.4	646.4	686.7	729.7	786.4	858.6	922.3	982.3
47.5°	540.3	545.4	554.3	571.0	600.1	632.6	672.8	723.6	787.0	850.8	901.4
50°	511.6	516.2	524.6	540.3	566.3	598.2	637.9	683.5	740.1	801.3	843.6
52.5°	483.0	485.5	493.4	511.1	533.0	564.4	599.9	641.8	694.8	745.6	788.4
55°	437.4	443.3	448.5	461.5	482.3	512.3	544.2	583.9	624.9	667.9	704.3
57.5°	389.9	396.3	403.8	415.3	431.9	459.7	488.4	520.5	555.5	591.2	621.7
60°	358.7	364.5	371.0	384.1	399.0	421.2	452.4	480.4	507.1	539.6	570.2
62.5°	327.9	333.8	341.4	351.8	366.2	387.3	413.4	437.7	465.5	493.8	516.6
65°	282.5	287.1	292.9	302.7	316.3	335.3	356.7	375.6	400.3	421.2	442.0
67.5°	232.7	241.4	249.1	257.0	268.6	286.2	301.7	319.8	336.6	352.0	371.0
70°	199.8	209.6	216.8	225.2	236.3	251.3	266.2	278.6	292.3	307.2	324.2
72.5°	172.3	179.9	185.5	194.5	204.6	218.4	232.4	242.6	253.7	264.0	280.5
75°	136.1	139.3	143.2	150.3	159.5	169.9	181.0	190.0	196.6	205.7	217.4
77.5°	97.8	104.0	106.6	111.7	118.2	124.7	132.0	139.7	145.9	149.2	158.2
80°	74.8	77.5	80.1	87.2	91.2	97.7	102.8	110.0	112.6	115.9	124.3
82.5°	58.2	59.8	61.3	63.3	65.6	72.2	77.4	81.9	84.5	85.7	92.0
85°	33.8	34.5	35.1	35.8	36.4	36.4	39.1	42.3	46.9	46.9	48.8
87.5°	17.2	17.4	17.0	16.0	16.6	16.1	16.1	15.6	16.6	17.4	18.4
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	27.7	26.1	23.9	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5
95°	28.7	27.1	26.7	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6
97.5°	32.6	32.4	62.9	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6
100°	49.5	54.1	91.8	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6
102.5°	210.5	260.7	265.5	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5
105°	386.0	383.6	382.2	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1
107.5°	479.5	478.3	476.4	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2
110°	542.7	542.2	540.5	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	604.1	604.2	603.4	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1
115°	694.0	693.4	693.7	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0
117.5°	785.8	785.9	785.3	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3
120°	841.6	841.0	841.2	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3
122.5°	897.4	897.1	896.7	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3
125°	974.6	973.8	974.3	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3
127.5°	1052.8	1053.0	1051.7	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0
130°	1099.4	1099.2	1098.4	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3
132.5°	1145.7	1145.4	1144.4	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5
135°	1209.2	1208.6	1207.5	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9
137.5°	1270.2	1269.6	1268.4	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7
140°	1307.8	1306.9	1306.4	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0
142.5°	1343.0	1342.4	1342.1	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4
145°	1393.3	1393.0	1393.0	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4
147.5°	1437.3	1437.0	1437.3	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4
150°	1465.6	1465.6	1465.8	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9
152.5°	1489.6	1489.1	1489.6	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4
155°	1522.0	1520.9	1521.8	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4
157.5°	1550.1	1548.7	1549.6	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6
160°	1568.1	1566.4	1566.7	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3
162.5°	1582.7	1581.1	1581.4	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1
165°	1603.0	1600.8	1600.8	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0
167.5°	1618.0	1615.6	1615.8	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7
170°	1627.6	1625.4	1625.1	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6
172.5°	1633.5	1631.3	1631.0	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4
175°	1640.1	1637.7	1637.4	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8
177.5°	1643.6	1641.8	1641.4	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1625.5	1630.2	1635.4	1645.4	1653.7	1657.3	1664.6	1669.8	1668.3	1675.5	1688.0
5°	1631.9	1649.5	1669.7	1690.5	1713.9	1733.5	1749.1	1764.7	1777.1	1792.0	1814.2
7.5°	1630.8	1662.2	1696.1	1733.5	1771.9	1805.1	1835.8	1867.0	1894.8	1925.1	1964.8
10°	1626.7	1668.3	1710.7	1759.5	1808.3	1854.6	1896.2	1935.3	1972.4	2012.1	2062.2
12.5°	1622.0	1669.9	1721.1	1779.8	1840.6	1896.2	1945.1	2001.4	2047.9	2099.1	2157.0
15°	1601.3	1665.7	1735.4	1811.6	1884.5	1959.3	2026.3	2095.4	2159.8	2221.0	2293.9
17.5°	1577.6	1652.0	1734.1	1824.1	1911.7	2002.7	2082.3	2169.2	2235.1	2317.2	2384.9
20°	1558.4	1638.4	1726.3	1827.2	1926.8	2027.6	2115.5	2204.1	2278.3	2360.9	2446.9
22.5°	1534.9	1622.8	1718.0	1822.5	1926.8	2037.0	2134.3	2222.3	2314.2	2407.3	2495.9
25°	1497.1	1588.3	1689.2	1803.8	1923.5	2036.1	2140.3	2249.7	2348.6	2449.5	2528.9
27.5°	1450.8	1546.5	1652.9	1771.1	1894.0	2009.3	2132.0	2248.5	2348.1	2445.2	2514.5
30°	1413.8	1514.7	1616.9	1736.8	1864.3	1987.9	2119.5	2236.0	2340.8	2428.0	2467.1
32.5°	1375.8	1471.5	1576.9	1698.2	1828.9	1961.9	2092.4	2211.5	2308.5	2360.9	2361.8
35°	1309.7	1399.5	1508.9	1628.0	1762.1	1906.6	2038.7	2155.9	2215.2	2219.7	2155.9
37.5°	1237.5	1320.0	1423.2	1542.5	1689.3	1833.0	1968.1	2046.2	2066.0	1999.7	1881.7
40°	1186.0	1262.2	1361.8	1484.2	1629.9	1778.4	1901.4	1958.7	1937.9	1830.4	1698.9
42.5°	1131.9	1202.8	1298.8	1419.6	1565.9	1715.9	1820.7	1851.4	1796.2	1672.2	1518.3
45°	1043.5	1108.6	1203.6	1325.4	1465.9	1606.5	1686.0	1670.3	1578.5	1431.4	1258.9
47.5°	951.5	1014.3	1099.8	1212.4	1356.4	1477.7	1531.5	1484.4	1353.8	1192.0	1051.7
50°	890.5	955.0	1033.7	1141.1	1272.6	1389.8	1424.2	1352.7	1207.5	1051.9	923.0
52.5°	830.6	885.7	962.9	1066.7	1192.4	1291.4	1309.7	1227.2	1077.3	937.8	823.5
55°	739.5	789.6	854.7	952.4	1061.0	1145.0	1135.2	1029.2	893.1	774.0	684.1
57.5°	651.3	689.1	749.3	840.7	936.2	992.5	956.9	866.4	739.6	642.1	566.3
60°	593.0	628.2	684.1	764.2	848.2	880.0	850.1	751.9	651.6	562.4	498.6
62.5°	537.8	568.8	616.9	691.3	759.1	778.0	746.0	660.1	569.8	493.7	440.8
65°	457.6	486.2	527.3	580.0	626.9	635.9	615.1	527.3	458.9	395.1	358.7
67.5°	384.8	403.6	435.6	481.2	506.1	511.4	471.2	416.0	355.7	316.5	289.0
70°	335.9	348.9	378.9	403.6	423.8	424.4	387.3	343.1	296.9	265.0	244.8
72.5°	288.5	301.0	323.7	340.6	356.0	351.0	317.0	282.1	244.8	220.7	205.7
75°	222.7	233.7	245.4	253.2	253.2	246.7	222.0	195.9	174.5	160.1	155.6
77.5°	161.8	171.0	174.9	173.7	171.3	161.2	145.5	128.5	120.8	114.1	110.6
80°	126.9	130.9	132.2	128.9	125.0	113.2	102.8	95.7	88.5	85.9	84.6
82.5°	94.1	97.5	94.1	95.1	86.4	76.8	71.1	68.6	65.6	64.6	63.3
85°	50.1	49.5	48.2	44.9	39.1	37.7	37.1	36.4	35.1	35.8	34.5
87.5°	18.5	17.5	16.1	16.1	16.7	16.1	17.0	17.4	17.9	17.7	19.1
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4
95°	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3
97.5°	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8
100°	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8
102.5°	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5
105°	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5
107.5°	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7
110°	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3





TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0
115°	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6
117.5°	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7
120°	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0
122.5°	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7
125°	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4
127.5°	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6
130°	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8
132.5°	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0
135°	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7
137.5°	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8
140°	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6
142.5°	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6
145°	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6
147.5°	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5
150°	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6
152.5°	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0
155°	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1
157.5°	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5
160°	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7
162.5°	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5
165°	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2
167.5°	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4
170°	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8
172.5°	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7
175°	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6
177.5°	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1694.8	1696.9	1698.4	1703.6	1704.1	1708.9	1704.1
5°	1835.0	1844.1	1858.5	1872.7	1874.0	1883.2	1866.9
7.5°	1992.3	2013.4	2026.5	2049.7	2058.8	2064.5	2055.1
10°	2100.6	2120.1	2154.6	2171.5	2188.5	2191.0	2183.3
12.5°	2205.3	2236.3	2263.4	2295.5	2294.7	2317.7	2309.3
15°	2344.7	2376.6	2414.3	2450.1	2463.2	2463.2	2473.6
17.5°	2444.2	2502.6	2541.7	2569.8	2600.5	2605.9	2602.2
20°	2511.4	2574.5	2616.1	2652.6	2673.4	2679.3	2679.3
22.5°	2561.3	2615.1	2655.8	2688.5	2705.7	2712.6	2710.5
25°	2596.0	2642.1	2666.9	2676.7	2681.2	2680.0	2667.6
27.5°	2548.5	2546.5	2530.9	2500.9	2478.4	2464.7	2449.1
30°	2458.0	2424.1	2385.1	2342.1	2286.8	2244.4	2231.4
32.5°	2323.1	2247.0	2180.9	2109.3	2049.8	2007.5	1989.8
35°	2062.2	1941.8	1843.5	1757.5	1695.1	1656.0	1643.0
37.5°	1752.6	1636.1	1514.3	1431.0	1379.2	1339.8	1325.0
40°	1555.8	1428.8	1322.7	1244.6	1191.2	1152.8	1152.2
42.5°	1376.1	1254.9	1155.0	1098.8	1041.2	1015.9	1015.7
45°	1126.7	1029.8	945.2	900.9	866.4	845.5	839.7
47.5°	932.9	852.7	796.4	761.1	733.0	719.7	711.1
50°	824.1	753.8	708.9	678.2	662.7	645.7	644.4
52.5°	733.4	676.7	641.7	616.9	597.0	586.9	587.2
55°	616.4	571.5	546.8	527.9	512.3	504.5	501.2
57.5°	519.3	485.6	467.7	450.3	443.7	437.6	435.9
60°	458.9	436.1	419.2	405.5	395.7	393.8	393.1
62.5°	409.0	385.1	373.4	362.8	355.7	352.7	351.5
65°	337.2	319.6	309.2	300.8	298.2	293.6	292.9
67.5°	271.8	261.3	254.4	248.5	245.0	244.8	244.8
70°	231.7	225.8	220.0	216.8	214.8	213.5	213.5
72.5°	197.4	193.1	188.3	186.5	186.1	184.8	184.3
75°	150.3	145.8	146.4	143.2	140.6	137.4	135.4
77.5°	106.6	103.4	102.7	102.3	100.1	99.7	100.8
80°	82.7	79.4	78.8	79.4	78.8	76.8	76.8
82.5°	62.9	60.2	59.5	59.1	58.5	59.1	58.0
85°	33.8	32.5	32.5	32.5	33.8	33.2	32.5
87.5°	18.3	18.2	18.9	18.5	18.6	18.2	18.8
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P333111-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)