

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332839-840

Luminaire Tested: **S124DIW-S1195D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332839-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7058.9 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	33
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.7
10°-20°	534.0	7.6
20°-30°	786.0	11.1
30°-40°	913.7	12.9
40°-50°	913.7	12.9
50°-60°	799.3	11.3
60°-70°	593.6	8.4
70°-80°	337.2	4.8
80°-90°	99.1	1.4
90°-100°	20.9	0.3
100°-110°	133.4	1.9
110°-120°	255.3	3.6
120°-130°	324.0	4.6
130°-140°	346.7	4.9
140°-150°	324.2	4.6
150°-160°	261.4	3.7
160°-170°	168.6	2.4
170°-180°	58.1	0.8
0°-30°	1509.5	21.4
0°-40°	2423.2	34.3
0°-60°	4136.2	58.6
0°-90°	5166.1	73.2
90°-120°	409.6	5.8
90°-150°	1404.6	19.9
90°-180°	1893.0	26.8
0°-180°	7058.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	1	6	10	13	14	6
95°	25	10	10	13	13	32
105°	138	140	143	146	130	144
115°	257	258	258	259	259	253
125°	362	363	362	364	364	323
135°	448	448	450	451	452	345
145°	517	518	519	519	520	323
155°	567	567	566	568	567	261
165°	598	596	596	599	595	169
175°	612	609	610	613	608	58
180°	612	612	612	612	612	



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	33.1	33.0	33.1
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	5.8	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3
95°	25.1	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7
97.5°	53.4	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1
100°	75.0	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4
102.5°	99.3	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4
105°	137.7	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7
107.5°	173.6	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4
110°	197.7	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	221.2	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9
115°	257.2	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3
117.5°	289.7	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5
120°	311.6	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3
122.5°	332.1	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1
125°	361.5	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7
127.5°	389.4	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9
130°	407.3	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3
132.5°	423.8	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5
135°	448.5	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1
137.5°	470.4	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8
140°	484.6	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9
142.5°	497.5	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9
145°	517.2	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7
147.5°	532.8	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0
150°	544.2	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5
152.5°	553.7	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5
155°	567.0	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5
157.5°	578.3	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0
160°	584.9	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7
162.5°	590.8	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2
165°	598.1	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7
167.5°	604.0	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3
170°	607.3	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8
172.5°	609.6	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0
175°	611.9	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6
177.5°	613.0	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	33.2	33.3	33.4	33.5	33.6	33.6	33.6	33.7
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	10.9	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	16.7	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	59.7	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	144.6	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	178.9	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.3	202.5	202.7	202.9	203.2	203.5	203.8	204.1



TEST NUMBER: P332839-840

CATALOG NUMBER: S124DIW-S1195D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	224.8	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.5	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.2	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.0	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.8	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.4	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.6	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.3	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.0	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.2	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.1	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.8	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.6	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	566.9	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	589.8	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	597.5	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	603.2	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	606.6	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	608.8	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	611.5	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	612.5	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)