

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333025-930

Luminaire Tested: **S124RDIW-S350D1050U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333025-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1050U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4583.9 lumens  
Efficiency: N/A  
Efficacy: 120.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14	10
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	1.0
10°-20°	132.0	2.9
20°-30°	190.6	4.2
30°-40°	216.1	4.7
40°-50°	208.7	4.6
50°-60°	173.5	3.8
60°-70°	119.8	2.6
70°-80°	60.7	1.3
80°-90°	18.8	0.4
90°-100°	37.8	0.8
100°-110°	240.8	5.3
110°-120°	460.7	10.1
120°-130°	584.9	12.8
130°-140°	625.8	13.7
140°-150°	585.2	12.8
150°-160°	471.9	10.3
160°-170°	304.4	6.6
170°-180°	104.9	2.3
0°-30°	370.0	8.1
0°-40°	586.1	12.8
0°-60°	968.3	21.1
0°-90°	1167.6	25.5
90°-120°	739.3	16.1
90°-150°	2535.2	55.3
90°-180°	3416.0	74.5
0°-180°	4583.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	2	11	18	23	25	3
95°	45	19	18	23	24	58
105°	249	254	258	263	236	260
115°	464	466	466	467	468	457
125°	653	656	654	657	658	582
135°	810	809	812	814	815	623
145°	933	936	936	937	938	583
155°	1023	1024	1022	1025	1023	472
165°	1080	1076	1076	1081	1075	305
175°	1104	1100	1100	1107	1098	105
180°	1104	1104	1104	1104	1104	



TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.6	7.4	7.3	7.2	7.0	7.1	7.3	7.5	7.7	8.0	8.1
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	10.4	10.5	10.6	10.8	10.8	11.7	13.1	14.6	16.1	17.5	18.6
95°	45.4	39.2	32.9	26.7	20.5	17.4	17.6	17.8	18.0	18.2	19.2
97.5°	96.4	100.4	104.3	108.2	112.0	103.8	83.2	62.8	42.3	21.8	21.9
100°	135.5	138.8	142.1	145.4	148.7	137.7	112.3	87.0	61.7	36.4	33.3
102.5°	179.1	181.5	183.9	186.4	188.7	188.3	185.1	181.7	178.4	175.1	141.5
105°	248.7	249.7	250.9	251.9	253.1	254.0	254.9	255.9	256.8	257.7	259.3
107.5°	313.2	313.8	314.3	314.9	315.4	316.3	317.6	318.9	320.1	321.3	322.1
110°	356.9	357.4	357.9	358.5	359.1	359.9	361.0	362.1	363.2	364.3	364.7



TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.2	400.1	401.1	402.1	403.1	403.9	404.4	404.9	405.4	405.9	405.9
115°	464.2	464.8	465.4	465.9	466.4	466.6	466.4	466.3	466.1	465.9	466.3
117.5°	522.9	523.6	524.3	525.1	525.8	526.4	526.8	527.2	527.6	528.0	527.9
120°	562.6	563.3	564.0	564.8	565.5	565.7	565.6	565.4	565.2	565.0	565.4
122.5°	599.6	600.0	600.4	600.9	601.3	601.7	601.9	602.2	602.4	602.7	602.9
125°	652.6	653.3	654.0	654.8	655.5	655.7	655.3	654.9	654.6	654.2	654.8
127.5°	702.8	703.0	703.2	703.4	703.5	704.0	704.9	705.7	706.5	707.4	707.4
130°	735.2	735.4	735.6	735.7	735.9	736.3	736.9	737.4	737.9	738.5	738.7
132.5°	764.9	765.2	765.6	765.9	766.2	766.8	767.4	768.2	768.8	769.6	769.7
135°	809.5	809.3	809.2	808.9	808.8	809.1	809.8	810.6	811.3	812.0	812.4
137.5°	849.0	849.1	849.1	849.2	849.3	849.7	850.5	851.3	852.2	853.0	853.4
140°	874.8	875.1	875.5	875.9	876.3	876.6	877.0	877.3	877.8	878.1	878.6
142.5°	897.9	898.5	899.2	899.9	900.6	901.0	901.2	901.4	901.6	901.9	902.3
145°	933.4	934.0	934.5	935.1	935.6	935.9	935.9	935.9	935.9	935.9	936.1
147.5°	961.6	962.7	963.8	964.7	965.8	966.2	966.0	965.9	965.6	965.5	965.6
150°	982.2	982.9	983.7	984.4	985.1	985.4	985.2	985.0	984.8	984.6	984.6
152.5°	999.3	1000.0	1000.5	1001.1	1001.7	1001.8	1001.5	1001.2	1000.9	1000.5	1000.8
155°	1023.4	1023.7	1023.9	1024.0	1024.2	1024.0	1023.4	1023.0	1022.4	1021.8	1022.5
157.5°	1043.8	1043.7	1043.6	1043.4	1043.3	1043.0	1042.4	1041.7	1041.1	1040.5	1041.5
160°	1055.6	1055.2	1054.6	1054.0	1053.4	1053.1	1053.0	1052.7	1052.6	1052.4	1053.4
162.5°	1066.2	1065.6	1064.9	1064.1	1063.5	1063.0	1062.8	1062.7	1062.5	1062.3	1063.4
165°	1079.6	1078.7	1077.8	1076.8	1076.0	1075.5	1075.5	1075.5	1075.5	1075.5	1077.0
167.5°	1090.2	1089.2	1088.3	1087.4	1086.4	1085.9	1085.7	1085.7	1085.6	1085.4	1087.0
170°	1096.2	1095.0	1094.0	1092.8	1091.8	1091.3	1091.4	1091.7	1091.8	1092.0	1093.5
172.5°	1100.1	1099.0	1097.9	1096.8	1095.7	1095.3	1095.4	1095.6	1095.8	1096.0	1097.5
175°	1104.4	1103.3	1102.2	1101.1	1100.0	1099.6	1099.8	1099.9	1100.1	1100.3	1102.0
177.5°	1106.4	1105.4	1104.3	1103.3	1102.3	1102.0	1102.2	1102.5	1102.8	1103.1	1104.2
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	8.2	8.4	8.6	8.7	8.9	9.0	9.1	9.3
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	19.7	20.8	21.9	22.5	22.6	22.7	22.7	22.8
95°	20.4	21.4	22.6	23.2	23.4	23.6	23.8	24.0
97.5°	22.0	22.2	22.3	22.4	22.6	22.7	22.9	23.2
100°	30.1	27.0	23.9	22.4	22.6	22.7	22.9	23.2
102.5°	107.8	74.1	40.4	23.6	23.6	23.7	23.7	23.8
105°	261.1	262.7	264.3	261.9	255.3	248.7	242.1	235.5
107.5°	322.9	323.8	324.6	325.3	326.0	326.7	327.4	328.1
110°	365.0	365.4	365.7	366.2	366.8	367.3	367.9	368.4





TEST NUMBER: P333025-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	405.8	405.7	405.6	405.9	406.7	407.3	408.1	408.7
115°	466.6	467.0	467.3	467.6	467.6	467.6	467.6	467.6
117.5°	527.8	527.8	527.7	527.7	527.6	527.5	527.4	527.3
120°	565.7	566.1	566.5	566.5	566.1	565.7	565.4	565.0
122.5°	603.2	603.3	603.6	603.5	603.2	602.8	602.4	602.0
125°	655.3	655.9	656.4	656.8	657.0	657.1	657.4	657.5
127.5°	707.2	707.1	706.9	706.9	706.7	706.5	706.4	706.3
130°	738.8	739.1	739.2	739.3	739.3	739.3	739.3	739.3
132.5°	769.9	770.1	770.3	770.3	770.1	770.0	769.9	769.7
135°	812.8	813.1	813.5	813.8	814.2	814.6	815.0	815.3
137.5°	853.8	854.2	854.6	854.8	854.6	854.5	854.4	854.3
140°	879.2	879.7	880.3	880.7	880.8	881.0	881.2	881.4
142.5°	902.7	903.1	903.5	903.7	903.8	903.8	903.8	903.8
145°	936.3	936.5	936.6	936.9	937.3	937.7	938.0	938.4
147.5°	965.8	965.9	966.0	966.2	966.5	966.6	966.8	966.9
150°	984.6	984.6	984.6	984.7	984.9	985.1	985.3	985.5
152.5°	1001.1	1001.4	1001.7	1001.8	1001.7	1001.5	1001.4	1001.4
155°	1023.3	1024.0	1024.7	1024.8	1024.3	1023.8	1023.2	1022.6
157.5°	1042.4	1043.3	1044.3	1044.3	1043.3	1042.4	1041.5	1040.5
160°	1054.6	1055.6	1056.8	1056.8	1055.6	1054.6	1053.4	1052.4
162.5°	1064.5	1065.6	1066.7	1066.7	1065.4	1064.1	1062.9	1061.6
165°	1078.5	1079.9	1081.4	1081.2	1079.6	1078.0	1076.4	1074.6
167.5°	1088.7	1090.3	1091.8	1091.8	1090.0	1088.1	1086.3	1084.4
170°	1094.9	1096.4	1097.9	1097.7	1095.8	1094.1	1092.2	1090.4
172.5°	1098.9	1100.4	1101.9	1101.6	1099.6	1097.6	1095.7	1093.6
175°	1103.6	1105.2	1106.9	1106.6	1104.4	1102.2	1100.0	1097.8
177.5°	1105.5	1106.6	1107.8	1107.5	1105.7	1104.0	1102.2	1100.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4

(END OF REPORT)