

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333029-930

Luminaire Tested: **S124RDIW-S350D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333029-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5542.1 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	0.9
10°-20°	132.0	2.4
20°-30°	190.6	3.4
30°-40°	216.1	3.9
40°-50°	208.7	3.8
50°-60°	173.5	3.1
60°-70°	119.8	2.2
70°-80°	60.7	1.1
80°-90°	19.7	0.4
90°-100°	48.4	0.9
100°-110°	308.3	5.6
110°-120°	589.8	10.6
120°-130°	748.7	13.5
130°-140°	801.1	14.5
140°-150°	749.1	13.5
150°-160°	604.1	10.9
160°-170°	389.6	7.0
170°-180°	134.3	2.4
0°-30°	370.0	6.7
0°-40°	586.1	10.6
0°-60°	968.3	17.5
0°-90°	1168.5	21.1
90°-120°	946.5	17.1
90°-150°	3245.5	58.6
90°-180°	4374.0	78.9
0°-180°	5542.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	3	15	23	29	32	4
95°	58	24	23	29	31	75
105°	318	325	330	337	301	333
115°	594	597	596	598	598	585
125°	835	839	838	841	842	746
135°	1036	1036	1040	1042	1044	798
145°	1195	1198	1198	1199	1201	746
155°	1310	1311	1308	1312	1309	604
165°	1382	1377	1377	1384	1376	390
175°	1414	1408	1409	1417	1405	135
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.7	7.7	7.7	7.7	7.6	7.7	8.1	8.4	8.6	9.0	9.2
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	13.3	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8
95°	58.1	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7
97.5°	123.5	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0
100°	173.4	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6
102.5°	229.3	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1
105°	318.3	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1
107.5°	401.0	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4
110°	456.8	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.9	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6
115°	594.3	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9
117.5°	669.4	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9
120°	720.2	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8
122.5°	767.5	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8
125°	835.4	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2
127.5°	899.7	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5
130°	941.2	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7
132.5°	979.3	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4
135°	1036.3	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0
137.5°	1086.9	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5
140°	1119.9	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8
142.5°	1149.5	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1
145°	1195.0	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4
147.5°	1231.1	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2
150°	1257.4	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5
152.5°	1279.4	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2
155°	1310.3	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0
157.5°	1336.3	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3
160°	1351.4	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7
162.5°	1365.0	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3
165°	1382.2	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8
167.5°	1395.7	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6
170°	1403.3	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9
172.5°	1408.3	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9
175°	1413.9	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7
177.5°	1416.4	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	9.4	9.6	9.9	10.0	10.2	10.4	10.5	10.7
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	25.3	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	26.1	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.2	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	38.6	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	138.0	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	334.2	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	413.4	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.3	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P333029-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.4	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.4	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.7	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.1	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	838.9	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.4	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	945.8	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.6	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.5	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.0	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1125.5	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1155.6	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.6	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.4	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1281.6	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.0	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1362.8	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1380.6	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1393.7	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1401.7	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1406.8	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1412.8	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1415.2	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)