

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-930

Luminaire Tested: **S124RDIW-S350D470U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333017-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D470U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2694.0 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	1.8
10°-20°	132.0	4.9
20°-30°	190.6	7.1
30°-40°	216.1	8.0
40°-50°	208.7	7.7
50°-60°	173.5	6.4
60°-70°	119.8	4.4
70°-80°	60.7	2.3
80°-90°	17.0	0.6
90°-100°	16.9	0.6
100°-110°	107.7	4.0
110°-120°	206.1	7.6
120°-130°	261.6	9.7
130°-140°	279.9	10.4
140°-150°	261.7	9.7
150°-160°	211.1	7.8
160°-170°	136.1	5.1
170°-180°	46.9	1.7
0°-30°	370.0	13.7
0°-40°	586.1	21.8
0°-60°	968.3	35.9
0°-90°	1165.9	43.3
90°-120°	330.7	12.3
90°-150°	1134.0	42.1
90°-180°	1528.0	56.7
0°-180°	2694.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	23
90°	1	5	8	10	11	2
95°	20	8	8	10	11	26
105°	111	113	115	118	105	116
115°	208	209	208	209	209	204
125°	292	293	293	294	294	261
135°	362	362	363	364	365	279
145°	418	419	419	419	420	261
155°	458	458	457	458	458	211
165°	483	481	481	484	481	136
175°	494	492	492	495	491	47
180°	494	494	494	494	494	



TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.3	6.9	6.6	6.2	5.9	5.7	5.8	5.8	5.9	6.0	6.0
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	4.6	4.7	4.7	4.8	4.9	5.2	5.9	6.5	7.2	7.8	8.3
95°	20.3	17.5	14.8	12.0	9.1	7.8	7.9	8.0	8.1	8.2	8.6
97.5°	43.1	44.9	46.6	48.3	50.1	46.4	37.3	28.0	18.9	9.8	9.8
100°	60.6	62.0	63.6	65.1	66.5	61.6	50.2	38.9	27.6	16.2	14.8
102.5°	80.1	81.2	82.3	83.3	84.5	84.2	82.8	81.3	79.8	78.4	63.3
105°	111.2	111.7	112.2	112.7	113.2	113.7	114.1	114.5	114.9	115.3	116.0
107.5°	140.1	140.4	140.6	140.9	141.1	141.5	142.0	142.6	143.2	143.7	144.1
110°	159.6	159.9	160.1	160.4	160.6	160.9	161.4	162.0	162.5	163.0	163.1



TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	178.6	179.0	179.4	179.9	180.3	180.7	180.9	181.1	181.3	181.6	181.6
115°	207.7	207.9	208.1	208.4	208.6	208.7	208.6	208.6	208.5	208.4	208.6
117.5°	233.9	234.2	234.6	234.9	235.2	235.5	235.6	235.8	236.0	236.2	236.1
120°	251.6	251.9	252.3	252.6	252.9	253.1	253.0	252.9	252.8	252.7	252.9
122.5°	268.2	268.4	268.6	268.8	269.0	269.1	269.2	269.4	269.5	269.6	269.7
125°	291.9	292.2	292.5	292.9	293.2	293.3	293.1	292.9	292.8	292.6	292.9
127.5°	314.4	314.5	314.5	314.6	314.7	315.0	315.3	315.7	316.1	316.4	316.4
130°	328.8	328.9	329.1	329.1	329.2	329.4	329.6	329.9	330.1	330.4	330.4
132.5°	342.2	342.3	342.4	342.6	342.8	343.0	343.3	343.6	343.9	344.2	344.3
135°	362.1	362.0	361.9	361.8	361.7	361.9	362.2	362.6	362.9	363.2	363.4
137.5°	379.8	379.8	379.8	379.8	379.9	380.1	380.4	380.8	381.2	381.6	381.7
140°	391.3	391.4	391.6	391.8	391.9	392.1	392.2	392.5	392.6	392.8	393.1
142.5°	401.6	401.9	402.3	402.5	402.8	403.0	403.1	403.2	403.3	403.4	403.6
145°	417.5	417.8	418.0	418.2	418.5	418.7	418.7	418.7	418.7	418.7	418.7
147.5°	430.2	430.6	431.0	431.5	432.0	432.2	432.1	432.0	431.9	431.9	431.9
150°	439.4	439.7	440.0	440.3	440.7	440.8	440.7	440.6	440.5	440.4	440.4
152.5°	447.0	447.3	447.5	447.8	448.1	448.1	448.0	447.8	447.7	447.5	447.7
155°	457.8	457.9	458.0	458.0	458.1	458.0	457.8	457.5	457.3	457.1	457.4
157.5°	466.9	466.8	466.8	466.8	466.7	466.5	466.3	465.9	465.7	465.5	465.9
160°	472.2	472.0	471.7	471.5	471.2	471.1	471.0	470.9	470.8	470.8	471.2
162.5°	477.0	476.6	476.3	476.0	475.7	475.5	475.4	475.3	475.2	475.2	475.6
165°	482.9	482.5	482.1	481.7	481.3	481.1	481.1	481.1	481.1	481.1	481.8
167.5°	487.6	487.2	486.8	486.4	485.9	485.7	485.7	485.6	485.6	485.5	486.2
170°	490.3	489.8	489.3	488.9	488.4	488.1	488.2	488.3	488.4	488.4	489.1
172.5°	492.1	491.6	491.1	490.6	490.2	489.9	490.0	490.1	490.2	490.2	490.9
175°	494.0	493.5	493.0	492.5	492.0	491.9	492.0	492.0	492.1	492.2	492.9
177.5°	494.9	494.5	494.0	493.5	493.1	492.9	493.0	493.2	493.3	493.4	493.9
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0



TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	6.0	6.0	6.0	6.1	6.2	6.4	6.4	6.5
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	8.8	9.3	9.8	10.0	10.1	10.1	10.2	10.2
95°	9.1	9.6	10.1	10.4	10.4	10.5	10.6	10.7
97.5°	9.9	9.9	9.9	10.0	10.1	10.2	10.3	10.4
100°	13.5	12.1	10.7	10.0	10.1	10.2	10.3	10.4
102.5°	48.2	33.2	18.1	10.6	10.6	10.6	10.6	10.7
105°	116.8	117.5	118.2	117.2	114.1	111.2	108.3	105.3
107.5°	144.5	144.8	145.2	145.5	145.9	146.1	146.4	146.8
110°	163.3	163.5	163.6	163.8	164.0	164.3	164.5	164.8





TEST NUMBER: P333017-930

CATALOG NUMBER: S124RDIW-S350D470U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.5	181.5	181.4	181.6	181.9	182.2	182.5	182.8
115°	208.7	208.9	209.0	209.1	209.1	209.1	209.1	209.1
117.5°	236.1	236.1	236.0	236.0	235.9	235.9	235.9	235.9
120°	253.1	253.2	253.4	253.4	253.2	253.1	252.9	252.7
122.5°	269.8	269.9	269.9	269.9	269.8	269.6	269.5	269.3
125°	293.1	293.3	293.6	293.8	293.8	293.9	294.0	294.1
127.5°	316.3	316.3	316.3	316.2	316.1	316.0	316.0	315.9
130°	330.5	330.6	330.7	330.7	330.7	330.7	330.7	330.7
132.5°	344.4	344.5	344.5	344.5	344.5	344.5	344.4	344.3
135°	363.5	363.7	363.9	364.0	364.2	364.4	364.5	364.7
137.5°	381.9	382.0	382.3	382.3	382.3	382.2	382.2	382.1
140°	393.3	393.5	393.8	394.0	394.0	394.1	394.2	394.3
142.5°	403.7	404.0	404.1	404.2	404.2	404.3	404.3	404.3
145°	418.8	418.9	419.0	419.1	419.2	419.4	419.6	419.7
147.5°	432.0	432.0	432.1	432.2	432.3	432.4	432.4	432.5
150°	440.4	440.4	440.4	440.5	440.6	440.7	440.8	440.8
152.5°	447.8	447.9	448.1	448.1	448.1	448.0	447.9	447.9
155°	457.7	458.0	458.4	458.4	458.2	458.0	457.7	457.5
157.5°	466.3	466.7	467.1	467.1	466.7	466.3	465.9	465.5
160°	471.7	472.2	472.7	472.7	472.2	471.7	471.2	470.8
162.5°	476.1	476.6	477.1	477.1	476.5	476.0	475.4	474.9
165°	482.4	483.1	483.7	483.6	482.9	482.2	481.4	480.7
167.5°	487.0	487.7	488.4	488.4	487.5	486.7	485.9	485.1
170°	489.8	490.4	491.1	491.1	490.2	489.3	488.5	487.7
172.5°	491.5	492.2	492.8	492.8	491.9	491.0	490.1	489.2
175°	493.7	494.4	495.1	495.0	494.0	493.0	492.0	491.1
177.5°	494.5	495.0	495.5	495.4	494.6	493.8	493.0	492.3
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0

(END OF REPORT)