

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333022-930

Luminaire Tested: **S124RDIW-S350D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333022-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3337.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37	36	32	30	27	24	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	12
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	1.4
10°-20°	132.0	4.0
20°-30°	190.6	5.7
30°-40°	216.1	6.5
40°-50°	208.7	6.3
50°-60°	173.5	5.2
60°-70°	119.8	3.6
70°-80°	60.7	1.8
80°-90°	17.9	0.5
90°-100°	51.6	1.5
100°-110°	152.9	4.6
110°-120°	259.5	7.8
120°-130°	342.1	10.3
130°-140°	384.2	11.5
140°-150°	377.6	11.3
150°-160°	317.6	9.5
160°-170°	211.3	6.3
170°-180°	74.0	2.2
0°-30°	370.0	11.1
0°-40°	586.1	17.6
0°-60°	968.3	29.0
0°-90°	1166.8	35.0
90°-120°	463.9	13.9
90°-150°	1567.9	47.0
90°-180°	2171.0	65.0
0°-180°	3337.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	2	8	13	17	18	3
95°	36	42	46	48	48	40
105°	141	142	144	146	148	150
115°	264	264	263	262	261	260
125°	384	384	384	382	381	342
135°	496	499	499	498	496	383
145°	602	604	605	604	603	377
155°	690	690	689	691	689	317
165°	751	749	748	751	749	212
175°	781	778	778	781	778	74
180°	782	782	782	782	782	



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.5	7.2	6.9	6.7	6.4	6.4	6.5	6.7	6.8	7.0	7.1
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	13.0	14.7	16.3	18.0	19.7	21.0	21.7	22.4	23.2	24.0	24.5
95°	36.3	37.5	38.7	39.9	41.2	42.2	43.1	44.1	45.1	46.0	46.4
97.5°	63.4	64.4	65.4	66.3	67.3	68.3	69.5	70.5	71.7	72.7	73.2
100°	84.7	85.3	85.8	86.3	86.8	87.7	88.9	90.2	91.4	92.6	92.9
102.5°	107.0	107.2	107.4	107.6	107.9	108.5	109.6	110.7	111.8	112.9	113.3
105°	141.0	141.1	141.3	141.4	141.5	141.9	142.4	142.9	143.5	144.0	144.4
107.5°	176.7	176.8	177.0	177.2	177.3	177.5	177.6	177.7	177.7	177.8	178.1
110°	200.9	201.1	201.5	201.7	201.9	202.0	201.9	201.8	201.6	201.5	201.2



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.1	226.2	226.2	226.2	226.2	225.9	225.7	225.4	225.2	225.2
115°	263.8	263.8	263.8	263.8	263.8	263.7	263.4	263.2	262.9	262.6	262.4
117.5°	299.4	299.5	299.6	299.7	299.9	299.8	299.6	299.5	299.2	299.1	298.6
120°	323.1	323.7	324.2	324.7	325.3	325.3	325.0	324.6	324.2	323.8	323.0
122.5°	347.8	348.1	348.2	348.5	348.7	348.7	348.5	348.3	348.1	348.0	347.5
125°	384.3	384.3	384.3	384.3	384.3	384.2	384.0	383.9	383.8	383.6	383.4
127.5°	417.3	417.7	418.1	418.5	418.9	419.0	418.7	418.6	418.3	418.2	417.8
130°	440.5	440.9	441.3	441.7	442.1	442.3	442.3	442.3	442.3	442.3	442.1
132.5°	464.2	464.6	464.8	465.1	465.5	465.5	465.4	465.3	465.2	465.0	464.8
135°	495.6	496.4	497.2	498.0	498.8	499.2	499.2	499.2	499.2	499.2	499.0
137.5°	529.7	530.1	530.4	530.8	531.2	531.5	531.7	531.9	532.1	532.4	532.0
140°	552.4	552.7	553.0	553.3	553.5	553.7	553.7	553.7	553.7	553.7	553.5
142.5°	573.2	573.6	573.8	574.1	574.4	574.5	574.3	574.2	574.1	574.0	574.0
145°	602.1	602.6	603.2	603.7	604.2	604.5	604.7	604.9	605.0	605.1	605.0
147.5°	630.6	631.3	631.9	632.6	633.2	633.5	633.4	633.2	633.2	633.1	632.9
150°	648.1	648.6	649.1	649.7	650.2	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	664.6	664.9	665.2	665.5	665.9	666.0	666.1	666.3	666.3	666.4	666.8
155°	689.8	689.8	689.8	689.8	689.8	689.7	689.6	689.5	689.3	689.3	689.7
157.5°	711.1	710.9	710.6	710.4	710.1	710.0	710.0	710.0	710.0	709.9	710.3
160°	723.7	723.6	723.4	723.3	723.2	723.0	722.9	722.8	722.6	722.5	722.9
162.5°	735.3	735.0	734.6	734.3	733.9	733.7	733.5	733.4	733.3	733.1	733.9
165°	751.0	750.6	750.2	749.7	749.3	749.0	748.7	748.4	748.2	747.9	748.7
167.5°	762.9	762.4	761.8	761.2	760.7	760.3	760.4	760.4	760.4	760.5	761.3
170°	769.7	769.0	768.3	767.7	767.0	766.7	766.9	767.0	767.1	767.3	768.1
172.5°	774.5	774.0	773.4	772.8	772.3	772.0	772.0	772.1	772.1	772.1	773.1
175°	781.2	780.5	779.8	779.2	778.5	778.1	778.0	777.8	777.7	777.6	778.5
177.5°	783.3	782.9	782.3	781.8	781.2	781.0	781.0	781.0	781.0	781.0	781.7
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	7.2	7.3	7.3	7.5	7.6	7.7	7.8	8.0
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	24.9	25.4	25.9	26.3	26.4	26.6	26.7	26.9
95°	46.8	47.2	47.6	47.8	47.8	47.8	47.8	47.8
97.5°	73.7	74.2	74.7	74.9	74.9	74.9	74.9	74.9
100°	93.1	93.4	93.7	93.8	93.8	93.8	93.8	93.8
102.5°	113.7	114.1	114.4	114.6	114.8	114.9	115.0	115.1
105°	144.8	145.2	145.6	146.0	146.4	146.8	147.2	147.7
107.5°	178.6	178.9	179.3	179.4	179.4	179.4	179.4	179.4
110°	201.0	200.7	200.4	200.5	200.9	201.3	201.7	202.1



TEST NUMBER: P333022-930

CATALOG NUMBER: S124RDIW-S350D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.1	225.0	225.0	225.0	225.1	225.2	225.3	225.3
115°	262.4	262.2	262.0	262.0	261.8	261.7	261.5	261.4
117.5°	298.2	297.7	297.2	296.9	296.6	296.3	296.0	295.8
120°	322.4	321.7	321.1	320.8	321.1	321.4	321.6	321.9
122.5°	347.0	346.6	346.1	345.6	345.1	344.6	344.2	343.7
125°	383.1	382.9	382.5	382.3	382.0	381.7	381.5	381.2
127.5°	417.6	417.4	417.0	416.8	416.6	416.4	416.1	416.0
130°	441.8	441.5	441.2	440.8	440.3	439.8	439.2	438.7
132.5°	464.6	464.3	464.0	463.7	463.6	463.3	463.1	462.9
135°	498.6	498.4	498.1	497.8	497.4	497.0	496.6	496.2
137.5°	531.7	531.3	531.0	530.8	530.9	531.0	531.1	531.2
140°	553.4	553.3	553.1	553.0	552.9	552.7	552.6	552.4
142.5°	574.0	573.9	573.9	573.9	573.8	573.8	573.8	573.7
145°	604.9	604.7	604.5	604.3	603.9	603.5	603.1	602.7
147.5°	632.8	632.8	632.6	632.5	632.3	632.3	632.1	631.9
150°	650.5	650.5	650.5	650.4	650.3	650.1	650.0	649.9
152.5°	667.1	667.4	667.7	667.7	667.4	667.1	666.7	666.3
155°	690.3	690.8	691.4	691.4	690.8	690.3	689.7	689.3
157.5°	710.7	711.1	711.5	711.5	711.0	710.6	710.1	709.6
160°	723.3	723.7	724.1	724.0	723.3	722.6	721.9	721.3
162.5°	734.6	735.3	736.1	736.1	735.4	734.7	734.1	733.4
165°	749.5	750.3	751.1	751.3	750.7	750.2	749.7	749.1
167.5°	762.1	762.9	763.7	763.7	762.9	762.1	761.2	760.3
170°	768.9	769.7	770.5	770.5	769.5	768.6	767.6	766.7
172.5°	774.0	774.9	775.8	775.8	774.8	773.9	772.9	772.0
175°	779.4	780.4	781.3	781.3	780.4	779.4	778.5	777.6
177.5°	782.4	783.2	784.0	783.9	783.0	782.2	781.3	780.5
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4

(END OF REPORT)