

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769-840

Luminaire Tested: **S124DIW-S575D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332769-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8921.3 lumens
Efficiency: N/A
Efficacy: 147.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7657	7657	7657	7657
5°	9018	7678	6776	7678
10°	10797	7643	6101	7643
15°	12774	7565	5602	7565
20°	14225	7487	5158	7487
25°	14455	7371	4851	7371
30°	12299	7260	4754	7260
35°	9456	7078	4755	7078
40°	7371	6866	4845	6866
45°	6146	6545	4925	6545
50°	5408	6154	5093	6154
55°	4954	5685	5298	5685
60°	4644	5265	5546	5265
65°	4323	4797	5748	4797
70°	3949	4331	5880	4331
75°	3531	3812	5808	3812
80°	2957	3124	5625	3124
85°	2177	2251	5391	2251



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	1.0
10°-20°	284.8	3.2
20°-30°	451.7	5.1
30°-40°	502.6	5.6
40°-50°	457.5	5.1
50°-60°	373.9	4.2
60°-70°	266.9	3.0
70°-80°	147.0	1.6
80°-90°	46.0	0.5
90°-100°	69.6	0.8
100°-110°	444.0	5.0
110°-120°	849.4	9.5
120°-130°	1078.3	12.1
130°-140°	1153.7	12.9
140°-150°	1078.8	12.1
150°-160°	870.0	9.8
160°-170°	561.1	6.3
170°-180°	193.4	2.2
0°-30°	828.9	9.3
0°-40°	1331.5	14.9
0°-60°	2162.9	24.2
0°-90°	2622.8	29.4
90°-120°	1363.1	15.3
90°-150°	4673.9	52.4
90°-180°	6298.0	70.6
0°-180°	8921.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	948	948	948	948	948	
5°	1113	947	836	947	1113	113
15°	1528	905	670	905	1528	432
25°	1623	828	545	828	1623	715
35°	960	718	482	718	960	609
45°	538	573	431	573	538	424
55°	352	404	376	404	352	318
65°	226	251	301	251	226	224
75°	113	122	186	122	113	120
85°	24	24	58	24	24	30
90°	46	4	46	4	46	20
95°	44	84	44	84	44	35
105°	434	458	434	458	434	379
115°	862	856	862	856	862	853
125°	1212	1203	1212	1203	1212	1080
135°	1503	1492	1503	1492	1503	1157
145°	1730	1721	1730	1721	1730	1081
155°	1885	1887	1885	1887	1885	869
165°	1981	1990	1981	1990	1981	560
175°	2024	2036	2024	2036	2024	193
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	1009.5	1009.2	1006.0	1005.4	1003.2	1000.4	999.8	994.7	984.6	980.0	978.7
5°	1112.8	1120.6	1110.3	1108.4	1107.2	1094.3	1087.6	1079.7	1061.7	1051.1	1042.8
7.5°	1236.0	1236.9	1232.4	1228.8	1218.8	1207.5	1190.5	1172.5	1150.9	1128.5	1111.7
10°	1317.1	1320.2	1315.1	1314.3	1294.2	1281.7	1256.6	1235.4	1210.9	1183.9	1159.1
12.5°	1402.6	1398.2	1395.5	1378.8	1375.0	1352.1	1322.9	1301.0	1263.4	1232.2	1199.3
15°	1528.4	1519.8	1514.3	1491.2	1479.8	1447.9	1416.8	1392.9	1343.8	1297.1	1261.6
17.5°	1602.4	1610.9	1598.2	1588.7	1559.2	1536.9	1505.2	1454.9	1416.4	1358.4	1313.7
20°	1655.8	1656.6	1649.5	1639.6	1616.5	1588.2	1553.6	1498.6	1452.6	1394.8	1333.5
22.5°	1670.2	1670.4	1667.4	1658.2	1640.6	1617.7	1582.9	1536.9	1481.3	1418.5	1357.2
25°	1622.8	1621.2	1624.8	1635.0	1628.3	1621.2	1601.1	1567.0	1515.1	1448.7	1382.7
27.5°	1446.4	1457.2	1477.2	1502.4	1526.6	1545.0	1550.2	1543.3	1511.1	1456.4	1387.4
30°	1319.4	1332.8	1347.7	1372.9	1421.6	1449.5	1480.2	1503.3	1490.4	1446.7	1382.3
32.5°	1179.8	1183.2	1205.3	1234.0	1278.6	1332.2	1380.8	1427.8	1443.5	1420.7	1366.9
35°	959.5	965.0	989.0	1017.2	1071.9	1137.5	1210.6	1275.8	1329.7	1351.3	1323.7
37.5°	783.0	798.8	815.7	846.1	894.2	953.3	1029.3	1113.6	1193.9	1247.6	1256.7
40°	699.4	709.2	721.4	744.6	785.5	843.6	908.8	1005.5	1090.8	1167.8	1193.0
42.5°	633.4	639.1	646.6	667.5	698.7	756.5	816.1	901.1	986.7	1078.8	1121.0
45°	538.3	544.2	556.7	569.0	592.5	632.6	688.0	757.9	843.9	932.8	1010.6
47.5°	469.6	473.4	480.9	493.9	513.9	540.4	585.4	643.8	723.6	809.8	892.7
50°	430.6	433.7	439.7	451.5	466.8	490.4	527.3	581.9	644.4	731.2	812.5
52.5°	399.8	401.1	405.5	413.4	425.7	445.5	475.7	520.9	579.1	656.4	737.4
55°	352.0	353.7	357.6	363.5	374.1	386.7	409.8	443.6	494.3	561.5	631.8
57.5°	312.8	313.9	317.2	319.4	328.2	338.4	356.2	380.3	418.8	475.7	538.6
60°	287.6	286.8	290.7	292.8	298.6	307.3	321.0	344.2	377.6	423.5	481.3
62.5°	263.1	262.0	265.3	267.9	271.2	278.6	289.9	308.0	335.2	376.8	426.7
65°	226.3	224.8	226.7	229.8	233.0	236.9	245.2	261.3	282.9	312.8	350.8
67.5°	189.3	191.1	191.4	192.9	194.7	200.1	205.7	217.1	232.4	256.3	288.5
70°	167.3	167.7	169.4	169.4	170.6	175.2	180.0	186.6	201.6	223.6	249.9
72.5°	145.4	147.0	146.4	147.6	148.6	151.7	155.1	161.5	174.2	190.6	212.8
75°	113.2	114.3	114.3	114.7	115.9	117.0	119.9	124.5	133.6	145.7	161.1
77.5°	82.5	82.7	83.2	84.6	84.6	86.5	88.6	92.3	96.8	105.1	114.5
80°	63.6	64.4	64.0	64.8	64.8	66.4	67.2	71.9	73.8	79.4	86.8
82.5°	46.7	47.5	47.4	48.5	49.1	49.4	50.5	52.4	54.3	59.3	62.3
85°	23.5	24.3	23.5	24.3	25.5	26.0	27.1	27.5	29.1	30.3	33.0
87.5°	16.1	16.9	16.8	16.9	17.4	17.5	17.4	16.7	17.5	17.4	18.1
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4	34.3	32.3	29.6
95°	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6	35.5	33.5	33.1
97.5°	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6	40.4	40.2	78.0
100°	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5	61.3	67.1	113.7
102.5°	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7	260.7	322.9	328.9
105°	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2	478.2	475.1	473.4
107.5°	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4	593.9	592.4	590.1
110°	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0	672.3	671.6	669.5



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1	748.2	748.4	747.4
115°	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3	859.6	858.9	859.3
117.5°	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2	973.3	973.4	972.7
120°	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7	1042.0
122.5°	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0	1111.6	1111.2	1110.6
125°	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2	1207.2	1206.2	1206.8
127.5°	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8	1304.0	1304.2	1302.6
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2	1361.8	1361.5	1360.5
132.5°	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5	1419.1	1418.8	1417.4
135°	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3	1497.7	1497.0	1495.7
137.5°	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1	1573.3	1572.6	1571.0
140°	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9	1619.9	1618.8	1618.2
142.5°	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3	1663.4	1662.7	1662.3
145°	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2	1725.8	1725.5	1725.5
147.5°	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5	1780.3	1780.0	1780.3
150°	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3	1815.3	1815.3	1815.6
152.5°	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6	1845.1	1844.5	1845.1
155°	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5	1885.2	1883.8	1884.9
157.5°	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2	1919.5
160°	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2	1940.6
162.5°	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6	1960.5	1958.4	1958.8
165°	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2	1985.5	1982.9	1982.9
167.5°	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1	2004.1	2001.1	2001.4
170°	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7	2016.0	2013.3	2013.0
172.5°	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0	2023.3	2020.6	2020.2
175°	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6	2031.5	2028.5	2028.2
177.5°	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0	2035.9	2033.7	2033.2
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	979.0	974.6	971.5	969.0	962.0	958.0	954.8	950.4	945.3	940.0	933.4
5°	1034.6	1021.2	1011.4	996.4	982.3	970.5	958.4	947.4	933.9	919.5	908.8
7.5°	1093.0	1073.1	1047.6	1025.5	1000.7	979.1	959.8	940.0	919.4	899.4	881.1
10°	1130.0	1104.5	1076.2	1042.8	1011.4	983.5	957.6	932.4	908.1	883.6	862.8
12.5°	1169.9	1138.1	1096.3	1057.2	1022.1	984.7	953.4	922.6	893.2	867.7	843.3
15°	1223.6	1177.6	1129.2	1077.0	1030.7	987.0	944.2	905.2	872.3	838.5	815.0
17.5°	1256.5	1199.6	1144.4	1089.7	1033.6	978.6	932.4	887.6	846.2	812.6	782.9
20°	1278.2	1221.6	1152.9	1098.2	1031.4	974.8	921.4	871.5	828.3	792.5	761.8
22.5°	1297.1	1231.6	1162.9	1091.0	1024.5	964.4	905.9	855.8	811.6	774.0	744.6
25°	1307.3	1232.2	1157.5	1086.0	1010.6	939.5	886.5	827.5	780.3	740.6	709.2
27.5°	1308.4	1228.1	1143.7	1064.2	986.3	920.1	853.1	800.4	751.5	709.5	679.3
30°	1304.8	1221.2	1130.4	1044.4	966.2	894.2	836.2	778.8	728.8	687.2	655.8
32.5°	1293.8	1206.7	1113.5	1022.4	941.4	871.0	811.0	756.5	707.8	666.8	633.8
35°	1262.0	1176.0	1076.6	981.9	899.0	827.9	773.7	718.2	669.5	630.7	598.8
37.5°	1212.3	1134.5	1033.5	935.4	854.0	782.6	728.8	678.8	634.9	595.3	562.7
40°	1168.9	1100.6	999.2	903.7	815.7	747.7	697.4	651.5	607.8	570.5	539.5
42.5°	1118.9	1059.3	965.8	864.7	779.8	711.6	662.6	621.3	580.2	545.7	514.6
45°	1029.9	990.6	902.5	809.0	720.6	656.2	609.5	573.3	538.7	504.9	479.0
47.5°	927.4	907.9	833.7	745.0	661.1	597.5	557.0	523.6	493.3	464.6	441.8
50°	858.5	849.1	785.1	699.4	619.2	559.6	518.7	490.0	464.0	438.9	417.3
52.5°	790.6	790.3	732.6	654.1	580.0	522.4	481.9	455.0	432.6	412.1	392.7
55°	686.8	697.8	652.7	582.7	516.3	464.4	427.9	403.9	388.2	371.3	356.8
57.5°	591.5	609.8	572.5	510.9	455.4	407.7	375.9	357.9	341.1	330.9	320.3
60°	529.3	546.5	517.5	465.6	413.3	372.4	342.2	326.1	311.5	304.5	297.0
62.5°	473.9	489.4	467.8	419.7	374.4	335.1	309.5	294.1	284.3	276.5	271.6
65°	394.9	407.9	389.4	354.5	315.5	284.1	263.3	251.1	241.7	238.5	233.0
67.5°	319.2	331.0	321.0	291.3	260.1	236.3	220.0	208.3	202.8	200.0	196.1
70°	274.3	286.1	275.4	249.5	225.5	205.5	190.2	183.5	177.6	176.4	171.0
72.5°	236.2	244.3	233.6	213.4	192.9	175.9	164.1	157.1	154.0	151.9	149.0
75°	177.2	184.3	177.2	161.5	146.9	135.1	124.9	122.2	118.7	117.4	115.5
77.5°	125.4	131.6	126.1	116.3	105.4	96.3	90.9	87.4	86.5	84.5	85.4
80°	95.8	99.8	94.7	88.1	79.4	73.1	69.2	67.2	64.8	64.0	65.6
82.5°	68.9	70.6	68.0	63.5	57.1	52.9	50.3	48.0	47.6	47.7	47.7
85°	35.7	35.3	34.9	31.0	29.1	26.4	24.7	24.3	23.9	24.7	25.5
87.5°	17.6	17.4	16.5	14.5	12.9	11.2	10.1	9.1	10.1	11.2	12.2
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2	19.4	19.6	19.8
95°	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7	72.2	60.8	49.3
97.5°	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8	185.0	192.2	199.4
100°	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7	255.9	262.0	268.0
102.5°	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1	334.7	339.1	343.6
105°	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4	460.4	462.4	464.5
107.5°	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4	578.6	579.6	580.6
110°	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9	658.9	659.9	661.0



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9	737.7	739.5	741.3
115°	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9	856.9	857.9	858.9
117.5°	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0	965.3	966.7	968.1
120°	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1	1038.4	1039.9	1041.2
122.5°	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3	1106.1	1106.9	1107.7
125°	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2	1204.5	1205.8	1207.2
127.5°	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7	1296.1	1296.4	1296.7
130°	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4	1355.7	1356.0	1356.5
132.5°	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2	1410.8	1411.5	1412.1
135°	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5	1492.1	1491.8	1491.5
137.5°	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3	1565.4	1565.5	1565.7
140°	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8	1613.5	1614.2	1614.8
142.5°	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4	1656.6	1657.9	1659.1
145°	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9	1721.9	1722.9	1723.9
147.5°	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0	1774.8	1776.8	1778.7
150°	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8	1812.1	1813.4	1814.8
152.5°	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4	1843.5	1844.6	1845.6
155°	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9	1887.2	1887.5	1887.9
157.5°	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4	1924.2	1924.0	1923.8
160°	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3	1945.3	1944.3	1943.3
162.5°	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8	1964.5	1963.2	1962.0
165°	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4	1988.7	1987.1	1985.4
167.5°	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9	2008.2	2006.4	2004.7
170°	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9	2018.9	2016.8	2014.8
172.5°	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2	2026.2	2024.2	2022.2
175°	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1	2034.1	2032.1	2030.0
177.5°	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8	2037.9	2036.0	2034.1
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	930.3	927.5	923.3	917.7	913.0	908.0	906.7	904.8	908.6	905.4	904.5
5°	899.8	891.5	880.9	868.8	861.7	851.4	849.5	845.6	841.6	841.2	837.3
7.5°	867.5	855.4	841.5	829.1	817.6	806.5	799.1	797.6	791.7	788.4	784.5
10°	846.8	831.8	815.7	804.0	790.5	778.8	770.5	765.8	761.8	757.5	753.7
12.5°	822.2	806.4	793.0	780.3	764.5	755.5	741.9	733.8	733.0	733.1	722.9
15°	793.7	778.0	757.5	739.5	730.8	713.6	706.1	696.6	690.7	684.9	680.1
17.5°	761.1	741.5	725.6	704.8	688.3	674.6	664.7	659.0	650.3	641.9	635.8
20°	740.6	719.8	703.0	681.0	662.9	646.0	637.7	629.9	623.2	616.1	609.5
22.5°	719.9	698.1	677.5	656.1	639.2	621.5	613.5	602.8	596.4	592.5	585.8
25°	687.2	663.7	640.1	619.7	602.4	586.6	576.0	567.7	560.7	557.5	553.2
27.5°	651.7	628.2	605.5	582.3	562.7	551.3	542.8	536.5	532.5	528.4	526.3
30°	629.0	604.7	580.4	558.8	540.7	529.3	521.4	517.1	513.9	512.0	510.0
32.5°	606.1	582.1	556.4	536.7	520.6	510.4	504.4	500.1	498.6	497.9	497.2
35°	569.4	545.0	521.4	503.7	488.4	484.4	479.4	477.0	476.3	479.0	480.2
37.5°	533.7	511.1	489.4	472.3	462.2	456.5	454.7	454.8	457.7	460.1	462.9
40°	510.8	488.8	468.4	453.4	444.0	440.5	439.7	441.6	444.7	447.6	450.7
42.5°	488.5	466.8	448.3	434.2	427.7	424.4	425.0	426.9	431.3	434.6	439.4
45°	453.8	435.8	417.7	406.3	400.8	401.5	401.5	405.1	409.4	414.5	419.6
47.5°	421.2	402.9	388.1	378.5	375.7	375.0	377.2	381.8	388.1	394.4	401.5
50°	399.2	381.9	368.9	360.3	357.2	358.3	361.5	365.8	373.2	381.1	388.6
52.5°	376.9	361.1	349.1	341.1	338.9	341.0	344.2	351.0	357.6	366.1	375.1
55°	342.2	328.9	319.4	313.6	312.8	314.0	317.5	325.0	334.4	345.0	353.7
57.5°	307.7	296.6	287.9	283.9	284.3	285.4	291.1	300.0	310.1	321.4	332.5
60°	284.5	274.3	267.2	264.1	264.5	266.8	273.9	282.2	294.7	305.7	317.5
62.5°	262.5	253.5	246.7	243.9	243.4	248.5	255.3	263.9	276.5	288.7	301.4
65°	227.1	220.0	214.5	213.0	214.1	218.0	226.7	238.1	248.7	261.7	275.1
67.5°	192.5	186.7	183.0	183.7	185.1	190.9	198.1	207.9	219.9	233.4	246.6
70°	170.6	165.0	161.9	162.3	164.6	171.7	178.0	187.8	200.8	214.5	225.5
72.5°	147.9	144.3	141.5	143.1	145.4	150.4	158.1	168.0	179.5	192.2	203.9
75°	113.5	113.5	112.0	113.2	116.7	121.4	127.3	137.5	149.0	159.2	168.5
77.5°	84.2	83.4	84.4	85.8	87.9	93.4	100.2	107.6	116.0	126.3	134.1
80°	64.4	64.8	66.8	69.2	70.0	74.2	81.3	88.1	94.7	103.3	110.8
82.5°	48.4	48.8	49.8	52.8	53.6	58.3	62.8	69.5	75.5	81.3	87.6
85°	26.4	26.4	28.3	29.5	31.4	34.5	37.4	41.3	46.8	50.7	56.6
87.5°	13.9	14.6	16.4	17.6	19.1	21.2	22.2	26.1	27.8	29.7	32.8
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4	38.4	40.4	41.5
95°	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6	39.6	41.6	42.8
97.5°	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6	40.8	41.0	41.3
100°	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5	49.8	44.0	41.3
102.5°	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7	136.6	74.6	43.6
105°	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2	484.3	487.4	482.7
107.5°	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4	596.9	598.3	599.8
110°	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0	673.7	674.3	675.2



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1	747.9	747.8	748.4
115°	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3	860.9	861.6	862.0
117.5°	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2	973.0	972.9	972.8
120°	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4
122.5°	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0	1112.4	1112.8	1112.6
125°	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2	1209.2	1210.2	1210.9
127.5°	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8	1303.6	1303.4	1303.1
130°	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2	1362.5	1362.8	1363.0
132.5°	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5	1419.8	1420.1	1420.2
135°	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3	1499.0	1499.8	1500.5
137.5°	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1	1574.8	1575.6	1575.8
140°	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9	1621.9	1623.0	1623.6
142.5°	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3	1665.0	1665.7	1666.1
145°	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2	1726.5	1726.8	1727.4
147.5°	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5	1780.8	1781.1	1781.4
150°	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3	1815.3	1815.3	1815.5
152.5°	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6	1846.1	1846.7	1846.8
155°	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5	1887.9	1889.3	1889.5
157.5°	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3
160°	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3
162.5°	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6	1964.6	1966.6	1966.4
165°	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2	1990.9	1993.7	1993.5
167.5°	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1	2010.0	2013.1	2012.9
170°	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7	2021.4	2024.2	2023.8
172.5°	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0	2028.7	2031.4	2030.9
175°	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6	2037.7	2040.7	2040.2
177.5°	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0	2040.2	2042.4	2041.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	903.8	903.2	901.0	900.7	901.0	903.2	903.8	904.5	905.4	908.6	904.8
5°	835.0	833.0	831.8	836.2	831.8	833.0	835.0	837.3	841.2	841.6	845.6
7.5°	783.0	781.4	778.0	776.9	778.0	781.4	783.0	784.5	788.4	791.7	797.6
10°	749.7	748.1	745.0	744.2	745.0	748.1	749.7	753.7	757.5	761.8	765.8
12.5°	717.6	714.5	713.9	714.7	713.9	714.5	717.6	722.9	733.1	733.0	733.8
15°	675.0	673.5	669.1	670.3	669.1	673.5	675.0	680.1	684.9	690.7	696.6
17.5°	633.1	631.2	625.9	630.6	625.9	631.2	633.1	635.8	641.9	650.3	659.0
20°	606.6	603.5	600.8	600.4	600.8	603.5	606.6	609.5	616.1	623.2	629.9
22.5°	581.5	578.7	578.5	575.8	578.5	578.7	581.5	585.8	592.5	596.4	602.8
25°	550.1	547.3	546.5	544.6	546.5	547.3	550.1	553.2	557.5	560.7	567.7
27.5°	525.9	524.6	523.2	523.8	523.2	524.6	525.9	526.3	528.4	532.5	536.5
30°	511.2	510.8	510.0	510.0	510.0	510.8	511.2	510.0	512.0	513.9	517.1
32.5°	499.0	498.9	499.3	499.3	499.3	498.9	499.0	497.2	497.9	498.6	500.1
35°	481.7	482.9	483.7	482.5	483.7	482.9	481.7	480.2	479.0	476.3	477.0
37.5°	466.2	467.4	468.5	469.8	468.5	467.4	466.2	462.9	460.1	457.7	454.8
40°	454.2	457.0	457.8	459.7	457.8	457.0	454.2	450.7	447.6	444.7	441.6
42.5°	442.9	446.0	448.0	448.4	448.0	446.0	442.9	439.4	434.6	431.3	426.9
45°	425.6	428.7	431.4	431.4	431.4	428.7	425.6	419.6	414.5	409.4	405.1
47.5°	407.6	412.1	414.9	415.6	414.9	412.1	407.6	401.5	394.4	388.1	381.8
50°	395.3	400.8	403.5	405.5	403.5	400.8	395.3	388.6	381.1	373.2	365.8
52.5°	383.3	388.8	392.5	393.5	392.5	388.8	383.3	375.1	366.1	357.6	351.0
55°	362.6	370.5	374.9	376.4	374.9	370.5	362.6	353.7	345.0	334.4	325.0
57.5°	343.2	350.4	355.5	356.6	355.5	350.4	343.2	332.5	321.4	310.1	300.0
60°	328.1	336.0	342.2	343.5	342.2	336.0	328.1	317.5	305.7	294.7	282.2
62.5°	312.7	320.8	326.5	329.6	326.5	320.8	312.7	301.4	288.7	276.5	263.9
65°	286.1	294.3	299.8	300.9	299.8	294.3	286.1	275.1	261.7	248.7	238.1
67.5°	257.0	265.2	268.8	271.1	268.8	265.2	257.0	246.6	233.4	219.9	207.9
70°	236.5	243.2	247.1	249.1	247.1	243.2	236.5	225.5	214.5	200.8	187.8
72.5°	213.3	220.3	224.8	225.2	224.8	220.3	213.3	203.9	192.2	179.5	168.0
75°	177.6	183.9	186.2	186.2	186.2	183.9	177.6	168.5	159.2	149.0	137.5
77.5°	140.6	143.8	146.8	147.4	146.8	143.8	140.6	134.1	126.3	116.0	107.6
80°	116.7	118.7	121.0	121.0	121.0	118.7	116.7	110.8	103.3	94.7	88.1
82.5°	92.2	93.8	96.1	95.8	96.1	93.8	92.2	87.6	81.3	75.5	69.5
85°	55.7	59.4	59.0	58.2	59.0	59.4	55.7	56.6	50.7	46.8	41.3
87.5°	33.8	34.3	35.4	36.2	35.4	34.3	33.8	32.8	29.7	27.8	26.1
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	41.6	41.8	41.9	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4
95°	43.1	43.5	43.8	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6
97.5°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6
100°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5
102.5°	43.6	43.7	43.8	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7
105°	470.6	458.4	446.3	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2
107.5°	601.1	602.3	603.6	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4
110°	676.2	677.2	678.2	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	749.7	750.9	752.2	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1
115°	862.0	862.0	862.0	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3
117.5°	972.6	972.5	972.4	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2
120°	1043.7	1043.0	1042.4	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0
122.5°	1112.0	1111.3	1110.5	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0
125°	1211.2	1211.5	1211.9	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2
127.5°	1302.9	1302.6	1302.3	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2
132.5°	1419.9	1419.6	1419.4	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5
135°	1501.1	1501.8	1502.5	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3
137.5°	1575.6	1575.4	1575.2	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1
140°	1624.0	1624.3	1624.6	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9
142.5°	1666.2	1666.3	1666.3	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3
145°	1728.0	1728.7	1729.4	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2
147.5°	1781.7	1782.0	1782.4	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5
150°	1815.8	1816.1	1816.5	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3
152.5°	1846.6	1846.4	1846.2	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6
155°	1888.4	1887.4	1886.4	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5
157.5°	1923.6	1921.8	1920.1	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8
160°	1946.3	1944.3	1942.3	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3
162.5°	1964.2	1961.9	1959.5	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6
165°	1990.4	1987.4	1984.4	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2
167.5°	2009.4	2006.1	2002.7	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1
170°	2020.4	2017.0	2013.7	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7
172.5°	2027.3	2023.7	2020.0	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0
175°	2036.1	2032.1	2028.0	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6
177.5°	2038.6	2035.3	2032.1	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	906.7	908.0	913.0	917.7	923.3	927.5	930.3	933.4	940.0	945.3	950.4
5°	849.5	851.4	861.7	868.8	880.9	891.5	899.8	908.8	919.5	933.9	947.4
7.5°	799.1	806.5	817.6	829.1	841.5	855.4	867.5	881.1	899.4	919.4	940.0
10°	770.5	778.8	790.5	804.0	815.7	831.8	846.8	862.8	883.6	908.1	932.4
12.5°	741.9	755.5	764.5	780.3	793.0	806.4	822.2	843.3	867.7	893.2	922.6
15°	706.1	713.6	730.8	739.5	757.5	778.0	793.7	815.0	838.5	872.3	905.2
17.5°	664.7	674.6	688.3	704.8	725.6	741.5	761.1	782.9	812.6	846.2	887.6
20°	637.7	646.0	662.9	681.0	703.0	719.8	740.6	761.8	792.5	828.3	871.5
22.5°	613.5	621.5	639.2	656.1	677.5	698.1	719.9	744.6	774.0	811.6	855.8
25°	576.0	586.6	602.4	619.7	640.1	663.7	687.2	709.2	740.6	780.3	827.5
27.5°	542.8	551.3	562.7	582.3	605.5	628.2	651.7	679.3	709.5	751.5	800.4
30°	521.4	529.3	540.7	558.8	580.4	604.7	629.0	655.8	687.2	728.8	778.8
32.5°	504.4	510.4	520.6	536.7	556.4	582.1	606.1	633.8	666.8	707.8	756.5
35°	479.4	484.4	488.4	503.7	521.4	545.0	569.4	598.8	630.7	669.5	718.2
37.5°	454.7	456.5	462.2	472.3	489.4	511.1	533.7	562.7	595.3	634.9	678.8
40°	439.7	440.5	444.0	453.4	468.4	488.8	510.8	539.5	570.5	607.8	651.5
42.5°	425.0	424.4	427.7	434.2	448.3	466.8	488.5	514.6	545.7	580.2	621.3
45°	401.5	401.5	400.8	406.3	417.7	435.8	453.8	479.0	504.9	538.7	573.3
47.5°	377.2	375.0	375.7	378.5	388.1	402.9	421.2	441.8	464.6	493.3	523.6
50°	361.5	358.3	357.2	360.3	368.9	381.9	399.2	417.3	438.9	464.0	490.0
52.5°	344.2	341.0	338.9	341.1	349.1	361.1	376.9	392.7	412.1	432.6	455.0
55°	317.5	314.0	312.8	313.6	319.4	328.9	342.2	356.8	371.3	388.2	403.9
57.5°	291.1	285.4	284.3	283.9	287.9	296.6	307.7	320.3	330.9	341.1	357.9
60°	273.9	266.8	264.5	264.1	267.2	274.3	284.5	297.0	304.5	311.5	326.1
62.5°	255.3	248.5	243.4	243.9	246.7	253.5	262.5	271.6	276.5	284.3	294.1
65°	226.7	218.0	214.1	213.0	214.5	220.0	227.1	233.0	238.5	241.7	251.1
67.5°	198.1	190.9	185.1	183.7	183.0	186.7	192.5	196.1	200.0	202.8	208.3
70°	178.0	171.7	164.6	162.3	161.9	165.0	170.6	171.0	176.4	177.6	183.5
72.5°	158.1	150.4	145.4	143.1	141.5	144.3	147.9	149.0	151.9	154.0	157.1
75°	127.3	121.4	116.7	113.2	112.0	113.5	113.5	115.5	117.4	118.7	122.2
77.5°	100.2	93.4	87.9	85.8	84.4	83.4	84.2	85.4	84.5	86.5	87.4
80°	81.3	74.2	70.0	69.2	66.8	64.8	64.4	65.6	64.0	64.8	67.2
82.5°	62.8	58.3	53.6	52.8	49.8	48.8	48.4	47.7	47.7	47.6	48.0
85°	37.4	34.5	31.4	29.5	28.3	26.4	26.4	25.5	24.7	23.9	24.3
87.5°	22.2	21.2	19.1	17.6	16.4	14.6	13.9	12.2	11.2	10.1	9.1
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	34.3	32.3	29.6	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2
95°	35.5	33.5	33.1	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7
97.5°	40.4	40.2	78.0	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8
100°	61.3	67.1	113.7	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7
102.5°	260.7	322.9	328.9	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1
105°	478.2	475.1	473.4	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4
107.5°	593.9	592.4	590.1	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4
110°	672.3	671.6	669.5	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	748.2	748.4	747.4	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9
115°	859.6	858.9	859.3	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9
117.5°	973.3	973.4	972.7	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0
120°	1042.4	1041.7	1042.0	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1
122.5°	1111.6	1111.2	1110.6	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3
125°	1207.2	1206.2	1206.8	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2
127.5°	1304.0	1304.2	1302.6	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7
130°	1361.8	1361.5	1360.5	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4
132.5°	1419.1	1418.8	1417.4	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2
135°	1497.7	1497.0	1495.7	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5
137.5°	1573.3	1572.6	1571.0	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3
140°	1619.9	1618.8	1618.2	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8
142.5°	1663.4	1662.7	1662.3	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4
145°	1725.8	1725.5	1725.5	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9
147.5°	1780.3	1780.0	1780.3	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0
150°	1815.3	1815.3	1815.6	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8
152.5°	1845.1	1844.5	1845.1	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4
155°	1885.2	1883.8	1884.9	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9
157.5°	1920.1	1918.2	1919.5	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4
160°	1942.3	1940.2	1940.6	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3
162.5°	1960.5	1958.4	1958.8	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8
165°	1985.5	1982.9	1982.9	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4
167.5°	2004.1	2001.1	2001.4	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9
170°	2016.0	2013.3	2013.0	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9
172.5°	2023.3	2020.6	2020.2	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2
175°	2031.5	2028.5	2028.2	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1
177.5°	2035.9	2033.7	2033.2	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	954.8	958.0	962.0	969.0	971.5	974.6	979.0	978.7	980.0	984.6	994.7
5°	958.4	970.5	982.3	996.4	1011.4	1021.2	1034.6	1042.8	1051.1	1061.7	1079.7
7.5°	959.8	979.1	1000.7	1025.5	1047.6	1073.1	1093.0	1111.7	1128.5	1150.9	1172.5
10°	957.6	983.5	1011.4	1042.8	1076.2	1104.5	1130.0	1159.1	1183.9	1210.9	1235.4
12.5°	953.4	984.7	1022.1	1057.2	1096.3	1138.1	1169.9	1199.3	1232.2	1263.4	1301.0
15°	944.2	987.0	1030.7	1077.0	1129.2	1177.6	1223.6	1261.6	1297.1	1343.8	1392.9
17.5°	932.4	978.6	1033.6	1089.7	1144.4	1199.6	1256.5	1313.7	1358.4	1416.4	1454.9
20°	921.4	974.8	1031.4	1098.2	1152.9	1221.6	1278.2	1333.5	1394.8	1452.6	1498.6
22.5°	905.9	964.4	1024.5	1091.0	1162.9	1231.6	1297.1	1357.2	1418.5	1481.3	1536.9
25°	886.5	939.5	1010.6	1086.0	1157.5	1232.2	1307.3	1382.7	1448.7	1515.1	1567.0
27.5°	853.1	920.1	986.3	1064.2	1143.7	1228.1	1308.4	1387.4	1456.4	1511.1	1543.3
30°	836.2	894.2	966.2	1044.4	1130.4	1221.2	1304.8	1382.3	1446.7	1490.4	1503.3
32.5°	811.0	871.0	941.4	1022.4	1113.5	1206.7	1293.8	1366.9	1420.7	1443.5	1427.8
35°	773.7	827.9	899.0	981.9	1076.6	1176.0	1262.0	1323.7	1351.3	1329.7	1275.8
37.5°	728.8	782.6	854.0	935.4	1033.5	1134.5	1212.3	1256.7	1247.6	1193.9	1113.6
40°	697.4	747.7	815.7	903.7	999.2	1100.6	1168.9	1193.0	1167.8	1090.8	1005.5
42.5°	662.6	711.6	779.8	864.7	965.8	1059.3	1118.9	1121.0	1078.8	986.7	901.1
45°	609.5	656.2	720.6	809.0	902.5	990.6	1029.9	1010.6	932.8	843.9	757.9
47.5°	557.0	597.5	661.1	745.0	833.7	907.9	927.4	892.7	809.8	723.6	643.8
50°	518.7	559.6	619.2	699.4	785.1	849.1	858.5	812.5	731.2	644.4	581.9
52.5°	481.9	522.4	580.0	654.1	732.6	790.3	790.6	737.4	656.4	579.1	520.9
55°	427.9	464.4	516.3	582.7	652.7	697.8	686.8	631.8	561.5	494.3	443.6
57.5°	375.9	407.7	455.4	510.9	572.5	609.8	591.5	538.6	475.7	418.8	380.3
60°	342.2	372.4	413.3	465.6	517.5	546.5	529.3	481.3	423.5	377.6	344.2
62.5°	309.5	335.1	374.4	419.7	467.8	489.4	473.9	426.7	376.8	335.2	308.0
65°	263.3	284.1	315.5	354.5	389.4	407.9	394.9	350.8	312.8	282.9	261.3
67.5°	220.0	236.3	260.1	291.3	321.0	331.0	319.2	288.5	256.3	232.4	217.1
70°	190.2	205.5	225.5	249.5	275.4	286.1	274.3	249.9	223.6	201.6	186.6
72.5°	164.1	175.9	192.9	213.4	233.6	244.3	236.2	212.8	190.6	174.2	161.5
75°	124.9	135.1	146.9	161.5	177.2	184.3	177.2	161.1	145.7	133.6	124.5
77.5°	90.9	96.3	105.4	116.3	126.1	131.6	125.4	114.5	105.1	96.8	92.3
80°	69.2	73.1	79.4	88.1	94.7	99.8	95.8	86.8	79.4	73.8	71.9
82.5°	50.3	52.9	57.1	63.5	68.0	70.6	68.9	62.3	59.3	54.3	52.4
85°	24.7	26.4	29.1	31.0	34.9	35.3	35.7	33.0	30.3	29.1	27.5
87.5°	10.1	11.2	12.9	14.5	16.5	17.4	17.6	18.1	17.4	17.5	16.7
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4
95°	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6
97.5°	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6
100°	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5
102.5°	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7
105°	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2
107.5°	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4
110°	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1
115°	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3
117.5°	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2
120°	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0
122.5°	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0
125°	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2
127.5°	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8
130°	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2
132.5°	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5
135°	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3
137.5°	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1
140°	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9
142.5°	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3
145°	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2
147.5°	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5
150°	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3
152.5°	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6
155°	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5
157.5°	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8
160°	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3
162.5°	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6
165°	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2
167.5°	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1
170°	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7
172.5°	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0
175°	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6
177.5°	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	999.8	1000.4	1003.2	1005.4	1006.0	1009.2	1009.5
5°	1087.6	1094.3	1107.2	1108.4	1110.3	1120.6	1112.8
7.5°	1190.5	1207.5	1218.8	1228.8	1232.4	1236.9	1236.0
10°	1256.6	1281.7	1294.2	1314.3	1315.1	1320.2	1317.1
12.5°	1322.9	1352.1	1375.0	1378.8	1395.5	1398.2	1402.6
15°	1416.8	1447.9	1479.8	1491.2	1514.3	1519.8	1528.4
17.5°	1505.2	1536.9	1559.2	1588.7	1598.2	1610.9	1602.4
20°	1553.6	1588.2	1616.5	1639.6	1649.5	1656.6	1655.8
22.5°	1582.9	1617.7	1640.6	1658.2	1667.4	1670.4	1670.2
25°	1601.1	1621.2	1628.3	1635.0	1624.8	1621.2	1622.8
27.5°	1550.2	1545.0	1526.6	1502.4	1477.2	1457.2	1446.4
30°	1480.2	1449.5	1421.6	1372.9	1347.7	1332.8	1319.4
32.5°	1380.8	1332.2	1278.6	1234.0	1205.3	1183.2	1179.8
35°	1210.6	1137.5	1071.9	1017.2	989.0	965.0	959.5
37.5°	1029.3	953.3	894.2	846.1	815.7	798.8	783.0
40°	908.8	843.6	785.5	744.6	721.4	709.2	699.4
42.5°	816.1	756.5	698.7	667.5	646.6	639.1	633.4
45°	688.0	632.6	592.5	569.0	556.7	544.2	538.3
47.5°	585.4	540.4	513.9	493.9	480.9	473.4	469.6
50°	527.3	490.4	466.8	451.5	439.7	433.7	430.6
52.5°	475.7	445.5	425.7	413.4	405.5	401.1	399.8
55°	409.8	386.7	374.1	363.5	357.6	353.7	352.0
57.5°	356.2	338.4	328.2	319.4	317.2	313.9	312.8
60°	321.0	307.3	298.6	292.8	290.7	286.8	287.6
62.5°	289.9	278.6	271.2	267.9	265.3	262.0	263.1
65°	245.2	236.9	233.0	229.8	226.7	224.8	226.3
67.5°	205.7	200.1	194.7	192.9	191.4	191.1	189.3
70°	180.0	175.2	170.6	169.4	169.4	167.7	167.3
72.5°	155.1	151.7	148.6	147.6	146.4	147.0	145.4
75°	119.9	117.0	115.9	114.7	114.3	114.3	113.2
77.5°	88.6	86.5	84.6	84.6	83.2	82.7	82.5
80°	67.2	66.4	64.8	64.8	64.0	64.4	63.6
82.5°	50.5	49.4	49.1	48.5	47.4	47.5	46.7
85°	27.1	26.0	25.5	24.3	23.5	24.3	23.5
87.5°	17.4	17.5	17.4	16.9	16.8	16.9	16.1
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P332769-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)