

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332773-840

Luminaire Tested: **S124DIW-S575D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332773-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8821.0 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	20	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	1.0
10°-20°	260.2	3.0
20°-30°	383.0	4.3
30°-40°	445.3	5.0
40°-50°	445.3	5.0
50°-60°	389.5	4.4
60°-70°	289.3	3.3
70°-80°	164.3	1.9
80°-90°	53.3	0.6
90°-100°	69.6	0.8
100°-110°	444.0	5.0
110°-120°	849.4	9.6
120°-130°	1078.3	12.2
130°-140°	1153.7	13.1
140°-150°	1078.8	12.2
150°-160°	870.0	9.9
160°-170°	561.1	6.4
170°-180°	193.4	2.2
0°-30°	735.6	8.3
0°-40°	1180.9	13.4
0°-60°	2015.7	22.9
0°-90°	2522.6	28.6
90°-120°	1363.1	15.5
90°-150°	4673.9	53.0
90°-180°	6298.0	71.4
0°-180°	8821.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	4	21	34	42	46	6
95°	84	35	34	42	44	108
105°	458	468	475	485	434	480
115°	856	860	859	862	862	842
125°	1203	1209	1206	1211	1212	1074
135°	1492	1491	1497	1500	1503	1149
145°	1721	1725	1726	1727	1730	1075
155°	1887	1888	1884	1889	1885	870
165°	1990	1983	1983	1994	1981	562
175°	2036	2028	2028	2040	2024	194
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	17.3	17.9	18.5	19.1	19.7	20.2	20.6	21.0	21.4	21.8	22.2
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	19.2	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3
95°	83.7	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5
97.5°	177.8	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4
100°	249.7	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3
102.5°	330.1	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7
105°	458.4	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2
107.5°	577.4	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9
110°	657.9	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	735.9	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2
115°	855.9	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6
117.5°	964.0	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3
120°	1037.1	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4
122.5°	1105.3	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6
125°	1203.2	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2
127.5°	1295.7	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0
130°	1355.4	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8
132.5°	1410.2	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1
135°	1492.5	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7
137.5°	1565.3	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3
140°	1612.8	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9
142.5°	1655.4	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4
145°	1720.9	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8
147.5°	1773.0	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3
150°	1810.8	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3
152.5°	1842.4	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1
155°	1886.9	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2
157.5°	1924.4	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1
160°	1946.3	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3
162.5°	1965.8	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5
165°	1990.4	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5
167.5°	2009.9	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1
170°	2020.9	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0
172.5°	2028.2	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3
175°	2036.1	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5
177.5°	2039.8	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	22.6	23.0	23.4	23.7	23.8	23.9	24.1	24.2
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	36.4	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	37.6	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.6	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	55.5	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	198.7	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	481.2	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	595.4	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.0	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P332773-840

CATALOG NUMBER: S124DIW-S575D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.1	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.3	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.2	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.0	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1208.2	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.8	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.2	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.5	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1498.3	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.1	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1620.9	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1664.3	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.2	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.5	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1845.6	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1886.5	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1962.6	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1988.2	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2007.1	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2018.7	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2026.0	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2034.6	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2038.0	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)