

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332749-840

Luminaire Tested: **S124DIW-S575D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332749-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D470U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4411.3 lumens  
Efficiency: N/A  
Efficacy: 146.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	59	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7917	7917	7917
5°	7942	7846	7903
10°	7891	7782	7820
15°	7796	7672	7691
20°	7669	7534	7541
25°	7525	7378	7357
30°	7347	7194	7127
35°	7164	7001	6908
40°	6973	6783	6658
45°	6774	6567	6441
50°	6553	6376	6178
55°	6315	6128	5928
60°	6077	5848	5670
65°	5809	5585	5358
70°	5509	5231	5028
75°	5050	4803	4682
80°	4491	4310	4203
85°	3927	3788	3714



TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.4	2.1
10°-20°	260.2	5.9
20°-30°	383.0	8.7
30°-40°	445.3	10.1
40°-50°	445.3	10.1
50°-60°	389.5	8.8
60°-70°	289.3	6.6
70°-80°	164.3	3.7
80°-90°	49.2	1.1
90°-100°	20.9	0.5
100°-110°	133.4	3.0
110°-120°	255.3	5.8
120°-130°	324.0	7.3
130°-140°	346.7	7.9
140°-150°	324.2	7.3
150°-160°	261.4	5.9
160°-170°	168.6	3.8
170°-180°	58.1	1.3
0°-30°	735.6	16.7
0°-40°	1180.9	26.8
0°-60°	2015.7	45.7
0°-90°	2518.5	57.1
90°-120°	409.6	9.3
90°-150°	1404.6	31.8
90°-180°	1893.0	42.9
0°-180°	4411.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	980	976	968	976	975	93
15°	933	929	918	922	920	263
25°	845	839	828	829	826	388
35°	727	721	710	705	701	454
45°	593	587	575	567	564	457
55°	449	446	435	426	421	402
65°	304	300	292	285	280	301
75°	162	158	154	151	150	172
85°	42	42	41	41	40	47
90°	1	6	10	13	14	3
95°	25	10	10	13	13	32
105°	138	140	143	146	130	144
115°	257	258	258	259	259	253
125°	362	363	362	364	364	323
135°	448	448	450	451	452	345
145°	517	518	519	519	520	323
155°	567	567	566	568	567	261
165°	598	596	596	599	595	169
175°	612	609	610	613	608	58
180°	612	612	612	612	612	



TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	983.2	982.8	982.4	982.0	981.6	980.6	979.1	977.5	975.9	974.4	975.8
5°	980.0	979.3	978.6	977.9	977.1	975.8	973.9	972.0	970.1	968.2	970.1
7.5°	970.8	970.1	969.5	968.8	968.1	966.6	964.5	962.4	960.2	958.1	959.7
10°	962.6	962.0	961.3	960.6	959.9	958.4	956.1	953.8	951.6	949.3	950.7
12.5°	952.0	951.3	950.6	949.9	949.2	947.7	945.2	942.8	940.4	938.0	939.5
15°	932.8	932.1	931.4	930.7	930.0	928.4	925.7	923.1	920.5	917.9	918.9
17.5°	909.7	908.8	908.0	907.1	906.2	904.5	902.0	899.6	897.1	894.6	895.2
20°	892.7	891.8	891.0	890.1	889.2	887.5	884.8	882.2	879.6	877.0	877.5
22.5°	874.4	873.3	872.2	871.0	869.9	868.0	865.4	862.7	860.1	857.5	858.5
25°	844.8	843.5	842.3	841.1	839.9	838.1	835.6	833.1	830.7	828.3	828.5
27.5°	810.8	809.6	808.3	807.1	805.8	804.1	801.7	799.5	797.2	795.0	794.6
30°	788.2	786.8	785.4	784.0	782.6	780.7	778.5	776.2	774.0	771.7	771.0
32.5°	764.3	763.1	761.7	760.5	759.3	757.4	755.1	752.7	750.2	747.8	747.0
35°	726.9	725.7	724.5	723.3	722.1	720.1	717.7	715.3	712.9	710.4	709.1
37.5°	687.4	686.3	685.2	684.1	683.0	681.2	678.5	675.9	673.3	670.7	669.3
40°	661.7	660.2	658.8	657.5	656.1	654.1	651.5	648.8	646.2	643.6	641.9
42.5°	634.0	633.2	632.4	631.5	630.7	628.7	625.9	623.0	620.1	617.2	615.2
45°	593.3	592.1	590.9	589.7	588.4	586.4	583.6	580.8	578.0	575.2	573.3
47.5°	550.7	549.9	549.1	548.2	547.3	545.6	543.1	540.5	537.9	535.3	533.1
50°	521.8	521.1	520.4	519.7	519.0	517.5	515.0	512.5	510.1	507.7	505.2
52.5°	493.5	492.7	491.8	491.0	490.2	488.5	485.8	483.3	480.7	478.1	475.9
55°	448.7	448.2	447.7	447.2	446.7	445.1	442.7	440.2	437.8	435.4	433.2
57.5°	406.0	405.4	404.8	404.1	403.5	402.1	399.7	397.3	394.9	392.4	390.4
60°	376.4	375.6	374.7	373.8	372.9	371.3	369.1	366.8	364.6	362.2	360.7
62.5°	347.5	346.8	346.0	345.3	344.6	343.0	340.6	338.2	335.8	333.4	331.9
65°	304.1	303.3	302.4	301.5	300.6	299.3	297.6	295.8	294.1	292.4	290.5
67.5°	260.4	259.6	258.8	258.0	257.2	256.0	254.3	252.7	251.0	249.2	247.6
70°	233.4	232.2	231.0	229.7	228.5	227.2	225.8	224.4	223.0	221.6	220.3
72.5°	204.5	203.3	202.1	200.8	199.5	198.4	197.3	196.2	195.1	193.9	192.8
75°	161.9	161.0	160.2	159.3	158.3	157.5	156.6	155.7	154.9	154.0	153.3
77.5°	121.2	120.8	120.4	120.1	119.7	119.1	118.3	117.5	116.7	116.0	115.7
80°	96.6	96.1	95.6	95.1	94.5	94.1	93.8	93.4	93.1	92.7	92.4
82.5°	72.8	72.5	72.3	72.0	71.8	71.6	71.6	71.5	71.4	71.4	71.1
85°	42.4	42.4	42.4	42.4	42.4	42.2	41.9	41.6	41.2	40.9	40.9
87.5°	16.7	16.7	16.8	16.9	17.0	17.0	17.1	17.1	17.1	17.1	17.3
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	5.8	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3
95°	25.1	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7
97.5°	53.4	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1
100°	75.0	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4
102.5°	99.3	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4
105°	137.7	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7
107.5°	173.6	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4
110°	197.7	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1



TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	221.2	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9
115°	257.2	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3
117.5°	289.7	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5
120°	311.6	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3
122.5°	332.1	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1
125°	361.5	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7
127.5°	389.4	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9
130°	407.3	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3
132.5°	423.8	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5
135°	448.5	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1
137.5°	470.4	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8
140°	484.6	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9
142.5°	497.5	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9
145°	517.2	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7
147.5°	532.8	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0
150°	544.2	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5
152.5°	553.7	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5
155°	567.0	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5
157.5°	578.3	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0
160°	584.9	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7
162.5°	590.8	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2
165°	598.1	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7
167.5°	604.0	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3
170°	607.3	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8
172.5°	609.6	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0
175°	611.9	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6
177.5°	613.0	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	980.7	980.7	980.7	980.7	980.7	980.7	980.7	980.7
2.5°	977.2	978.7	980.1	980.7	980.5	980.4	980.3	980.1
5°	972.0	973.9	975.8	976.6	976.2	975.9	975.5	975.2
7.5°	961.2	962.7	964.2	964.9	964.7	964.5	964.3	964.0
10°	952.1	953.5	954.9	955.4	955.0	954.7	954.3	954.0
12.5°	941.1	942.6	944.1	944.6	944.1	943.6	943.2	942.7
15°	920.0	921.0	922.0	922.3	921.8	921.3	920.7	920.2
17.5°	896.0	896.6	897.3	897.4	897.1	896.7	896.4	896.1
20°	878.1	878.6	879.1	879.2	878.8	878.5	878.2	877.8
22.5°	859.4	860.3	861.3	861.4	860.8	860.2	859.6	858.9
25°	828.6	828.8	829.0	828.7	828.0	827.3	826.6	825.9
27.5°	794.2	793.7	793.2	792.6	791.7	790.9	790.0	789.1
30°	770.3	769.6	768.9	768.1	767.2	766.4	765.5	764.6
32.5°	746.1	745.3	744.5	743.6	742.8	741.8	740.9	740.1
35°	707.9	706.7	705.5	704.5	703.6	702.7	701.9	700.9
37.5°	668.0	666.6	665.3	664.1	663.0	661.8	660.7	659.4
40°	640.2	638.3	636.6	635.3	634.4	633.6	632.7	631.8
42.5°	613.2	611.1	609.0	607.7	607.2	606.6	606.0	605.4
45°	571.4	569.5	567.5	566.3	565.8	565.3	564.7	564.2
47.5°	531.0	528.8	526.6	524.9	523.6	522.2	520.9	519.6
50°	502.7	500.3	497.9	496.1	495.0	494.0	493.0	491.9
52.5°	473.7	471.6	469.5	467.7	466.4	465.0	463.7	462.4
55°	431.2	429.1	427.0	425.4	424.3	423.3	422.2	421.2
57.5°	388.5	386.5	384.5	382.9	381.9	380.9	379.9	378.9
60°	359.1	357.6	356.0	354.8	353.9	353.0	352.1	351.2
62.5°	330.5	329.0	327.6	326.5	325.6	324.8	323.9	323.0
65°	288.8	287.1	285.4	284.1	283.2	282.3	281.4	280.5
67.5°	245.9	244.3	242.6	241.6	241.4	241.2	240.9	240.7
70°	218.8	217.4	216.0	215.1	214.5	214.0	213.5	213.0
72.5°	191.7	190.6	189.5	188.6	188.1	187.6	187.1	186.5
75°	152.6	151.9	151.3	150.8	150.6	150.5	150.3	150.1
77.5°	115.5	115.3	115.1	114.8	114.3	113.9	113.4	113.0
80°	92.0	91.7	91.3	91.1	90.9	90.7	90.6	90.4
82.5°	70.9	70.7	70.5	70.3	70.2	70.0	69.8	69.6
85°	40.9	40.9	40.9	40.8	40.6	40.4	40.3	40.1
87.5°	17.4	17.5	17.6	17.7	17.7	17.8	17.8	17.9
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	10.9	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	16.7	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	59.7	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	144.6	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	178.9	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.3	202.5	202.7	202.9	203.2	203.5	203.8	204.1





TEST NUMBER: P332749-840

CATALOG NUMBER: S124DIW-S575D470U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	224.8	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.5	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.2	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.0	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.8	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.4	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.6	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.3	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.0	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.2	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.1	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.8	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.6	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	566.9	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	589.8	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	597.5	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	603.2	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	606.6	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	608.8	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	611.5	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	612.5	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)