

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333045-930

Luminaire Tested: **S124RDIW-S575D1050U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333045-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D1050U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5333.8 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.8	1.5
10°-20°	217.0	4.1
20°-30°	313.4	5.9
30°-40°	355.3	6.7
40°-50°	343.1	6.4
50°-60°	285.3	5.3
60°-70°	197.0	3.7
70°-80°	99.8	1.9
80°-90°	28.8	0.5
90°-100°	37.8	0.7
100°-110°	240.8	4.5
110°-120°	460.7	8.6
120°-130°	584.9	11.0
130°-140°	625.8	11.7
140°-150°	585.2	11.0
150°-160°	471.9	8.8
160°-170°	304.4	5.7
170°-180°	104.9	2.0
0°-30°	608.3	11.4
0°-40°	963.6	18.1
0°-60°	1591.9	29.8
0°-90°	1917.5	36.0
90°-120°	739.3	13.9
90°-150°	2535.2	47.5
90°-180°	3416.0	64.0
0°-180°	5333.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	2	11	18	23	25	4
95°	45	19	18	23	24	58
105°	249	254	258	263	236	260
115°	464	466	466	467	468	457
125°	653	656	654	657	658	582
135°	810	809	812	814	815	623
145°	933	936	936	937	938	583
155°	1023	1024	1022	1025	1023	472
165°	1080	1076	1076	1081	1075	305
175°	1104	1100	1100	1107	1098	105
180°	1104	1104	1104	1104	1104	



TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.1	11.7	11.2	10.7	10.2	10.0	10.2	10.4	10.6	10.8	10.8
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	10.4	10.5	10.6	10.8	10.8	11.7	13.1	14.6	16.1	17.5	18.6
95°	45.4	39.2	32.9	26.7	20.5	17.4	17.6	17.8	18.0	18.2	19.2
97.5°	96.4	100.4	104.3	108.2	112.0	103.8	83.2	62.8	42.3	21.8	21.9
100°	135.5	138.8	142.1	145.4	148.7	137.7	112.3	87.0	61.7	36.4	33.3
102.5°	179.1	181.5	183.9	186.4	188.7	188.3	185.1	181.7	178.4	175.1	141.5
105°	248.7	249.7	250.9	251.9	253.1	254.0	254.9	255.9	256.8	257.7	259.3
107.5°	313.2	313.8	314.3	314.9	315.4	316.3	317.6	318.9	320.1	321.3	322.1
110°	356.9	357.4	357.9	358.5	359.1	359.9	361.0	362.1	363.2	364.3	364.7



TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.2	400.1	401.1	402.1	403.1	403.9	404.4	404.9	405.4	405.9	405.9
115°	464.2	464.8	465.4	465.9	466.4	466.6	466.4	466.3	466.1	465.9	466.3
117.5°	522.9	523.6	524.3	525.1	525.8	526.4	526.8	527.2	527.6	528.0	527.9
120°	562.6	563.3	564.0	564.8	565.5	565.7	565.6	565.4	565.2	565.0	565.4
122.5°	599.6	600.0	600.4	600.9	601.3	601.7	601.9	602.2	602.4	602.7	602.9
125°	652.6	653.3	654.0	654.8	655.5	655.7	655.3	654.9	654.6	654.2	654.8
127.5°	702.8	703.0	703.2	703.4	703.5	704.0	704.9	705.7	706.5	707.4	707.4
130°	735.2	735.4	735.6	735.7	735.9	736.3	736.9	737.4	737.9	738.5	738.7
132.5°	764.9	765.2	765.6	765.9	766.2	766.8	767.4	768.2	768.8	769.6	769.7
135°	809.5	809.3	809.2	808.9	808.8	809.1	809.8	810.6	811.3	812.0	812.4
137.5°	849.0	849.1	849.1	849.2	849.3	849.7	850.5	851.3	852.2	853.0	853.4
140°	874.8	875.1	875.5	875.9	876.3	876.6	877.0	877.3	877.8	878.1	878.6
142.5°	897.9	898.5	899.2	899.9	900.6	901.0	901.2	901.4	901.6	901.9	902.3
145°	933.4	934.0	934.5	935.1	935.6	935.9	935.9	935.9	935.9	935.9	936.1
147.5°	961.6	962.7	963.8	964.7	965.8	966.2	966.0	965.9	965.6	965.5	965.6
150°	982.2	982.9	983.7	984.4	985.1	985.4	985.2	985.0	984.8	984.6	984.6
152.5°	999.3	1000.0	1000.5	1001.1	1001.7	1001.8	1001.5	1001.2	1000.9	1000.5	1000.8
155°	1023.4	1023.7	1023.9	1024.0	1024.2	1024.0	1023.4	1023.0	1022.4	1021.8	1022.5
157.5°	1043.8	1043.7	1043.6	1043.4	1043.3	1043.0	1042.4	1041.7	1041.1	1040.5	1041.5
160°	1055.6	1055.2	1054.6	1054.0	1053.4	1053.1	1053.0	1052.7	1052.6	1052.4	1053.4
162.5°	1066.2	1065.6	1064.9	1064.1	1063.5	1063.0	1062.8	1062.7	1062.5	1062.3	1063.4
165°	1079.6	1078.7	1077.8	1076.8	1076.0	1075.5	1075.5	1075.5	1075.5	1075.5	1077.0
167.5°	1090.2	1089.2	1088.3	1087.4	1086.4	1085.9	1085.7	1085.7	1085.6	1085.4	1087.0
170°	1096.2	1095.0	1094.0	1092.8	1091.8	1091.3	1091.4	1091.7	1091.8	1092.0	1093.5
172.5°	1100.1	1099.0	1097.9	1096.8	1095.7	1095.3	1095.4	1095.6	1095.8	1096.0	1097.5
175°	1104.4	1103.3	1102.2	1101.1	1100.0	1099.6	1099.8	1099.9	1100.1	1100.3	1102.0
177.5°	1106.4	1105.4	1104.3	1103.3	1102.3	1102.0	1102.2	1102.5	1102.8	1103.1	1104.2
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	10.9	11.1	11.2	11.3	11.5	11.7	11.9	12.1
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	19.7	20.8	21.9	22.5	22.6	22.7	22.7	22.8
95°	20.4	21.4	22.6	23.2	23.4	23.6	23.8	24.0
97.5°	22.0	22.2	22.3	22.4	22.6	22.7	22.9	23.2
100°	30.1	27.0	23.9	22.4	22.6	22.7	22.9	23.2
102.5°	107.8	74.1	40.4	23.6	23.6	23.7	23.7	23.8
105°	261.1	262.7	264.3	261.9	255.3	248.7	242.1	235.5
107.5°	322.9	323.8	324.6	325.3	326.0	326.7	327.4	328.1
110°	365.0	365.4	365.7	366.2	366.8	367.3	367.9	368.4





TEST NUMBER: P333045-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	405.8	405.7	405.6	405.9	406.7	407.3	408.1	408.7
115°	466.6	467.0	467.3	467.6	467.6	467.6	467.6	467.6
117.5°	527.8	527.8	527.7	527.7	527.6	527.5	527.4	527.3
120°	565.7	566.1	566.5	566.5	566.1	565.7	565.4	565.0
122.5°	603.2	603.3	603.6	603.5	603.2	602.8	602.4	602.0
125°	655.3	655.9	656.4	656.8	657.0	657.1	657.4	657.5
127.5°	707.2	707.1	706.9	706.9	706.7	706.5	706.4	706.3
130°	738.8	739.1	739.2	739.3	739.3	739.3	739.3	739.3
132.5°	769.9	770.1	770.3	770.3	770.1	770.0	769.9	769.7
135°	812.8	813.1	813.5	813.8	814.2	814.6	815.0	815.3
137.5°	853.8	854.2	854.6	854.8	854.6	854.5	854.4	854.3
140°	879.2	879.7	880.3	880.7	880.8	881.0	881.2	881.4
142.5°	902.7	903.1	903.5	903.7	903.8	903.8	903.8	903.8
145°	936.3	936.5	936.6	936.9	937.3	937.7	938.0	938.4
147.5°	965.8	965.9	966.0	966.2	966.5	966.6	966.8	966.9
150°	984.6	984.6	984.6	984.7	984.9	985.1	985.3	985.5
152.5°	1001.1	1001.4	1001.7	1001.8	1001.7	1001.5	1001.4	1001.4
155°	1023.3	1024.0	1024.7	1024.8	1024.3	1023.8	1023.2	1022.6
157.5°	1042.4	1043.3	1044.3	1044.3	1043.3	1042.4	1041.5	1040.5
160°	1054.6	1055.6	1056.8	1056.8	1055.6	1054.6	1053.4	1052.4
162.5°	1064.5	1065.6	1066.7	1066.7	1065.4	1064.1	1062.9	1061.6
165°	1078.5	1079.9	1081.4	1081.2	1079.6	1078.0	1076.4	1074.6
167.5°	1088.7	1090.3	1091.8	1091.8	1090.0	1088.1	1086.3	1084.4
170°	1094.9	1096.4	1097.9	1097.7	1095.8	1094.1	1092.2	1090.4
172.5°	1098.9	1100.4	1101.9	1101.6	1099.6	1097.6	1095.7	1093.6
175°	1103.6	1105.2	1106.9	1106.6	1104.4	1102.2	1100.0	1097.8
177.5°	1105.5	1106.6	1107.8	1107.5	1105.7	1104.0	1102.2	1100.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4

(END OF REPORT)