

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333054-930

Luminaire Tested: **S124RDIW-S575D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333054-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1560U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6329.1 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	32	26				
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	27	22				
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19				
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	19	18	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12				
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11				
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10				
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9				
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.2
10°-20°	217.0	3.4
20°-30°	313.4	5.0
30°-40°	355.3	5.6
40°-50°	343.1	5.4
50°-60°	285.3	4.5
60°-70°	197.0	3.1
70°-80°	99.8	1.6
80°-90°	30.4	0.5
90°-100°	104.8	1.7
100°-110°	310.6	4.9
110°-120°	527.1	8.3
120°-130°	695.1	11.0
130°-140°	780.6	12.3
140°-150°	767.1	12.1
150°-160°	645.2	10.2
160°-170°	429.2	6.8
170°-180°	150.3	2.4
0°-30°	608.3	9.6
0°-40°	963.6	15.2
0°-60°	1591.9	25.2
0°-90°	1919.1	30.3
90°-120°	942.5	14.9
90°-150°	3185.3	50.3
90°-180°	4410.0	69.7
0°-180°	6329.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	4	17	27	34	37	6
95°	74	85	93	97	97	82
105°	286	288	293	296	300	304
115°	536	536	534	532	531	528
125°	781	781	779	777	774	695
135°	1007	1014	1014	1012	1008	779
145°	1223	1228	1229	1228	1224	765
155°	1401	1401	1400	1405	1400	645
165°	1526	1522	1520	1526	1522	430
175°	1587	1581	1580	1587	1580	151
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.4	12.1	11.8	11.5	11.2	11.3	11.6	11.9	12.2	12.5	12.7
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	26.3	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7
95°	73.8	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2
97.5°	128.8	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7
100°	172.1	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7
102.5°	217.4	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2
105°	286.4	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4
107.5°	359.0	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9
110°	408.1	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.3	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5
115°	536.0	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3
117.5°	608.3	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6
120°	656.5	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3
122.5°	706.6	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0
125°	780.6	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9
127.5°	847.7	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9
130°	895.0	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1
132.5°	943.1	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4
135°	1006.8	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7
137.5°	1076.2	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8
140°	1122.4	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5
142.5°	1164.7	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1
145°	1223.2	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1281.2	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9
150°	1316.6	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.1	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6
155°	1401.4	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3
157.5°	1444.7	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1
160°	1470.3	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7
162.5°	1493.9	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9
165°	1525.6	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1
167.5°	1550.0	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7
170°	1563.7	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4
172.5°	1573.5	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5
175°	1587.1	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6
177.5°	1591.5	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	13.0	13.1	13.4	13.6	13.8	14.0	14.3	14.5
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	50.6	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.1	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	149.8	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.1	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	230.9	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	294.2	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	362.7	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	408.3	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P333054-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.3	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	533.0	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	605.7	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	654.9	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	705.0	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	778.3	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	848.4	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.6	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.8	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1013.1	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1080.2	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.3	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.8	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.7	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.3	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1443.9	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1469.5	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1492.4	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1522.7	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1548.3	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1562.1	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1572.4	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1589.7	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)