

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332791-840

Luminaire Tested: **S124DIW-S795D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332791-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1050U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7675.6 lumens
Efficiency: N/A
Efficacy: 145.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.2	1.6
10°-20°	355.7	4.6
20°-30°	523.5	6.8
30°-40°	608.6	7.9
40°-50°	608.7	7.9
50°-60°	532.4	6.9
60°-70°	395.4	5.2
70°-80°	224.6	2.9
80°-90°	68.8	0.9
90°-100°	46.8	0.6
100°-110°	298.3	3.9
110°-120°	570.7	7.4
120°-130°	724.4	9.4
130°-140°	775.1	10.1
140°-150°	724.8	9.4
150°-160°	584.5	7.6
160°-170°	377.0	4.9
170°-180°	129.9	1.7
0°-30°	1005.5	13.1
0°-40°	1614.1	21.0
0°-60°	2755.2	35.9
0°-90°	3444.0	44.9
90°-120°	915.8	11.9
90°-150°	3140.1	40.9
90°-180°	4232.0	55.1
0°-180°	7675.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	3	14	22	28	31	6
95°	56	23	22	28	30	72
105°	308	314	319	326	292	322
115°	575	578	577	579	579	566
125°	808	812	810	813	814	721
135°	1003	1002	1006	1008	1010	772
145°	1156	1159	1159	1160	1162	722
155°	1268	1268	1266	1269	1267	584
165°	1337	1332	1332	1339	1331	378
175°	1368	1362	1363	1371	1360	130
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.9	23.2	23.5	23.9	24.2	24.4	24.6	24.7	24.9	25.1	25.4
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	12.9	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0
95°	56.2	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8
97.5°	119.5	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2
100°	167.8	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2
102.5°	221.9	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2
105°	308.0	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2
107.5°	388.0	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0
110°	442.0	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	494.4	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7
115°	575.0	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5
117.5°	647.6	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9
120°	696.8	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3
122.5°	742.7	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8
125°	808.3	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0
127.5°	870.5	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2
130°	910.6	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9
132.5°	947.5	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4
135°	1002.7	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2
137.5°	1051.6	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0
140°	1083.6	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3
142.5°	1112.2	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6
145°	1156.2	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5
147.5°	1191.1	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1
150°	1216.6	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6
152.5°	1237.8	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6
155°	1267.7	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6
157.5°	1292.9	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0
160°	1307.6	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8
162.5°	1320.7	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2
165°	1337.3	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0
167.5°	1350.4	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5
170°	1357.8	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4
172.5°	1362.6	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4
175°	1368.0	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9
177.5°	1370.4	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	25.7	26.0	26.3	26.4	26.5	26.6	26.7	26.8
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	24.4	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	25.2	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.3	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	37.3	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	133.5	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	323.4	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	400.0	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.1	452.6	453.0	453.6	454.3	454.9	455.7	456.4



TEST NUMBER: P332791-840

CATALOG NUMBER: S124DIW-S795D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	502.6	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	577.9	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.1	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	811.7	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	876.0	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.1	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.6	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1006.7	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1057.5	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.0	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.1	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.7	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.3	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.0	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1267.5	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1318.5	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1335.8	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1348.5	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1356.2	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1361.2	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1367.0	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1369.3	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)