

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333066-930

Luminaire Tested: **S124RDIW-S795D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333066-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1050U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5582.8 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82		67	67	67		53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68		59	58	56		47	46	45	40
2	89	82	76	71	81	75	70	66	63	60	56		52	50	47		42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48		46	43	40		37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41		41	38	35		34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35		37	33	30		30	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31		34	30	26		28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27		31	27	24		25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24		28	24	21		23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22		26	22	19		22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20		24	20	17		20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	1.9
10°-20°	296.7	5.3
20°-30°	428.4	7.7
30°-40°	485.6	8.7
40°-50°	468.9	8.4
50°-60°	389.9	7.0
60°-70°	269.3	4.8
70°-80°	136.5	2.4
80°-90°	38.2	0.7
90°-100°	70.4	1.3
100°-110°	208.7	3.7
110°-120°	354.2	6.3
120°-130°	467.0	8.4
130°-140°	524.5	9.4
140°-150°	515.4	9.2
150°-160°	433.5	7.8
160°-170°	288.4	5.2
170°-180°	101.0	1.8
0°-30°	831.5	14.9
0°-40°	1317.1	23.6
0°-60°	2176.0	39.0
0°-90°	2619.9	46.9
90°-120°	633.2	11.3
90°-150°	2140.1	38.3
90°-180°	2963.0	53.1
0°-180°	5582.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	2	11	18	23	25	5
95°	50	57	63	65	65	55
105°	192	193	197	199	202	204
115°	360	360	358	358	357	355
125°	524	524	524	522	520	467
135°	676	681	681	680	677	523
145°	822	825	826	825	823	514
155°	942	942	941	944	941	433
165°	1025	1023	1021	1025	1022	289
175°	1066	1062	1061	1066	1061	101
180°	1068	1068	1068	1068	1068	



TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.5	15.7	14.8	13.9	13.1	12.8	13.0	13.0	13.2	13.4	13.5
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	17.7	20.0	22.3	24.6	26.9	28.6	29.6	30.7	31.7	32.7	33.3
95°	49.6	51.2	52.8	54.5	56.2	57.6	58.9	60.2	61.5	62.8	63.3
97.5°	86.6	87.9	89.2	90.5	91.9	93.3	94.7	96.3	97.8	99.3	100.0
100°	115.6	116.3	117.1	117.8	118.5	119.8	121.4	123.0	124.7	126.4	126.7
102.5°	146.0	146.3	146.6	146.9	147.2	148.1	149.6	151.1	152.6	154.1	154.7
105°	192.4	192.7	192.8	193.0	193.1	193.6	194.4	195.1	195.8	196.6	197.1
107.5°	241.2	241.4	241.6	241.8	242.1	242.2	242.3	242.5	242.6	242.6	243.2
110°	274.2	274.6	274.9	275.3	275.7	275.7	275.6	275.4	275.2	275.0	274.7



TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.6	308.7	308.8	308.8	308.8	308.8	308.4	308.1	307.8	307.4	307.4
115°	360.1	360.1	360.1	360.1	360.1	360.0	359.5	359.2	358.8	358.5	358.2
117.5°	408.7	408.8	409.0	409.1	409.3	409.2	409.0	408.7	408.5	408.1	407.6
120°	441.1	441.8	442.5	443.3	444.0	444.1	443.5	443.0	442.5	441.9	441.0
122.5°	474.7	475.1	475.3	475.6	475.9	476.0	475.6	475.4	475.2	474.9	474.3
125°	524.5	524.5	524.5	524.5	524.5	524.4	524.2	524.0	523.8	523.7	523.3
127.5°	569.6	570.1	570.6	571.2	571.8	571.9	571.6	571.3	571.0	570.7	570.4
130°	601.3	601.9	602.3	602.9	603.5	603.7	603.7	603.7	603.7	603.7	603.4
132.5°	633.7	634.1	634.5	634.9	635.3	635.4	635.3	635.1	635.0	634.8	634.5
135°	676.5	677.5	678.7	679.7	680.9	681.4	681.4	681.4	681.4	681.4	681.0
137.5°	723.0	723.5	724.1	724.6	725.0	725.5	725.8	726.1	726.4	726.7	726.2
140°	754.1	754.5	754.8	755.2	755.5	755.7	755.7	755.7	755.7	755.7	755.5
142.5°	782.5	782.9	783.3	783.6	784.0	784.1	783.9	783.7	783.7	783.5	783.4
145°	821.8	822.6	823.3	824.0	824.8	825.2	825.4	825.6	825.7	825.9	825.7
147.5°	860.8	861.7	862.6	863.4	864.3	864.7	864.5	864.4	864.2	864.1	864.0
150°	884.6	885.3	886.1	886.8	887.5	887.9	887.9	887.9	887.9	887.9	887.9
152.5°	907.0	907.5	907.9	908.3	908.8	909.1	909.2	909.4	909.5	909.7	910.1
155°	941.6	941.6	941.6	941.6	941.6	941.5	941.3	941.1	940.9	940.8	941.5
157.5°	970.6	970.3	970.0	969.6	969.3	969.1	969.1	969.1	969.0	969.0	969.6
160°	987.8	987.7	987.4	987.2	987.1	986.9	986.7	986.5	986.3	986.2	986.7
162.5°	1003.6	1003.2	1002.7	1002.2	1001.8	1001.4	1001.3	1001.1	1000.9	1000.7	1001.7
165°	1025.0	1024.4	1023.9	1023.4	1022.8	1022.3	1022.0	1021.6	1021.2	1020.8	1022.0
167.5°	1041.3	1040.6	1039.8	1039.0	1038.3	1037.9	1038.0	1038.0	1038.0	1038.0	1039.1
170°	1050.6	1049.7	1048.7	1047.8	1046.9	1046.5	1046.8	1046.9	1047.1	1047.3	1048.4
172.5°	1057.2	1056.4	1055.6	1054.9	1054.1	1053.8	1053.8	1053.9	1053.9	1053.9	1055.2
175°	1066.2	1065.4	1064.5	1063.6	1062.6	1062.1	1061.8	1061.7	1061.5	1061.4	1062.6
177.5°	1069.3	1068.5	1067.8	1067.1	1066.3	1065.9	1065.9	1065.9	1065.9	1065.9	1067.0
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0



TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	13.5	13.5	13.6	13.8	14.0	14.2	14.4	14.7
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	34.0	34.7	35.4	35.8	36.0	36.2	36.4	36.7
95°	63.8	64.4	65.0	65.2	65.2	65.2	65.2	65.2
97.5°	100.6	101.3	101.9	102.2	102.2	102.2	102.2	102.2
100°	127.1	127.4	127.8	128.0	128.0	128.0	128.0	128.0
102.5°	155.2	155.6	156.2	156.5	156.6	156.8	156.9	157.1
105°	197.7	198.2	198.8	199.3	199.9	200.4	201.0	201.5
107.5°	243.7	244.2	244.8	244.9	244.9	244.9	244.8	244.8
110°	274.3	273.9	273.5	273.7	274.2	274.8	275.3	275.9





TEST NUMBER: P333066-930

CATALOG NUMBER: S124RDIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	307.3	307.2	307.1	307.1	307.3	307.4	307.4	307.6
115°	358.1	357.9	357.8	357.5	357.3	357.2	357.0	356.8
117.5°	406.9	406.3	405.7	405.2	404.8	404.5	404.1	403.7
120°	440.0	439.1	438.2	437.9	438.3	438.6	439.0	439.4
122.5°	473.7	473.0	472.4	471.7	471.1	470.4	469.8	469.1
125°	522.9	522.5	522.2	521.8	521.5	521.1	520.7	520.3
127.5°	570.0	569.6	569.2	568.9	568.6	568.3	568.0	567.8
130°	603.0	602.7	602.3	601.8	601.0	600.3	599.6	598.8
132.5°	634.1	633.7	633.3	633.0	632.8	632.4	632.1	631.9
135°	680.7	680.3	680.0	679.5	678.9	678.3	677.8	677.3
137.5°	725.7	725.2	724.7	724.6	724.6	724.8	724.9	725.0
140°	755.4	755.2	755.0	754.8	754.6	754.5	754.2	754.1
142.5°	783.4	783.3	783.3	783.3	783.3	783.3	783.2	783.2
145°	825.6	825.4	825.2	824.8	824.3	823.7	823.2	822.6
147.5°	863.8	863.6	863.5	863.3	863.2	863.0	862.7	862.6
150°	887.9	887.9	887.9	887.8	887.6	887.5	887.2	887.0
152.5°	910.5	911.0	911.4	911.4	910.9	910.4	910.0	909.5
155°	942.2	943.0	943.7	943.7	943.0	942.2	941.5	940.8
157.5°	970.1	970.6	971.2	971.2	970.5	969.9	969.3	968.7
160°	987.2	987.8	988.4	988.1	987.2	986.3	985.5	984.5
162.5°	1002.7	1003.6	1004.7	1004.7	1003.8	1002.9	1001.9	1001.0
165°	1023.0	1024.2	1025.2	1025.4	1024.7	1023.9	1023.2	1022.5
167.5°	1040.2	1041.3	1042.4	1042.4	1041.3	1040.2	1039.0	1037.9
170°	1049.5	1050.6	1051.7	1051.6	1050.4	1049.0	1047.7	1046.4
172.5°	1056.4	1057.6	1058.9	1058.8	1057.6	1056.3	1055.0	1053.7
175°	1063.9	1065.2	1066.5	1066.5	1065.2	1063.9	1062.6	1061.4
177.5°	1068.0	1069.0	1070.1	1070.0	1068.8	1067.6	1066.5	1065.3
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0

(END OF REPORT)