

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332780-840

Luminaire Tested: **S124DIW-S795D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332780-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D470U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5083.4 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	85	75	67	61	79	71	64	58	63	58	53	56	52	48	50	47	44	40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	45	41	38	35
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	46	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.2	2.5
10°-20°	355.7	7.0
20°-30°	523.5	10.3
30°-40°	608.6	12.0
40°-50°	608.7	12.0
50°-60°	532.4	10.5
60°-70°	395.4	7.8
70°-80°	224.6	4.4
80°-90°	66.6	1.3
90°-100°	39.0	0.8
100°-110°	115.6	2.3
110°-120°	196.2	3.9
120°-130°	258.7	5.1
130°-140°	290.6	5.7
140°-150°	285.5	5.6
150°-160°	240.2	4.7
160°-170°	159.8	3.1
170°-180°	56.0	1.1
0°-30°	1005.5	19.8
0°-40°	1614.1	31.8
0°-60°	2755.2	54.2
0°-90°	3441.8	67.7
90°-120°	350.9	6.9
90°-150°	1185.7	23.3
90°-180°	1642.0	32.3
0°-180°	5083.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	1	6	10	13	14	5
95°	28	32	35	36	36	31
105°	107	107	109	110	112	113
115°	200	199	199	198	198	197
125°	290	290	290	289	288	259
135°	375	377	378	377	375	290
145°	455	457	458	457	456	285
155°	522	522	521	523	521	240
165°	568	566	566	568	566	160
175°	591	589	588	591	588	56
180°	592	592	592	592	592	



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.6	22.6	22.7	22.7	22.7	22.7	22.7	22.7	22.6	22.6	22.7
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	9.8	11.1	12.3	13.6	14.9	15.9	16.5	17.0	17.6	18.1	18.5
95°	27.5	28.4	29.3	30.2	31.1	31.9	32.6	33.3	34.0	34.7	35.0
97.5°	48.0	48.7	49.4	50.2	50.9	51.7	52.5	53.3	54.1	55.0	55.3
100°	64.0	64.4	64.8	65.2	65.7	66.3	67.3	68.2	69.1	70.0	70.2
102.5°	80.9	81.1	81.2	81.4	81.6	82.1	82.9	83.7	84.5	85.4	85.6
105°	106.6	106.7	106.8	106.9	107.0	107.2	107.7	108.1	108.5	108.9	109.2
107.5°	133.6	133.7	133.9	134.0	134.1	134.2	134.3	134.3	134.4	134.4	134.7
110°	151.9	152.1	152.3	152.5	152.7	152.8	152.7	152.6	152.5	152.4	152.2



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.0	171.0	171.1	171.1	171.2	171.1	170.9	170.7	170.5	170.4	170.3
115°	199.5	199.5	199.5	199.5	199.5	199.4	199.2	199.0	198.8	198.6	198.5
117.5°	226.4	226.5	226.6	226.7	226.7	226.7	226.6	226.4	226.3	226.1	225.8
120°	244.4	244.8	245.2	245.6	246.0	246.0	245.7	245.4	245.1	244.8	244.3
122.5°	263.1	263.2	263.4	263.5	263.7	263.7	263.6	263.4	263.3	263.2	262.8
125°	290.5	290.5	290.5	290.5	290.5	290.5	290.4	290.3	290.2	290.1	289.9
127.5°	315.6	315.9	316.2	316.5	316.8	316.9	316.7	316.5	316.4	316.2	316.0
130°	333.2	333.5	333.8	334.1	334.4	334.5	334.5	334.5	334.5	334.5	334.3
132.5°	351.0	351.3	351.5	351.7	351.9	352.0	351.9	351.8	351.8	351.7	351.5
135°	374.8	375.4	376.0	376.6	377.2	377.5	377.5	377.5	377.5	377.5	377.3
137.5°	400.6	400.9	401.1	401.4	401.7	401.9	402.1	402.3	402.4	402.6	402.3
140°	417.8	418.0	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7	418.6
142.5°	433.5	433.7	433.9	434.1	434.3	434.4	434.3	434.2	434.1	434.0	434.0
145°	455.3	455.8	456.2	456.6	457.0	457.2	457.3	457.4	457.5	457.6	457.5
147.5°	477.0	477.4	477.9	478.4	478.9	479.1	479.0	478.9	478.9	478.8	478.7
150°	490.1	490.5	490.9	491.3	491.7	491.9	491.9	491.9	491.9	491.9	491.9
152.5°	502.5	502.8	503.0	503.3	503.5	503.7	503.7	503.8	503.9	504.0	504.2
155°	521.7	521.7	521.7	521.7	521.7	521.6	521.5	521.4	521.3	521.2	521.6
157.5°	537.8	537.6	537.5	537.2	537.0	536.9	536.9	536.9	536.8	536.8	537.1
160°	547.3	547.2	547.1	547.0	546.9	546.8	546.7	546.6	546.5	546.4	546.7
162.5°	556.1	555.8	555.5	555.3	555.0	554.8	554.7	554.6	554.5	554.4	555.0
165°	567.8	567.5	567.2	566.9	566.6	566.4	566.2	566.0	565.8	565.6	566.2
167.5°	576.9	576.5	576.1	575.7	575.2	575.0	575.0	575.1	575.1	575.1	575.7
170°	582.1	581.6	581.1	580.6	580.1	579.9	580.0	580.1	580.2	580.3	580.9
172.5°	585.7	585.3	584.9	584.5	584.0	583.8	583.8	583.9	583.9	583.9	584.6
175°	590.8	590.3	589.8	589.3	588.8	588.4	588.3	588.2	588.1	588.0	588.8
177.5°	592.4	592.0	591.6	591.2	590.8	590.6	590.6	590.6	590.6	590.6	591.2
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	22.9	23.0	23.1	23.2	23.2	23.3	23.3	23.3
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	18.9	19.2	19.6	19.8	20.0	20.1	20.2	20.3
95°	35.3	35.6	36.0	36.2	36.2	36.2	36.2	36.2
97.5°	55.7	56.1	56.5	56.7	56.7	56.7	56.7	56.7
100°	70.4	70.6	70.8	70.9	70.9	70.9	70.9	70.9
102.5°	85.9	86.2	86.5	86.7	86.7	86.8	86.9	87.1
105°	109.6	109.9	110.2	110.5	110.8	111.1	111.4	111.7
107.5°	135.0	135.3	135.6	135.7	135.7	135.7	135.6	135.6
110°	152.0	151.8	151.6	151.6	151.9	152.2	152.5	152.8



TEST NUMBER: P332780-840

CATALOG NUMBER: S124DIW-S795D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.3	170.2	170.2	170.2	170.3	170.3	170.4	170.4
115°	198.4	198.3	198.2	198.1	198.0	197.9	197.8	197.7
117.5°	225.5	225.1	224.8	224.5	224.3	224.1	223.9	223.7
120°	243.8	243.3	242.8	242.7	242.9	243.1	243.3	243.5
122.5°	262.5	262.1	261.8	261.4	261.1	260.6	260.2	259.9
125°	289.7	289.5	289.3	289.1	288.9	288.7	288.5	288.3
127.5°	315.8	315.6	315.4	315.2	315.1	314.9	314.8	314.6
130°	334.1	333.9	333.7	333.4	333.0	332.5	332.1	331.7
132.5°	351.3	351.1	350.9	350.7	350.5	350.4	350.2	350.1
135°	377.1	376.9	376.7	376.5	376.2	375.9	375.6	375.3
137.5°	402.0	401.8	401.5	401.4	401.5	401.5	401.6	401.7
140°	418.5	418.4	418.3	418.2	418.1	418.0	417.9	417.8
142.5°	434.0	434.0	434.0	433.9	433.9	433.9	433.9	433.9
145°	457.4	457.3	457.2	457.0	456.7	456.4	456.1	455.8
147.5°	478.6	478.5	478.5	478.4	478.3	478.2	478.1	478.0
150°	491.9	491.9	491.9	491.9	491.8	491.7	491.6	491.5
152.5°	504.5	504.7	505.0	504.9	504.7	504.4	504.2	503.9
155°	522.0	522.4	522.8	522.8	522.4	522.0	521.6	521.2
157.5°	537.5	537.8	538.1	538.1	537.8	537.3	537.0	536.6
160°	547.0	547.3	547.6	547.5	547.0	546.5	545.9	545.4
162.5°	555.5	556.1	556.6	556.6	556.1	555.6	555.1	554.6
165°	566.8	567.4	568.0	568.2	567.7	567.3	566.9	566.5
167.5°	576.3	576.9	577.5	577.5	576.9	576.3	575.6	575.0
170°	581.5	582.1	582.7	582.6	581.9	581.2	580.5	579.8
172.5°	585.3	586.0	586.6	586.6	585.9	585.2	584.5	583.8
175°	589.5	590.2	590.9	590.9	590.2	589.5	588.8	588.0
177.5°	591.8	592.3	592.9	592.8	592.2	591.6	590.9	590.3
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7

(END OF REPORT)