

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332821

Luminaire Tested: **S124DIW-S1020D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332821
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8622.1 lumens
Efficiency: N/A
Efficacy: 140.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	43	43	43	51		
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	36	36	36	43		
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36	36	36	31	31	31	36		
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	26	26	26	31		
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	23	23	23	26		
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23	20	20	20	23		
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20	20	20	18	18	18	20		
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18	18	18	16	16	16	18		
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	14	14	14	16		
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	13	13	13	14		
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.9
10°-20°	457.8	5.3
20°-30°	673.9	7.8
30°-40°	783.4	9.1
40°-50°	783.4	9.1
50°-60°	685.3	7.9
60°-70°	508.9	5.9
70°-80°	289.1	3.4
80°-90°	87.4	1.0
90°-100°	46.3	0.5
100°-110°	295.4	3.4
110°-120°	565.1	6.6
120°-130°	717.4	8.3
130°-140°	767.5	8.9
140°-150°	717.7	8.3
150°-160°	578.8	6.7
160°-170°	373.3	4.3
170°-180°	128.7	1.5
0°-30°	1294.2	15.0
0°-40°	2077.6	24.1
0°-60°	3546.4	41.1
0°-90°	4431.8	51.4
90°-120°	906.8	10.5
90°-150°	3109.5	36.1
90°-180°	4190.0	48.6
0°-180°	8622.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	3	14	22	28	30	7
95°	56	23	22	28	29	72
105°	305	311	316	323	289	319
115°	569	572	571	573	574	560
125°	800	804	802	805	806	714
135°	993	992	996	998	1000	765
145°	1145	1148	1148	1149	1151	715
155°	1255	1256	1253	1257	1254	579
165°	1324	1319	1319	1326	1318	374
175°	1355	1349	1350	1358	1346	129
180°	1355	1355	1355	1355	1355	



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.4	29.6	29.9	30.1	30.4	30.5	30.7	30.8	30.9	31.0	31.3
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	12.8	12.9	13.0	13.2	13.3	14.3	16.1	17.9	19.7	21.5	22.8
95°	55.7	48.1	40.4	32.8	25.1	21.4	21.6	21.8	22.1	22.3	23.6
97.5°	118.3	123.1	127.9	132.7	137.4	127.3	102.1	77.0	51.9	26.7	26.9
100°	166.2	170.2	174.3	178.3	182.4	168.9	137.8	106.7	75.7	44.6	40.8
102.5°	219.7	222.6	225.6	228.6	231.5	231.0	227.0	222.9	218.8	214.8	173.5
105°	305.0	306.3	307.7	309.0	310.4	311.6	312.7	313.9	315.0	316.1	318.1
107.5°	384.2	384.9	385.5	386.2	386.9	388.0	389.5	391.1	392.6	394.1	395.1
110°	437.7	438.4	439.0	439.7	440.4	441.4	442.8	444.1	445.5	446.8	447.3



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.6	490.8	492.0	493.2	494.4	495.4	496.0	496.6	497.2	497.9	497.8
115°	569.4	570.1	570.8	571.4	572.1	572.3	572.1	571.9	571.7	571.4	571.9
117.5°	641.3	642.2	643.1	644.0	644.9	645.6	646.1	646.6	647.1	647.6	647.5
120°	690.0	690.9	691.8	692.7	693.6	693.9	693.7	693.5	693.2	693.0	693.5
122.5°	735.4	735.9	736.4	737.0	737.5	738.0	738.3	738.6	738.9	739.2	739.5
125°	800.4	801.3	802.2	803.1	804.0	804.2	803.8	803.3	802.9	802.4	803.1
127.5°	862.0	862.2	862.5	862.7	862.9	863.5	864.6	865.6	866.6	867.7	867.6
130°	901.7	902.0	902.2	902.4	902.6	903.1	903.8	904.4	905.1	905.8	906.0
132.5°	938.2	938.6	939.0	939.4	939.8	940.5	941.3	942.2	943.0	943.9	944.1
135°	992.9	992.7	992.5	992.2	992.0	992.4	993.3	994.2	995.1	996.0	996.4
137.5°	1041.3	1041.4	1041.5	1041.6	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7
140°	1073.0	1073.4	1073.9	1074.3	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7
142.5°	1101.3	1102.1	1102.9	1103.8	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7
145°	1144.9	1145.6	1146.2	1146.9	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2
147.5°	1179.5	1180.8	1182.1	1183.3	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4
150°	1204.7	1205.6	1206.5	1207.4	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7
152.5°	1225.7	1226.5	1227.2	1227.9	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5
155°	1255.3	1255.6	1255.8	1256.0	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2
157.5°	1280.3	1280.1	1280.0	1279.8	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4
160°	1294.8	1294.2	1293.5	1292.8	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1
162.5°	1307.8	1307.0	1306.1	1305.2	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3
165°	1324.2	1323.1	1322.0	1320.8	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0
167.5°	1337.2	1336.0	1334.9	1333.7	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3
170°	1344.5	1343.1	1341.8	1340.4	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2
172.5°	1349.3	1348.0	1346.6	1345.3	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1
175°	1354.6	1353.3	1351.9	1350.6	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6
177.5°	1357.0	1355.8	1354.5	1353.3	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	31.5	31.8	32.1	32.3	32.4	32.4	32.5	32.6
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	24.2	25.5	26.9	27.6	27.7	27.8	27.9	28.0
95°	25.0	26.3	27.7	28.5	28.7	28.9	29.2	29.4
97.5°	27.0	27.2	27.3	27.5	27.7	27.9	28.1	28.4
100°	36.9	33.1	29.3	27.5	27.7	27.9	28.1	28.4
102.5°	132.2	90.9	49.6	29.0	29.0	29.1	29.1	29.2
105°	320.2	322.2	324.2	321.2	313.1	305.0	296.9	288.8
107.5°	396.1	397.1	398.1	399.0	399.9	400.7	401.6	402.4
110°	447.7	448.2	448.6	449.2	449.9	450.5	451.2	451.9



TEST NUMBER: P332821

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.7	497.6	497.5	497.9	498.8	499.6	500.5	501.3
115°	572.3	572.8	573.2	573.5	573.5	573.5	573.5	573.5
117.5°	647.4	647.4	647.3	647.2	647.1	647.0	646.9	646.8
120°	693.9	694.4	694.8	694.8	694.4	693.9	693.5	693.0
122.5°	739.8	740.0	740.3	740.2	739.8	739.3	738.9	738.4
125°	803.8	804.5	805.1	805.6	805.8	806.0	806.3	806.5
127.5°	867.4	867.3	867.1	867.0	866.8	866.6	866.4	866.3
130°	906.2	906.5	906.7	906.8	906.8	906.8	906.8	906.8
132.5°	944.3	944.6	944.8	944.8	944.6	944.4	944.3	944.1
135°	996.9	997.3	997.8	998.2	998.7	999.1	999.6	1000.0
137.5°	1047.2	1047.7	1048.2	1048.4	1048.2	1048.1	1048.0	1047.8
140°	1078.4	1079.0	1079.7	1080.2	1080.4	1080.6	1080.8	1081.1
142.5°	1107.2	1107.7	1108.2	1108.4	1108.5	1108.5	1108.6	1108.6
145°	1148.4	1148.6	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1184.6	1184.7	1184.9	1185.1	1185.4	1185.6	1185.8	1186.0
150°	1207.7	1207.7	1207.7	1207.8	1208.0	1208.3	1208.5	1208.7
152.5°	1227.9	1228.2	1228.6	1228.7	1228.6	1228.4	1228.3	1228.2
155°	1255.1	1256.0	1256.9	1257.0	1256.3	1255.7	1255.0	1254.3
157.5°	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2
160°	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8
162.5°	1305.6	1307.0	1308.3	1308.3	1306.7	1305.2	1303.7	1302.1
165°	1322.8	1324.6	1326.4	1326.2	1324.2	1322.2	1320.2	1318.1
167.5°	1335.3	1337.3	1339.2	1339.1	1336.9	1334.6	1332.4	1330.1
170°	1343.0	1344.8	1346.6	1346.4	1344.1	1341.9	1339.6	1337.4
172.5°	1347.9	1349.7	1351.5	1351.2	1348.7	1346.3	1343.9	1341.4
175°	1353.6	1355.6	1357.7	1357.3	1354.6	1351.9	1349.2	1346.5
177.5°	1355.9	1357.3	1358.8	1358.4	1356.2	1354.1	1351.9	1349.8
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6

(END OF REPORT)