

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333085-840

Luminaire Tested: **S124RDIW-S1020D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333085-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D1050U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8448.6 lumens  
Efficiency: N/A  
Efficacy: 138.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	60	75	67	61	56	57	53	49	48	45	42	39	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.3	2.0
10°-20°	477.7	5.7
20°-30°	689.8	8.2
30°-40°	781.8	9.3
40°-50°	755.0	8.9
50°-60°	627.8	7.4
60°-70°	433.5	5.1
70°-80°	219.7	2.6
80°-90°	60.3	0.7
90°-100°	46.8	0.6
100°-110°	298.3	3.5
110°-120°	570.7	6.8
120°-130°	724.4	8.6
130°-140°	775.1	9.2
140°-150°	724.8	8.6
150°-160°	584.5	6.9
160°-170°	377.0	4.5
170°-180°	129.9	1.5
0°-30°	1338.7	15.8
0°-40°	2120.6	25.1
0°-60°	3503.4	41.5
0°-90°	4217.0	49.9
90°-120°	915.8	10.8
90°-150°	3140.1	37.2
90°-180°	4232.0	50.1
0°-180°	8448.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	3	14	22	28	31	6
95°	56	23	22	28	30	72
105°	308	314	319	326	292	322
115°	575	578	577	579	579	566
125°	808	812	810	813	814	721
135°	1003	1002	1006	1008	1010	772
145°	1156	1159	1159	1160	1162	722
155°	1268	1268	1266	1269	1267	584
165°	1337	1332	1332	1339	1331	378
175°	1368	1362	1363	1371	1360	130
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.3	24.8	23.3	21.8	20.4	19.7	19.8	19.9	20.0	20.1	20.2
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	12.9	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0
95°	56.2	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8
97.5°	119.5	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2
100°	167.8	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2
102.5°	221.9	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2
105°	308.0	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2
107.5°	388.0	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0
110°	442.0	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7



TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	494.4	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7
115°	575.0	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5
117.5°	647.6	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9
120°	696.8	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3
122.5°	742.7	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8
125°	808.3	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0
127.5°	870.5	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2
130°	910.6	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9
132.5°	947.5	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4
135°	1002.7	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2
137.5°	1051.6	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0
140°	1083.6	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3
142.5°	1112.2	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6
145°	1156.2	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5
147.5°	1191.1	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1
150°	1216.6	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6
152.5°	1237.8	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6
155°	1267.7	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6
157.5°	1292.9	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0
160°	1307.6	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8
162.5°	1320.7	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2
165°	1337.3	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0
167.5°	1350.4	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5
170°	1357.8	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4
172.5°	1362.6	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4
175°	1368.0	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9
177.5°	1370.4	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	20.2	20.2	20.2	20.4	20.8	21.1	21.4	21.8
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	24.4	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	25.2	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.3	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	37.3	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	133.5	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	323.4	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	400.0	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.1	452.6	453.0	453.6	454.3	454.9	455.7	456.4





TEST NUMBER: P333085-840

CATALOG NUMBER: S124RDIW-S1020D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	502.6	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	577.9	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.1	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	811.7	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	876.0	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.1	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.6	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1006.7	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1057.5	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.0	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.1	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.7	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.3	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.0	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1267.5	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1318.5	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1335.8	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1348.5	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1356.2	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1361.2	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1367.0	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1369.3	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)