

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332812

Luminaire Tested: **S124DIW-S1020D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332812
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7269.7 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	84	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50	46
3	84	75	67	62	79	71	64	59	62	57	53	55	51	48	48	45	43	39
4	77	66	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	29
6	66	54	45	39	62	51	43	38	45	39	35	40	35	32	35	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	29	26	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13472	13472	13472	13472
5°	15866	13507	11921	13507
10°	18996	13448	10733	13448
15°	22476	13312	9857	13312
20°	25027	13173	9075	13173
25°	25432	12968	8535	12968
30°	21640	12773	8364	12773
35°	16638	12454	8366	12454
40°	12968	12079	8524	12079
45°	10813	11515	8667	11515
50°	9516	10827	8960	10827
55°	8718	10003	9322	10003
60°	8170	9265	9755	9265
65°	7607	8437	10115	8437
70°	6951	7619	10346	7619
75°	6210	6706	10221	6706
80°	5207	5495	9898	5495
85°	3844	3974	9476	3974



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.6	2.2
10°-20°	501.1	6.9
20°-30°	794.6	10.9
30°-40°	884.3	12.2
40°-50°	805.0	11.1
50°-60°	657.8	9.0
60°-70°	469.6	6.5
70°-80°	258.6	3.6
80°-90°	73.5	1.0
90°-100°	63.3	0.9
100°-110°	187.5	2.6
110°-120°	318.2	4.4
120°-130°	419.6	5.8
130°-140°	471.3	6.5
140°-150°	463.1	6.4
150°-160°	389.5	5.4
160°-170°	259.1	3.6
170°-180°	90.7	1.2
0°-30°	1458.3	20.1
0°-40°	2342.7	32.2
0°-60°	3805.5	52.3
0°-90°	4607.2	63.4
90°-120°	569.0	7.8
90°-150°	1923.1	26.5
90°-180°	2662.0	36.6
0°-180°	7269.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1669	1669	1669	1669	1669	
5°	1958	1667	1471	1667	1958	199
15°	2689	1593	1179	1593	2689	760
25°	2855	1456	958	1456	2855	1259
35°	1688	1264	849	1264	1688	1072
45°	947	1009	759	1009	947	746
55°	619	711	662	711	619	560
65°	398	442	530	442	398	394
75°	199	215	328	215	199	212
85°	42	43	102	43	42	51
90°	22	2	22	2	22	13
95°	59	44	59	44	59	61
105°	181	173	181	173	181	191
115°	321	324	321	324	321	317
125°	468	471	468	471	468	417
135°	609	608	609	608	609	470
145°	739	738	739	738	739	463
155°	845	846	845	846	845	389
165°	919	921	919	921	919	259
175°	954	958	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1776.1	1775.6	1770.0	1768.9	1765.0	1760.1	1759.0	1750.1	1732.4	1724.1	1721.9
5°	1957.8	1971.6	1953.6	1950.2	1948.1	1925.3	1913.5	1899.7	1867.9	1849.2	1834.7
7.5°	2174.6	2176.2	2168.4	2162.0	2144.4	2124.5	2094.7	2062.9	2025.0	1985.6	1955.8
10°	2317.3	2322.8	2313.8	2312.4	2277.2	2255.0	2210.8	2173.5	2130.6	2082.9	2039.4
12.5°	2467.7	2459.9	2455.4	2425.8	2419.3	2378.9	2327.5	2289.1	2223.0	2168.1	2110.1
15°	2689.2	2674.0	2664.3	2623.5	2603.5	2547.5	2492.8	2450.7	2364.3	2282.0	2219.8
17.5°	2819.1	2834.4	2812.0	2795.2	2743.4	2704.1	2648.3	2559.8	2492.2	2390.0	2311.5
20°	2913.2	2914.5	2902.1	2884.8	2844.0	2794.3	2733.4	2636.6	2555.8	2454.1	2346.3
22.5°	2938.6	2938.9	2933.6	2917.4	2886.6	2846.2	2784.9	2704.1	2606.1	2495.6	2387.8
25°	2855.1	2852.3	2858.6	2876.5	2864.8	2852.3	2817.1	2756.9	2665.7	2548.8	2432.7
27.5°	2544.8	2563.9	2599.0	2643.3	2685.9	2718.4	2727.5	2715.2	2658.6	2562.5	2440.9
30°	2321.4	2344.9	2371.2	2415.4	2501.1	2550.2	2604.2	2644.9	2622.1	2545.4	2432.0
32.5°	2075.9	2081.7	2120.7	2171.0	2249.5	2343.9	2429.4	2512.2	2539.7	2499.5	2404.9
35°	1688.2	1697.8	1740.0	1789.8	1885.9	2001.3	2129.9	2244.7	2339.4	2377.4	2329.0
37.5°	1377.6	1405.4	1435.2	1488.7	1573.3	1677.2	1810.8	1959.3	2100.5	2195.0	2211.1
40°	1230.5	1247.8	1269.2	1310.0	1381.9	1484.2	1599.0	1769.1	1919.1	2054.6	2098.8
42.5°	1114.4	1124.5	1137.6	1174.5	1229.3	1331.0	1435.8	1585.4	1736.0	1898.0	1972.2
45°	947.1	957.5	979.6	1001.0	1042.5	1113.0	1210.5	1333.5	1484.9	1641.2	1778.0
47.5°	826.2	832.9	846.0	869.0	904.2	950.7	1030.0	1132.8	1273.1	1424.8	1570.6
50°	757.7	763.2	773.6	794.3	821.3	862.7	927.7	1023.8	1133.7	1286.5	1429.6
52.5°	703.5	705.7	713.3	727.4	748.8	783.7	837.0	916.5	1018.7	1154.9	1297.4
55°	619.4	622.2	629.1	639.5	658.1	680.2	721.0	780.5	869.7	987.9	1111.6
57.5°	550.3	552.2	558.0	562.0	577.4	595.4	626.7	669.2	736.8	837.0	947.5
60°	506.0	504.7	511.6	515.0	525.4	540.6	564.8	605.6	664.3	745.2	846.8
62.5°	462.9	461.0	466.8	471.3	477.3	490.3	510.0	542.0	589.7	662.8	750.6
65°	398.2	395.4	398.9	404.4	409.9	416.9	431.4	459.7	497.7	550.3	617.3
67.5°	333.2	336.1	336.7	339.4	342.6	352.0	362.0	382.0	408.8	450.9	507.7
70°	294.5	295.2	298.0	298.0	300.0	308.3	316.6	328.4	354.6	393.4	439.7
72.5°	255.8	258.7	257.6	259.8	261.3	266.8	272.9	284.1	306.5	335.3	374.4
75°	199.1	201.2	201.2	201.9	203.9	206.0	210.8	219.1	235.0	256.5	283.4
77.5°	145.2	145.5	146.4	148.9	148.9	152.2	155.8	162.5	170.3	185.0	201.4
80°	112.0	113.4	112.7	114.1	114.1	116.8	118.2	126.5	130.0	139.6	152.8
82.5°	82.1	83.5	83.4	85.3	86.4	87.0	88.9	92.2	95.7	104.2	109.6
85°	41.5	42.9	41.5	42.9	44.9	45.6	47.7	48.4	51.2	53.2	58.1
87.5°	16.6	18.2	18.1	18.6	19.7	20.1	20.5	19.7	21.7	22.1	24.0
90°	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3	17.3	16.3	15.0
92.5°	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6	30.0	29.4	28.5
95°	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4	56.9	56.4	55.3
97.5°	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4	89.8	89.2	87.9
100°	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2	113.9	113.6	112.1
102.5°	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4	139.0	138.5	137.1
105°	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6	177.1	176.6	176.0
107.5°	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0	218.5	218.1	218.0
110°	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5	246.8	247.1	247.3



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1	276.2	276.2	276.5
115°	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8	321.9	322.1	322.4
117.5°	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7	366.2	366.8	367.0
120°	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4	396.2	397.1	397.6
122.5°	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6	426.2	426.8	427.0
125°	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9	470.2	470.5	470.7
127.5°	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2	512.5	512.9	513.1
130°	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9	542.2	542.5	542.5
132.5°	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8	570.1	570.4	570.6
135°	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6	612.0	612.3	612.3
137.5°	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1	652.5	653.0	652.7
140°	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8	678.9	679.1	679.1
142.5°	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0	704.0	704.0	704.2
145°	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2	776.3	776.5	776.6
150°	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2	817.8	817.4	817.3
155°	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4	845.5
157.5°	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7	871.2	870.7	870.8
160°	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2	886.7	886.2	886.3
162.5°	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0	900.1	899.2	899.4
165°	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3	918.3	917.3	917.7
167.5°	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8	933.8	932.8	932.7
170°	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1	942.1	941.1	940.9
172.5°	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3	948.2	947.0	947.0
175°	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7	953.9
177.5°	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7	958.8	957.9	957.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1722.5	1714.7	1709.2	1704.8	1692.6	1685.4	1679.9	1672.1	1663.3	1653.9	1642.3
5°	1820.2	1796.7	1779.4	1753.2	1728.3	1707.5	1686.1	1666.7	1643.2	1617.7	1599.0
7.5°	1922.9	1888.0	1843.2	1804.3	1760.6	1722.6	1688.6	1653.7	1617.5	1582.4	1550.2
10°	1988.2	1943.3	1893.5	1834.7	1779.4	1730.3	1684.7	1640.5	1597.6	1554.7	1518.1
12.5°	2058.4	2002.4	1928.9	1860.2	1798.2	1732.6	1677.5	1623.3	1571.6	1526.5	1483.8
15°	2152.7	2071.8	1986.8	1894.9	1813.3	1736.6	1661.2	1592.8	1534.7	1475.2	1433.8
17.5°	2210.7	2110.6	2013.4	1917.3	1818.5	1721.8	1640.5	1561.5	1488.8	1429.8	1377.5
20°	2248.8	2149.3	2028.3	1932.2	1814.7	1715.1	1621.1	1533.3	1457.3	1394.4	1340.4
22.5°	2282.0	2167.0	2046.0	1919.5	1802.5	1696.9	1594.0	1505.7	1428.0	1361.7	1310.0
25°	2300.0	2167.9	2036.6	1910.8	1778.0	1652.9	1559.6	1455.9	1372.9	1303.1	1247.8
27.5°	2301.9	2160.7	2012.1	1872.3	1735.3	1618.8	1501.0	1408.3	1322.2	1248.4	1195.3
30°	2295.8	2148.6	1988.9	1837.5	1699.9	1573.4	1471.1	1370.2	1282.4	1209.1	1153.8
32.5°	2276.5	2123.1	1959.0	1798.8	1656.2	1532.5	1426.9	1330.9	1245.3	1173.1	1115.1
35°	2220.5	2069.1	1894.2	1727.6	1581.7	1456.6	1361.2	1263.7	1178.0	1109.5	1053.6
37.5°	2133.0	1996.1	1818.3	1645.9	1502.6	1376.9	1282.4	1194.3	1117.0	1047.5	990.1
40°	2056.6	1936.3	1758.0	1590.0	1435.2	1315.6	1227.1	1146.2	1069.5	1003.8	949.2
42.5°	1968.7	1863.9	1699.4	1521.4	1372.1	1252.0	1165.7	1093.1	1020.8	960.1	905.5
45°	1811.9	1742.8	1587.9	1423.4	1267.9	1154.5	1072.2	1008.6	947.8	888.3	842.7
47.5°	1631.6	1597.3	1467.0	1310.7	1163.1	1051.3	980.0	921.2	867.9	817.5	777.3
50°	1510.5	1493.9	1381.2	1230.5	1089.5	984.4	912.5	862.1	816.4	772.2	734.2
52.5°	1391.0	1390.5	1288.9	1150.9	1020.4	919.2	847.8	800.7	761.1	725.2	691.0
55°	1208.4	1227.8	1148.3	1025.2	908.4	817.1	752.8	710.7	683.0	653.3	627.7
57.5°	1040.7	1072.8	1007.2	898.8	801.4	717.3	661.3	629.6	600.2	582.2	563.6
60°	931.2	961.6	910.5	819.2	727.3	655.4	602.1	573.8	548.2	535.8	522.6
62.5°	833.9	861.0	823.1	738.5	658.7	589.5	544.6	517.4	500.1	486.5	477.8
65°	694.8	717.6	685.1	623.6	555.1	499.8	463.2	441.7	425.2	419.6	409.9
67.5°	561.6	582.4	564.8	512.5	457.6	415.8	387.1	366.5	356.7	351.9	345.0
70°	482.5	503.3	484.6	439.0	396.8	361.6	334.6	322.8	312.5	310.4	300.7
72.5°	415.6	429.7	411.1	375.4	339.3	309.6	288.7	276.4	271.0	267.3	262.0
75°	311.8	324.2	311.8	284.1	258.5	237.8	219.8	215.0	208.8	206.7	203.2
77.5°	220.7	231.4	221.9	204.6	185.5	169.5	159.8	153.6	152.2	148.6	150.3
80°	168.7	175.6	166.6	154.9	139.6	128.6	121.7	118.2	114.1	112.7	115.4
82.5°	121.1	124.2	119.6	111.7	100.4	93.2	88.5	84.5	83.6	83.9	83.9
85°	62.9	62.2	61.5	54.6	51.2	46.3	43.6	42.9	42.2	43.6	44.9
87.5°	23.8	24.0	23.2	20.7	18.7	16.7	15.7	14.8	15.7	16.7	17.6
90°	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2	4.0	5.9	7.7
92.5°	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9	18.0	20.0	22.1
95°	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5	46.0	47.5	49.0
97.5°	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8	79.0	80.2	81.3
100°	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9	104.6	105.2	105.9
102.5°	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2	131.5	131.7	132.0
105°	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9	173.1	173.3	173.4
107.5°	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7	216.9	217.1	217.3
110°	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4	246.7	247.1	247.4



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3	277.3	277.4	277.5
115°	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6	323.6	323.6	323.6
117.5°	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2	367.4	367.5	367.6
120°	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3	397.0	397.6	398.3
122.5°	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6	426.9	427.1	427.4
125°	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3
127.5°	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8	512.3	512.8	513.3
130°	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3	540.8	541.3	541.8
132.5°	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4	569.8	570.1	570.5
135°	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9	608.8	609.8	610.8
137.5°	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7	650.2	650.6	651.1
140°	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6	677.9	678.3	678.6
142.5°	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1	703.5	703.8	704.1
145°	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5	739.1	739.8	740.5
147.5°	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5	774.3	775.1	775.9
150°	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9	795.5	796.2	796.9
152.5°	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1	815.5	815.9	816.3
155°	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1	846.1	846.1	846.1
157.5°	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2	871.9	871.6	871.3
160°	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7	887.5	887.3	887.2
162.5°	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9	901.5	901.0	900.6
165°	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1	920.6	920.1	919.6
167.5°	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7	935.1	934.4	933.7
170°	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1	943.2	942.4	941.6
172.5°	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0	949.3	948.6	947.9
175°	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2	957.3	956.5	955.7
177.5°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1636.7	1631.8	1624.6	1614.6	1606.3	1597.5	1595.3	1591.9	1598.6	1593.0	1591.4
5°	1583.1	1568.6	1549.9	1528.5	1516.0	1498.1	1494.6	1487.7	1480.8	1480.1	1473.2
7.5°	1526.3	1505.0	1480.5	1458.7	1438.5	1418.8	1406.0	1403.2	1393.0	1387.0	1380.1
10°	1489.8	1463.5	1435.2	1414.4	1390.9	1370.2	1355.7	1347.4	1340.4	1332.8	1325.9
12.5°	1446.6	1418.7	1395.3	1372.9	1345.0	1329.2	1305.3	1290.9	1289.6	1289.7	1271.7
15°	1396.4	1368.8	1332.8	1301.0	1285.8	1255.4	1242.3	1225.7	1215.3	1204.9	1196.7
17.5°	1339.1	1304.6	1276.6	1240.1	1211.0	1186.8	1169.6	1159.6	1144.0	1129.3	1118.7
20°	1303.1	1266.5	1236.7	1198.0	1166.2	1136.5	1122.0	1108.2	1096.4	1084.0	1072.2
22.5°	1266.6	1228.3	1191.9	1154.3	1124.8	1093.4	1079.4	1060.6	1049.4	1042.5	1030.7
25°	1209.1	1167.6	1126.1	1090.2	1059.8	1032.1	1013.5	998.9	986.5	981.0	973.4
27.5°	1146.6	1105.4	1065.3	1024.5	990.0	969.9	955.0	944.0	936.9	929.5	926.1
30°	1106.8	1063.9	1021.1	983.0	951.2	931.2	917.4	909.8	904.2	900.8	897.3
32.5°	1066.4	1024.1	979.0	944.3	915.8	898.0	887.5	879.9	877.1	875.9	874.6
35°	1001.7	958.8	917.4	886.3	859.3	852.4	843.4	839.2	837.9	842.7	844.8
37.5°	939.1	899.3	861.1	830.9	813.3	803.2	800.1	800.3	805.2	809.5	814.5
40°	898.7	860.0	824.0	797.8	781.2	775.0	773.6	777.0	782.6	787.4	792.9
42.5°	859.4	821.3	788.6	764.0	752.4	746.7	747.6	751.0	758.8	764.7	773.0
45°	798.5	766.7	734.9	714.8	705.1	706.5	706.5	712.7	720.3	729.3	738.3
47.5°	741.1	709.0	682.9	666.0	661.0	659.8	663.7	671.8	682.7	693.8	706.4
50°	702.4	671.9	649.1	633.9	628.4	630.5	636.0	643.6	656.7	670.6	683.7
52.5°	663.1	635.4	614.3	600.2	596.3	600.1	605.6	617.6	629.1	644.0	659.9
55°	602.1	578.6	562.0	551.7	550.3	552.4	558.6	571.7	588.3	607.0	622.2
57.5°	541.4	521.8	506.6	499.4	500.1	502.0	512.3	527.9	545.6	565.5	585.1
60°	500.5	482.5	470.1	464.6	465.2	469.4	481.8	496.4	518.5	537.8	558.6
62.5°	461.8	446.0	434.1	429.2	428.2	437.3	449.2	464.3	486.4	508.0	530.4
65°	399.6	387.1	377.5	374.7	376.8	383.7	398.9	418.9	437.6	460.4	483.9
67.5°	338.7	328.5	321.9	323.1	325.6	335.8	348.6	365.8	387.0	410.6	433.9
70°	300.0	290.3	284.8	285.5	289.7	302.1	313.2	330.4	353.3	377.5	396.8
72.5°	260.2	253.8	248.9	251.8	255.9	264.5	278.3	295.6	315.7	338.2	358.6
75°	199.8	199.8	197.0	199.1	205.3	213.6	224.0	242.0	262.0	280.0	296.6
77.5°	148.2	146.7	148.5	151.0	154.6	164.4	176.3	189.1	204.2	222.2	235.9
80°	113.4	114.1	117.5	121.7	123.1	130.7	143.1	154.9	166.6	181.8	194.9
82.5°	85.2	85.9	87.7	92.9	94.3	102.5	110.5	122.2	132.9	143.1	154.0
85°	46.3	46.3	49.8	51.8	55.3	60.8	65.7	72.6	82.3	89.2	99.5
87.5°	19.6	19.9	22.4	23.8	25.7	28.7	30.0	36.3	38.7	41.7	46.8
90°	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3	19.3	20.3	20.9
92.5°	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6	31.2	31.8	32.2
95°	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4	57.9	58.4	58.6
97.5°	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4	91.0	91.6	91.9
100°	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2	114.5	114.9	115.0
102.5°	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4	139.9	140.3	140.6
105°	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6	178.1	178.6	179.1
107.5°	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0	219.4	219.9	220.1
110°	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5	246.2	245.8	245.9



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1	276.0	276.0	276.0
115°	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8	321.6	321.4	321.3
117.5°	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7	365.1	364.5	364.1
120°	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4	394.6	393.8	393.5
122.5°	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6	425.1	424.5	423.9
125°	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9	469.6	469.2	468.9
127.5°	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2	511.9	511.5	511.2
130°	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9	541.5	541.2	540.7
132.5°	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8	569.5	569.1	568.8
135°	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6	611.3	611.0	610.6
137.5°	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1	651.7	651.3	651.1
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8	678.6	678.4	678.3
142.5°	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0	703.9	703.9	703.9
145°	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9	741.7	741.5	741.2
147.5°	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2	776.1	775.9	775.8
150°	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.8
152.5°	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2	818.6	819.0	819.0
155°	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7	847.3	848.0	848.0
157.5°	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7	872.2	872.7	872.7
160°	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2	887.7	888.2	888.0
162.5°	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0	901.9	902.8	902.8
165°	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3	920.3	921.3	921.5
167.5°	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8	935.7	936.7	936.7
170°	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1	944.1	945.1	945.0
172.5°	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3	950.4	951.5	951.5
175°	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0	957.2	958.3	958.3
177.5°	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7	960.6	961.6	961.5
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1590.3	1589.2	1585.3	1584.8	1585.3	1589.2	1590.3	1591.4	1593.0	1598.6	1591.9
5°	1469.0	1465.6	1463.5	1471.1	1463.5	1465.6	1469.0	1473.2	1480.1	1480.8	1487.7
7.5°	1377.6	1374.9	1368.8	1366.9	1368.8	1374.9	1377.6	1380.1	1387.0	1393.0	1403.2
10°	1319.0	1316.2	1310.7	1309.3	1310.7	1316.2	1319.0	1325.9	1332.8	1340.4	1347.4
12.5°	1262.6	1257.1	1256.0	1257.3	1256.0	1257.1	1262.6	1271.7	1289.7	1289.6	1290.9
15°	1187.7	1184.9	1177.3	1179.4	1177.3	1184.9	1187.7	1196.7	1204.9	1215.3	1225.7
17.5°	1113.8	1110.5	1101.3	1109.4	1101.3	1110.5	1113.8	1118.7	1129.3	1144.0	1159.6
20°	1067.4	1061.8	1057.0	1056.3	1057.0	1061.8	1067.4	1072.2	1084.0	1096.4	1108.2
22.5°	1023.1	1018.2	1017.7	1013.2	1017.7	1018.2	1023.1	1030.7	1042.5	1049.4	1060.6
25°	967.8	963.0	961.6	958.2	961.6	963.0	967.8	973.4	981.0	986.5	998.9
27.5°	925.4	923.0	920.5	921.6	920.5	923.0	925.4	926.1	929.5	936.9	944.0
30°	899.4	898.7	897.3	897.3	897.3	898.7	899.4	897.3	900.8	904.2	909.8
32.5°	877.8	877.7	878.5	878.5	878.5	877.7	877.8	874.6	875.9	877.1	879.9
35°	847.5	849.6	851.0	848.9	851.0	849.6	847.5	844.8	842.7	837.9	839.2
37.5°	820.2	822.2	824.2	826.5	824.2	822.2	820.2	814.5	809.5	805.2	800.3
40°	799.1	804.0	805.4	808.8	805.4	804.0	799.1	792.9	787.4	782.6	777.0
42.5°	779.2	784.6	788.2	788.9	788.2	784.6	779.2	773.0	764.7	758.8	751.0
45°	748.7	754.2	759.1	759.1	759.1	754.2	748.7	738.3	729.3	720.3	712.7
47.5°	717.0	725.0	729.9	731.1	729.9	725.0	717.0	706.4	693.8	682.7	671.8
50°	695.5	705.1	710.0	713.4	710.0	705.1	695.5	683.7	670.6	656.7	643.6
52.5°	674.4	684.1	690.6	692.4	690.6	684.1	674.4	659.9	644.0	629.1	617.6
55°	638.1	651.9	659.5	662.3	659.5	651.9	638.1	622.2	607.0	588.3	571.7
57.5°	603.8	616.5	625.4	627.4	625.4	616.5	603.8	585.1	565.5	545.6	527.9
60°	577.2	591.1	602.1	604.2	602.1	591.1	577.2	558.6	537.8	518.5	496.4
62.5°	550.1	564.5	574.5	579.9	574.5	564.5	550.1	530.4	508.0	486.4	464.3
65°	503.3	517.8	527.5	529.5	527.5	517.8	503.3	483.9	460.4	437.6	418.9
67.5°	452.1	466.6	473.0	477.0	473.0	466.6	452.1	433.9	410.6	387.0	365.8
70°	416.2	427.9	434.8	438.3	434.8	427.9	416.2	396.8	377.5	353.3	330.4
72.5°	375.2	387.5	395.6	396.3	395.6	387.5	375.2	358.6	338.2	315.7	295.6
75°	312.5	323.5	327.7	327.7	327.7	323.5	312.5	296.6	280.0	262.0	242.0
77.5°	247.3	253.0	258.3	259.4	258.3	253.0	247.3	235.9	222.2	204.2	189.1
80°	205.3	208.8	212.9	212.9	212.9	208.8	205.3	194.9	181.8	166.6	154.9
82.5°	162.2	165.1	169.2	168.7	169.2	165.1	162.2	154.0	143.1	132.9	122.2
85°	98.2	104.4	103.7	102.3	103.7	104.4	98.2	99.5	89.2	82.3	72.6
87.5°	48.5	49.1	50.8	52.0	50.8	49.1	48.5	46.8	41.7	38.7	36.3
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3
92.5°	32.4	32.6	32.8	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6
95°	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4
97.5°	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4
100°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2
102.5°	140.8	140.9	141.0	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4
105°	179.6	180.1	180.6	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6
107.5°	220.1	220.1	220.0	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0
110°	246.4	246.9	247.4	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	276.1	276.2	276.3	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1
115°	321.1	321.0	320.8	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8
117.5°	363.8	363.4	363.1	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7
120°	393.9	394.2	394.5	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4
122.5°	423.3	422.7	422.2	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6
125°	468.6	468.2	467.9	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9
127.5°	511.0	510.7	510.4	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2
130°	540.1	539.4	538.7	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9
132.5°	568.6	568.3	568.0	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8
135°	610.1	609.6	609.1	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6
137.5°	651.2	651.3	651.4	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1
140°	678.1	677.9	677.8	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8
142.5°	703.8	703.8	703.8	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0
145°	740.7	740.2	739.7	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9
147.5°	775.6	775.5	775.3	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2
150°	797.6	797.4	797.3	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9
152.5°	818.6	818.2	817.7	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2
155°	847.3	846.7	846.0	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7
157.5°	872.1	871.6	871.0	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7
160°	887.2	886.3	885.5	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2
162.5°	902.0	901.2	900.4	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0
165°	920.8	920.1	919.5	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3
167.5°	935.7	934.7	933.7	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8
170°	943.8	942.7	941.5	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1
172.5°	950.3	949.2	948.0	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3
175°	957.2	956.0	954.9	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0
177.5°	960.4	959.4	958.3	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1595.3	1597.5	1606.3	1614.6	1624.6	1631.8	1636.7	1642.3	1653.9	1663.3	1672.1
5°	1494.6	1498.1	1516.0	1528.5	1549.9	1568.6	1583.1	1599.0	1617.7	1643.2	1666.7
7.5°	1406.0	1418.8	1438.5	1458.7	1480.5	1505.0	1526.3	1550.2	1582.4	1617.5	1653.7
10°	1355.7	1370.2	1390.9	1414.4	1435.2	1463.5	1489.8	1518.1	1554.7	1597.6	1640.5
12.5°	1305.3	1329.2	1345.0	1372.9	1395.3	1418.7	1446.6	1483.8	1526.5	1571.6	1623.3
15°	1242.3	1255.4	1285.8	1301.0	1332.8	1368.8	1396.4	1433.8	1475.2	1534.7	1592.8
17.5°	1169.6	1186.8	1211.0	1240.1	1276.6	1304.6	1339.1	1377.5	1429.8	1488.8	1561.5
20°	1122.0	1136.5	1166.2	1198.0	1236.7	1266.5	1303.1	1340.4	1394.4	1457.3	1533.3
22.5°	1079.4	1093.4	1124.8	1154.3	1191.9	1228.3	1266.6	1310.0	1361.7	1428.0	1505.7
25°	1013.5	1032.1	1059.8	1090.2	1126.1	1167.6	1209.1	1247.8	1303.1	1372.9	1455.9
27.5°	955.0	969.9	990.0	1024.5	1065.3	1105.4	1146.6	1195.3	1248.4	1322.2	1408.3
30°	917.4	931.2	951.2	983.0	1021.1	1063.9	1106.8	1153.8	1209.1	1282.4	1370.2
32.5°	887.5	898.0	915.8	944.3	979.0	1024.1	1066.4	1115.1	1173.1	1245.3	1330.9
35°	843.4	852.4	859.3	886.3	917.4	958.8	1001.7	1053.6	1109.5	1178.0	1263.7
37.5°	800.1	803.2	813.3	830.9	861.1	899.3	939.1	990.1	1047.5	1117.0	1194.3
40°	773.6	775.0	781.2	797.8	824.0	860.0	898.7	949.2	1003.8	1069.5	1146.2
42.5°	747.6	746.7	752.4	764.0	788.6	821.3	859.4	905.5	960.1	1020.8	1093.1
45°	706.5	706.5	705.1	714.8	734.9	766.7	798.5	842.7	888.3	947.8	1008.6
47.5°	663.7	659.8	661.0	666.0	682.9	709.0	741.1	777.3	817.5	867.9	921.2
50°	636.0	630.5	628.4	633.9	649.1	671.9	702.4	734.2	772.2	816.4	862.1
52.5°	605.6	600.1	596.3	600.2	614.3	635.4	663.1	691.0	725.2	761.1	800.7
55°	558.6	552.4	550.3	551.7	562.0	578.6	602.1	627.7	653.3	683.0	710.7
57.5°	512.3	502.0	500.1	499.4	506.6	521.8	541.4	563.6	582.2	600.2	629.6
60°	481.8	469.4	465.2	464.6	470.1	482.5	500.5	522.6	535.8	548.2	573.8
62.5°	449.2	437.3	428.2	429.2	434.1	446.0	461.8	477.8	486.5	500.1	517.4
65°	398.9	383.7	376.8	374.7	377.5	387.1	399.6	409.9	419.6	425.2	441.7
67.5°	348.6	335.8	325.6	323.1	321.9	328.5	338.7	345.0	351.9	356.7	366.5
70°	313.2	302.1	289.7	285.5	284.8	290.3	300.0	300.7	310.4	312.5	322.8
72.5°	278.3	264.5	255.9	251.8	248.9	253.8	260.2	262.0	267.3	271.0	276.4
75°	224.0	213.6	205.3	199.1	197.0	199.8	199.8	203.2	206.7	208.8	215.0
77.5°	176.3	164.4	154.6	151.0	148.5	146.7	148.2	150.3	148.6	152.2	153.6
80°	143.1	130.7	123.1	121.7	117.5	114.1	113.4	115.4	112.7	114.1	118.2
82.5°	110.5	102.5	94.3	92.9	87.7	85.9	85.2	83.9	83.9	83.6	84.5
85°	65.7	60.8	55.3	51.8	49.8	46.3	46.3	44.9	43.6	42.2	42.9
87.5°	30.0	28.7	25.7	23.8	22.4	19.9	19.6	17.6	16.7	15.7	14.8
90°	17.3	16.3	15.0	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2
92.5°	30.0	29.4	28.5	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9
95°	56.9	56.4	55.3	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5
97.5°	89.8	89.2	87.9	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8
100°	113.9	113.6	112.1	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9
102.5°	139.0	138.5	137.1	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2
105°	177.1	176.6	176.0	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9
107.5°	218.5	218.1	218.0	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7
110°	246.8	247.1	247.3	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	276.2	276.2	276.5	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3
115°	321.9	322.1	322.4	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6
117.5°	366.2	366.8	367.0	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2
120°	396.2	397.1	397.6	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3
122.5°	426.2	426.8	427.0	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6
125°	470.2	470.5	470.7	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3
127.5°	512.5	512.9	513.1	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8
130°	542.2	542.5	542.5	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3
132.5°	570.1	570.4	570.6	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4
135°	612.0	612.3	612.3	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9
137.5°	652.5	653.0	652.7	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6
142.5°	704.0	704.0	704.2	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1
145°	742.0	742.2	742.0	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5
147.5°	776.3	776.5	776.6	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5
150°	797.9	797.9	797.9	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9
152.5°	817.8	817.4	817.3	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1
155°	846.0	845.4	845.5	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1
157.5°	871.2	870.7	870.8	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2
160°	886.7	886.2	886.3	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7
162.5°	900.1	899.2	899.4	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9
165°	918.3	917.3	917.7	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1
167.5°	933.8	932.8	932.7	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7
170°	942.1	941.1	940.9	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1
172.5°	948.2	947.0	947.0	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0
175°	954.9	953.7	953.9	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2
177.5°	958.8	957.9	957.9	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1679.9	1685.4	1692.6	1704.8	1709.2	1714.7	1722.5	1721.9	1724.1	1732.4	1750.1
5°	1686.1	1707.5	1728.3	1753.2	1779.4	1796.7	1820.2	1834.7	1849.2	1867.9	1899.7
7.5°	1688.6	1722.6	1760.6	1804.3	1843.2	1888.0	1922.9	1955.8	1985.6	2025.0	2062.9
10°	1684.7	1730.3	1779.4	1834.7	1893.5	1943.3	1988.2	2039.4	2082.9	2130.6	2173.5
12.5°	1677.5	1732.6	1798.2	1860.2	1928.9	2002.4	2058.4	2110.1	2168.1	2223.0	2289.1
15°	1661.2	1736.6	1813.3	1894.9	1986.8	2071.8	2152.7	2219.8	2282.0	2364.3	2450.7
17.5°	1640.5	1721.8	1818.5	1917.3	2013.4	2110.6	2210.7	2311.5	2390.0	2492.2	2559.8
20°	1621.1	1715.1	1814.7	1932.2	2028.3	2149.3	2248.8	2346.3	2454.1	2555.8	2636.6
22.5°	1594.0	1696.9	1802.5	1919.5	2046.0	2167.0	2282.0	2387.8	2495.6	2606.1	2704.1
25°	1559.6	1652.9	1778.0	1910.8	2036.6	2167.9	2300.0	2432.7	2548.8	2665.7	2756.9
27.5°	1501.0	1618.8	1735.3	1872.3	2012.1	2160.7	2301.9	2440.9	2562.5	2658.6	2715.2
30°	1471.1	1573.4	1699.9	1837.5	1988.9	2148.6	2295.8	2432.0	2545.4	2622.1	2644.9
32.5°	1426.9	1532.5	1656.2	1798.8	1959.0	2123.1	2276.5	2404.9	2499.5	2539.7	2512.2
35°	1361.2	1456.6	1581.7	1727.6	1894.2	2069.1	2220.5	2329.0	2377.4	2339.4	2244.7
37.5°	1282.4	1376.9	1502.6	1645.9	1818.3	1996.1	2133.0	2211.1	2195.0	2100.5	1959.3
40°	1227.1	1315.6	1435.2	1590.0	1758.0	1936.3	2056.6	2098.8	2054.6	1919.1	1769.1
42.5°	1165.7	1252.0	1372.1	1521.4	1699.4	1863.9	1968.7	1972.2	1898.0	1736.0	1585.4
45°	1072.2	1154.5	1267.9	1423.4	1587.9	1742.8	1811.9	1778.0	1641.2	1484.9	1333.5
47.5°	980.0	1051.3	1163.1	1310.7	1467.0	1597.3	1631.6	1570.6	1424.8	1273.1	1132.8
50°	912.5	984.4	1089.5	1230.5	1381.2	1493.9	1510.5	1429.6	1286.5	1133.7	1023.8
52.5°	847.8	919.2	1020.4	1150.9	1288.9	1390.5	1391.0	1297.4	1154.9	1018.7	916.5
55°	752.8	817.1	908.4	1025.2	1148.3	1227.8	1208.4	1111.6	987.9	869.7	780.5
57.5°	661.3	717.3	801.4	898.8	1007.2	1072.8	1040.7	947.5	837.0	736.8	669.2
60°	602.1	655.4	727.3	819.2	910.5	961.6	931.2	846.8	745.2	664.3	605.6
62.5°	544.6	589.5	658.7	738.5	823.1	861.0	833.9	750.6	662.8	589.7	542.0
65°	463.2	499.8	555.1	623.6	685.1	717.6	694.8	617.3	550.3	497.7	459.7
67.5°	387.1	415.8	457.6	512.5	564.8	582.4	561.6	507.7	450.9	408.8	382.0
70°	334.6	361.6	396.8	439.0	484.6	503.3	482.5	439.7	393.4	354.6	328.4
72.5°	288.7	309.6	339.3	375.4	411.1	429.7	415.6	374.4	335.3	306.5	284.1
75°	219.8	237.8	258.5	284.1	311.8	324.2	311.8	283.4	256.5	235.0	219.1
77.5°	159.8	169.5	185.5	204.6	221.9	231.4	220.7	201.4	185.0	170.3	162.5
80°	121.7	128.6	139.6	154.9	166.6	175.6	168.7	152.8	139.6	130.0	126.5
82.5°	88.5	93.2	100.4	111.7	119.6	124.2	121.1	109.6	104.2	95.7	92.2
85°	43.6	46.3	51.2	54.6	61.5	62.2	62.9	58.1	53.2	51.2	48.4
87.5°	15.7	16.7	18.7	20.7	23.2	24.0	23.8	24.0	22.1	21.7	19.7
90°	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3
92.5°	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6
95°	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4
97.5°	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4
100°	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2
102.5°	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4
105°	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6
107.5°	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0
110°	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1
115°	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8
117.5°	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7
120°	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4
122.5°	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6
125°	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9
127.5°	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2
130°	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9
132.5°	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8
135°	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6
137.5°	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1
140°	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8
142.5°	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0
145°	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9
147.5°	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2
150°	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2
155°	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7
157.5°	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7
160°	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2
162.5°	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0
165°	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3
167.5°	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8
170°	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1
172.5°	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3
175°	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0
177.5°	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1759.0	1760.1	1765.0	1768.9	1770.0	1775.6	1776.1
5°	1913.5	1925.3	1948.1	1950.2	1953.6	1971.6	1957.8
7.5°	2094.7	2124.5	2144.4	2162.0	2168.4	2176.2	2174.6
10°	2210.8	2255.0	2277.2	2312.4	2313.8	2322.8	2317.3
12.5°	2327.5	2378.9	2419.3	2425.8	2455.4	2459.9	2467.7
15°	2492.8	2547.5	2603.5	2623.5	2664.3	2674.0	2689.2
17.5°	2648.3	2704.1	2743.4	2795.2	2812.0	2834.4	2819.1
20°	2733.4	2794.3	2844.0	2884.8	2902.1	2914.5	2913.2
22.5°	2784.9	2846.2	2886.6	2917.4	2933.6	2938.9	2938.6
25°	2817.1	2852.3	2864.8	2876.5	2858.6	2852.3	2855.1
27.5°	2727.5	2718.4	2685.9	2643.3	2599.0	2563.9	2544.8
30°	2604.2	2550.2	2501.1	2415.4	2371.2	2344.9	2321.4
32.5°	2429.4	2343.9	2249.5	2171.0	2120.7	2081.7	2075.9
35°	2129.9	2001.3	1885.9	1789.8	1740.0	1697.8	1688.2
37.5°	1810.8	1677.2	1573.3	1488.7	1435.2	1405.4	1377.6
40°	1599.0	1484.2	1381.9	1310.0	1269.2	1247.8	1230.5
42.5°	1435.8	1331.0	1229.3	1174.5	1137.6	1124.5	1114.4
45°	1210.5	1113.0	1042.5	1001.0	979.6	957.5	947.1
47.5°	1030.0	950.7	904.2	869.0	846.0	832.9	826.2
50°	927.7	862.7	821.3	794.3	773.6	763.2	757.7
52.5°	837.0	783.7	748.8	727.4	713.3	705.7	703.5
55°	721.0	680.2	658.1	639.5	629.1	622.2	619.4
57.5°	626.7	595.4	577.4	562.0	558.0	552.2	550.3
60°	564.8	540.6	525.4	515.0	511.6	504.7	506.0
62.5°	510.0	490.3	477.3	471.3	466.8	461.0	462.9
65°	431.4	416.9	409.9	404.4	398.9	395.4	398.2
67.5°	362.0	352.0	342.6	339.4	336.7	336.1	333.2
70°	316.6	308.3	300.0	298.0	298.0	295.2	294.5
72.5°	272.9	266.8	261.3	259.8	257.6	258.7	255.8
75°	210.8	206.0	203.9	201.9	201.2	201.2	199.1
77.5°	155.8	152.2	148.9	148.9	146.4	145.5	145.2
80°	118.2	116.8	114.1	114.1	112.7	113.4	112.0
82.5°	88.9	87.0	86.4	85.3	83.4	83.5	82.1
85°	47.7	45.6	44.9	42.9	41.5	42.9	41.5
87.5°	20.5	20.1	19.7	18.6	18.1	18.2	16.6
90°	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.2	245.8	245.9	246.4	246.9	247.4	247.9



TEST NUMBER: P332812

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)