

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333081-840

Luminaire Tested: **S124RDIW-S1020D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333081-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7316.1 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	88	88	88		75	75	75		63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73		66	65	63		56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61		59	56	53		50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51		52	48	45		44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44		47	42	39		40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38		42	38	34		36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33		38	33	30		33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30		35	30	27		30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26		32	27	24		28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24		29	25	22		26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22		27	23	20		24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	2.3
10°-20°	477.7	6.5
20°-30°	689.8	9.4
30°-40°	781.8	10.7
40°-50°	755.0	10.3
50°-60°	627.8	8.6
60°-70°	433.5	5.9
70°-80°	219.7	3.0
80°-90°	59.3	0.8
90°-100°	34.3	0.5
100°-110°	218.6	3.0
110°-120°	418.1	5.7
120°-130°	530.7	7.3
130°-140°	567.9	7.8
140°-150°	531.0	7.3
150°-160°	428.2	5.9
160°-170°	276.2	3.8
170°-180°	95.2	1.3
0°-30°	1338.7	18.3
0°-40°	2120.6	29.0
0°-60°	3503.4	47.9
0°-90°	4215.9	57.6
90°-120°	670.9	9.2
90°-150°	2300.6	31.4
90°-180°	3100.0	42.4
0°-180°	7316.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	2	10	16	21	22	5
95°	41	17	16	21	22	53
105°	226	230	234	239	214	236
115°	421	423	423	424	424	414
125°	592	595	594	596	597	529
135°	735	734	737	738	740	566
145°	847	849	849	850	852	529
155°	929	929	927	930	928	428
165°	980	976	976	981	975	277
175°	1002	998	998	1004	996	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.2	24.5	22.9	21.3	19.7	18.9	18.9	18.9	18.9	19.0	18.9
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	9.5	9.6	9.7	9.7	9.8	10.6	11.9	13.2	14.5	15.9	16.9
95°	41.2	35.5	29.9	24.2	18.6	15.9	16.0	16.2	16.4	16.5	17.5
97.5°	87.6	91.1	94.6	98.2	101.7	94.1	75.5	57.0	38.4	19.8	19.9
100°	122.9	125.9	129.0	131.9	134.9	124.9	102.0	79.0	55.9	33.0	30.2
102.5°	162.5	164.7	166.9	169.2	171.3	170.9	167.9	164.9	161.9	159.0	128.4
105°	225.6	226.6	227.6	228.6	229.6	230.6	231.4	232.2	233.1	233.9	235.4
107.5°	284.3	284.8	285.3	285.8	286.3	287.1	288.2	289.3	290.4	291.5	292.4
110°	323.9	324.4	324.9	325.4	325.8	326.6	327.6	328.6	329.6	330.5	330.9



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	362.2	363.1	364.1	364.9	365.8	366.5	367.0	367.4	367.9	368.4	368.3
115°	421.3	421.8	422.3	422.7	423.2	423.4	423.2	423.1	422.9	422.7	423.1
117.5°	474.5	475.1	475.8	476.5	477.2	477.7	478.1	478.4	478.8	479.2	479.1
120°	510.5	511.2	511.8	512.5	513.1	513.4	513.2	513.1	512.9	512.7	513.1
122.5°	544.1	544.4	544.8	545.2	545.6	545.9	546.2	546.4	546.6	546.9	547.1
125°	592.2	592.9	593.5	594.2	594.8	595.0	594.7	594.4	594.0	593.7	594.2
127.5°	637.7	637.9	638.1	638.2	638.4	638.9	639.6	640.5	641.2	642.0	641.9
130°	667.1	667.3	667.5	667.6	667.8	668.1	668.6	669.1	669.6	670.1	670.3
132.5°	694.2	694.5	694.8	695.0	695.3	695.8	696.4	697.1	697.7	698.3	698.5
135°	734.6	734.5	734.3	734.1	734.0	734.2	734.9	735.5	736.2	736.9	737.2
137.5°	770.4	770.5	770.6	770.6	770.7	771.1	771.8	772.5	773.4	774.1	774.4
140°	793.9	794.2	794.5	794.9	795.2	795.5	795.9	796.2	796.5	796.9	797.3
142.5°	814.9	815.5	816.1	816.6	817.2	817.6	817.8	818.0	818.2	818.4	818.8
145°	847.1	847.6	848.1	848.6	849.1	849.3	849.3	849.3	849.3	849.3	849.5
147.5°	872.7	873.6	874.5	875.5	876.5	876.8	876.7	876.5	876.3	876.2	876.3
150°	891.3	891.9	892.6	893.3	893.9	894.2	894.0	893.8	893.7	893.5	893.5
152.5°	906.9	907.4	908.0	908.5	909.0	909.1	908.8	908.6	908.3	908.0	908.2
155°	928.8	929.0	929.1	929.3	929.5	929.3	928.8	928.3	927.8	927.3	928.0
157.5°	947.3	947.2	947.1	947.0	946.8	946.4	945.9	945.3	944.7	944.2	945.0
160°	958.0	957.5	957.0	956.5	956.0	955.6	955.5	955.3	955.1	955.0	956.0
162.5°	967.6	966.9	966.3	965.7	965.0	964.6	964.5	964.3	964.1	964.0	965.0
165°	979.8	978.9	978.1	977.2	976.4	976.0	976.0	976.0	976.0	976.0	977.3
167.5°	989.4	988.5	987.6	986.7	985.8	985.4	985.3	985.2	985.1	985.0	986.4
170°	994.7	993.7	992.7	991.7	990.8	990.3	990.5	990.7	990.8	991.0	992.3
172.5°	998.4	997.3	996.3	995.3	994.3	993.9	994.1	994.2	994.4	994.6	995.9
175°	1002.2	1001.2	1000.3	999.3	998.3	997.8	997.9	998.2	998.4	998.5	1000.0
177.5°	1004.0	1003.1	1002.2	1001.2	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	18.9	18.8	18.8	18.9	19.2	19.5	19.8	20.1
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	17.9	18.9	19.9	20.4	20.5	20.6	20.6	20.7
95°	18.5	19.5	20.5	21.1	21.2	21.4	21.6	21.7
97.5°	20.0	20.1	20.2	20.3	20.5	20.7	20.8	21.0
100°	27.4	24.4	21.6	20.3	20.5	20.7	20.8	21.0
102.5°	97.9	67.3	36.8	21.4	21.5	21.5	21.5	21.6
105°	236.9	238.3	239.8	237.6	231.7	225.6	219.6	213.7
107.5°	293.1	293.8	294.6	295.2	295.9	296.5	297.1	297.7
110°	331.2	331.5	331.9	332.3	332.9	333.4	333.9	334.4



TEST NUMBER: P333081-840

CATALOG NUMBER: S124RDIW-S1020D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.2	368.2	368.1	368.4	369.0	369.6	370.3	370.9
115°	423.4	423.7	424.1	424.2	424.2	424.2	424.2	424.2
117.5°	479.0	479.0	478.9	478.8	478.8	478.7	478.6	478.6
120°	513.4	513.7	514.0	514.0	513.7	513.4	513.1	512.7
122.5°	547.3	547.5	547.8	547.6	547.3	546.9	546.6	546.3
125°	594.7	595.2	595.7	596.0	596.2	596.3	596.5	596.7
127.5°	641.8	641.7	641.6	641.5	641.4	641.2	641.1	641.0
130°	670.4	670.7	670.9	670.9	670.9	670.9	670.9	670.9
132.5°	698.6	698.8	699.0	699.0	698.9	698.7	698.6	698.5
135°	737.5	737.9	738.2	738.5	738.8	739.2	739.5	739.8
137.5°	774.8	775.2	775.5	775.7	775.6	775.5	775.4	775.3
140°	797.8	798.3	798.8	799.2	799.3	799.5	799.7	799.8
142.5°	819.2	819.5	819.9	820.1	820.1	820.1	820.2	820.2
145°	849.6	849.8	850.0	850.2	850.5	850.9	851.2	851.5
147.5°	876.4	876.6	876.7	876.9	877.0	877.2	877.4	877.5
150°	893.5	893.5	893.5	893.6	893.8	893.9	894.1	894.2
152.5°	908.5	908.7	909.0	909.1	909.0	908.9	908.8	908.7
155°	928.6	929.3	929.9	930.0	929.5	929.0	928.5	928.1
157.5°	945.9	946.8	947.7	947.7	946.8	945.9	945.0	944.2
160°	957.0	958.0	959.0	959.0	958.0	957.0	956.0	955.0
162.5°	966.0	966.9	968.0	968.0	966.8	965.6	964.5	963.4
165°	978.7	980.0	981.3	981.3	979.8	978.3	976.7	975.2
167.5°	988.0	989.4	990.9	990.8	989.1	987.4	985.7	984.1
170°	993.6	995.0	996.3	996.1	994.5	992.8	991.2	989.5
172.5°	997.2	998.6	999.9	999.7	997.8	996.1	994.3	992.5
175°	1001.5	1003.0	1004.5	1004.2	1002.2	1000.3	998.3	996.2
177.5°	1003.2	1004.2	1005.3	1005.0	1003.4	1001.8	1000.3	998.7
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2

(END OF REPORT)