

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333104-840

Luminaire Tested: **S124RDIW-S1195D1050U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333104-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8732.5 lumens  
Efficiency: N/A  
Efficacy: 129.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	92	84	78	73	85	79	74	69	69	65	62	59	57	54	51	49	47	43
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	43	40	37
4	77	66	59	53	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	48	41	35	56	46	39	34	40	35	31	36	31	28	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	40	33	28	49	38	31	27	34	28	25	30	26	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16156	16156	16156	16156
5°	18739	16204	14323	16204
10°	22168	16133	12782	16133
15°	25607	15984	10984	15984
20°	28511	15779	9933	15779
25°	29432	15577	9222	15577
30°	25765	15333	8793	15333
35°	20056	14970	8535	14970
40°	15039	14556	8395	14556
45°	11875	13891	8322	13891
50°	10025	13123	8081	13123
55°	8739	12279	7648	12279
60°	7863	11404	6770	11404
65°	6930	10457	5822	10457
70°	6243	9477	5254	9477
75°	5231	8400	4476	8400
80°	4421	7159	4198	7159
85°	3733	5604	3733	5604



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.9	2.2
10°-20°	584.9	6.7
20°-30°	914.8	10.5
30°-40°	1017.0	11.6
40°-50°	902.3	10.3
50°-60°	703.1	8.1
60°-70°	460.3	5.3
70°-80°	226.4	2.6
80°-90°	59.8	0.7
90°-100°	87.2	1.0
100°-110°	258.4	3.0
110°-120°	438.7	5.0
120°-130°	578.4	6.6
130°-140°	649.6	7.4
140°-150°	638.4	7.3
150°-160°	536.9	6.1
160°-170°	357.2	4.1
170°-180°	125.1	1.4
0°-30°	1693.6	19.4
0°-40°	2710.6	31.0
0°-60°	4316.0	49.4
0°-90°	5062.5	58.0
90°-120°	784.3	9.0
90°-150°	2650.7	30.4
90°-180°	3670.0	42.0
0°-180°	8732.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	2312	2000	1767	2000	2312	234
15°	3064	1912	1314	1912	3064	871
25°	3304	1749	1035	1749	3304	1466
35°	2035	1519	866	1519	2035	1276
45°	1040	1217	729	1217	1040	824
55°	621	872	543	872	621	565
65°	363	547	305	547	363	365
75°	168	269	144	269	168	185
85°	40	60	40	60	40	46
90°	31	3	31	3	31	17
95°	81	61	81	61	81	84
105°	250	238	250	238	250	263
115°	442	446	442	446	442	437
125°	644	650	644	650	644	575
135°	839	838	839	838	839	648
145°	1019	1018	1019	1018	1019	638
155°	1165	1166	1165	1166	1165	536
165°	1266	1270	1266	1270	1266	357
175°	1315	1321	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2110.8	2116.7	2110.8	2110.2	2103.8	2101.8	2099.2	2090.8	2075.4	2066.4	2068.3
5°	2312.4	2332.6	2321.3	2319.7	2302.0	2284.2	2272.9	2247.2	2219.7	2201.2	2185.9
7.5°	2545.6	2557.2	2550.1	2538.8	2510.1	2493.9	2467.7	2433.7	2384.5	2346.9	2312.6
10°	2704.3	2713.9	2710.8	2689.8	2668.8	2626.1	2601.9	2554.4	2492.2	2443.1	2397.1
12.5°	2860.3	2870.7	2842.4	2843.3	2803.6	2770.0	2731.6	2671.7	2600.0	2536.6	2479.0
15°	3063.9	3051.0	3051.0	3034.8	2990.5	2943.8	2904.3	2841.4	2751.1	2675.2	2595.5
17.5°	3223.2	3227.7	3221.1	3183.1	3148.3	3099.9	3027.5	2954.1	2870.2	2768.4	2686.8
20°	3318.7	3318.7	3311.4	3285.6	3240.5	3188.9	3110.7	3030.8	2924.4	2822.0	2730.1
22.5°	3357.4	3359.9	3351.4	3330.1	3289.5	3239.1	3172.6	3091.5	2981.8	2866.5	2752.7
25°	3304.2	3319.5	3321.0	3315.5	3303.4	3272.7	3215.5	3132.4	3034.0	2909.1	2786.5
27.5°	3033.5	3052.9	3069.9	3097.8	3134.8	3154.2	3156.7	3114.5	3028.7	2908.4	2785.1
30°	2763.9	2780.1	2832.5	2901.0	2954.3	3002.6	3044.5	3055.9	3007.5	2899.4	2769.6
32.5°	2464.7	2486.6	2539.0	2612.7	2701.4	2783.3	2877.5	2925.5	2924.3	2859.4	2739.3
35°	2035.1	2051.2	2099.6	2177.0	2283.4	2405.2	2554.4	2670.4	2749.5	2743.8	2670.4
37.5°	1641.2	1659.5	1708.4	1772.5	1875.7	2026.5	2170.8	2330.8	2476.9	2559.0	2534.5
40°	1427.1	1427.9	1475.5	1541.7	1638.4	1769.8	1927.0	2104.4	2267.2	2400.3	2426.1
42.5°	1258.1	1258.3	1289.7	1361.0	1430.7	1554.4	1704.5	1880.6	2071.2	2224.8	2293.2
45°	1040.1	1047.3	1073.2	1115.9	1170.7	1275.6	1395.6	1559.3	1773.0	1955.2	2068.9
47.5°	880.8	891.4	907.9	942.7	986.4	1056.2	1155.6	1302.6	1476.4	1676.9	1838.7
50°	798.2	799.8	820.8	840.1	878.1	933.7	1020.8	1143.3	1302.9	1495.6	1675.5
52.5°	727.3	726.9	739.5	764.1	794.9	838.2	908.5	1020.1	1161.6	1334.4	1520.0
55°	620.9	624.9	634.5	653.9	677.3	707.9	763.6	847.4	958.7	1106.2	1274.8
57.5°	539.9	542.0	549.6	557.7	579.3	601.5	643.3	701.5	795.4	916.1	1073.2
60°	487.0	487.8	490.2	502.3	519.3	540.2	568.5	617.6	696.6	807.1	931.3
62.5°	435.4	436.9	440.6	449.4	462.5	477.0	506.5	546.0	611.5	705.8	817.7
65°	362.8	363.7	369.3	372.5	382.9	395.9	417.7	444.2	489.4	568.5	653.1
67.5°	303.2	303.2	303.5	307.8	315.1	323.7	336.7	358.0	392.0	440.6	515.2
70°	264.5	264.5	266.1	268.5	272.6	279.7	287.0	303.2	328.2	367.7	425.0
72.5°	228.3	228.9	230.6	231.1	233.2	239.1	244.5	254.8	273.4	303.2	349.4
75°	167.7	170.2	174.2	177.4	181.4	180.6	186.2	192.7	198.3	216.1	242.7
77.5°	124.8	123.5	124.0	126.7	127.2	128.1	132.1	137.0	141.3	149.7	159.2
80°	95.1	95.1	97.6	98.4	97.6	98.4	102.4	104.8	106.4	109.7	118.6
82.5°	71.9	73.2	72.4	73.2	73.7	74.5	77.9	78.4	80.0	81.3	85.0
85°	40.3	41.1	41.9	40.3	40.3	40.3	41.9	42.7	44.3	43.5	45.1
87.5°	20.3	19.6	20.2	20.1	20.6	19.8	20.2	21.2	19.6	20.0	19.6
90°	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2	23.8	22.5	20.7
92.5°	45.4	45.1	44.8	44.6	44.3	43.8	42.9	42.1	41.3	40.5	39.3
95°	80.8	80.8	80.8	80.8	80.8	80.5	79.8	79.1	78.5	77.8	76.1
97.5°	126.6	126.6	126.6	126.6	126.6	126.2	125.4	124.6	123.8	123.0	121.1
100°	158.5	158.5	158.5	158.5	158.5	158.3	157.8	157.4	156.9	156.5	154.5
102.5°	194.6	194.4	194.2	194.0	193.9	193.5	192.8	192.2	191.6	190.9	189.0
105°	249.6	248.9	248.2	247.6	246.9	246.2	245.5	244.9	244.2	243.5	242.6
107.5°	303.3	303.3	303.4	303.4	303.4	303.2	302.5	301.8	301.2	300.5	300.4
110°	341.7	341.0	340.3	339.6	339.0	338.8	339.3	339.7	340.2	340.6	340.9



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.0	380.8	380.7	380.6	380.4	380.4	380.5	380.6	380.7	380.8	381.2
115°	441.9	442.2	442.4	442.6	442.8	443.1	443.3	443.5	443.7	444.0	444.4
117.5°	500.1	500.5	501.0	501.4	501.9	502.5	503.2	504.0	504.8	505.5	505.9
120°	544.2	543.8	543.3	542.9	542.4	542.8	543.9	545.0	546.2	547.3	548.1
122.5°	581.1	581.9	582.7	583.5	584.3	585.1	585.9	586.7	587.4	588.2	588.5
125°	644.5	645.0	645.4	645.9	646.3	646.8	647.2	647.7	648.1	648.6	648.8
127.5°	703.3	703.6	704.0	704.3	704.7	705.1	705.6	706.0	706.5	706.9	707.3
130°	741.7	742.7	743.6	744.5	745.4	746.0	746.5	746.9	747.4	747.8	747.8
132.5°	782.6	782.9	783.4	783.8	784.1	784.5	785.0	785.4	785.9	786.3	786.5
135°	838.9	839.6	840.2	840.9	841.6	842.2	842.6	843.1	843.5	844.0	844.0
137.5°	898.0	897.9	897.8	897.6	897.5	897.7	898.3	898.9	899.5	900.1	899.7
140°	934.0	934.2	934.5	934.7	934.9	935.1	935.4	935.6	935.8	936.0	936.0
142.5°	970.1	970.1	970.2	970.2	970.2	970.3	970.3	970.4	970.4	970.5	970.7
145°	1019.0	1019.7	1020.3	1021.0	1021.7	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1068.4	1068.6	1068.9	1069.1	1069.3	1069.5	1069.8	1070.0	1070.2	1070.3	1070.5
150°	1098.7	1098.9	1099.2	1099.4	1099.6	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1126.6	1127.1	1127.7	1128.3	1128.9	1128.9	1128.4	1127.8	1127.3	1126.8	1126.6
155°	1165.3	1166.2	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3	1165.5
157.5°	1199.8	1200.6	1201.3	1202.1	1203.0	1203.0	1202.2	1201.6	1200.9	1200.2	1200.2
160°	1219.4	1220.6	1221.7	1222.8	1224.0	1224.3	1223.6	1222.8	1222.1	1221.5	1221.7
162.5°	1239.9	1241.0	1242.2	1243.3	1244.5	1244.5	1243.1	1241.9	1240.7	1239.5	1239.7
165°	1266.5	1267.4	1268.3	1269.2	1270.1	1269.9	1268.6	1267.2	1265.9	1264.5	1265.0
167.5°	1285.6	1287.0	1288.4	1289.8	1291.2	1291.2	1289.8	1288.5	1287.1	1285.8	1285.7
170°	1296.2	1297.8	1299.4	1301.0	1302.5	1302.6	1301.3	1299.9	1298.6	1297.2	1297.0
172.5°	1305.1	1306.8	1308.4	1310.0	1311.5	1311.6	1310.0	1308.5	1307.0	1305.4	1305.4
175°	1314.6	1316.2	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6	1314.8
177.5°	1319.5	1321.0	1322.4	1323.8	1325.3	1325.4	1324.1	1322.9	1321.6	1320.3	1320.3
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2061.8	2052.9	2048.3	2038.0	2025.7	2019.2	2013.5	2005.1	1994.1	1982.5	1974.1
5°	2166.5	2147.2	2122.9	2094.0	2068.1	2043.2	2021.3	1999.6	1974.6	1948.8	1923.0
7.5°	2273.9	2235.8	2194.7	2147.2	2100.8	2058.8	2020.0	1983.0	1941.1	1903.5	1869.3
10°	2348.7	2297.1	2239.9	2179.4	2118.9	2066.5	2014.9	1968.1	1916.5	1870.6	1831.9
12.5°	2409.3	2348.7	2279.9	2204.5	2131.8	2068.4	2009.1	1948.1	1889.5	1839.7	1788.1
15°	2509.9	2426.9	2334.2	2243.9	2149.6	2063.3	1983.5	1912.5	1845.6	1775.4	1726.3
17.5°	2579.2	2480.6	2367.9	2259.4	2148.0	2046.2	1954.1	1869.7	1792.4	1720.8	1662.2
20°	2620.4	2511.5	2386.6	2263.2	2138.3	2029.4	1930.3	1836.7	1756.9	1679.5	1619.0
22.5°	2643.6	2523.1	2386.6	2257.5	2128.0	2010.0	1901.2	1803.8	1716.9	1639.5	1572.6
25°	2651.1	2522.0	2382.6	2234.2	2092.3	1967.3	1854.4	1748.8	1652.0	1574.7	1503.7
27.5°	2640.8	2488.8	2346.0	2193.7	2047.3	1915.6	1797.1	1686.1	1589.2	1506.1	1433.4
30°	2625.2	2462.4	2309.2	2151.2	2002.8	1876.2	1751.2	1644.9	1544.1	1457.7	1384.4
32.5°	2591.7	2430.1	2265.3	2103.4	1953.2	1822.7	1704.1	1597.1	1498.2	1410.1	1332.1
35°	2525.3	2361.6	2182.6	2016.5	1869.0	1733.5	1622.2	1519.0	1424.7	1330.4	1248.1
37.5°	2437.7	2270.5	2092.4	1910.6	1762.8	1635.0	1532.9	1436.0	1343.9	1257.8	1166.7
40°	2355.2	2202.8	2018.9	1838.4	1686.8	1563.4	1469.1	1381.2	1288.5	1203.0	1111.9
42.5°	2255.2	2125.4	1939.6	1758.4	1608.7	1489.9	1402.0	1316.1	1231.7	1148.8	1053.8
45°	2088.3	1989.9	1815.7	1641.6	1490.9	1373.1	1292.5	1216.7	1142.5	1063.5	974.0
47.5°	1897.0	1830.4	1680.1	1501.8	1362.3	1256.4	1178.5	1116.5	1053.8	974.8	896.3
50°	1764.1	1721.4	1576.3	1413.4	1280.4	1182.9	1103.0	1044.9	992.5	916.8	846.6
52.5°	1622.2	1599.5	1476.9	1321.2	1192.7	1097.0	1028.9	976.5	923.5	860.6	795.0
55°	1406.1	1418.3	1314.2	1179.6	1058.6	978.1	915.9	872.4	827.3	774.1	723.3
57.5°	1185.3	1229.4	1159.6	1041.4	928.1	853.5	806.8	770.1	732.3	688.1	644.7
60°	1053.0	1090.0	1050.6	946.5	847.4	778.1	734.6	706.3	668.4	628.1	595.0
62.5°	924.0	963.7	940.3	856.3	764.2	704.6	666.1	639.9	611.7	576.5	542.2
65°	761.9	787.7	776.5	718.4	653.1	602.3	566.8	547.4	521.7	495.8	465.2
67.5°	583.6	633.4	626.8	596.0	539.6	499.9	476.7	459.6	436.1	416.9	396.1
70°	479.8	525.7	524.9	499.9	469.3	432.1	416.1	401.5	380.5	362.0	345.1
72.5°	392.6	434.7	441.0	421.8	400.9	372.8	357.4	347.4	327.0	314.3	300.5
75°	275.0	305.6	313.7	313.7	304.0	289.4	275.8	269.3	254.8	243.5	235.4
77.5°	180.3	199.7	212.2	215.1	216.6	211.8	200.5	195.9	184.8	180.8	173.0
80°	127.3	140.3	154.8	159.7	163.7	162.1	157.2	154.0	143.5	139.5	136.2
82.5°	88.1	95.1	107.0	117.8	116.5	120.8	116.5	114.0	106.1	104.6	101.4
85°	45.9	46.8	48.4	55.6	59.7	61.3	62.1	60.5	58.1	58.1	52.4
87.5°	19.3	18.3	19.2	18.8	18.9	21.0	22.4	22.5	21.1	19.7	18.3
90°	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0	5.6	8.1	10.6
92.5°	38.0	36.7	35.4	33.3	30.5	27.7	24.7	21.9	24.7	27.7	30.5
95°	74.5	73.0	71.4	69.6	67.6	65.4	63.4	61.4	63.4	65.4	67.6
97.5°	119.3	117.3	115.5	113.8	112.1	110.5	108.9	107.2	108.9	110.5	112.1
100°	152.4	150.4	148.3	146.8	145.9	145.0	144.1	143.2	144.1	145.0	145.9
102.5°	187.1	185.3	183.4	182.3	182.0	181.6	181.3	180.9	181.3	181.6	182.0
105°	241.7	240.8	239.8	239.2	239.0	238.8	238.6	238.3	238.6	238.8	239.0
107.5°	300.3	300.1	300.0	299.8	299.5	299.2	299.0	298.7	299.0	299.2	299.5
110°	341.1	341.3	341.5	341.4	341.0	340.5	340.1	339.6	340.1	340.5	341.0





TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	381.6	382.0	382.4	382.5	382.4	382.4	382.3	382.2	382.3	382.4	382.4
115°	444.9	445.4	445.9	446.1	446.1	446.1	446.1	446.1	446.1	446.1	446.1
117.5°	506.2	506.5	506.9	507.0	506.8	506.5	506.3	506.2	506.3	506.5	506.8
120°	548.7	549.4	550.1	550.0	549.1	548.2	547.2	546.3	547.2	548.2	549.1
122.5°	588.9	589.2	589.6	589.5	589.2	588.8	588.4	588.0	588.4	588.8	589.2
125°	649.0	649.2	649.5	649.6	649.6	649.6	649.6	649.6	649.6	649.6	649.6
127.5°	707.6	708.0	708.4	708.2	707.5	706.8	706.2	705.5	706.2	706.8	707.5
130°	747.8	747.8	747.8	747.5	746.8	746.1	745.5	744.8	745.5	746.1	746.8
132.5°	786.7	786.9	787.0	786.9	786.4	785.9	785.4	784.9	785.4	785.9	786.4
135°	844.0	844.0	844.0	843.3	841.9	840.6	839.2	837.9	839.2	840.6	841.9
137.5°	899.4	899.0	898.6	898.1	897.5	896.9	896.2	895.5	896.2	896.9	897.5
140°	936.0	936.0	936.0	935.8	935.4	934.9	934.5	934.0	934.5	934.9	935.4
142.5°	970.8	971.0	971.2	971.1	970.6	970.2	969.7	969.3	969.7	970.2	970.6
145°	1022.6	1022.4	1022.1	1021.6	1020.7	1019.8	1018.9	1017.9	1018.9	1019.8	1020.7
147.5°	1070.7	1070.9	1071.1	1070.6	1069.4	1068.4	1067.3	1066.2	1067.3	1068.4	1069.4
150°	1099.7	1099.7	1099.7	1099.3	1098.4	1097.5	1096.6	1095.7	1096.6	1097.5	1098.4
152.5°	1126.4	1126.2	1126.0	1125.7	1125.1	1124.6	1124.1	1123.5	1124.1	1124.6	1125.1
155°	1165.7	1165.9	1166.2	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3
157.5°	1200.3	1200.3	1200.4	1200.6	1201.0	1201.4	1201.8	1202.2	1201.8	1201.4	1201.0
160°	1221.9	1222.1	1222.4	1222.6	1222.8	1223.0	1223.4	1223.6	1223.4	1223.0	1222.8
162.5°	1240.0	1240.2	1240.4	1240.8	1241.4	1242.0	1242.6	1243.1	1242.6	1242.0	1241.4
165°	1265.4	1265.9	1266.3	1266.9	1267.6	1268.2	1268.9	1269.6	1268.9	1268.2	1267.6
167.5°	1285.7	1285.7	1285.6	1286.1	1287.0	1288.0	1288.9	1289.8	1288.9	1288.0	1287.0
170°	1296.8	1296.6	1296.3	1296.8	1297.9	1299.0	1300.2	1301.3	1300.2	1299.0	1297.9
172.5°	1305.4	1305.3	1305.3	1305.7	1306.7	1307.6	1308.5	1309.5	1308.5	1307.6	1306.7
175°	1315.0	1315.2	1315.6	1316.2	1317.4	1318.5	1319.6	1320.7	1319.6	1318.5	1317.4
177.5°	1320.3	1320.3	1320.3	1320.8	1321.7	1322.6	1323.5	1324.4	1323.5	1322.6	1321.7
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1965.1	1958.6	1950.3	1940.6	1928.9	1918.6	1914.1	1918.0	1920.0	1914.8	1914.1
5°	1905.2	1885.1	1869.0	1844.8	1825.4	1809.3	1798.1	1793.2	1794.8	1781.9	1778.7
7.5°	1838.1	1814.1	1787.7	1759.0	1732.2	1708.5	1696.1	1689.3	1675.7	1669.8	1660.0
10°	1794.8	1762.5	1736.8	1702.8	1672.2	1644.1	1630.3	1619.0	1605.3	1598.8	1585.2
12.5°	1750.3	1712.8	1684.5	1649.3	1618.0	1584.1	1570.9	1550.0	1528.5	1515.0	1497.4
15°	1687.6	1642.4	1607.7	1565.8	1528.7	1490.1	1455.3	1416.6	1402.1	1371.5	1353.7
17.5°	1614.2	1568.4	1525.5	1469.3	1412.0	1363.9	1327.0	1289.9	1267.7	1248.1	1239.1
20°	1565.8	1523.9	1464.2	1398.9	1335.2	1282.0	1252.1	1228.0	1203.8	1190.1	1180.4
22.5°	1520.0	1466.4	1397.1	1326.7	1262.9	1221.3	1196.1	1171.2	1151.5	1138.5	1125.6
25°	1443.3	1373.1	1299.7	1219.1	1175.6	1139.3	1111.9	1091.7	1079.6	1062.7	1056.2
27.5°	1364.4	1279.4	1198.5	1144.3	1098.9	1065.7	1041.9	1026.7	1011.4	1000.6	992.2
30°	1303.7	1217.5	1144.9	1093.3	1047.3	1020.0	1000.6	982.9	970.8	961.9	955.4
32.5°	1243.7	1157.5	1096.5	1041.1	1004.8	978.1	957.4	944.1	934.6	923.2	919.3
35°	1157.0	1080.5	1027.2	977.2	940.1	915.9	899.8	886.2	878.1	874.8	872.4
37.5°	1073.7	1010.9	953.7	912.7	879.7	860.6	841.6	834.9	829.3	823.5	826.2
40°	1020.8	961.9	911.1	867.6	840.9	820.0	808.7	800.6	795.8	795.8	795.8
42.5°	974.9	917.4	867.9	828.9	802.2	784.6	771.9	765.2	763.6	763.0	766.8
45°	903.8	850.6	800.6	768.4	745.8	728.1	720.8	715.2	715.2	718.4	719.2
47.5°	833.3	783.6	743.4	707.3	686.6	675.5	669.2	666.3	666.6	669.8	673.6
50°	790.1	740.9	701.5	669.2	649.8	639.3	633.7	632.2	633.7	633.7	639.3
52.5°	743.1	699.0	660.1	633.1	611.2	601.4	598.2	596.0	596.9	599.6	602.0
55°	674.1	634.5	597.4	571.7	555.5	549.1	541.8	542.6	541.0	542.6	542.6
57.5°	604.9	569.4	534.9	514.4	500.2	490.9	482.9	485.2	482.8	482.5	481.2
60°	560.4	521.7	494.2	475.7	459.6	451.5	444.2	445.9	443.4	441.8	438.6
62.5°	512.0	479.8	453.6	435.8	422.8	413.4	406.2	404.6	399.0	393.4	386.4
65°	441.8	415.3	391.8	375.0	362.8	355.6	349.9	345.1	333.0	320.1	313.7
67.5°	373.7	354.5	332.6	318.3	308.5	299.0	288.2	279.9	268.6	261.6	257.5
70°	329.7	311.2	292.7	278.9	268.5	259.6	247.5	241.9	233.8	230.6	226.6
72.5°	287.8	270.5	253.4	241.0	229.7	222.9	213.4	207.7	204.2	202.9	198.8
75°	224.2	210.5	197.5	186.2	177.4	172.6	168.5	164.5	162.9	155.6	151.6
77.5°	163.5	154.5	146.4	138.4	132.1	128.9	121.1	116.4	113.7	110.3	109.5
80°	127.3	121.0	112.9	108.1	99.2	95.9	92.7	91.9	91.1	90.3	89.5
82.5°	95.8	89.4	81.3	78.4	75.9	74.0	72.1	71.3	70.5	71.0	70.8
85°	48.4	45.1	45.1	44.3	43.5	42.7	41.9	41.9	41.1	41.9	41.1
87.5°	18.8	18.5	18.9	18.0	19.0	19.3	19.0	19.2	20.2	19.2	19.3
90°	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2	26.6	28.0	28.9
92.5°	33.3	35.4	36.7	38.0	39.3	40.5	41.3	42.1	42.9	43.8	44.3
95°	69.6	71.4	73.0	74.5	76.1	77.8	78.5	79.1	79.8	80.5	80.8
97.5°	113.8	115.5	117.3	119.3	121.1	123.0	123.8	124.6	125.4	126.2	126.6
100°	146.8	148.3	150.4	152.4	154.5	156.5	156.9	157.4	157.8	158.3	158.5
102.5°	182.3	183.4	185.3	187.1	189.0	190.9	191.6	192.2	192.8	193.5	193.9
105°	239.2	239.8	240.8	241.7	242.6	243.5	244.2	244.9	245.5	246.2	246.9
107.5°	299.8	300.0	300.1	300.3	300.4	300.5	301.2	301.8	302.5	303.2	303.4
110°	341.4	341.5	341.3	341.1	340.9	340.6	340.2	339.7	339.3	338.8	339.0



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.5	382.4	382.0	381.6	381.2	380.8	380.7	380.6	380.5	380.4	380.4
115°	446.1	445.9	445.4	444.9	444.4	444.0	443.7	443.5	443.3	443.1	442.8
117.5°	507.0	506.9	506.5	506.2	505.9	505.5	504.8	504.0	503.2	502.5	501.9
120°	550.0	550.1	549.4	548.7	548.1	547.3	546.2	545.0	543.9	542.8	542.4
122.5°	589.5	589.6	589.2	588.9	588.5	588.2	587.4	586.7	585.9	585.1	584.3
125°	649.6	649.5	649.2	649.0	648.8	648.6	648.1	647.7	647.2	646.8	646.3
127.5°	708.2	708.4	708.0	707.6	707.3	706.9	706.5	706.0	705.6	705.1	704.7
130°	747.5	747.8	747.8	747.8	747.8	747.8	747.4	746.9	746.5	746.0	745.4
132.5°	786.9	787.0	786.9	786.7	786.5	786.3	785.9	785.4	785.0	784.5	784.1
135°	843.3	844.0	844.0	844.0	844.0	844.0	843.5	843.1	842.6	842.2	841.6
137.5°	898.1	898.6	899.0	899.4	899.7	900.1	899.5	898.9	898.3	897.7	897.5
140°	935.8	936.0	936.0	936.0	936.0	936.0	935.8	935.6	935.4	935.1	934.9
142.5°	971.1	971.2	971.0	970.8	970.7	970.5	970.4	970.4	970.3	970.3	970.2
145°	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8	1022.6	1022.4	1022.1	1021.7
147.5°	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2	1070.0	1069.8	1069.5	1069.3
150°	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.6
152.5°	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3	1127.8	1128.4	1128.9	1128.9
155°	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2	1167.1	1168.0	1168.9	1168.9
157.5°	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9	1201.6	1202.2	1203.0	1203.0
160°	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1	1222.8	1223.6	1224.3	1224.0
162.5°	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7	1241.9	1243.1	1244.5	1244.5
165°	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9	1267.2	1268.6	1269.9	1270.1
167.5°	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1	1288.5	1289.8	1291.2	1291.2
170°	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6	1299.9	1301.3	1302.6	1302.5
172.5°	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0	1308.5	1310.0	1311.6	1311.5
175°	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2	1317.8	1319.4	1321.0	1321.0
177.5°	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6	1322.9	1324.1	1325.4	1325.3
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1910.3	1911.6	1907.0	1905.7	1907.0	1911.6	1910.3	1914.1	1914.8	1920.0	1918.0
5°	1772.2	1770.6	1766.6	1767.4	1766.6	1770.6	1772.2	1778.7	1781.9	1794.8	1793.2
7.5°	1654.2	1647.9	1649.6	1643.3	1649.6	1647.9	1654.2	1660.0	1669.8	1675.7	1689.3
10°	1582.0	1573.1	1565.8	1559.3	1565.8	1573.1	1582.0	1585.2	1598.8	1605.3	1619.0
12.5°	1483.3	1475.6	1465.8	1467.7	1465.8	1475.6	1483.3	1497.4	1515.0	1528.5	1550.0
15°	1343.2	1331.2	1311.8	1314.2	1311.8	1331.2	1343.2	1353.7	1371.5	1402.1	1416.6
17.5°	1224.8	1224.9	1216.1	1218.1	1216.1	1224.9	1224.8	1239.1	1248.1	1267.7	1289.9
20°	1163.5	1157.8	1158.6	1156.2	1158.6	1157.8	1163.5	1180.4	1190.1	1203.8	1228.0
22.5°	1120.8	1114.0	1108.3	1103.3	1108.3	1114.0	1120.8	1125.6	1138.5	1151.5	1171.2
25°	1048.9	1044.1	1036.9	1035.3	1036.9	1044.1	1048.9	1056.2	1062.7	1079.6	1091.7
27.5°	985.7	984.8	981.9	978.2	981.9	984.8	985.7	992.2	1000.6	1011.4	1026.7
30°	949.0	947.4	945.7	943.3	945.7	947.4	949.0	955.4	961.9	970.8	982.9
32.5°	916.1	915.1	913.5	913.7	913.5	915.1	916.1	919.3	923.2	934.6	944.1
35°	869.2	868.4	866.8	866.0	866.8	868.4	869.2	872.4	874.8	878.1	886.2
37.5°	825.4	827.4	826.5	826.3	826.5	827.4	825.4	826.2	823.5	829.3	834.9
40°	795.0	795.8	797.4	796.6	797.4	795.8	795.0	795.8	795.8	795.8	800.6
42.5°	769.8	770.0	772.2	769.5	772.2	770.0	769.8	766.8	763.0	763.6	765.2
45°	724.9	729.7	728.9	728.9	728.9	729.7	724.9	719.2	718.4	715.2	715.2
47.5°	675.7	679.8	681.0	680.9	681.0	679.8	675.7	673.6	669.8	666.6	666.3
50°	643.4	641.8	644.2	643.4	644.2	641.8	643.4	639.3	633.7	633.7	632.2
52.5°	604.1	604.4	604.2	603.4	604.2	604.4	604.1	602.0	599.6	596.9	596.0
55°	543.4	544.2	542.6	543.4	542.6	544.2	543.4	542.6	542.6	541.0	542.6
57.5°	477.7	473.7	475.3	473.4	475.3	473.7	477.7	481.2	482.5	482.8	485.2
60°	430.6	424.1	422.5	419.3	422.5	424.1	430.6	438.6	441.8	443.4	445.9
62.5°	377.7	373.1	367.7	370.2	367.7	373.1	377.7	386.4	393.4	399.0	404.6
65°	307.2	304.0	301.5	304.8	301.5	304.0	307.2	313.7	320.1	333.0	345.1
67.5°	254.3	252.6	252.6	251.0	252.6	252.6	254.3	257.5	261.6	268.6	279.9
70°	226.6	224.2	224.2	222.6	224.2	224.2	226.6	226.6	230.6	233.8	241.9
72.5°	198.1	195.8	196.4	195.4	196.4	195.8	198.1	198.8	202.9	204.2	207.7
75°	146.7	142.7	142.7	143.5	142.7	142.7	146.7	151.6	155.6	162.9	164.5
77.5°	109.5	108.7	109.8	108.4	109.8	108.7	109.5	109.5	110.3	113.7	116.4
80°	89.5	88.7	87.9	90.3	87.9	88.7	89.5	89.5	90.3	91.1	91.9
82.5°	69.5	69.4	69.2	72.2	69.2	69.4	69.5	70.8	71.0	70.5	71.3
85°	41.9	40.3	41.9	40.3	41.9	40.3	41.9	41.1	41.9	41.1	41.9
87.5°	20.7	20.2	19.6	20.3	19.6	20.2	20.7	19.3	19.2	20.2	19.2
90°	29.3	29.8	30.2	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2
92.5°	44.6	44.8	45.1	45.4	45.1	44.8	44.6	44.3	43.8	42.9	42.1
95°	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.5	79.8	79.1
97.5°	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.2	125.4	124.6
100°	158.5	158.5	158.5	158.5	158.5	158.5	158.5	158.5	158.3	157.8	157.4
102.5°	194.0	194.2	194.4	194.6	194.4	194.2	194.0	193.9	193.5	192.8	192.2
105°	247.6	248.2	248.9	249.6	248.9	248.2	247.6	246.9	246.2	245.5	244.9
107.5°	303.4	303.4	303.3	303.3	303.3	303.4	303.4	303.4	303.2	302.5	301.8
110°	339.6	340.3	341.0	341.7	341.0	340.3	339.6	339.0	338.8	339.3	339.7



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	380.6	380.7	380.8	381.0	380.8	380.7	380.6	380.4	380.4	380.5	380.6
115°	442.6	442.4	442.2	441.9	442.2	442.4	442.6	442.8	443.1	443.3	443.5
117.5°	501.4	501.0	500.5	500.1	500.5	501.0	501.4	501.9	502.5	503.2	504.0
120°	542.9	543.3	543.8	544.2	543.8	543.3	542.9	542.4	542.8	543.9	545.0
122.5°	583.5	582.7	581.9	581.1	581.9	582.7	583.5	584.3	585.1	585.9	586.7
125°	645.9	645.4	645.0	644.5	645.0	645.4	645.9	646.3	646.8	647.2	647.7
127.5°	704.3	704.0	703.6	703.3	703.6	704.0	704.3	704.7	705.1	705.6	706.0
130°	744.5	743.6	742.7	741.7	742.7	743.6	744.5	745.4	746.0	746.5	746.9
132.5°	783.8	783.4	782.9	782.6	782.9	783.4	783.8	784.1	784.5	785.0	785.4
135°	840.9	840.2	839.6	838.9	839.6	840.2	840.9	841.6	842.2	842.6	843.1
137.5°	897.6	897.8	897.9	898.0	897.9	897.8	897.6	897.5	897.7	898.3	898.9
140°	934.7	934.5	934.2	934.0	934.2	934.5	934.7	934.9	935.1	935.4	935.6
142.5°	970.2	970.2	970.1	970.1	970.1	970.2	970.2	970.2	970.3	970.3	970.4
145°	1021.0	1020.3	1019.7	1019.0	1019.7	1020.3	1021.0	1021.7	1022.1	1022.4	1022.6
147.5°	1069.1	1068.9	1068.6	1068.4	1068.6	1068.9	1069.1	1069.3	1069.5	1069.8	1070.0
150°	1099.4	1099.2	1098.9	1098.7	1098.9	1099.2	1099.4	1099.6	1099.7	1099.7	1099.7
152.5°	1128.3	1127.7	1127.1	1126.6	1127.1	1127.7	1128.3	1128.9	1128.9	1128.4	1127.8
155°	1168.0	1167.1	1166.2	1165.3	1166.2	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1
157.5°	1202.1	1201.3	1200.6	1199.8	1200.6	1201.3	1202.1	1203.0	1203.0	1202.2	1201.6
160°	1222.8	1221.7	1220.6	1219.4	1220.6	1221.7	1222.8	1224.0	1224.3	1223.6	1222.8
162.5°	1243.3	1242.2	1241.0	1239.9	1241.0	1242.2	1243.3	1244.5	1244.5	1243.1	1241.9
165°	1269.2	1268.3	1267.4	1266.5	1267.4	1268.3	1269.2	1270.1	1269.9	1268.6	1267.2
167.5°	1289.8	1288.4	1287.0	1285.6	1287.0	1288.4	1289.8	1291.2	1291.2	1289.8	1288.5
170°	1301.0	1299.4	1297.8	1296.2	1297.8	1299.4	1301.0	1302.5	1302.6	1301.3	1299.9
172.5°	1310.0	1308.4	1306.8	1305.1	1306.8	1308.4	1310.0	1311.5	1311.6	1310.0	1308.5
175°	1319.4	1317.8	1316.2	1314.6	1316.2	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8
177.5°	1323.8	1322.4	1321.0	1319.5	1321.0	1322.4	1323.8	1325.3	1325.4	1324.1	1322.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1914.1	1918.6	1928.9	1940.6	1950.3	1958.6	1965.1	1974.1	1982.5	1994.1	2005.1
5°	1798.1	1809.3	1825.4	1844.8	1869.0	1885.1	1905.2	1923.0	1948.8	1974.6	1999.6
7.5°	1696.1	1708.5	1732.2	1759.0	1787.7	1814.1	1838.1	1869.3	1903.5	1941.1	1983.0
10°	1630.3	1644.1	1672.2	1702.8	1736.8	1762.5	1794.8	1831.9	1870.6	1916.5	1968.1
12.5°	1570.9	1584.1	1618.0	1649.3	1684.5	1712.8	1750.3	1788.1	1839.7	1889.5	1948.1
15°	1455.3	1490.1	1528.7	1565.8	1607.7	1642.4	1687.6	1726.3	1775.4	1845.6	1912.5
17.5°	1327.0	1363.9	1412.0	1469.3	1525.5	1568.4	1614.2	1662.2	1720.8	1792.4	1869.7
20°	1252.1	1282.0	1335.2	1398.9	1464.2	1523.9	1565.8	1619.0	1679.5	1756.9	1836.7
22.5°	1196.1	1221.3	1262.9	1326.7	1397.1	1466.4	1520.0	1572.6	1639.5	1716.9	1803.8
25°	1111.9	1139.3	1175.6	1219.1	1299.7	1373.1	1443.3	1503.7	1574.7	1652.0	1748.8
27.5°	1041.9	1065.7	1098.9	1144.3	1198.5	1279.4	1364.4	1433.4	1506.1	1589.2	1686.1
30°	1000.6	1020.0	1047.3	1093.3	1144.9	1217.5	1303.7	1384.4	1457.7	1544.1	1644.9
32.5°	957.4	978.1	1004.8	1041.1	1096.5	1157.5	1243.7	1332.1	1410.1	1498.2	1597.1
35°	899.8	915.9	940.1	977.2	1027.2	1080.5	1157.0	1248.1	1330.4	1424.7	1519.0
37.5°	841.6	860.6	879.7	912.7	953.7	1010.9	1073.7	1166.7	1257.8	1343.9	1436.0
40°	808.7	820.0	840.9	867.6	911.1	961.9	1020.8	1111.9	1203.0	1288.5	1381.2
42.5°	771.9	784.6	802.2	828.9	867.9	917.4	974.9	1053.8	1148.8	1231.7	1316.1
45°	720.8	728.1	745.8	768.4	800.6	850.6	903.8	974.0	1063.5	1142.5	1216.7
47.5°	669.2	675.5	686.6	707.3	743.4	783.6	833.3	896.3	974.8	1053.8	1116.5
50°	633.7	639.3	649.8	669.2	701.5	740.9	790.1	846.6	916.8	992.5	1044.9
52.5°	598.2	601.4	611.2	633.1	660.1	699.0	743.1	795.0	860.6	923.5	976.5
55°	541.8	549.1	555.5	571.7	597.4	634.5	674.1	723.3	774.1	827.3	872.4
57.5°	482.9	490.9	500.2	514.4	534.9	569.4	604.9	644.7	688.1	732.3	770.1
60°	444.2	451.5	459.6	475.7	494.2	521.7	560.4	595.0	628.1	668.4	706.3
62.5°	406.2	413.4	422.8	435.8	453.6	479.8	512.0	542.2	576.5	611.7	639.9
65°	349.9	355.6	362.8	375.0	391.8	415.3	441.8	465.2	495.8	521.7	547.4
67.5°	288.2	299.0	308.5	318.3	332.6	354.5	373.7	396.1	416.9	436.1	459.6
70°	247.5	259.6	268.5	278.9	292.7	311.2	329.7	345.1	362.0	380.5	401.5
72.5°	213.4	222.9	229.7	241.0	253.4	270.5	287.8	300.5	314.3	327.0	347.4
75°	168.5	172.6	177.4	186.2	197.5	210.5	224.2	235.4	243.5	254.8	269.3
77.5°	121.1	128.9	132.1	138.4	146.4	154.5	163.5	173.0	180.8	184.8	195.9
80°	92.7	95.9	99.2	108.1	112.9	121.0	127.3	136.2	139.5	143.5	154.0
82.5°	72.1	74.0	75.9	78.4	81.3	89.4	95.8	101.4	104.6	106.1	114.0
85°	41.9	42.7	43.5	44.3	45.1	45.1	48.4	52.4	58.1	58.1	60.5
87.5°	19.0	19.3	19.0	18.0	18.9	18.5	18.8	18.3	19.7	21.1	22.5
90°	23.8	22.5	20.7	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0
92.5°	41.3	40.5	39.3	38.0	36.7	35.4	33.3	30.5	27.7	24.7	21.9
95°	78.5	77.8	76.1	74.5	73.0	71.4	69.6	67.6	65.4	63.4	61.4
97.5°	123.8	123.0	121.1	119.3	117.3	115.5	113.8	112.1	110.5	108.9	107.2
100°	156.9	156.5	154.5	152.4	150.4	148.3	146.8	145.9	145.0	144.1	143.2
102.5°	191.6	190.9	189.0	187.1	185.3	183.4	182.3	182.0	181.6	181.3	180.9
105°	244.2	243.5	242.6	241.7	240.8	239.8	239.2	239.0	238.8	238.6	238.3
107.5°	301.2	300.5	300.4	300.3	300.1	300.0	299.8	299.5	299.2	299.0	298.7
110°	340.2	340.6	340.9	341.1	341.3	341.5	341.4	341.0	340.5	340.1	339.6



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	380.7	380.8	381.2	381.6	382.0	382.4	382.5	382.4	382.4	382.3	382.2
115°	443.7	444.0	444.4	444.9	445.4	445.9	446.1	446.1	446.1	446.1	446.1
117.5°	504.8	505.5	505.9	506.2	506.5	506.9	507.0	506.8	506.5	506.3	506.2
120°	546.2	547.3	548.1	548.7	549.4	550.1	550.0	549.1	548.2	547.2	546.3
122.5°	587.4	588.2	588.5	588.9	589.2	589.6	589.5	589.2	588.8	588.4	588.0
125°	648.1	648.6	648.8	649.0	649.2	649.5	649.6	649.6	649.6	649.6	649.6
127.5°	706.5	706.9	707.3	707.6	708.0	708.4	708.2	707.5	706.8	706.2	705.5
130°	747.4	747.8	747.8	747.8	747.8	747.8	747.5	746.8	746.1	745.5	744.8
132.5°	785.9	786.3	786.5	786.7	786.9	787.0	786.9	786.4	785.9	785.4	784.9
135°	843.5	844.0	844.0	844.0	844.0	844.0	843.3	841.9	840.6	839.2	837.9
137.5°	899.5	900.1	899.7	899.4	899.0	898.6	898.1	897.5	896.9	896.2	895.5
140°	935.8	936.0	936.0	936.0	936.0	936.0	935.8	935.4	934.9	934.5	934.0
142.5°	970.4	970.5	970.7	970.8	971.0	971.2	971.1	970.6	970.2	969.7	969.3
145°	1022.8	1023.0	1022.8	1022.6	1022.4	1022.1	1021.6	1020.7	1019.8	1018.9	1017.9
147.5°	1070.2	1070.3	1070.5	1070.7	1070.9	1071.1	1070.6	1069.4	1068.4	1067.3	1066.2
150°	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.3	1098.4	1097.5	1096.6	1095.7
152.5°	1127.3	1126.8	1126.6	1126.4	1126.2	1126.0	1125.7	1125.1	1124.6	1124.1	1123.5
155°	1166.2	1165.3	1165.5	1165.7	1165.9	1166.2	1166.3	1166.3	1166.3	1166.3	1166.3
157.5°	1200.9	1200.2	1200.2	1200.3	1200.3	1200.4	1200.6	1201.0	1201.4	1201.8	1202.2
160°	1222.1	1221.5	1221.7	1221.9	1222.1	1222.4	1222.6	1222.8	1223.0	1223.4	1223.6
162.5°	1240.7	1239.5	1239.7	1240.0	1240.2	1240.4	1240.8	1241.4	1242.0	1242.6	1243.1
165°	1265.9	1264.5	1265.0	1265.4	1265.9	1266.3	1266.9	1267.6	1268.2	1268.9	1269.6
167.5°	1287.1	1285.8	1285.7	1285.7	1285.7	1285.6	1286.1	1287.0	1288.0	1288.9	1289.8
170°	1298.6	1297.2	1297.0	1296.8	1296.6	1296.3	1296.8	1297.9	1299.0	1300.2	1301.3
172.5°	1307.0	1305.4	1305.4	1305.4	1305.3	1305.3	1305.7	1306.7	1307.6	1308.5	1309.5
175°	1316.2	1314.6	1314.8	1315.0	1315.2	1315.6	1316.2	1317.4	1318.5	1319.6	1320.7
177.5°	1321.6	1320.3	1320.3	1320.3	1320.3	1320.3	1320.8	1321.7	1322.6	1323.5	1324.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2013.5	2019.2	2025.7	2038.0	2048.3	2052.9	2061.8	2068.3	2066.4	2075.4	2090.8
5°	2021.3	2043.2	2068.1	2094.0	2122.9	2147.2	2166.5	2185.9	2201.2	2219.7	2247.2
7.5°	2020.0	2058.8	2100.8	2147.2	2194.7	2235.8	2273.9	2312.6	2346.9	2384.5	2433.7
10°	2014.9	2066.5	2118.9	2179.4	2239.9	2297.1	2348.7	2397.1	2443.1	2492.2	2554.4
12.5°	2009.1	2068.4	2131.8	2204.5	2279.9	2348.7	2409.3	2479.0	2536.6	2600.0	2671.7
15°	1983.5	2063.3	2149.6	2243.9	2334.2	2426.9	2509.9	2595.5	2675.2	2751.1	2841.4
17.5°	1954.1	2046.2	2148.0	2259.4	2367.9	2480.6	2579.2	2686.8	2768.4	2870.2	2954.1
20°	1930.3	2029.4	2138.3	2263.2	2386.6	2511.5	2620.4	2730.1	2822.0	2924.4	3030.8
22.5°	1901.2	2010.0	2128.0	2257.5	2386.6	2523.1	2643.6	2752.7	2866.5	2981.8	3091.5
25°	1854.4	1967.3	2092.3	2234.2	2382.6	2522.0	2651.1	2786.5	2909.1	3034.0	3132.4
27.5°	1797.1	1915.6	2047.3	2193.7	2346.0	2488.8	2640.8	2785.1	2908.4	3028.7	3114.5
30°	1751.2	1876.2	2002.8	2151.2	2309.2	2462.4	2625.2	2769.6	2899.4	3007.5	3055.9
32.5°	1704.1	1822.7	1953.2	2103.4	2265.3	2430.1	2591.7	2739.3	2859.4	2924.3	2925.5
35°	1622.2	1733.5	1869.0	2016.5	2182.6	2361.6	2525.3	2670.4	2743.8	2749.5	2670.4
37.5°	1532.9	1635.0	1762.8	1910.6	2092.4	2270.5	2437.7	2534.5	2559.0	2476.9	2330.8
40°	1469.1	1563.4	1686.8	1838.4	2018.9	2202.8	2355.2	2426.1	2400.3	2267.2	2104.4
42.5°	1402.0	1489.9	1608.7	1758.4	1939.6	2125.4	2255.2	2293.2	2224.8	2071.2	1880.6
45°	1292.5	1373.1	1490.9	1641.6	1815.7	1989.9	2088.3	2068.9	1955.2	1773.0	1559.3
47.5°	1178.5	1256.4	1362.3	1501.8	1680.1	1830.4	1897.0	1838.7	1676.9	1476.4	1302.6
50°	1103.0	1182.9	1280.4	1413.4	1576.3	1721.4	1764.1	1675.5	1495.6	1302.9	1143.3
52.5°	1028.9	1097.0	1192.7	1321.2	1476.9	1599.5	1622.2	1520.0	1334.4	1161.6	1020.1
55°	915.9	978.1	1058.6	1179.6	1314.2	1418.3	1406.1	1274.8	1106.2	958.7	847.4
57.5°	806.8	853.5	928.1	1041.4	1159.6	1229.4	1185.3	1073.2	916.1	795.4	701.5
60°	734.6	778.1	847.4	946.5	1050.6	1090.0	1053.0	931.3	807.1	696.6	617.6
62.5°	666.1	704.6	764.2	856.3	940.3	963.7	924.0	817.7	705.8	611.5	546.0
65°	566.8	602.3	653.1	718.4	776.5	787.7	761.9	653.1	568.5	489.4	444.2
67.5°	476.7	499.9	539.6	596.0	626.8	633.4	583.6	515.2	440.6	392.0	358.0
70°	416.1	432.1	469.3	499.9	524.9	525.7	479.8	425.0	367.7	328.2	303.2
72.5°	357.4	372.8	400.9	421.8	441.0	434.7	392.6	349.4	303.2	273.4	254.8
75°	275.8	289.4	304.0	313.7	313.7	305.6	275.0	242.7	216.1	198.3	192.7
77.5°	200.5	211.8	216.6	215.1	212.2	199.7	180.3	159.2	149.7	141.3	137.0
80°	157.2	162.1	163.7	159.7	154.8	140.3	127.3	118.6	109.7	106.4	104.8
82.5°	116.5	120.8	116.5	117.8	107.0	95.1	88.1	85.0	81.3	80.0	78.4
85°	62.1	61.3	59.7	55.6	48.4	46.8	45.9	45.1	43.5	44.3	42.7
87.5°	22.4	21.0	18.9	18.8	19.2	18.3	19.3	19.6	20.0	19.6	21.2
90°	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2
92.5°	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3	42.1
95°	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5	79.1
97.5°	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8	124.6
100°	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9	157.4
102.5°	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6	192.2
105°	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2	244.9
107.5°	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2	301.8
110°	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2	339.7





TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7	380.6
115°	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7	443.5
117.5°	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8	504.0
120°	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2	545.0
122.5°	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4	586.7
125°	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1	647.7
127.5°	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5	706.0
130°	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4	746.9
132.5°	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9	785.4
135°	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5	843.1
137.5°	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5	898.9
140°	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8	935.6
142.5°	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4	970.4
145°	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8	1022.6
147.5°	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2	1070.0
150°	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3	1127.8
155°	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2	1167.1
157.5°	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9	1201.6
160°	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1	1222.8
162.5°	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7	1241.9
165°	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9	1267.2
167.5°	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1	1288.5
170°	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6	1299.9
172.5°	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0	1308.5
175°	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2	1317.8
177.5°	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6	1322.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2099.2	2101.8	2103.8	2110.2	2110.8	2116.7	2110.8
5°	2272.9	2284.2	2302.0	2319.7	2321.3	2332.6	2312.4
7.5°	2467.7	2493.9	2510.1	2538.8	2550.1	2557.2	2545.6
10°	2601.9	2626.1	2668.8	2689.8	2710.8	2713.9	2704.3
12.5°	2731.6	2770.0	2803.6	2843.3	2842.4	2870.7	2860.3
15°	2904.3	2943.8	2990.5	3034.8	3051.0	3051.0	3063.9
17.5°	3027.5	3099.9	3148.3	3183.1	3221.1	3227.7	3223.2
20°	3110.7	3188.9	3240.5	3285.6	3311.4	3318.7	3318.7
22.5°	3172.6	3239.1	3289.5	3330.1	3351.4	3359.9	3357.4
25°	3215.5	3272.7	3303.4	3315.5	3321.0	3319.5	3304.2
27.5°	3156.7	3154.2	3134.8	3097.8	3069.9	3052.9	3033.5
30°	3044.5	3002.6	2954.3	2901.0	2832.5	2780.1	2763.9
32.5°	2877.5	2783.3	2701.4	2612.7	2539.0	2486.6	2464.7
35°	2554.4	2405.2	2283.4	2177.0	2099.6	2051.2	2035.1
37.5°	2170.8	2026.5	1875.7	1772.5	1708.4	1659.5	1641.2
40°	1927.0	1769.8	1638.4	1541.7	1475.5	1427.9	1427.1
42.5°	1704.5	1554.4	1430.7	1361.0	1289.7	1258.3	1258.1
45°	1395.6	1275.6	1170.7	1115.9	1073.2	1047.3	1040.1
47.5°	1155.6	1056.2	986.4	942.7	907.9	891.4	880.8
50°	1020.8	933.7	878.1	840.1	820.8	799.8	798.2
52.5°	908.5	838.2	794.9	764.1	739.5	726.9	727.3
55°	763.6	707.9	677.3	653.9	634.5	624.9	620.9
57.5°	643.3	601.5	579.3	557.7	549.6	542.0	539.9
60°	568.5	540.2	519.3	502.3	490.2	487.8	487.0
62.5°	506.5	477.0	462.5	449.4	440.6	436.9	435.4
65°	417.7	395.9	382.9	372.5	369.3	363.7	362.8
67.5°	336.7	323.7	315.1	307.8	303.5	303.2	303.2
70°	287.0	279.7	272.6	268.5	266.1	264.5	264.5
72.5°	244.5	239.1	233.2	231.1	230.6	228.9	228.3
75°	186.2	180.6	181.4	177.4	174.2	170.2	167.7
77.5°	132.1	128.1	127.2	126.7	124.0	123.5	124.8
80°	102.4	98.4	97.6	98.4	97.6	95.1	95.1
82.5°	77.9	74.5	73.7	73.2	72.4	73.2	71.9
85°	41.9	40.3	40.3	40.3	41.9	41.1	40.3
87.5°	20.2	19.8	20.6	20.1	20.2	19.6	20.3
90°	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.3	338.8	339.0	339.6	340.3	341.0	341.7



TEST NUMBER: P333104-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)