

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333106-840

Luminaire Tested: **S124RDIW-S1195D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333106-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8539.6 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49
2	91	84	78	73	85	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	36	34	30
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.8	2.3
10°-20°	551.7	6.5
20°-30°	796.6	9.3
30°-40°	903.0	10.6
40°-50°	872.0	10.2
50°-60°	725.1	8.5
60°-70°	500.7	5.9
70°-80°	253.8	3.0
80°-90°	69.1	0.8
90°-100°	87.2	1.0
100°-110°	258.4	3.0
110°-120°	438.7	5.1
120°-130°	578.4	6.8
130°-140°	649.6	7.6
140°-150°	638.4	7.5
150°-160°	536.9	6.3
160°-170°	357.2	4.2
170°-180°	125.1	1.5
0°-30°	1546.1	18.1
0°-40°	2449.1	28.7
0°-60°	4046.2	47.4
0°-90°	4869.7	57.0
90°-120°	784.3	9.2
90°-150°	2650.7	31.0
90°-180°	3670.0	43.0
0°-180°	8539.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	3	14	22	28	31	8
95°	61	70	78	81	81	68
105°	238	240	244	247	250	253
115°	446	446	444	443	442	440
125°	650	650	649	647	644	579
135°	838	844	844	842	839	648
145°	1018	1022	1023	1022	1019	637
155°	1166	1166	1165	1169	1165	536
165°	1270	1267	1264	1270	1266	358
175°	1321	1316	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.3	28.5	26.7	24.9	23.1	22.2	22.3	22.4	22.5	22.5	22.5
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	21.9	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3
95°	61.4	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5
97.5°	107.2	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8
100°	143.2	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9
102.5°	180.9	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6
105°	238.3	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2
107.5°	298.7	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2
110°	339.6	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.2	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7
115°	446.1	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7
117.5°	506.2	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8
120°	546.3	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2
122.5°	588.0	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4
125°	649.6	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1
127.5°	705.5	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5
130°	744.8	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4
132.5°	784.9	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9
135°	837.9	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5
137.5°	895.5	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5
140°	934.0	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8
142.5°	969.3	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4
145°	1017.9	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1066.2	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2
150°	1095.7	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1123.5	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3
155°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2
157.5°	1202.2	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9
160°	1223.6	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1
162.5°	1243.1	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7
165°	1269.6	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9
167.5°	1289.8	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1
170°	1301.3	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6
172.5°	1309.5	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0
175°	1320.7	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2
177.5°	1324.4	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	22.5	22.5	22.5	22.7	23.0	23.4	23.8	24.2
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.1	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.1	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	124.6	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.4	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.2	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	244.9	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	301.8	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.7	339.3	338.8	339.0	339.6	340.3	341.0	341.7



TEST NUMBER: P333106-840

CATALOG NUMBER: S124RDIW-S1195D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.6	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.5	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	504.0	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	545.0	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	586.7	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.7	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	706.0	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.9	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.4	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	843.1	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.9	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.6	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.4	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.6	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1070.0	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1127.8	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1201.6	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1222.8	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1241.9	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1267.2	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1288.5	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1299.9	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1308.5	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1322.9	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)