

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332857

Luminaire Tested: **S124DIW-S1195D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332857  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10483.2 lumens  
Efficiency: N/A  
Efficacy: 137.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	1.8
10°-20°	528.8	5.0
20°-30°	778.3	7.4
30°-40°	904.8	8.6
40°-50°	904.8	8.6
50°-60°	791.5	7.5
60°-70°	587.8	5.6
70°-80°	333.9	3.2
80°-90°	101.4	1.0
90°-100°	59.3	0.6
100°-110°	378.2	3.6
110°-120°	723.4	6.9
120°-130°	918.4	8.8
130°-140°	982.6	9.4
140°-150°	918.8	8.8
150°-160°	741.0	7.1
160°-170°	477.9	4.6
170°-180°	164.7	1.6
0°-30°	1494.7	14.3
0°-40°	2399.5	22.9
0°-60°	4095.8	39.1
0°-90°	5118.9	48.8
90°-120°	1160.9	11.1
90°-150°	3980.7	38.0
90°-180°	5364.0	51.2
0°-180°	10483.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	4	18	28	36	39	8
95°	71	30	28	36	38	92
105°	390	398	405	413	370	408
115°	729	733	732	734	734	717
125°	1025	1029	1027	1031	1032	914
135°	1271	1270	1275	1278	1280	979
145°	1466	1469	1470	1471	1474	916
155°	1607	1608	1604	1609	1606	741
165°	1695	1689	1689	1698	1688	479
175°	1734	1727	1728	1738	1724	165
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	34.0	34.3	34.7	35.0	35.4	35.7	35.8	36.0	36.2	36.4	36.7
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	16.3	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2
95°	71.3	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3
97.5°	151.5	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4
100°	212.7	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2
102.5°	281.2	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1
105°	390.4	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3
107.5°	491.8	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8
110°	560.3	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6



TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.7	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3
115°	728.9	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1
117.5°	821.0	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0
120°	883.3	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8
122.5°	941.4	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7
125°	1024.7	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1
127.5°	1103.5	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6
130°	1154.4	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9
132.5°	1201.1	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6
135°	1271.1	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6
137.5°	1333.1	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0
140°	1373.6	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6
142.5°	1409.9	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8
145°	1465.7	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9
147.5°	1510.0	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2
150°	1542.2	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1
152.5°	1569.2	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5
155°	1607.1	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6
157.5°	1639.0	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3
160°	1657.6	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2
162.5°	1674.2	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7
165°	1695.3	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1
167.5°	1711.9	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9
170°	1721.2	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0
172.5°	1727.4	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2
175°	1734.2	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3
177.5°	1737.3	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	37.1	37.4	37.7	38.0	38.1	38.2	38.3	38.4
90°	32.0	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	31.0	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	32.0	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.6	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	47.3	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	169.3	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	409.9	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	507.1	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.2	573.7	574.3	575.0	575.9	576.8	577.6	578.5





TEST NUMBER: P332857

CATALOG NUMBER: S124DIW-S1195D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.1	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	732.7	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.8	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.0	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.0	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.1	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1208.9	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.2	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1340.6	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1380.5	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1417.4	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.1	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.5	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1571.9	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1606.8	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1671.5	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1693.4	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1709.4	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1719.3	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1725.5	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1732.9	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1735.8	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)