

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333111-840

Luminaire Tested: **S124RDIW-S1195D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333111-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11362.9 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16156	16156	16156	16156
5°	18739	16204	14323	16204
10°	22168	16133	12782	16133
15°	25607	15984	10984	15984
20°	28511	15779	9933	15779
25°	29432	15577	9222	15577
30°	25765	15333	8793	15333
35°	20056	14970	8535	14970
40°	15039	14556	8395	14556
45°	11875	13891	8322	13891
50°	10025	13123	8081	13123
55°	8739	12279	7648	12279
60°	7863	11404	6770	11404
65°	6930	10457	5822	10457
70°	6243	9477	5254	9477
75°	5231	8400	4476	8400
80°	4421	7159	4198	7159
85°	3733	5604	3733	5604



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.9	1.7
10°-20°	584.9	5.1
20°-30°	914.8	8.1
30°-40°	1017.0	9.0
40°-50°	902.3	7.9
50°-60°	703.1	6.2
60°-70°	460.3	4.1
70°-80°	226.4	2.0
80°-90°	61.7	0.5
90°-100°	69.6	0.6
100°-110°	444.0	3.9
110°-120°	849.4	7.5
120°-130°	1078.3	9.5
130°-140°	1153.7	10.2
140°-150°	1078.8	9.5
150°-160°	870.0	7.7
160°-170°	561.1	4.9
170°-180°	193.4	1.7
0°-30°	1693.6	14.9
0°-40°	2710.6	23.9
0°-60°	4316.0	38.0
0°-90°	5064.4	44.6
90°-120°	1363.1	12.0
90°-150°	4673.9	41.1
90°-180°	6298.0	55.4
0°-180°	11362.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	2312	2000	1767	2000	2312	234
15°	3064	1912	1314	1912	3064	871
25°	3304	1749	1035	1749	3304	1466
35°	2035	1519	866	1519	2035	1276
45°	1040	1217	729	1217	1040	824
55°	621	872	543	872	621	565
65°	363	547	305	547	363	365
75°	168	269	144	269	168	185
85°	40	60	40	60	40	47
90°	46	4	46	4	46	21
95°	44	84	44	84	44	35
105°	434	458	434	458	434	379
115°	862	856	862	856	862	853
125°	1212	1203	1212	1203	1212	1080
135°	1503	1492	1503	1492	1503	1157
145°	1730	1721	1730	1721	1730	1081
155°	1885	1887	1885	1887	1885	869
165°	1981	1990	1981	1990	1981	560
175°	2024	2036	2024	2036	2024	193
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2110.8	2116.7	2110.8	2110.2	2103.8	2101.8	2099.2	2090.8	2075.4	2066.4	2068.3
5°	2312.4	2332.6	2321.3	2319.7	2302.0	2284.2	2272.9	2247.2	2219.7	2201.2	2185.9
7.5°	2545.6	2557.2	2550.1	2538.8	2510.1	2493.9	2467.7	2433.7	2384.5	2346.9	2312.6
10°	2704.3	2713.9	2710.8	2689.8	2668.8	2626.1	2601.9	2554.4	2492.2	2443.1	2397.1
12.5°	2860.3	2870.7	2842.4	2843.3	2803.6	2770.0	2731.6	2671.7	2600.0	2536.6	2479.0
15°	3063.9	3051.0	3051.0	3034.8	2990.5	2943.8	2904.3	2841.4	2751.1	2675.2	2595.5
17.5°	3223.2	3227.7	3221.1	3183.1	3148.3	3099.9	3027.5	2954.1	2870.2	2768.4	2686.8
20°	3318.7	3318.7	3311.4	3285.6	3240.5	3188.9	3110.7	3030.8	2924.4	2822.0	2730.1
22.5°	3357.4	3359.9	3351.4	3330.1	3289.5	3239.1	3172.6	3091.5	2981.8	2866.5	2752.7
25°	3304.2	3319.5	3321.0	3315.5	3303.4	3272.7	3215.5	3132.4	3034.0	2909.1	2786.5
27.5°	3033.5	3052.9	3069.9	3097.8	3134.8	3154.2	3156.7	3114.5	3028.7	2908.4	2785.1
30°	2763.9	2780.1	2832.5	2901.0	2954.3	3002.6	3044.5	3055.9	3007.5	2899.4	2769.6
32.5°	2464.7	2486.6	2539.0	2612.7	2701.4	2783.3	2877.5	2925.5	2924.3	2859.4	2739.3
35°	2035.1	2051.2	2099.6	2177.0	2283.4	2405.2	2554.4	2670.4	2749.5	2743.8	2670.4
37.5°	1641.2	1659.5	1708.4	1772.5	1875.7	2026.5	2170.8	2330.8	2476.9	2559.0	2534.5
40°	1427.1	1427.9	1475.5	1541.7	1638.4	1769.8	1927.0	2104.4	2267.2	2400.3	2426.1
42.5°	1258.1	1258.3	1289.7	1361.0	1430.7	1554.4	1704.5	1880.6	2071.2	2224.8	2293.2
45°	1040.1	1047.3	1073.2	1115.9	1170.7	1275.6	1395.6	1559.3	1773.0	1955.2	2068.9
47.5°	880.8	891.4	907.9	942.7	986.4	1056.2	1155.6	1302.6	1476.4	1676.9	1838.7
50°	798.2	799.8	820.8	840.1	878.1	933.7	1020.8	1143.3	1302.9	1495.6	1675.5
52.5°	727.3	726.9	739.5	764.1	794.9	838.2	908.5	1020.1	1161.6	1334.4	1520.0
55°	620.9	624.9	634.5	653.9	677.3	707.9	763.6	847.4	958.7	1106.2	1274.8
57.5°	539.9	542.0	549.6	557.7	579.3	601.5	643.3	701.5	795.4	916.1	1073.2
60°	487.0	487.8	490.2	502.3	519.3	540.2	568.5	617.6	696.6	807.1	931.3
62.5°	435.4	436.9	440.6	449.4	462.5	477.0	506.5	546.0	611.5	705.8	817.7
65°	362.8	363.7	369.3	372.5	382.9	395.9	417.7	444.2	489.4	568.5	653.1
67.5°	303.2	303.2	303.5	307.8	315.1	323.7	336.7	358.0	392.0	440.6	515.2
70°	264.5	264.5	266.1	268.5	272.6	279.7	287.0	303.2	328.2	367.7	425.0
72.5°	228.3	228.9	230.6	231.1	233.2	239.1	244.5	254.8	273.4	303.2	349.4
75°	167.7	170.2	174.2	177.4	181.4	180.6	186.2	192.7	198.3	216.1	242.7
77.5°	124.8	123.5	124.0	126.7	127.2	128.1	132.1	137.0	141.3	149.7	159.2
80°	95.1	95.1	97.6	98.4	97.6	98.4	102.4	104.8	106.4	109.7	118.6
82.5°	71.9	73.2	72.4	73.2	73.7	74.5	77.9	78.4	80.0	81.3	85.0
85°	40.3	41.1	41.9	40.3	40.3	40.3	41.9	42.7	44.3	43.5	45.1
87.5°	23.3	22.5	23.0	22.9	23.4	22.5	22.7	23.6	21.9	22.2	21.6
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4	34.3	32.3	29.6
95°	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6	35.5	33.5	33.1
97.5°	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6	40.4	40.2	78.0
100°	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5	61.3	67.1	113.7
102.5°	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7	260.7	322.9	328.9
105°	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2	478.2	475.1	473.4
107.5°	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4	593.9	592.4	590.1
110°	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0	672.3	671.6	669.5



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1	748.2	748.4	747.4
115°	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3	859.6	858.9	859.3
117.5°	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2	973.3	973.4	972.7
120°	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7	1042.0
122.5°	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0	1111.6	1111.2	1110.6
125°	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2	1207.2	1206.2	1206.8
127.5°	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8	1304.0	1304.2	1302.6
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2	1361.8	1361.5	1360.5
132.5°	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5	1419.1	1418.8	1417.4
135°	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3	1497.7	1497.0	1495.7
137.5°	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1	1573.3	1572.6	1571.0
140°	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9	1619.9	1618.8	1618.2
142.5°	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3	1663.4	1662.7	1662.3
145°	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2	1725.8	1725.5	1725.5
147.5°	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5	1780.3	1780.0	1780.3
150°	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3	1815.3	1815.3	1815.6
152.5°	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6	1845.1	1844.5	1845.1
155°	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5	1885.2	1883.8	1884.9
157.5°	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2	1919.5
160°	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2	1940.6
162.5°	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6	1960.5	1958.4	1958.8
165°	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2	1985.5	1982.9	1982.9
167.5°	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1	2004.1	2001.1	2001.4
170°	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7	2016.0	2013.3	2013.0
172.5°	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0	2023.3	2020.6	2020.2
175°	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6	2031.5	2028.5	2028.2
177.5°	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0	2035.9	2033.7	2033.2
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2061.8	2052.9	2048.3	2038.0	2025.7	2019.2	2013.5	2005.1	1994.1	1982.5	1974.1
5°	2166.5	2147.2	2122.9	2094.0	2068.1	2043.2	2021.3	1999.6	1974.6	1948.8	1923.0
7.5°	2273.9	2235.8	2194.7	2147.2	2100.8	2058.8	2020.0	1983.0	1941.1	1903.5	1869.3
10°	2348.7	2297.1	2239.9	2179.4	2118.9	2066.5	2014.9	1968.1	1916.5	1870.6	1831.9
12.5°	2409.3	2348.7	2279.9	2204.5	2131.8	2068.4	2009.1	1948.1	1889.5	1839.7	1788.1
15°	2509.9	2426.9	2334.2	2243.9	2149.6	2063.3	1983.5	1912.5	1845.6	1775.4	1726.3
17.5°	2579.2	2480.6	2367.9	2259.4	2148.0	2046.2	1954.1	1869.7	1792.4	1720.8	1662.2
20°	2620.4	2511.5	2386.6	2263.2	2138.3	2029.4	1930.3	1836.7	1756.9	1679.5	1619.0
22.5°	2643.6	2523.1	2386.6	2257.5	2128.0	2010.0	1901.2	1803.8	1716.9	1639.5	1572.6
25°	2651.1	2522.0	2382.6	2234.2	2092.3	1967.3	1854.4	1748.8	1652.0	1574.7	1503.7
27.5°	2640.8	2488.8	2346.0	2193.7	2047.3	1915.6	1797.1	1686.1	1589.2	1506.1	1433.4
30°	2625.2	2462.4	2309.2	2151.2	2002.8	1876.2	1751.2	1644.9	1544.1	1457.7	1384.4
32.5°	2591.7	2430.1	2265.3	2103.4	1953.2	1822.7	1704.1	1597.1	1498.2	1410.1	1332.1
35°	2525.3	2361.6	2182.6	2016.5	1869.0	1733.5	1622.2	1519.0	1424.7	1330.4	1248.1
37.5°	2437.7	2270.5	2092.4	1910.6	1762.8	1635.0	1532.9	1436.0	1343.9	1257.8	1166.7
40°	2355.2	2202.8	2018.9	1838.4	1686.8	1563.4	1469.1	1381.2	1288.5	1203.0	1111.9
42.5°	2255.2	2125.4	1939.6	1758.4	1608.7	1489.9	1402.0	1316.1	1231.7	1148.8	1053.8
45°	2088.3	1989.9	1815.7	1641.6	1490.9	1373.1	1292.5	1216.7	1142.5	1063.5	974.0
47.5°	1897.0	1830.4	1680.1	1501.8	1362.3	1256.4	1178.5	1116.5	1053.8	974.8	896.3
50°	1764.1	1721.4	1576.3	1413.4	1280.4	1182.9	1103.0	1044.9	992.5	916.8	846.6
52.5°	1622.2	1599.5	1476.9	1321.2	1192.7	1097.0	1028.9	976.5	923.5	860.6	795.0
55°	1406.1	1418.3	1314.2	1179.6	1058.6	978.1	915.9	872.4	827.3	774.1	723.3
57.5°	1185.3	1229.4	1159.6	1041.4	928.1	853.5	806.8	770.1	732.3	688.1	644.7
60°	1053.0	1090.0	1050.6	946.5	847.4	778.1	734.6	706.3	668.4	628.1	595.0
62.5°	924.0	963.7	940.3	856.3	764.2	704.6	666.1	639.9	611.7	576.5	542.2
65°	761.9	787.7	776.5	718.4	653.1	602.3	566.8	547.4	521.7	495.8	465.2
67.5°	583.6	633.4	626.8	596.0	539.6	499.9	476.7	459.6	436.1	416.9	396.1
70°	479.8	525.7	524.9	499.9	469.3	432.1	416.1	401.5	380.5	362.0	345.1
72.5°	392.6	434.7	441.0	421.8	400.9	372.8	357.4	347.4	327.0	314.3	300.5
75°	275.0	305.6	313.7	313.7	304.0	289.4	275.8	269.3	254.8	243.5	235.4
77.5°	180.3	199.7	212.2	215.1	216.6	211.8	200.5	195.9	184.8	180.8	173.0
80°	127.3	140.3	154.8	159.7	163.7	162.1	157.2	154.0	143.5	139.5	136.2
82.5°	88.1	95.1	107.0	117.8	116.5	120.8	116.5	114.0	106.1	104.6	101.4
85°	45.9	46.8	48.4	55.6	59.7	61.3	62.1	60.5	58.1	58.1	52.4
87.5°	21.1	19.9	20.7	20.0	19.9	21.7	22.9	22.8	21.6	20.5	19.3
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2	19.4	19.6	19.8
95°	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7	72.2	60.8	49.3
97.5°	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8	185.0	192.2	199.4
100°	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7	255.9	262.0	268.0
102.5°	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1	334.7	339.1	343.6
105°	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4	460.4	462.4	464.5
107.5°	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4	578.6	579.6	580.6
110°	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9	658.9	659.9	661.0



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9	737.7	739.5	741.3
115°	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9	856.9	857.9	858.9
117.5°	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0	965.3	966.7	968.1
120°	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1	1038.4	1039.9	1041.2
122.5°	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3	1106.1	1106.9	1107.7
125°	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2	1204.5	1205.8	1207.2
127.5°	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7	1296.1	1296.4	1296.7
130°	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4	1355.7	1356.0	1356.5
132.5°	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2	1410.8	1411.5	1412.1
135°	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5	1492.1	1491.8	1491.5
137.5°	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3	1565.4	1565.5	1565.7
140°	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8	1613.5	1614.2	1614.8
142.5°	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4	1656.6	1657.9	1659.1
145°	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9	1721.9	1722.9	1723.9
147.5°	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0	1774.8	1776.8	1778.7
150°	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8	1812.1	1813.4	1814.8
152.5°	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4	1843.5	1844.6	1845.6
155°	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9	1887.2	1887.5	1887.9
157.5°	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4	1924.2	1924.0	1923.8
160°	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3	1945.3	1944.3	1943.3
162.5°	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8	1964.5	1963.2	1962.0
165°	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4	1988.7	1987.1	1985.4
167.5°	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9	2008.2	2006.4	2004.7
170°	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9	2018.9	2016.8	2014.8
172.5°	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2	2026.2	2024.2	2022.2
175°	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1	2034.1	2032.1	2030.0
177.5°	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8	2037.9	2036.0	2034.1
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1965.1	1958.6	1950.3	1940.6	1928.9	1918.6	1914.1	1918.0	1920.0	1914.8	1914.1
5°	1905.2	1885.1	1869.0	1844.8	1825.4	1809.3	1798.1	1793.2	1794.8	1781.9	1778.7
7.5°	1838.1	1814.1	1787.7	1759.0	1732.2	1708.5	1696.1	1689.3	1675.7	1669.8	1660.0
10°	1794.8	1762.5	1736.8	1702.8	1672.2	1644.1	1630.3	1619.0	1605.3	1598.8	1585.2
12.5°	1750.3	1712.8	1684.5	1649.3	1618.0	1584.1	1570.9	1550.0	1528.5	1515.0	1497.4
15°	1687.6	1642.4	1607.7	1565.8	1528.7	1490.1	1455.3	1416.6	1402.1	1371.5	1353.7
17.5°	1614.2	1568.4	1525.5	1469.3	1412.0	1363.9	1327.0	1289.9	1267.7	1248.1	1239.1
20°	1565.8	1523.9	1464.2	1398.9	1335.2	1282.0	1252.1	1228.0	1203.8	1190.1	1180.4
22.5°	1520.0	1466.4	1397.1	1326.7	1262.9	1221.3	1196.1	1171.2	1151.5	1138.5	1125.6
25°	1443.3	1373.1	1299.7	1219.1	1175.6	1139.3	1111.9	1091.7	1079.6	1062.7	1056.2
27.5°	1364.4	1279.4	1198.5	1144.3	1098.9	1065.7	1041.9	1026.7	1011.4	1000.6	992.2
30°	1303.7	1217.5	1144.9	1093.3	1047.3	1020.0	1000.6	982.9	970.8	961.9	955.4
32.5°	1243.7	1157.5	1096.5	1041.1	1004.8	978.1	957.4	944.1	934.6	923.2	919.3
35°	1157.0	1080.5	1027.2	977.2	940.1	915.9	899.8	886.2	878.1	874.8	872.4
37.5°	1073.7	1010.9	953.7	912.7	879.7	860.6	841.6	834.9	829.3	823.5	826.2
40°	1020.8	961.9	911.1	867.6	840.9	820.0	808.7	800.6	795.8	795.8	795.8
42.5°	974.9	917.4	867.9	828.9	802.2	784.6	771.9	765.2	763.6	763.0	766.8
45°	903.8	850.6	800.6	768.4	745.8	728.1	720.8	715.2	715.2	718.4	719.2
47.5°	833.3	783.6	743.4	707.3	686.6	675.5	669.2	666.3	666.6	669.8	673.6
50°	790.1	740.9	701.5	669.2	649.8	639.3	633.7	632.2	633.7	633.7	639.3
52.5°	743.1	699.0	660.1	633.1	611.2	601.4	598.2	596.0	596.9	599.6	602.0
55°	674.1	634.5	597.4	571.7	555.5	549.1	541.8	542.6	541.0	542.6	542.6
57.5°	604.9	569.4	534.9	514.4	500.2	490.9	482.9	485.2	482.8	482.5	481.2
60°	560.4	521.7	494.2	475.7	459.6	451.5	444.2	445.9	443.4	441.8	438.6
62.5°	512.0	479.8	453.6	435.8	422.8	413.4	406.2	404.6	399.0	393.4	386.4
65°	441.8	415.3	391.8	375.0	362.8	355.6	349.9	345.1	333.0	320.1	313.7
67.5°	373.7	354.5	332.6	318.3	308.5	299.0	288.2	279.9	268.6	261.6	257.5
70°	329.7	311.2	292.7	278.9	268.5	259.6	247.5	241.9	233.8	230.6	226.6
72.5°	287.8	270.5	253.4	241.0	229.7	222.9	213.4	207.7	204.2	202.9	198.8
75°	224.2	210.5	197.5	186.2	177.4	172.6	168.5	164.5	162.9	155.6	151.6
77.5°	163.5	154.5	146.4	138.4	132.1	128.9	121.1	116.4	113.7	110.3	109.5
80°	127.3	121.0	112.9	108.1	99.2	95.9	92.7	91.9	91.1	90.3	89.5
82.5°	95.8	89.4	81.3	78.4	75.9	74.0	72.1	71.3	70.5	71.0	70.8
85°	48.4	45.1	45.1	44.3	43.5	42.7	41.9	41.9	41.1	41.9	41.1
87.5°	20.0	20.0	20.6	19.8	21.0	21.5	21.3	21.7	22.7	21.9	22.1
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4	38.4	40.4	41.5
95°	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6	39.6	41.6	42.8
97.5°	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6	40.8	41.0	41.3
100°	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5	49.8	44.0	41.3
102.5°	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7	136.6	74.6	43.6
105°	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2	484.3	487.4	482.7
107.5°	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4	596.9	598.3	599.8
110°	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0	673.7	674.3	675.2



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1	747.9	747.8	748.4
115°	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3	860.9	861.6	862.0
117.5°	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2	973.0	972.9	972.8
120°	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4
122.5°	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0	1112.4	1112.8	1112.6
125°	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2	1209.2	1210.2	1210.9
127.5°	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8	1303.6	1303.4	1303.1
130°	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2	1362.5	1362.8	1363.0
132.5°	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5	1419.8	1420.1	1420.2
135°	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3	1499.0	1499.8	1500.5
137.5°	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1	1574.8	1575.6	1575.8
140°	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9	1621.9	1623.0	1623.6
142.5°	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3	1665.0	1665.7	1666.1
145°	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2	1726.5	1726.8	1727.4
147.5°	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5	1780.8	1781.1	1781.4
150°	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3	1815.3	1815.3	1815.5
152.5°	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6	1846.1	1846.7	1846.8
155°	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5	1887.9	1889.3	1889.5
157.5°	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3
160°	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3
162.5°	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6	1964.6	1966.6	1966.4
165°	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2	1990.9	1993.7	1993.5
167.5°	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1	2010.0	2013.1	2012.9
170°	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7	2021.4	2024.2	2023.8
172.5°	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0	2028.7	2031.4	2030.9
175°	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6	2037.7	2040.7	2040.2
177.5°	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0	2040.2	2042.4	2041.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1910.3	1911.6	1907.0	1905.7	1907.0	1911.6	1910.3	1914.1	1914.8	1920.0	1918.0
5°	1772.2	1770.6	1766.6	1767.4	1766.6	1770.6	1772.2	1778.7	1781.9	1794.8	1793.2
7.5°	1654.2	1647.9	1649.6	1643.3	1649.6	1647.9	1654.2	1660.0	1669.8	1675.7	1689.3
10°	1582.0	1573.1	1565.8	1559.3	1565.8	1573.1	1582.0	1585.2	1598.8	1605.3	1619.0
12.5°	1483.3	1475.6	1465.8	1467.7	1465.8	1475.6	1483.3	1497.4	1515.0	1528.5	1550.0
15°	1343.2	1331.2	1311.8	1314.2	1311.8	1331.2	1343.2	1353.7	1371.5	1402.1	1416.6
17.5°	1224.8	1224.9	1216.1	1218.1	1216.1	1224.9	1224.8	1239.1	1248.1	1267.7	1289.9
20°	1163.5	1157.8	1158.6	1156.2	1158.6	1157.8	1163.5	1180.4	1190.1	1203.8	1228.0
22.5°	1120.8	1114.0	1108.3	1103.3	1108.3	1114.0	1120.8	1125.6	1138.5	1151.5	1171.2
25°	1048.9	1044.1	1036.9	1035.3	1036.9	1044.1	1048.9	1056.2	1062.7	1079.6	1091.7
27.5°	985.7	984.8	981.9	978.2	981.9	984.8	985.7	992.2	1000.6	1011.4	1026.7
30°	949.0	947.4	945.7	943.3	945.7	947.4	949.0	955.4	961.9	970.8	982.9
32.5°	916.1	915.1	913.5	913.7	913.5	915.1	916.1	919.3	923.2	934.6	944.1
35°	869.2	868.4	866.8	866.0	866.8	868.4	869.2	872.4	874.8	878.1	886.2
37.5°	825.4	827.4	826.5	826.3	826.5	827.4	825.4	826.2	823.5	829.3	834.9
40°	795.0	795.8	797.4	796.6	797.4	795.8	795.0	795.8	795.8	795.8	800.6
42.5°	769.8	770.0	772.2	769.5	772.2	770.0	769.8	766.8	763.0	763.6	765.2
45°	724.9	729.7	728.9	728.9	728.9	729.7	724.9	719.2	718.4	715.2	715.2
47.5°	675.7	679.8	681.0	680.9	681.0	679.8	675.7	673.6	669.8	666.6	666.3
50°	643.4	641.8	644.2	643.4	644.2	641.8	643.4	639.3	633.7	633.7	632.2
52.5°	604.1	604.4	604.2	603.4	604.2	604.4	604.1	602.0	599.6	596.9	596.0
55°	543.4	544.2	542.6	543.4	542.6	544.2	543.4	542.6	542.6	541.0	542.6
57.5°	477.7	473.7	475.3	473.4	475.3	473.7	477.7	481.2	482.5	482.8	485.2
60°	430.6	424.1	422.5	419.3	422.5	424.1	430.6	438.6	441.8	443.4	445.9
62.5°	377.7	373.1	367.7	370.2	367.7	373.1	377.7	386.4	393.4	399.0	404.6
65°	307.2	304.0	301.5	304.8	301.5	304.0	307.2	313.7	320.1	333.0	345.1
67.5°	254.3	252.6	252.6	251.0	252.6	252.6	254.3	257.5	261.6	268.6	279.9
70°	226.6	224.2	224.2	222.6	224.2	224.2	226.6	226.6	230.6	233.8	241.9
72.5°	198.1	195.8	196.4	195.4	196.4	195.8	198.1	198.8	202.9	204.2	207.7
75°	146.7	142.7	142.7	143.5	142.7	142.7	146.7	151.6	155.6	162.9	164.5
77.5°	109.5	108.7	109.8	108.4	109.8	108.7	109.5	109.5	110.3	113.7	116.4
80°	89.5	88.7	87.9	90.3	87.9	88.7	89.5	89.5	90.3	91.1	91.9
82.5°	69.5	69.4	69.2	72.2	69.2	69.4	69.5	70.8	71.0	70.5	71.3
85°	41.9	40.3	41.9	40.3	41.9	40.3	41.9	41.1	41.9	41.1	41.9
87.5°	23.5	23.0	22.5	23.3	22.5	23.0	23.5	22.1	21.9	22.7	21.7
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	41.6	41.8	41.9	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4
95°	43.1	43.5	43.8	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6
97.5°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6
100°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5
102.5°	43.6	43.7	43.8	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7
105°	470.6	458.4	446.3	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2
107.5°	601.1	602.3	603.6	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4
110°	676.2	677.2	678.2	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	749.7	750.9	752.2	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1
115°	862.0	862.0	862.0	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3
117.5°	972.6	972.5	972.4	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2
120°	1043.7	1043.0	1042.4	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0
122.5°	1112.0	1111.3	1110.5	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0
125°	1211.2	1211.5	1211.9	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2
127.5°	1302.9	1302.6	1302.3	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2
132.5°	1419.9	1419.6	1419.4	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5
135°	1501.1	1501.8	1502.5	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3
137.5°	1575.6	1575.4	1575.2	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1
140°	1624.0	1624.3	1624.6	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9
142.5°	1666.2	1666.3	1666.3	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3
145°	1728.0	1728.7	1729.4	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2
147.5°	1781.7	1782.0	1782.4	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5
150°	1815.8	1816.1	1816.5	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3
152.5°	1846.6	1846.4	1846.2	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6
155°	1888.4	1887.4	1886.4	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5
157.5°	1923.6	1921.8	1920.1	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8
160°	1946.3	1944.3	1942.3	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3
162.5°	1964.2	1961.9	1959.5	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6
165°	1990.4	1987.4	1984.4	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2
167.5°	2009.4	2006.1	2002.7	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1
170°	2020.4	2017.0	2013.7	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7
172.5°	2027.3	2023.7	2020.0	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0
175°	2036.1	2032.1	2028.0	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6
177.5°	2038.6	2035.3	2032.1	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1914.1	1918.6	1928.9	1940.6	1950.3	1958.6	1965.1	1974.1	1982.5	1994.1	2005.1
5°	1798.1	1809.3	1825.4	1844.8	1869.0	1885.1	1905.2	1923.0	1948.8	1974.6	1999.6
7.5°	1696.1	1708.5	1732.2	1759.0	1787.7	1814.1	1838.1	1869.3	1903.5	1941.1	1983.0
10°	1630.3	1644.1	1672.2	1702.8	1736.8	1762.5	1794.8	1831.9	1870.6	1916.5	1968.1
12.5°	1570.9	1584.1	1618.0	1649.3	1684.5	1712.8	1750.3	1788.1	1839.7	1889.5	1948.1
15°	1455.3	1490.1	1528.7	1565.8	1607.7	1642.4	1687.6	1726.3	1775.4	1845.6	1912.5
17.5°	1327.0	1363.9	1412.0	1469.3	1525.5	1568.4	1614.2	1662.2	1720.8	1792.4	1869.7
20°	1252.1	1282.0	1335.2	1398.9	1464.2	1523.9	1565.8	1619.0	1679.5	1756.9	1836.7
22.5°	1196.1	1221.3	1262.9	1326.7	1397.1	1466.4	1520.0	1572.6	1639.5	1716.9	1803.8
25°	1111.9	1139.3	1175.6	1219.1	1299.7	1373.1	1443.3	1503.7	1574.7	1652.0	1748.8
27.5°	1041.9	1065.7	1098.9	1144.3	1198.5	1279.4	1364.4	1433.4	1506.1	1589.2	1686.1
30°	1000.6	1020.0	1047.3	1093.3	1144.9	1217.5	1303.7	1384.4	1457.7	1544.1	1644.9
32.5°	957.4	978.1	1004.8	1041.1	1096.5	1157.5	1243.7	1332.1	1410.1	1498.2	1597.1
35°	899.8	915.9	940.1	977.2	1027.2	1080.5	1157.0	1248.1	1330.4	1424.7	1519.0
37.5°	841.6	860.6	879.7	912.7	953.7	1010.9	1073.7	1166.7	1257.8	1343.9	1436.0
40°	808.7	820.0	840.9	867.6	911.1	961.9	1020.8	1111.9	1203.0	1288.5	1381.2
42.5°	771.9	784.6	802.2	828.9	867.9	917.4	974.9	1053.8	1148.8	1231.7	1316.1
45°	720.8	728.1	745.8	768.4	800.6	850.6	903.8	974.0	1063.5	1142.5	1216.7
47.5°	669.2	675.5	686.6	707.3	743.4	783.6	833.3	896.3	974.8	1053.8	1116.5
50°	633.7	639.3	649.8	669.2	701.5	740.9	790.1	846.6	916.8	992.5	1044.9
52.5°	598.2	601.4	611.2	633.1	660.1	699.0	743.1	795.0	860.6	923.5	976.5
55°	541.8	549.1	555.5	571.7	597.4	634.5	674.1	723.3	774.1	827.3	872.4
57.5°	482.9	490.9	500.2	514.4	534.9	569.4	604.9	644.7	688.1	732.3	770.1
60°	444.2	451.5	459.6	475.7	494.2	521.7	560.4	595.0	628.1	668.4	706.3
62.5°	406.2	413.4	422.8	435.8	453.6	479.8	512.0	542.2	576.5	611.7	639.9
65°	349.9	355.6	362.8	375.0	391.8	415.3	441.8	465.2	495.8	521.7	547.4
67.5°	288.2	299.0	308.5	318.3	332.6	354.5	373.7	396.1	416.9	436.1	459.6
70°	247.5	259.6	268.5	278.9	292.7	311.2	329.7	345.1	362.0	380.5	401.5
72.5°	213.4	222.9	229.7	241.0	253.4	270.5	287.8	300.5	314.3	327.0	347.4
75°	168.5	172.6	177.4	186.2	197.5	210.5	224.2	235.4	243.5	254.8	269.3
77.5°	121.1	128.9	132.1	138.4	146.4	154.5	163.5	173.0	180.8	184.8	195.9
80°	92.7	95.9	99.2	108.1	112.9	121.0	127.3	136.2	139.5	143.5	154.0
82.5°	72.1	74.0	75.9	78.4	81.3	89.4	95.8	101.4	104.6	106.1	114.0
85°	41.9	42.7	43.5	44.3	45.1	45.1	48.4	52.4	58.1	58.1	60.5
87.5°	21.3	21.5	21.0	19.8	20.6	20.0	20.0	19.3	20.5	21.6	22.8
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	34.3	32.3	29.6	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2
95°	35.5	33.5	33.1	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7
97.5°	40.4	40.2	78.0	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8
100°	61.3	67.1	113.7	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7
102.5°	260.7	322.9	328.9	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1
105°	478.2	475.1	473.4	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4
107.5°	593.9	592.4	590.1	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4
110°	672.3	671.6	669.5	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	748.2	748.4	747.4	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9
115°	859.6	858.9	859.3	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9
117.5°	973.3	973.4	972.7	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0
120°	1042.4	1041.7	1042.0	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1
122.5°	1111.6	1111.2	1110.6	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3
125°	1207.2	1206.2	1206.8	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2
127.5°	1304.0	1304.2	1302.6	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7
130°	1361.8	1361.5	1360.5	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4
132.5°	1419.1	1418.8	1417.4	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2
135°	1497.7	1497.0	1495.7	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5
137.5°	1573.3	1572.6	1571.0	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3
140°	1619.9	1618.8	1618.2	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8
142.5°	1663.4	1662.7	1662.3	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4
145°	1725.8	1725.5	1725.5	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9
147.5°	1780.3	1780.0	1780.3	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0
150°	1815.3	1815.3	1815.6	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8
152.5°	1845.1	1844.5	1845.1	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4
155°	1885.2	1883.8	1884.9	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9
157.5°	1920.1	1918.2	1919.5	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4
160°	1942.3	1940.2	1940.6	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3
162.5°	1960.5	1958.4	1958.8	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8
165°	1985.5	1982.9	1982.9	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4
167.5°	2004.1	2001.1	2001.4	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9
170°	2016.0	2013.3	2013.0	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9
172.5°	2023.3	2020.6	2020.2	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2
175°	2031.5	2028.5	2028.2	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1
177.5°	2035.9	2033.7	2033.2	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2013.5	2019.2	2025.7	2038.0	2048.3	2052.9	2061.8	2068.3	2066.4	2075.4	2090.8
5°	2021.3	2043.2	2068.1	2094.0	2122.9	2147.2	2166.5	2185.9	2201.2	2219.7	2247.2
7.5°	2020.0	2058.8	2100.8	2147.2	2194.7	2235.8	2273.9	2312.6	2346.9	2384.5	2433.7
10°	2014.9	2066.5	2118.9	2179.4	2239.9	2297.1	2348.7	2397.1	2443.1	2492.2	2554.4
12.5°	2009.1	2068.4	2131.8	2204.5	2279.9	2348.7	2409.3	2479.0	2536.6	2600.0	2671.7
15°	1983.5	2063.3	2149.6	2243.9	2334.2	2426.9	2509.9	2595.5	2675.2	2751.1	2841.4
17.5°	1954.1	2046.2	2148.0	2259.4	2367.9	2480.6	2579.2	2686.8	2768.4	2870.2	2954.1
20°	1930.3	2029.4	2138.3	2263.2	2386.6	2511.5	2620.4	2730.1	2822.0	2924.4	3030.8
22.5°	1901.2	2010.0	2128.0	2257.5	2386.6	2523.1	2643.6	2752.7	2866.5	2981.8	3091.5
25°	1854.4	1967.3	2092.3	2234.2	2382.6	2522.0	2651.1	2786.5	2909.1	3034.0	3132.4
27.5°	1797.1	1915.6	2047.3	2193.7	2346.0	2488.8	2640.8	2785.1	2908.4	3028.7	3114.5
30°	1751.2	1876.2	2002.8	2151.2	2309.2	2462.4	2625.2	2769.6	2899.4	3007.5	3055.9
32.5°	1704.1	1822.7	1953.2	2103.4	2265.3	2430.1	2591.7	2739.3	2859.4	2924.3	2925.5
35°	1622.2	1733.5	1869.0	2016.5	2182.6	2361.6	2525.3	2670.4	2743.8	2749.5	2670.4
37.5°	1532.9	1635.0	1762.8	1910.6	2092.4	2270.5	2437.7	2534.5	2559.0	2476.9	2330.8
40°	1469.1	1563.4	1686.8	1838.4	2018.9	2202.8	2355.2	2426.1	2400.3	2267.2	2104.4
42.5°	1402.0	1489.9	1608.7	1758.4	1939.6	2125.4	2255.2	2293.2	2224.8	2071.2	1880.6
45°	1292.5	1373.1	1490.9	1641.6	1815.7	1989.9	2088.3	2068.9	1955.2	1773.0	1559.3
47.5°	1178.5	1256.4	1362.3	1501.8	1680.1	1830.4	1897.0	1838.7	1676.9	1476.4	1302.6
50°	1103.0	1182.9	1280.4	1413.4	1576.3	1721.4	1764.1	1675.5	1495.6	1302.9	1143.3
52.5°	1028.9	1097.0	1192.7	1321.2	1476.9	1599.5	1622.2	1520.0	1334.4	1161.6	1020.1
55°	915.9	978.1	1058.6	1179.6	1314.2	1418.3	1406.1	1274.8	1106.2	958.7	847.4
57.5°	806.8	853.5	928.1	1041.4	1159.6	1229.4	1185.3	1073.2	916.1	795.4	701.5
60°	734.6	778.1	847.4	946.5	1050.6	1090.0	1053.0	931.3	807.1	696.6	617.6
62.5°	666.1	704.6	764.2	856.3	940.3	963.7	924.0	817.7	705.8	611.5	546.0
65°	566.8	602.3	653.1	718.4	776.5	787.7	761.9	653.1	568.5	489.4	444.2
67.5°	476.7	499.9	539.6	596.0	626.8	633.4	583.6	515.2	440.6	392.0	358.0
70°	416.1	432.1	469.3	499.9	524.9	525.7	479.8	425.0	367.7	328.2	303.2
72.5°	357.4	372.8	400.9	421.8	441.0	434.7	392.6	349.4	303.2	273.4	254.8
75°	275.8	289.4	304.0	313.7	313.7	305.6	275.0	242.7	216.1	198.3	192.7
77.5°	200.5	211.8	216.6	215.1	212.2	199.7	180.3	159.2	149.7	141.3	137.0
80°	157.2	162.1	163.7	159.7	154.8	140.3	127.3	118.6	109.7	106.4	104.8
82.5°	116.5	120.8	116.5	117.8	107.0	95.1	88.1	85.0	81.3	80.0	78.4
85°	62.1	61.3	59.7	55.6	48.4	46.8	45.9	45.1	43.5	44.3	42.7
87.5°	22.9	21.7	19.9	20.0	20.7	19.9	21.1	21.6	22.2	21.9	23.6
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4
95°	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6
97.5°	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6
100°	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5
102.5°	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7
105°	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2
107.5°	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4
110°	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1
115°	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3
117.5°	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2
120°	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0
122.5°	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0
125°	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2
127.5°	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8
130°	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2
132.5°	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5
135°	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3
137.5°	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1
140°	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9
142.5°	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3
145°	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2
147.5°	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5
150°	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3
152.5°	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6
155°	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5
157.5°	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8
160°	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3
162.5°	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6
165°	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2
167.5°	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1
170°	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7
172.5°	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0
175°	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6
177.5°	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2099.2	2101.8	2103.8	2110.2	2110.8	2116.7	2110.8
5°	2272.9	2284.2	2302.0	2319.7	2321.3	2332.6	2312.4
7.5°	2467.7	2493.9	2510.1	2538.8	2550.1	2557.2	2545.6
10°	2601.9	2626.1	2668.8	2689.8	2710.8	2713.9	2704.3
12.5°	2731.6	2770.0	2803.6	2843.3	2842.4	2870.7	2860.3
15°	2904.3	2943.8	2990.5	3034.8	3051.0	3051.0	3063.9
17.5°	3027.5	3099.9	3148.3	3183.1	3221.1	3227.7	3223.2
20°	3110.7	3188.9	3240.5	3285.6	3311.4	3318.7	3318.7
22.5°	3172.6	3239.1	3289.5	3330.1	3351.4	3359.9	3357.4
25°	3215.5	3272.7	3303.4	3315.5	3321.0	3319.5	3304.2
27.5°	3156.7	3154.2	3134.8	3097.8	3069.9	3052.9	3033.5
30°	3044.5	3002.6	2954.3	2901.0	2832.5	2780.1	2763.9
32.5°	2877.5	2783.3	2701.4	2612.7	2539.0	2486.6	2464.7
35°	2554.4	2405.2	2283.4	2177.0	2099.6	2051.2	2035.1
37.5°	2170.8	2026.5	1875.7	1772.5	1708.4	1659.5	1641.2
40°	1927.0	1769.8	1638.4	1541.7	1475.5	1427.9	1427.1
42.5°	1704.5	1554.4	1430.7	1361.0	1289.7	1258.3	1258.1
45°	1395.6	1275.6	1170.7	1115.9	1073.2	1047.3	1040.1
47.5°	1155.6	1056.2	986.4	942.7	907.9	891.4	880.8
50°	1020.8	933.7	878.1	840.1	820.8	799.8	798.2
52.5°	908.5	838.2	794.9	764.1	739.5	726.9	727.3
55°	763.6	707.9	677.3	653.9	634.5	624.9	620.9
57.5°	643.3	601.5	579.3	557.7	549.6	542.0	539.9
60°	568.5	540.2	519.3	502.3	490.2	487.8	487.0
62.5°	506.5	477.0	462.5	449.4	440.6	436.9	435.4
65°	417.7	395.9	382.9	372.5	369.3	363.7	362.8
67.5°	336.7	323.7	315.1	307.8	303.5	303.2	303.2
70°	287.0	279.7	272.6	268.5	266.1	264.5	264.5
72.5°	244.5	239.1	233.2	231.1	230.6	228.9	228.3
75°	186.2	180.6	181.4	177.4	174.2	170.2	167.7
77.5°	132.1	128.1	127.2	126.7	124.0	123.5	124.8
80°	102.4	98.4	97.6	98.4	97.6	95.1	95.1
82.5°	77.9	74.5	73.7	73.2	72.4	73.2	71.9
85°	41.9	40.3	40.3	40.3	41.9	41.1	40.3
87.5°	22.7	22.5	23.4	22.9	23.0	22.5	23.3
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P333111-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)