

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863

Luminaire Tested: **S124DIW-S1195D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11356.6 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45				
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38				
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27				
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20				
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	1.7
10°-20°	528.8	4.7
20°-30°	778.3	6.9
30°-40°	904.8	8.0
40°-50°	904.8	8.0
50°-60°	791.5	7.0
60°-70°	587.8	5.2
70°-80°	333.9	2.9
80°-90°	102.2	0.9
90°-100°	69.0	0.6
100°-110°	439.7	3.9
110°-120°	841.1	7.4
120°-130°	1067.8	9.4
130°-140°	1142.4	10.1
140°-150°	1068.3	9.4
150°-160°	861.5	7.6
160°-170°	555.6	4.9
170°-180°	191.5	1.7
0°-30°	1494.7	13.2
0°-40°	2399.5	21.1
0°-60°	4095.8	36.1
0°-90°	5119.7	45.1
90°-120°	1349.8	11.9
90°-150°	4628.2	40.8
90°-180°	6237.0	54.9
0°-180°	11356.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	4	21	33	42	45	9
95°	83	35	33	42	44	107
105°	454	463	470	480	430	475
115°	848	852	850	853	854	834
125°	1191	1197	1194	1199	1200	1063
135°	1478	1477	1482	1485	1488	1138
145°	1704	1708	1709	1710	1713	1064
155°	1868	1870	1865	1871	1867	861
165°	1971	1964	1964	1974	1962	557
175°	2016	2008	2009	2021	2004	192
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	34.1	34.6	35.0	35.5	35.9	36.3	36.5	36.8	37.0	37.3	37.7
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	19.0	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0
95°	82.9	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2
97.5°	176.1	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0
100°	247.3	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7
102.5°	326.9	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2
105°	453.9	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5
107.5°	571.8	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1
110°	651.5	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	728.7	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9
115°	847.5	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2
117.5°	954.6	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8
120°	1027.0	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2
122.5°	1094.5	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7
125°	1191.4	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4
127.5°	1283.0	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3
130°	1342.2	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5
132.5°	1396.4	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2
135°	1477.9	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1
137.5°	1550.0	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9
140°	1597.0	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1
142.5°	1639.2	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2
145°	1704.1	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9
147.5°	1755.7	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9
150°	1793.1	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6
152.5°	1824.4	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1
155°	1868.5	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8
157.5°	1905.6	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3
160°	1927.3	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3
162.5°	1946.6	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3
165°	1971.0	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1
167.5°	1990.3	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5
170°	2001.2	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3
172.5°	2008.4	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5
175°	2016.2	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7
177.5°	2019.9	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	38.1	38.5	38.9	39.2	39.3	39.4	39.6	39.7
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	36.0	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	37.2	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.2	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	55.0	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	196.8	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	476.5	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	589.6	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	666.4	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P332863

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	740.8	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	851.9	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.7	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.1	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1196.4	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1291.1	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1348.9	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.6	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1483.7	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1558.7	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1605.1	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.0	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.3	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.1	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1827.6	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1868.1	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1943.4	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1968.8	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1987.5	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	1999.0	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2006.2	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2014.7	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2018.1	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)