

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333112-840

Luminaire Tested: **S124RDIW-S1195D1560U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333112-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10526.9 lumens  
Efficiency: N/A  
Efficacy: 127.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	80	73	71	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	71	67	64	61	57	53	51	49	43	42	40	35
3	82	73	66	60	75	67	61	56	57	52	49	48	44	42	39	37	35	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16156	16156	16156	16156
5°	18739	16204	14323	16204
10°	22168	16133	12782	16133
15°	25607	15984	10984	15984
20°	28511	15779	9933	15779
25°	29432	15577	9222	15577
30°	25765	15333	8793	15333
35°	20056	14970	8535	14970
40°	15039	14556	8395	14556
45°	11875	13891	8322	13891
50°	10025	13123	8081	13123
55°	8739	12279	7648	12279
60°	7863	11404	6770	11404
65°	6930	10457	5822	10457
70°	6243	9477	5254	9477
75°	5231	8400	4476	8400
80°	4421	7159	4198	7159
85°	3733	5604	3733	5604



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.9	1.8
10°-20°	584.9	5.6
20°-30°	914.8	8.7
30°-40°	1017.0	9.7
40°-50°	902.3	8.6
50°-60°	703.1	6.7
60°-70°	460.3	4.4
70°-80°	226.4	2.2
80°-90°	61.7	0.6
90°-100°	129.9	1.2
100°-110°	384.7	3.7
110°-120°	652.9	6.2
120°-130°	861.0	8.2
130°-140°	966.9	9.2
140°-150°	950.1	9.0
150°-160°	799.1	7.6
160°-170°	531.7	5.1
170°-180°	186.2	1.8
0°-30°	1693.6	16.1
0°-40°	2710.6	25.7
0°-60°	4316.0	41.0
0°-90°	5064.4	48.1
90°-120°	1167.5	11.1
90°-150°	3945.5	37.5
90°-180°	5463.0	51.9
0°-180°	10526.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	2312	2000	1767	2000	2312	234
15°	3064	1912	1314	1912	3064	871
25°	3304	1749	1035	1749	3304	1466
35°	2035	1519	866	1519	2035	1276
45°	1040	1217	729	1217	1040	824
55°	621	872	543	872	621	565
65°	363	547	305	547	363	365
75°	168	269	144	269	168	185
85°	40	60	40	60	40	47
90°	46	4	46	4	46	25
95°	120	91	120	91	120	125
105°	372	355	372	355	372	392
115°	658	664	658	664	658	650
125°	959	967	959	967	959	856
135°	1249	1247	1249	1247	1249	964
145°	1517	1515	1517	1515	1517	949
155°	1734	1736	1734	1736	1734	798
165°	1885	1890	1885	1890	1885	531
175°	1957	1966	1957	1966	1957	186
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2110.8	2116.7	2110.8	2110.2	2103.8	2101.8	2099.2	2090.8	2075.4	2066.4	2068.3
5°	2312.4	2332.6	2321.3	2319.7	2302.0	2284.2	2272.9	2247.2	2219.7	2201.2	2185.9
7.5°	2545.6	2557.2	2550.1	2538.8	2510.1	2493.9	2467.7	2433.7	2384.5	2346.9	2312.6
10°	2704.3	2713.9	2710.8	2689.8	2668.8	2626.1	2601.9	2554.4	2492.2	2443.1	2397.1
12.5°	2860.3	2870.7	2842.4	2843.3	2803.6	2770.0	2731.6	2671.7	2600.0	2536.6	2479.0
15°	3063.9	3051.0	3051.0	3034.8	2990.5	2943.8	2904.3	2841.4	2751.1	2675.2	2595.5
17.5°	3223.2	3227.7	3221.1	3183.1	3148.3	3099.9	3027.5	2954.1	2870.2	2768.4	2686.8
20°	3318.7	3318.7	3311.4	3285.6	3240.5	3188.9	3110.7	3030.8	2924.4	2822.0	2730.1
22.5°	3357.4	3359.9	3351.4	3330.1	3289.5	3239.1	3172.6	3091.5	2981.8	2866.5	2752.7
25°	3304.2	3319.5	3321.0	3315.5	3303.4	3272.7	3215.5	3132.4	3034.0	2909.1	2786.5
27.5°	3033.5	3052.9	3069.9	3097.8	3134.8	3154.2	3156.7	3114.5	3028.7	2908.4	2785.1
30°	2763.9	2780.1	2832.5	2901.0	2954.3	3002.6	3044.5	3055.9	3007.5	2899.4	2769.6
32.5°	2464.7	2486.6	2539.0	2612.7	2701.4	2783.3	2877.5	2925.5	2924.3	2859.4	2739.3
35°	2035.1	2051.2	2099.6	2177.0	2283.4	2405.2	2554.4	2670.4	2749.5	2743.8	2670.4
37.5°	1641.2	1659.5	1708.4	1772.5	1875.7	2026.5	2170.8	2330.8	2476.9	2559.0	2534.5
40°	1427.1	1427.9	1475.5	1541.7	1638.4	1769.8	1927.0	2104.4	2267.2	2400.3	2426.1
42.5°	1258.1	1258.3	1289.7	1361.0	1430.7	1554.4	1704.5	1880.6	2071.2	2224.8	2293.2
45°	1040.1	1047.3	1073.2	1115.9	1170.7	1275.6	1395.6	1559.3	1773.0	1955.2	2068.9
47.5°	880.8	891.4	907.9	942.7	986.4	1056.2	1155.6	1302.6	1476.4	1676.9	1838.7
50°	798.2	799.8	820.8	840.1	878.1	933.7	1020.8	1143.3	1302.9	1495.6	1675.5
52.5°	727.3	726.9	739.5	764.1	794.9	838.2	908.5	1020.1	1161.6	1334.4	1520.0
55°	620.9	624.9	634.5	653.9	677.3	707.9	763.6	847.4	958.7	1106.2	1274.8
57.5°	539.9	542.0	549.6	557.7	579.3	601.5	643.3	701.5	795.4	916.1	1073.2
60°	487.0	487.8	490.2	502.3	519.3	540.2	568.5	617.6	696.6	807.1	931.3
62.5°	435.4	436.9	440.6	449.4	462.5	477.0	506.5	546.0	611.5	705.8	817.7
65°	362.8	363.7	369.3	372.5	382.9	395.9	417.7	444.2	489.4	568.5	653.1
67.5°	303.2	303.2	303.5	307.8	315.1	323.7	336.7	358.0	392.0	440.6	515.2
70°	264.5	264.5	266.1	268.5	272.6	279.7	287.0	303.2	328.2	367.7	425.0
72.5°	228.3	228.9	230.6	231.1	233.2	239.1	244.5	254.8	273.4	303.2	349.4
75°	167.7	170.2	174.2	177.4	181.4	180.6	186.2	192.7	198.3	216.1	242.7
77.5°	124.8	123.5	124.0	126.7	127.2	128.1	132.1	137.0	141.3	149.7	159.2
80°	95.1	95.1	97.6	98.4	97.6	98.4	102.4	104.8	106.4	109.7	118.6
82.5°	71.9	73.2	72.4	73.2	73.7	74.5	77.9	78.4	80.0	81.3	85.0
85°	40.3	41.1	41.9	40.3	40.3	40.3	41.9	42.7	44.3	43.5	45.1
87.5°	23.3	22.5	23.0	22.9	23.4	22.5	22.7	23.6	21.9	22.2	21.6
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7	61.5	60.3	58.4
95°	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8	116.7	115.7	113.4
97.5°	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5	184.2	183.0	180.3
100°	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3	233.7	233.0	229.9
102.5°	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0	285.1	284.2	281.3
105°	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5	363.5	362.4	361.0
107.5°	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3	448.3	447.4	447.2
110°	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7	506.3	507.1	507.4



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4	566.6	566.7	567.3
115°	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1	660.6	660.9	661.6
117.5°	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2	751.3	752.6	753.0
120°	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2	812.9	814.7	815.7
122.5°	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2	874.4	875.6	876.1
125°	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0	964.7	965.4	965.7
127.5°	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9	1051.5	1052.2	1052.8
130°	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8	1112.5	1113.1	1113.1
132.5°	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0	1169.7	1170.3	1170.6
135°	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9	1255.6	1256.3	1256.3
137.5°	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0	1338.8	1339.7	1339.2
140°	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6	1392.9	1393.3	1393.3
142.5°	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3	1444.4	1444.4	1444.7
145°	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6	1592.8	1593.1	1593.4
150°	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7	1677.9	1677.1	1676.9
155°	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3	1734.7
157.5°	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5	1787.5	1786.5	1786.6
160°	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2	1819.2	1818.2	1818.5
162.5°	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6	1846.7	1844.9	1845.2
165°	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1	1884.1	1882.1	1882.8
167.5°	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8	1915.8	1913.8	1913.7
170°	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9	1932.8	1930.8	1930.5
172.5°	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6	1945.3	1943.0	1942.9
175°	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7	1957.0
177.5°	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0	1967.1	1965.2	1965.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2061.8	2052.9	2048.3	2038.0	2025.7	2019.2	2013.5	2005.1	1994.1	1982.5	1974.1
5°	2166.5	2147.2	2122.9	2094.0	2068.1	2043.2	2021.3	1999.6	1974.6	1948.8	1923.0
7.5°	2273.9	2235.8	2194.7	2147.2	2100.8	2058.8	2020.0	1983.0	1941.1	1903.5	1869.3
10°	2348.7	2297.1	2239.9	2179.4	2118.9	2066.5	2014.9	1968.1	1916.5	1870.6	1831.9
12.5°	2409.3	2348.7	2279.9	2204.5	2131.8	2068.4	2009.1	1948.1	1889.5	1839.7	1788.1
15°	2509.9	2426.9	2334.2	2243.9	2149.6	2063.3	1983.5	1912.5	1845.6	1775.4	1726.3
17.5°	2579.2	2480.6	2367.9	2259.4	2148.0	2046.2	1954.1	1869.7	1792.4	1720.8	1662.2
20°	2620.4	2511.5	2386.6	2263.2	2138.3	2029.4	1930.3	1836.7	1756.9	1679.5	1619.0
22.5°	2643.6	2523.1	2386.6	2257.5	2128.0	2010.0	1901.2	1803.8	1716.9	1639.5	1572.6
25°	2651.1	2522.0	2382.6	2234.2	2092.3	1967.3	1854.4	1748.8	1652.0	1574.7	1503.7
27.5°	2640.8	2488.8	2346.0	2193.7	2047.3	1915.6	1797.1	1686.1	1589.2	1506.1	1433.4
30°	2625.2	2462.4	2309.2	2151.2	2002.8	1876.2	1751.2	1644.9	1544.1	1457.7	1384.4
32.5°	2591.7	2430.1	2265.3	2103.4	1953.2	1822.7	1704.1	1597.1	1498.2	1410.1	1332.1
35°	2525.3	2361.6	2182.6	2016.5	1869.0	1733.5	1622.2	1519.0	1424.7	1330.4	1248.1
37.5°	2437.7	2270.5	2092.4	1910.6	1762.8	1635.0	1532.9	1436.0	1343.9	1257.8	1166.7
40°	2355.2	2202.8	2018.9	1838.4	1686.8	1563.4	1469.1	1381.2	1288.5	1203.0	1111.9
42.5°	2255.2	2125.4	1939.6	1758.4	1608.7	1489.9	1402.0	1316.1	1231.7	1148.8	1053.8
45°	2088.3	1989.9	1815.7	1641.6	1490.9	1373.1	1292.5	1216.7	1142.5	1063.5	974.0
47.5°	1897.0	1830.4	1680.1	1501.8	1362.3	1256.4	1178.5	1116.5	1053.8	974.8	896.3
50°	1764.1	1721.4	1576.3	1413.4	1280.4	1182.9	1103.0	1044.9	992.5	916.8	846.6
52.5°	1622.2	1599.5	1476.9	1321.2	1192.7	1097.0	1028.9	976.5	923.5	860.6	795.0
55°	1406.1	1418.3	1314.2	1179.6	1058.6	978.1	915.9	872.4	827.3	774.1	723.3
57.5°	1185.3	1229.4	1159.6	1041.4	928.1	853.5	806.8	770.1	732.3	688.1	644.7
60°	1053.0	1090.0	1050.6	946.5	847.4	778.1	734.6	706.3	668.4	628.1	595.0
62.5°	924.0	963.7	940.3	856.3	764.2	704.6	666.1	639.9	611.7	576.5	542.2
65°	761.9	787.7	776.5	718.4	653.1	602.3	566.8	547.4	521.7	495.8	465.2
67.5°	583.6	633.4	626.8	596.0	539.6	499.9	476.7	459.6	436.1	416.9	396.1
70°	479.8	525.7	524.9	499.9	469.3	432.1	416.1	401.5	380.5	362.0	345.1
72.5°	392.6	434.7	441.0	421.8	400.9	372.8	357.4	347.4	327.0	314.3	300.5
75°	275.0	305.6	313.7	313.7	304.0	289.4	275.8	269.3	254.8	243.5	235.4
77.5°	180.3	199.7	212.2	215.1	216.6	211.8	200.5	195.9	184.8	180.8	173.0
80°	127.3	140.3	154.8	159.7	163.7	162.1	157.2	154.0	143.5	139.5	136.2
82.5°	88.1	95.1	107.0	117.8	116.5	120.8	116.5	114.0	106.1	104.6	101.4
85°	45.9	46.8	48.4	55.6	59.7	61.3	62.1	60.5	58.1	58.1	52.4
87.5°	21.1	19.9	20.7	20.0	19.9	21.7	22.9	22.8	21.6	20.5	19.3
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6	36.9	41.1	45.3
95°	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4	94.4	97.5	100.5
97.5°	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6	162.0	164.4	166.9
100°	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2	214.5	215.9	217.2
102.5°	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2	269.7	270.3	270.8
105°	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8	355.2	355.5	355.8
107.5°	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6	445.0	445.5	445.9
110°	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5	506.2	506.9	507.6





TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9	569.1	569.2	569.3
115°	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9
117.5°	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5	753.7	754.0	754.3
120°	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1	814.5	815.9	817.2
122.5°	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3	875.8	876.4	876.9
125°	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9	966.9	966.9	966.9
127.5°	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1	1051.1	1052.1	1053.1
130°	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5	1109.5	1110.5	1111.6
132.5°	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2	1169.0	1169.7	1170.4
135°	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1	1249.1	1251.1	1253.2
137.5°	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0	1333.9	1334.8	1335.8
140°	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3	1390.9	1391.6	1392.3
142.5°	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6	1443.3	1444.0	1444.6
145°	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1	1516.4	1517.8	1519.1
147.5°	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0	1588.6	1590.2	1591.9
150°	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8	1632.1	1633.6	1634.9
152.5°	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2	1673.0	1673.9	1674.7
155°	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5	1788.9	1788.3	1787.7
160°	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2	1820.8	1820.5	1820.2
162.5°	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4	1849.6	1848.7	1847.8
165°	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7	1888.6	1887.6	1886.6
167.5°	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9	1918.4	1917.0	1915.6
170°	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9	1935.2	1933.5	1931.8
172.5°	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0	1947.6	1946.2	1944.8
175°	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8	1964.1	1962.5	1960.8
177.5°	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3	1969.9	1968.6	1967.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1965.1	1958.6	1950.3	1940.6	1928.9	1918.6	1914.1	1918.0	1920.0	1914.8	1914.1
5°	1905.2	1885.1	1869.0	1844.8	1825.4	1809.3	1798.1	1793.2	1794.8	1781.9	1778.7
7.5°	1838.1	1814.1	1787.7	1759.0	1732.2	1708.5	1696.1	1689.3	1675.7	1669.8	1660.0
10°	1794.8	1762.5	1736.8	1702.8	1672.2	1644.1	1630.3	1619.0	1605.3	1598.8	1585.2
12.5°	1750.3	1712.8	1684.5	1649.3	1618.0	1584.1	1570.9	1550.0	1528.5	1515.0	1497.4
15°	1687.6	1642.4	1607.7	1565.8	1528.7	1490.1	1455.3	1416.6	1402.1	1371.5	1353.7
17.5°	1614.2	1568.4	1525.5	1469.3	1412.0	1363.9	1327.0	1289.9	1267.7	1248.1	1239.1
20°	1565.8	1523.9	1464.2	1398.9	1335.2	1282.0	1252.1	1228.0	1203.8	1190.1	1180.4
22.5°	1520.0	1466.4	1397.1	1326.7	1262.9	1221.3	1196.1	1171.2	1151.5	1138.5	1125.6
25°	1443.3	1373.1	1299.7	1219.1	1175.6	1139.3	1111.9	1091.7	1079.6	1062.7	1056.2
27.5°	1364.4	1279.4	1198.5	1144.3	1098.9	1065.7	1041.9	1026.7	1011.4	1000.6	992.2
30°	1303.7	1217.5	1144.9	1093.3	1047.3	1020.0	1000.6	982.9	970.8	961.9	955.4
32.5°	1243.7	1157.5	1096.5	1041.1	1004.8	978.1	957.4	944.1	934.6	923.2	919.3
35°	1157.0	1080.5	1027.2	977.2	940.1	915.9	899.8	886.2	878.1	874.8	872.4
37.5°	1073.7	1010.9	953.7	912.7	879.7	860.6	841.6	834.9	829.3	823.5	826.2
40°	1020.8	961.9	911.1	867.6	840.9	820.0	808.7	800.6	795.8	795.8	795.8
42.5°	974.9	917.4	867.9	828.9	802.2	784.6	771.9	765.2	763.6	763.0	766.8
45°	903.8	850.6	800.6	768.4	745.8	728.1	720.8	715.2	715.2	718.4	719.2
47.5°	833.3	783.6	743.4	707.3	686.6	675.5	669.2	666.3	666.6	669.8	673.6
50°	790.1	740.9	701.5	669.2	649.8	639.3	633.7	632.2	633.7	633.7	639.3
52.5°	743.1	699.0	660.1	633.1	611.2	601.4	598.2	596.0	596.9	599.6	602.0
55°	674.1	634.5	597.4	571.7	555.5	549.1	541.8	542.6	541.0	542.6	542.6
57.5°	604.9	569.4	534.9	514.4	500.2	490.9	482.9	485.2	482.8	482.5	481.2
60°	560.4	521.7	494.2	475.7	459.6	451.5	444.2	445.9	443.4	441.8	438.6
62.5°	512.0	479.8	453.6	435.8	422.8	413.4	406.2	404.6	399.0	393.4	386.4
65°	441.8	415.3	391.8	375.0	362.8	355.6	349.9	345.1	333.0	320.1	313.7
67.5°	373.7	354.5	332.6	318.3	308.5	299.0	288.2	279.9	268.6	261.6	257.5
70°	329.7	311.2	292.7	278.9	268.5	259.6	247.5	241.9	233.8	230.6	226.6
72.5°	287.8	270.5	253.4	241.0	229.7	222.9	213.4	207.7	204.2	202.9	198.8
75°	224.2	210.5	197.5	186.2	177.4	172.6	168.5	164.5	162.9	155.6	151.6
77.5°	163.5	154.5	146.4	138.4	132.1	128.9	121.1	116.4	113.7	110.3	109.5
80°	127.3	121.0	112.9	108.1	99.2	95.9	92.7	91.9	91.1	90.3	89.5
82.5°	95.8	89.4	81.3	78.4	75.9	74.0	72.1	71.3	70.5	71.0	70.8
85°	48.4	45.1	45.1	44.3	43.5	42.7	41.9	41.9	41.1	41.9	41.1
87.5°	20.0	20.0	20.6	19.8	21.0	21.5	21.3	21.7	22.7	21.9	22.1
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7	63.9	65.1	65.9
95°	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8	118.8	119.8	120.3
97.5°	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5	186.7	187.9	188.5
100°	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3	235.0	235.7	236.0
102.5°	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0	287.0	287.9	288.5
105°	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5	365.5	366.5	367.5
107.5°	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3	450.2	451.2	451.6
110°	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7	505.0	504.3	504.5



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4	566.3	566.2	566.2
115°	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1	659.8	659.5	659.1
117.5°	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2	749.1	747.9	747.0
120°	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2	809.6	807.9	807.4
122.5°	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2	872.1	871.0	869.8
125°	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0	963.4	962.7	962.0
127.5°	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9	1050.2	1049.5	1048.8
130°	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8	1111.1	1110.3	1109.3
132.5°	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0	1168.3	1167.6	1167.0
135°	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9	1254.3	1253.5	1252.6
137.5°	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0	1337.1	1336.2	1335.8
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6	1392.3	1391.9	1391.6
142.5°	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3	1444.2	1444.2	1444.1
145°	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.7
147.5°	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6	1592.3	1592.0	1591.6
150°	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8
152.5°	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7	1679.5	1680.3	1680.3
155°	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8
157.5°	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5	1789.5	1790.5	1790.4
160°	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2	1821.2	1822.2	1821.8
162.5°	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6	1850.4	1852.2	1852.3
165°	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1	1888.1	1890.2	1890.6
167.5°	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8	1919.9	1921.9	1921.9
170°	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9	1936.9	1938.9	1938.7
172.5°	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6	1949.8	1952.2	1952.2
175°	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2
177.5°	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0	1970.9	1972.8	1972.7
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1910.3	1911.6	1907.0	1905.7	1907.0	1911.6	1910.3	1914.1	1914.8	1920.0	1918.0
5°	1772.2	1770.6	1766.6	1767.4	1766.6	1770.6	1772.2	1778.7	1781.9	1794.8	1793.2
7.5°	1654.2	1647.9	1649.6	1643.3	1649.6	1647.9	1654.2	1660.0	1669.8	1675.7	1689.3
10°	1582.0	1573.1	1565.8	1559.3	1565.8	1573.1	1582.0	1585.2	1598.8	1605.3	1619.0
12.5°	1483.3	1475.6	1465.8	1467.7	1465.8	1475.6	1483.3	1497.4	1515.0	1528.5	1550.0
15°	1343.2	1331.2	1311.8	1314.2	1311.8	1331.2	1343.2	1353.7	1371.5	1402.1	1416.6
17.5°	1224.8	1224.9	1216.1	1218.1	1216.1	1224.9	1224.8	1239.1	1248.1	1267.7	1289.9
20°	1163.5	1157.8	1158.6	1156.2	1158.6	1157.8	1163.5	1180.4	1190.1	1203.8	1228.0
22.5°	1120.8	1114.0	1108.3	1103.3	1108.3	1114.0	1120.8	1125.6	1138.5	1151.5	1171.2
25°	1048.9	1044.1	1036.9	1035.3	1036.9	1044.1	1048.9	1056.2	1062.7	1079.6	1091.7
27.5°	985.7	984.8	981.9	978.2	981.9	984.8	985.7	992.2	1000.6	1011.4	1026.7
30°	949.0	947.4	945.7	943.3	945.7	947.4	949.0	955.4	961.9	970.8	982.9
32.5°	916.1	915.1	913.5	913.7	913.5	915.1	916.1	919.3	923.2	934.6	944.1
35°	869.2	868.4	866.8	866.0	866.8	868.4	869.2	872.4	874.8	878.1	886.2
37.5°	825.4	827.4	826.5	826.3	826.5	827.4	825.4	826.2	823.5	829.3	834.9
40°	795.0	795.8	797.4	796.6	797.4	795.8	795.0	795.8	795.8	795.8	800.6
42.5°	769.8	770.0	772.2	769.5	772.2	770.0	769.8	766.8	763.0	763.6	765.2
45°	724.9	729.7	728.9	728.9	728.9	729.7	724.9	719.2	718.4	715.2	715.2
47.5°	675.7	679.8	681.0	680.9	681.0	679.8	675.7	673.6	669.8	666.6	666.3
50°	643.4	641.8	644.2	643.4	644.2	641.8	643.4	639.3	633.7	633.7	632.2
52.5°	604.1	604.4	604.2	603.4	604.2	604.4	604.1	602.0	599.6	596.9	596.0
55°	543.4	544.2	542.6	543.4	542.6	544.2	543.4	542.6	542.6	541.0	542.6
57.5°	477.7	473.7	475.3	473.4	475.3	473.7	477.7	481.2	482.5	482.8	485.2
60°	430.6	424.1	422.5	419.3	422.5	424.1	430.6	438.6	441.8	443.4	445.9
62.5°	377.7	373.1	367.7	370.2	367.7	373.1	377.7	386.4	393.4	399.0	404.6
65°	307.2	304.0	301.5	304.8	301.5	304.0	307.2	313.7	320.1	333.0	345.1
67.5°	254.3	252.6	252.6	251.0	252.6	252.6	254.3	257.5	261.6	268.6	279.9
70°	226.6	224.2	224.2	222.6	224.2	224.2	226.6	226.6	230.6	233.8	241.9
72.5°	198.1	195.8	196.4	195.4	196.4	195.8	198.1	198.8	202.9	204.2	207.7
75°	146.7	142.7	142.7	143.5	142.7	142.7	146.7	151.6	155.6	162.9	164.5
77.5°	109.5	108.7	109.8	108.4	109.8	108.7	109.5	109.5	110.3	113.7	116.4
80°	89.5	88.7	87.9	90.3	87.9	88.7	89.5	89.5	90.3	91.1	91.9
82.5°	69.5	69.4	69.2	72.2	69.2	69.4	69.5	70.8	71.0	70.5	71.3
85°	41.9	40.3	41.9	40.3	41.9	40.3	41.9	41.1	41.9	41.1	41.9
87.5°	23.5	23.0	22.5	23.3	22.5	23.0	23.5	22.1	21.9	22.7	21.7
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	66.3	66.8	67.2	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7
95°	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8
97.5°	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5
100°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3
102.5°	288.8	289.1	289.3	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0
105°	368.5	369.5	370.5	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5
107.5°	451.5	451.5	451.4	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3
110°	505.5	506.5	507.6	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	566.4	566.6	566.8	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4
115°	658.8	658.5	658.1	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1
117.5°	746.3	745.7	745.0	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2
120°	808.1	808.7	809.4	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2
122.5°	868.6	867.4	866.2	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2
125°	961.3	960.7	960.0	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0
127.5°	1048.3	1047.8	1047.2	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9
130°	1108.0	1106.7	1105.3	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8
132.5°	1166.5	1166.0	1165.4	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0
135°	1251.6	1250.6	1249.6	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9
137.5°	1336.1	1336.3	1336.5	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0
140°	1391.3	1390.9	1390.6	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6
142.5°	1444.0	1444.0	1443.9	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3
145°	1519.6	1518.6	1517.6	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1
147.5°	1591.3	1591.0	1590.6	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6
150°	1636.4	1636.1	1635.8	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9
152.5°	1679.4	1678.6	1677.7	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7
155°	1738.4	1737.1	1735.8	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1
157.5°	1789.3	1788.2	1787.0	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5
160°	1820.2	1818.5	1816.7	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2
162.5°	1850.6	1849.0	1847.2	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6
165°	1889.2	1887.8	1886.4	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1
167.5°	1919.8	1917.6	1915.5	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8
170°	1936.4	1934.0	1931.7	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9
172.5°	1949.7	1947.4	1945.0	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6
175°	1963.8	1961.5	1959.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5
177.5°	1970.4	1968.3	1966.2	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1914.1	1918.6	1928.9	1940.6	1950.3	1958.6	1965.1	1974.1	1982.5	1994.1	2005.1
5°	1798.1	1809.3	1825.4	1844.8	1869.0	1885.1	1905.2	1923.0	1948.8	1974.6	1999.6
7.5°	1696.1	1708.5	1732.2	1759.0	1787.7	1814.1	1838.1	1869.3	1903.5	1941.1	1983.0
10°	1630.3	1644.1	1672.2	1702.8	1736.8	1762.5	1794.8	1831.9	1870.6	1916.5	1968.1
12.5°	1570.9	1584.1	1618.0	1649.3	1684.5	1712.8	1750.3	1788.1	1839.7	1889.5	1948.1
15°	1455.3	1490.1	1528.7	1565.8	1607.7	1642.4	1687.6	1726.3	1775.4	1845.6	1912.5
17.5°	1327.0	1363.9	1412.0	1469.3	1525.5	1568.4	1614.2	1662.2	1720.8	1792.4	1869.7
20°	1252.1	1282.0	1335.2	1398.9	1464.2	1523.9	1565.8	1619.0	1679.5	1756.9	1836.7
22.5°	1196.1	1221.3	1262.9	1326.7	1397.1	1466.4	1520.0	1572.6	1639.5	1716.9	1803.8
25°	1111.9	1139.3	1175.6	1219.1	1299.7	1373.1	1443.3	1503.7	1574.7	1652.0	1748.8
27.5°	1041.9	1065.7	1098.9	1144.3	1198.5	1279.4	1364.4	1433.4	1506.1	1589.2	1686.1
30°	1000.6	1020.0	1047.3	1093.3	1144.9	1217.5	1303.7	1384.4	1457.7	1544.1	1644.9
32.5°	957.4	978.1	1004.8	1041.1	1096.5	1157.5	1243.7	1332.1	1410.1	1498.2	1597.1
35°	899.8	915.9	940.1	977.2	1027.2	1080.5	1157.0	1248.1	1330.4	1424.7	1519.0
37.5°	841.6	860.6	879.7	912.7	953.7	1010.9	1073.7	1166.7	1257.8	1343.9	1436.0
40°	808.7	820.0	840.9	867.6	911.1	961.9	1020.8	1111.9	1203.0	1288.5	1381.2
42.5°	771.9	784.6	802.2	828.9	867.9	917.4	974.9	1053.8	1148.8	1231.7	1316.1
45°	720.8	728.1	745.8	768.4	800.6	850.6	903.8	974.0	1063.5	1142.5	1216.7
47.5°	669.2	675.5	686.6	707.3	743.4	783.6	833.3	896.3	974.8	1053.8	1116.5
50°	633.7	639.3	649.8	669.2	701.5	740.9	790.1	846.6	916.8	992.5	1044.9
52.5°	598.2	601.4	611.2	633.1	660.1	699.0	743.1	795.0	860.6	923.5	976.5
55°	541.8	549.1	555.5	571.7	597.4	634.5	674.1	723.3	774.1	827.3	872.4
57.5°	482.9	490.9	500.2	514.4	534.9	569.4	604.9	644.7	688.1	732.3	770.1
60°	444.2	451.5	459.6	475.7	494.2	521.7	560.4	595.0	628.1	668.4	706.3
62.5°	406.2	413.4	422.8	435.8	453.6	479.8	512.0	542.2	576.5	611.7	639.9
65°	349.9	355.6	362.8	375.0	391.8	415.3	441.8	465.2	495.8	521.7	547.4
67.5°	288.2	299.0	308.5	318.3	332.6	354.5	373.7	396.1	416.9	436.1	459.6
70°	247.5	259.6	268.5	278.9	292.7	311.2	329.7	345.1	362.0	380.5	401.5
72.5°	213.4	222.9	229.7	241.0	253.4	270.5	287.8	300.5	314.3	327.0	347.4
75°	168.5	172.6	177.4	186.2	197.5	210.5	224.2	235.4	243.5	254.8	269.3
77.5°	121.1	128.9	132.1	138.4	146.4	154.5	163.5	173.0	180.8	184.8	195.9
80°	92.7	95.9	99.2	108.1	112.9	121.0	127.3	136.2	139.5	143.5	154.0
82.5°	72.1	74.0	75.9	78.4	81.3	89.4	95.8	101.4	104.6	106.1	114.0
85°	41.9	42.7	43.5	44.3	45.1	45.1	48.4	52.4	58.1	58.1	60.5
87.5°	21.3	21.5	21.0	19.8	20.6	20.0	20.0	19.3	20.5	21.6	22.8
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	61.5	60.3	58.4	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6
95°	116.7	115.7	113.4	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4
97.5°	184.2	183.0	180.3	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6
100°	233.7	233.0	229.9	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2
102.5°	285.1	284.2	281.3	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2
105°	363.5	362.4	361.0	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8
107.5°	448.3	447.4	447.2	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6
110°	506.3	507.1	507.4	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	566.6	566.7	567.3	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9
115°	660.6	660.9	661.6	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9
117.5°	751.3	752.6	753.0	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5
120°	812.9	814.7	815.7	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1
122.5°	874.4	875.6	876.1	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3
125°	964.7	965.4	965.7	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9
127.5°	1051.5	1052.2	1052.8	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1
130°	1112.5	1113.1	1113.1	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5
132.5°	1169.7	1170.3	1170.6	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2
135°	1255.6	1256.3	1256.3	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1
137.5°	1338.8	1339.7	1339.2	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3
142.5°	1444.4	1444.4	1444.7	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6
145°	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1
147.5°	1592.8	1593.1	1593.4	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0
150°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8
152.5°	1677.9	1677.1	1676.9	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2
155°	1735.8	1734.3	1734.7	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1787.5	1786.5	1786.6	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5
160°	1819.2	1818.2	1818.5	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2
162.5°	1846.7	1844.9	1845.2	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4
165°	1884.1	1882.1	1882.8	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7
167.5°	1915.8	1913.8	1913.7	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9
170°	1932.8	1930.8	1930.5	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9
172.5°	1945.3	1943.0	1942.9	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0
175°	1959.0	1956.7	1957.0	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8
177.5°	1967.1	1965.2	1965.2	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2013.5	2019.2	2025.7	2038.0	2048.3	2052.9	2061.8	2068.3	2066.4	2075.4	2090.8
5°	2021.3	2043.2	2068.1	2094.0	2122.9	2147.2	2166.5	2185.9	2201.2	2219.7	2247.2
7.5°	2020.0	2058.8	2100.8	2147.2	2194.7	2235.8	2273.9	2312.6	2346.9	2384.5	2433.7
10°	2014.9	2066.5	2118.9	2179.4	2239.9	2297.1	2348.7	2397.1	2443.1	2492.2	2554.4
12.5°	2009.1	2068.4	2131.8	2204.5	2279.9	2348.7	2409.3	2479.0	2536.6	2600.0	2671.7
15°	1983.5	2063.3	2149.6	2243.9	2334.2	2426.9	2509.9	2595.5	2675.2	2751.1	2841.4
17.5°	1954.1	2046.2	2148.0	2259.4	2367.9	2480.6	2579.2	2686.8	2768.4	2870.2	2954.1
20°	1930.3	2029.4	2138.3	2263.2	2386.6	2511.5	2620.4	2730.1	2822.0	2924.4	3030.8
22.5°	1901.2	2010.0	2128.0	2257.5	2386.6	2523.1	2643.6	2752.7	2866.5	2981.8	3091.5
25°	1854.4	1967.3	2092.3	2234.2	2382.6	2522.0	2651.1	2786.5	2909.1	3034.0	3132.4
27.5°	1797.1	1915.6	2047.3	2193.7	2346.0	2488.8	2640.8	2785.1	2908.4	3028.7	3114.5
30°	1751.2	1876.2	2002.8	2151.2	2309.2	2462.4	2625.2	2769.6	2899.4	3007.5	3055.9
32.5°	1704.1	1822.7	1953.2	2103.4	2265.3	2430.1	2591.7	2739.3	2859.4	2924.3	2925.5
35°	1622.2	1733.5	1869.0	2016.5	2182.6	2361.6	2525.3	2670.4	2743.8	2749.5	2670.4
37.5°	1532.9	1635.0	1762.8	1910.6	2092.4	2270.5	2437.7	2534.5	2559.0	2476.9	2330.8
40°	1469.1	1563.4	1686.8	1838.4	2018.9	2202.8	2355.2	2426.1	2400.3	2267.2	2104.4
42.5°	1402.0	1489.9	1608.7	1758.4	1939.6	2125.4	2255.2	2293.2	2224.8	2071.2	1880.6
45°	1292.5	1373.1	1490.9	1641.6	1815.7	1989.9	2088.3	2068.9	1955.2	1773.0	1559.3
47.5°	1178.5	1256.4	1362.3	1501.8	1680.1	1830.4	1897.0	1838.7	1676.9	1476.4	1302.6
50°	1103.0	1182.9	1280.4	1413.4	1576.3	1721.4	1764.1	1675.5	1495.6	1302.9	1143.3
52.5°	1028.9	1097.0	1192.7	1321.2	1476.9	1599.5	1622.2	1520.0	1334.4	1161.6	1020.1
55°	915.9	978.1	1058.6	1179.6	1314.2	1418.3	1406.1	1274.8	1106.2	958.7	847.4
57.5°	806.8	853.5	928.1	1041.4	1159.6	1229.4	1185.3	1073.2	916.1	795.4	701.5
60°	734.6	778.1	847.4	946.5	1050.6	1090.0	1053.0	931.3	807.1	696.6	617.6
62.5°	666.1	704.6	764.2	856.3	940.3	963.7	924.0	817.7	705.8	611.5	546.0
65°	566.8	602.3	653.1	718.4	776.5	787.7	761.9	653.1	568.5	489.4	444.2
67.5°	476.7	499.9	539.6	596.0	626.8	633.4	583.6	515.2	440.6	392.0	358.0
70°	416.1	432.1	469.3	499.9	524.9	525.7	479.8	425.0	367.7	328.2	303.2
72.5°	357.4	372.8	400.9	421.8	441.0	434.7	392.6	349.4	303.2	273.4	254.8
75°	275.8	289.4	304.0	313.7	313.7	305.6	275.0	242.7	216.1	198.3	192.7
77.5°	200.5	211.8	216.6	215.1	212.2	199.7	180.3	159.2	149.7	141.3	137.0
80°	157.2	162.1	163.7	159.7	154.8	140.3	127.3	118.6	109.7	106.4	104.8
82.5°	116.5	120.8	116.5	117.8	107.0	95.1	88.1	85.0	81.3	80.0	78.4
85°	62.1	61.3	59.7	55.6	48.4	46.8	45.9	45.1	43.5	44.3	42.7
87.5°	22.9	21.7	19.9	20.0	20.7	19.9	21.1	21.6	22.2	21.9	23.6
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7
95°	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8
97.5°	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5
100°	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3
102.5°	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0
105°	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5
107.5°	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3
110°	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7





TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4
115°	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1
117.5°	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2
120°	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2
122.5°	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2
125°	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0
127.5°	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9
130°	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8
132.5°	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0
135°	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9
137.5°	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0
140°	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6
142.5°	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3
145°	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1
147.5°	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6
150°	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7
155°	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1
157.5°	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5
160°	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2
162.5°	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6
165°	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1
167.5°	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8
170°	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9
172.5°	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6
175°	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5
177.5°	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2099.2	2101.8	2103.8	2110.2	2110.8	2116.7	2110.8
5°	2272.9	2284.2	2302.0	2319.7	2321.3	2332.6	2312.4
7.5°	2467.7	2493.9	2510.1	2538.8	2550.1	2557.2	2545.6
10°	2601.9	2626.1	2668.8	2689.8	2710.8	2713.9	2704.3
12.5°	2731.6	2770.0	2803.6	2843.3	2842.4	2870.7	2860.3
15°	2904.3	2943.8	2990.5	3034.8	3051.0	3051.0	3063.9
17.5°	3027.5	3099.9	3148.3	3183.1	3221.1	3227.7	3223.2
20°	3110.7	3188.9	3240.5	3285.6	3311.4	3318.7	3318.7
22.5°	3172.6	3239.1	3289.5	3330.1	3351.4	3359.9	3357.4
25°	3215.5	3272.7	3303.4	3315.5	3321.0	3319.5	3304.2
27.5°	3156.7	3154.2	3134.8	3097.8	3069.9	3052.9	3033.5
30°	3044.5	3002.6	2954.3	2901.0	2832.5	2780.1	2763.9
32.5°	2877.5	2783.3	2701.4	2612.7	2539.0	2486.6	2464.7
35°	2554.4	2405.2	2283.4	2177.0	2099.6	2051.2	2035.1
37.5°	2170.8	2026.5	1875.7	1772.5	1708.4	1659.5	1641.2
40°	1927.0	1769.8	1638.4	1541.7	1475.5	1427.9	1427.1
42.5°	1704.5	1554.4	1430.7	1361.0	1289.7	1258.3	1258.1
45°	1395.6	1275.6	1170.7	1115.9	1073.2	1047.3	1040.1
47.5°	1155.6	1056.2	986.4	942.7	907.9	891.4	880.8
50°	1020.8	933.7	878.1	840.1	820.8	799.8	798.2
52.5°	908.5	838.2	794.9	764.1	739.5	726.9	727.3
55°	763.6	707.9	677.3	653.9	634.5	624.9	620.9
57.5°	643.3	601.5	579.3	557.7	549.6	542.0	539.9
60°	568.5	540.2	519.3	502.3	490.2	487.8	487.0
62.5°	506.5	477.0	462.5	449.4	440.6	436.9	435.4
65°	417.7	395.9	382.9	372.5	369.3	363.7	362.8
67.5°	336.7	323.7	315.1	307.8	303.5	303.2	303.2
70°	287.0	279.7	272.6	268.5	266.1	264.5	264.5
72.5°	244.5	239.1	233.2	231.1	230.6	228.9	228.3
75°	186.2	180.6	181.4	177.4	174.2	170.2	167.7
77.5°	132.1	128.1	127.2	126.7	124.0	123.5	124.8
80°	102.4	98.4	97.6	98.4	97.6	95.1	95.1
82.5°	77.9	74.5	73.7	73.2	72.4	73.2	71.9
85°	41.9	40.3	40.3	40.3	41.9	41.1	40.3
87.5°	22.7	22.5	23.4	22.9	23.0	22.5	23.3
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P333112-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)