

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332864

Luminaire Tested: **S124DIW-S1195D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332864
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10528.8 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	97	93	89	86	90	86	83	79	72	70	68	60	58	57	48	47	46	41					41			
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34					34			
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29					29			
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25					25			
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22					22			
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19					19			
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17					17			
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15					15			
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14					14			
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	1.8
10°-20°	528.8	5.0
20°-30°	778.3	7.4
30°-40°	904.8	8.6
40°-50°	904.8	8.6
50°-60°	791.5	7.5
60°-70°	587.8	5.6
70°-80°	333.9	3.2
80°-90°	102.2	1.0
90°-100°	128.6	1.2
100°-110°	380.9	3.6
110°-120°	646.6	6.1
120°-130°	852.5	8.1
130°-140°	957.5	9.1
140°-150°	940.9	8.9
150°-160°	791.3	7.5
160°-170°	526.5	5.0
170°-180°	184.4	1.8
0°-30°	1494.7	14.2
0°-40°	2399.5	22.8
0°-60°	4095.8	38.9
0°-90°	5119.7	48.6
90°-120°	1156.1	11.0
90°-150°	3906.9	37.1
90°-180°	5409.0	51.4
0°-180°	10528.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	4	21	33	42	45	10
95°	90	104	115	119	119	101
105°	351	353	359	363	368	373
115°	657	657	654	653	651	648
125°	958	957	956	953	950	853
135°	1235	1244	1244	1241	1236	955
145°	1500	1506	1508	1506	1502	939
155°	1719	1719	1717	1723	1717	791
165°	1871	1867	1864	1872	1867	527
175°	1947	1939	1938	1947	1938	185
180°	1950	1950	1950	1950	1950	



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	34.1	34.6	35.0	35.5	35.9	36.3	36.5	36.8	37.0	37.3	37.7
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	32.3	36.5	40.7	44.9	49.2	52.2	54.1	56.0	57.8	59.7	60.9
95°	90.5	93.5	96.5	99.5	102.5	105.2	107.6	109.9	112.3	114.6	115.6
97.5°	158.0	160.4	162.8	165.3	167.7	170.3	173.0	175.7	178.5	181.2	182.4
100°	211.1	212.4	213.8	215.1	216.5	218.6	221.7	224.7	227.7	230.7	231.4
102.5°	266.6	267.1	267.7	268.2	268.7	270.4	273.1	275.9	278.6	281.4	282.3
105°	351.3	351.7	352.0	352.3	352.7	353.5	354.8	356.2	357.5	358.9	359.9
107.5°	440.3	440.7	441.1	441.5	441.9	442.2	442.4	442.6	442.8	443.0	443.9
110°	500.6	501.3	501.9	502.6	503.3	503.5	503.1	502.8	502.4	502.1	501.4



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	563.3	563.5	563.6	563.7	563.9	563.6	563.0	562.4	561.8	561.2	561.1
115°	657.4	657.4	657.4	657.4	657.4	657.1	656.4	655.7	655.1	654.4	654.1
117.5°	746.1	746.3	746.6	746.9	747.2	747.1	746.6	746.1	745.6	745.2	744.0
120°	805.2	806.5	807.9	809.2	810.5	810.7	809.7	808.7	807.7	806.7	805.0
122.5°	866.7	867.2	867.8	868.3	868.8	868.9	868.4	867.9	867.5	867.0	865.9
125°	957.5	957.5	957.5	957.5	957.5	957.3	957.0	956.6	956.3	956.0	955.3
127.5°	1039.8	1040.8	1041.8	1042.8	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2
130°	1097.7	1098.7	1099.7	1100.7	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6
132.5°	1156.8	1157.6	1158.3	1159.0	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3
135°	1234.9	1236.9	1238.9	1241.0	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3
137.5°	1320.0	1320.9	1321.8	1322.8	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7
140°	1376.7	1377.3	1378.0	1378.7	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3
142.5°	1428.5	1429.2	1429.9	1430.5	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3
145°	1500.3	1501.6	1503.0	1504.3	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5
147.5°	1571.5	1573.1	1574.7	1576.3	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2
150°	1614.9	1616.2	1617.6	1618.9	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1655.9	1656.7	1657.5	1658.3	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5
155°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8
157.5°	1772.0	1771.4	1770.8	1770.2	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0
160°	1803.4	1803.0	1802.7	1802.4	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4
162.5°	1832.3	1831.5	1830.6	1829.7	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7
165°	1871.2	1870.2	1869.2	1868.2	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7
167.5°	1901.1	1899.7	1898.3	1896.9	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1
170°	1918.0	1916.3	1914.6	1912.9	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9
172.5°	1930.0	1928.6	1927.2	1925.8	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3
175°	1946.6	1944.9	1943.3	1941.6	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9
177.5°	1952.0	1950.7	1949.4	1948.0	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	38.1	38.5	38.9	39.2	39.3	39.4	39.6	39.7
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	62.1	63.3	64.5	65.3	65.7	66.1	66.5	66.9
95°	116.6	117.6	118.6	119.1	119.1	119.1	119.1	119.1
97.5°	183.7	184.9	186.1	186.7	186.7	186.7	186.7	186.7
100°	232.0	232.7	233.4	233.7	233.7	233.7	233.7	233.7
102.5°	283.2	284.2	285.1	285.7	286.0	286.3	286.5	286.8
105°	360.9	361.9	362.9	363.9	364.9	365.9	366.9	367.9
107.5°	444.9	445.8	446.8	447.2	447.1	447.1	447.0	446.9
110°	500.8	500.1	499.4	499.6	500.6	501.6	502.6	503.6



TEST NUMBER: P332864

CATALOG NUMBER: S124DIW-S1195D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	560.9	560.8	560.7	560.7	560.9	561.1	561.3	561.5
115°	653.7	653.4	653.1	652.7	652.4	652.1	651.7	651.4
117.5°	742.9	741.8	740.6	739.7	739.0	738.4	737.7	737.0
120°	803.3	801.7	800.0	799.5	800.2	800.8	801.5	802.2
122.5°	864.7	863.6	862.5	861.3	860.1	858.9	857.7	856.5
125°	954.6	954.0	953.3	952.6	951.9	951.3	950.6	949.9
127.5°	1040.6	1039.9	1039.2	1038.6	1038.1	1037.6	1037.0	1036.5
130°	1100.9	1100.2	1099.5	1098.5	1097.2	1095.9	1094.5	1093.2
132.5°	1157.6	1156.9	1156.2	1155.6	1155.1	1154.6	1154.0	1153.5
135°	1242.6	1242.0	1241.3	1240.4	1239.4	1238.4	1237.4	1236.4
137.5°	1324.9	1324.0	1323.1	1322.8	1323.0	1323.2	1323.4	1323.6
140°	1379.0	1378.7	1378.3	1378.0	1377.7	1377.3	1377.0	1376.7
142.5°	1430.2	1430.1	1430.1	1430.0	1429.9	1429.9	1429.8	1429.7
145°	1507.2	1506.8	1506.5	1505.8	1504.8	1503.8	1502.8	1501.8
147.5°	1577.0	1576.7	1576.4	1576.1	1575.8	1575.5	1575.1	1574.8
150°	1620.9	1620.9	1620.9	1620.8	1620.4	1620.1	1619.8	1619.4
152.5°	1662.3	1663.1	1663.9	1663.9	1663.0	1662.2	1661.3	1660.4
155°	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4
157.5°	1771.0	1772.0	1773.0	1772.9	1771.8	1770.7	1769.5	1768.4
160°	1802.4	1803.4	1804.4	1804.0	1802.4	1800.7	1799.0	1797.3
162.5°	1830.5	1832.3	1834.1	1834.2	1832.5	1830.9	1829.2	1827.5
165°	1867.7	1869.7	1871.7	1872.1	1870.7	1869.4	1868.0	1866.7
167.5°	1899.1	1901.1	1903.1	1903.1	1901.0	1898.9	1896.8	1894.7
170°	1916.0	1918.0	1920.0	1919.8	1917.5	1915.1	1912.8	1910.4
172.5°	1928.6	1930.8	1933.1	1933.1	1930.7	1928.4	1926.0	1923.7
175°	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6
177.5°	1949.8	1951.6	1953.5	1953.4	1951.2	1949.1	1947.0	1944.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6

(END OF REPORT)