

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333113-840

Luminaire Tested: **S124RDIW-S1195D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333113-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11170.1 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.8	1.8
10°-20°	551.7	4.9
20°-30°	796.6	7.1
30°-40°	903.0	8.1
40°-50°	872.0	7.8
50°-60°	725.1	6.5
60°-70°	500.7	4.5
70°-80°	253.8	2.3
80°-90°	71.0	0.6
90°-100°	69.6	0.6
100°-110°	444.0	4.0
110°-120°	849.4	7.6
120°-130°	1078.3	9.7
130°-140°	1153.7	10.3
140°-150°	1078.8	9.7
150°-160°	870.0	7.8
160°-170°	561.1	5.0
170°-180°	193.4	1.7
0°-30°	1546.1	13.8
0°-40°	2449.1	21.9
0°-60°	4046.2	36.2
0°-90°	4871.6	43.6
90°-120°	1363.1	12.2
90°-150°	4673.9	41.8
90°-180°	6298.0	56.4
0°-180°	11170.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	4	21	34	42	46	8
95°	84	35	34	42	44	108
105°	458	468	475	485	434	480
115°	856	860	859	862	862	842
125°	1203	1209	1206	1211	1212	1074
135°	1492	1491	1497	1500	1503	1149
145°	1721	1725	1726	1727	1730	1075
155°	1887	1888	1884	1889	1885	870
165°	1990	1983	1983	1994	1981	562
175°	2036	2028	2028	2040	2024	194
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.6	29.1	27.5	26.0	24.4	23.7	24.0	24.2	24.5	24.7	24.8
90°	4.5	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5
92.5°	19.2	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3
95°	83.7	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5
97.5°	177.8	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4
100°	249.7	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3
102.5°	330.1	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7
105°	458.4	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2
107.5°	577.4	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9
110°	657.9	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	735.9	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2
115°	855.9	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6
117.5°	964.0	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3
120°	1037.1	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4
122.5°	1105.3	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6
125°	1203.2	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2
127.5°	1295.7	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0
130°	1355.4	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8
132.5°	1410.2	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1
135°	1492.5	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7
137.5°	1565.3	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3
140°	1612.8	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9
142.5°	1655.4	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4
145°	1720.9	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8
147.5°	1773.0	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3
150°	1810.8	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3
152.5°	1842.4	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1
155°	1886.9	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2
157.5°	1924.4	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1
160°	1946.3	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3
162.5°	1965.8	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5
165°	1990.4	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5
167.5°	2009.9	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1
170°	2020.9	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0
172.5°	2028.2	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3
175°	2036.1	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5
177.5°	2039.8	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	25.0	25.1	25.2	25.5	26.0	26.4	26.8	27.2
90°	37.6	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	36.4	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	37.6	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.6	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	55.5	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	198.7	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	481.2	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	595.4	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.0	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P333113-840

CATALOG NUMBER: S124RDIW-S1195D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.1	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.3	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.2	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.0	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1208.2	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.8	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.2	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.5	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1498.3	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.1	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1620.9	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1664.3	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.2	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.5	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1845.6	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1886.5	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1962.6	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1988.2	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2007.1	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2018.7	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2026.0	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2034.6	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2038.0	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)