

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333098-840

Luminaire Tested: **S124RDIW-S1195D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333098-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6509.1 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	68	64				
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57	54				
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46				
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40				
5	73	61	53	47	70	59	51	46	54	48	43	49	44	40	45	41	38	35				
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31				
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	33	30	27				
8	59	46	38	33	56	44	37	32	41	35	30	38	32	28	35	30	27	25				
9	55	42	34	29	52	41	33	29	38	31	27	35	29	26	32	28	24	22				
10	51	39	31	26	49	37	31	26	35	29	25	32	27	23	30	25	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.8	3.0
10°-20°	551.7	8.5
20°-30°	796.6	12.2
30°-40°	903.0	13.9
40°-50°	872.0	13.4
50°-60°	725.1	11.1
60°-70°	500.7	7.7
70°-80°	253.8	3.9
80°-90°	66.9	1.0
90°-100°	39.0	0.6
100°-110°	115.6	1.8
110°-120°	196.2	3.0
120°-130°	258.7	4.0
130°-140°	290.6	4.5
140°-150°	285.5	4.4
150°-160°	240.2	3.7
160°-170°	159.8	2.5
170°-180°	56.0	0.9
0°-30°	1546.1	23.8
0°-40°	2449.1	37.6
0°-60°	4046.2	62.2
0°-90°	4867.5	74.8
90°-120°	350.9	5.4
90°-150°	1185.7	18.2
90°-180°	1642.0	25.2
0°-180°	6509.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	1	6	10	13	14	6
95°	28	32	35	36	36	31
105°	107	107	109	110	112	113
115°	200	199	199	198	198	197
125°	290	290	290	289	288	259
135°	375	377	378	377	375	290
145°	455	457	458	457	456	285
155°	522	522	521	523	521	240
165°	568	566	566	568	566	160
175°	591	589	588	591	588	56
180°	592	592	592	592	592	



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.0	27.9	25.9	23.7	21.7	20.6	20.4	20.3	20.2	20.1	19.9
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	9.8	11.1	12.3	13.6	14.9	15.9	16.5	17.0	17.6	18.1	18.5
95°	27.5	28.4	29.3	30.2	31.1	31.9	32.6	33.3	34.0	34.7	35.0
97.5°	48.0	48.7	49.4	50.2	50.9	51.7	52.5	53.3	54.1	55.0	55.3
100°	64.0	64.4	64.8	65.2	65.7	66.3	67.3	68.2	69.1	70.0	70.2
102.5°	80.9	81.1	81.2	81.4	81.6	82.1	82.9	83.7	84.5	85.4	85.6
105°	106.6	106.7	106.8	106.9	107.0	107.2	107.7	108.1	108.5	108.9	109.2
107.5°	133.6	133.7	133.9	134.0	134.1	134.2	134.3	134.3	134.4	134.4	134.7
110°	151.9	152.1	152.3	152.5	152.7	152.8	152.7	152.6	152.5	152.4	152.2



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.0	171.0	171.1	171.1	171.2	171.1	170.9	170.7	170.5	170.4	170.3
115°	199.5	199.5	199.5	199.5	199.5	199.4	199.2	199.0	198.8	198.6	198.5
117.5°	226.4	226.5	226.6	226.7	226.7	226.7	226.6	226.4	226.3	226.1	225.8
120°	244.4	244.8	245.2	245.6	246.0	246.0	245.7	245.4	245.1	244.8	244.3
122.5°	263.1	263.2	263.4	263.5	263.7	263.7	263.6	263.4	263.3	263.2	262.8
125°	290.5	290.5	290.5	290.5	290.5	290.5	290.4	290.3	290.2	290.1	289.9
127.5°	315.6	315.9	316.2	316.5	316.8	316.9	316.7	316.5	316.4	316.2	316.0
130°	333.2	333.5	333.8	334.1	334.4	334.5	334.5	334.5	334.5	334.5	334.3
132.5°	351.0	351.3	351.5	351.7	351.9	352.0	351.9	351.8	351.8	351.7	351.5
135°	374.8	375.4	376.0	376.6	377.2	377.5	377.5	377.5	377.5	377.5	377.3
137.5°	400.6	400.9	401.1	401.4	401.7	401.9	402.1	402.3	402.4	402.6	402.3
140°	417.8	418.0	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7	418.6
142.5°	433.5	433.7	433.9	434.1	434.3	434.4	434.3	434.2	434.1	434.0	434.0
145°	455.3	455.8	456.2	456.6	457.0	457.2	457.3	457.4	457.5	457.6	457.5
147.5°	477.0	477.4	477.9	478.4	478.9	479.1	479.0	478.9	478.9	478.8	478.7
150°	490.1	490.5	490.9	491.3	491.7	491.9	491.9	491.9	491.9	491.9	491.9
152.5°	502.5	502.8	503.0	503.3	503.5	503.7	503.7	503.8	503.9	504.0	504.2
155°	521.7	521.7	521.7	521.7	521.7	521.6	521.5	521.4	521.3	521.2	521.6
157.5°	537.8	537.6	537.5	537.2	537.0	536.9	536.9	536.9	536.8	536.8	537.1
160°	547.3	547.2	547.1	547.0	546.9	546.8	546.7	546.6	546.5	546.4	546.7
162.5°	556.1	555.8	555.5	555.3	555.0	554.8	554.7	554.6	554.5	554.4	555.0
165°	567.8	567.5	567.2	566.9	566.6	566.4	566.2	566.0	565.8	565.6	566.2
167.5°	576.9	576.5	576.1	575.7	575.2	575.0	575.0	575.1	575.1	575.1	575.7
170°	582.1	581.6	581.1	580.6	580.1	579.9	580.0	580.1	580.2	580.3	580.9
172.5°	585.7	585.3	584.9	584.5	584.0	583.8	583.8	583.9	583.9	583.9	584.6
175°	590.8	590.3	589.8	589.3	588.8	588.4	588.3	588.2	588.1	588.0	588.8
177.5°	592.4	592.0	591.6	591.2	590.8	590.6	590.6	590.6	590.6	590.6	591.2
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	19.8	19.6	19.4	19.5	19.8	20.2	20.5	20.8
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	18.9	19.2	19.6	19.8	20.0	20.1	20.2	20.3
95°	35.3	35.6	36.0	36.2	36.2	36.2	36.2	36.2
97.5°	55.7	56.1	56.5	56.7	56.7	56.7	56.7	56.7
100°	70.4	70.6	70.8	70.9	70.9	70.9	70.9	70.9
102.5°	85.9	86.2	86.5	86.7	86.7	86.8	86.9	87.1
105°	109.6	109.9	110.2	110.5	110.8	111.1	111.4	111.7
107.5°	135.0	135.3	135.6	135.7	135.7	135.7	135.6	135.6
110°	152.0	151.8	151.6	151.6	151.9	152.2	152.5	152.8



TEST NUMBER: P333098-840

CATALOG NUMBER: S124RDIW-S1195D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.3	170.2	170.2	170.2	170.3	170.3	170.4	170.4
115°	198.4	198.3	198.2	198.1	198.0	197.9	197.8	197.7
117.5°	225.5	225.1	224.8	224.5	224.3	224.1	223.9	223.7
120°	243.8	243.3	242.8	242.7	242.9	243.1	243.3	243.5
122.5°	262.5	262.1	261.8	261.4	261.1	260.6	260.2	259.9
125°	289.7	289.5	289.3	289.1	288.9	288.7	288.5	288.3
127.5°	315.8	315.6	315.4	315.2	315.1	314.9	314.8	314.6
130°	334.1	333.9	333.7	333.4	333.0	332.5	332.1	331.7
132.5°	351.3	351.1	350.9	350.7	350.5	350.4	350.2	350.1
135°	377.1	376.9	376.7	376.5	376.2	375.9	375.6	375.3
137.5°	402.0	401.8	401.5	401.4	401.5	401.5	401.6	401.7
140°	418.5	418.4	418.3	418.2	418.1	418.0	417.9	417.8
142.5°	434.0	434.0	434.0	433.9	433.9	433.9	433.9	433.9
145°	457.4	457.3	457.2	457.0	456.7	456.4	456.1	455.8
147.5°	478.6	478.5	478.5	478.4	478.3	478.2	478.1	478.0
150°	491.9	491.9	491.9	491.9	491.8	491.7	491.6	491.5
152.5°	504.5	504.7	505.0	504.9	504.7	504.4	504.2	503.9
155°	522.0	522.4	522.8	522.8	522.4	522.0	521.6	521.2
157.5°	537.5	537.8	538.1	538.1	537.8	537.3	537.0	536.6
160°	547.0	547.3	547.6	547.5	547.0	546.5	545.9	545.4
162.5°	555.5	556.1	556.6	556.6	556.1	555.6	555.1	554.6
165°	566.8	567.4	568.0	568.2	567.7	567.3	566.9	566.5
167.5°	576.3	576.9	577.5	577.5	576.9	576.3	575.6	575.0
170°	581.5	582.1	582.7	582.6	581.9	581.2	580.5	579.8
172.5°	585.3	586.0	586.6	586.6	585.9	585.2	584.5	583.8
175°	589.5	590.2	590.9	590.9	590.2	589.5	588.8	588.0
177.5°	591.8	592.3	592.9	592.8	592.2	591.6	590.9	590.3
180°	591.7	591.7	591.7	591.7	591.7	591.7	591.7	591.7

(END OF REPORT)