

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332734

Luminaire Tested: **S124DIW-S350D1340U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332734
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1340U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6233.6 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25								
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22								
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24	18								
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16								
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18	13								
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12								
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10								
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12	9								
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8								
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7								
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4612	4612	4612	4612
5°	5431	4624	4081	4624
10°	6503	4604	3674	4604
15°	7694	4557	3375	4557
20°	8568	4509	3107	4509
25°	8706	4440	2922	4440
30°	7408	4373	2864	4373
35°	5695	4263	2864	4263
40°	4440	4135	2918	4135
45°	3701	3942	2967	3942
50°	3258	3706	3067	3706
55°	2985	3424	3191	3424
60°	2796	3171	3339	3171
65°	2604	2888	3463	2888
70°	2379	2608	3541	2608
75°	2127	2296	3500	2296
80°	1781	1883	3389	1883
85°	1315	1362	3242	1362



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	0.9
10°-20°	171.6	2.8
20°-30°	272.0	4.4
30°-40°	302.8	4.9
40°-50°	275.6	4.4
50°-60°	225.2	3.6
60°-70°	160.8	2.6
70°-80°	88.5	1.4
80°-90°	29.2	0.5
90°-100°	110.6	1.8
100°-110°	327.6	5.3
110°-120°	556.1	8.9
120°-130°	733.3	11.8
130°-140°	823.5	13.2
140°-150°	809.2	13.0
150°-160°	680.6	10.9
160°-170°	452.8	7.3
170°-180°	158.6	2.5
0°-30°	499.3	8.0
0°-40°	802.0	12.9
0°-60°	1302.8	20.9
0°-90°	1581.3	25.4
90°-120°	994.3	16.0
90°-150°	3360.3	53.9
90°-180°	4652.0	74.6
0°-180°	6233.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	571	571	571	571	571	
5°	670	571	504	571	670	68
15°	921	545	404	545	921	260
25°	977	498	328	498	977	431
35°	578	433	291	433	578	367
45°	324	345	260	345	324	255
55°	212	243	227	243	212	192
65°	136	151	181	151	136	135
75°	68	74	112	74	68	72
85°	14	15	35	15	14	18
90°	39	4	39	4	39	20
95°	102	78	102	78	102	107
105°	316	302	316	302	316	333
115°	560	565	560	565	560	554
125°	817	824	817	824	817	729
135°	1063	1062	1063	1062	1063	821
145°	1292	1290	1292	1290	1292	808
155°	1477	1478	1477	1478	1477	680
165°	1606	1609	1606	1609	1606	452
175°	1666	1674	1666	1674	1666	158
180°	1677	1677	1677	1677	1677	



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	608.0	607.9	606.0	605.6	604.3	602.6	602.2	599.1	593.1	590.2	589.5
5°	670.2	675.0	668.8	667.6	666.9	659.1	655.1	650.4	639.5	633.1	628.1
7.5°	744.5	745.0	742.3	740.2	734.1	727.3	717.1	706.2	693.2	679.8	669.6
10°	793.3	795.2	792.1	791.7	779.6	772.0	756.9	744.1	729.4	713.1	698.2
12.5°	844.8	842.2	840.6	830.5	828.2	814.4	796.8	783.7	761.0	742.2	722.4
15°	920.6	915.4	912.1	898.2	891.3	872.1	853.4	839.0	809.4	781.2	759.9
17.5°	965.1	970.3	962.7	956.9	939.2	925.7	906.6	876.3	853.2	818.2	791.3
20°	997.3	997.8	993.5	987.6	973.7	956.6	935.8	902.7	875.0	840.2	803.2
22.5°	1006.0	1006.1	1004.3	998.8	988.2	974.4	953.4	925.7	892.2	854.4	817.4
25°	977.4	976.5	978.6	984.8	980.8	976.5	964.4	943.8	912.6	872.6	832.8
27.5°	871.2	877.8	889.8	904.9	919.5	930.6	933.7	929.5	910.2	877.3	835.6
30°	794.7	802.8	811.8	826.9	856.3	873.1	891.5	905.5	897.7	871.4	832.6
32.5°	710.7	712.7	726.0	743.2	770.1	802.4	831.7	860.1	869.5	855.7	823.3
35°	577.9	581.3	595.7	612.7	645.6	685.2	729.2	768.5	800.9	813.9	797.3
37.5°	471.6	481.1	491.3	509.6	538.6	574.2	619.9	670.8	719.1	751.5	757.0
40°	421.3	427.2	434.5	448.5	473.1	508.1	547.4	605.6	657.0	703.4	718.5
42.5°	381.5	385.0	389.5	402.1	420.8	455.7	491.6	542.8	594.3	649.8	675.2
45°	324.2	327.8	335.4	342.7	356.9	381.0	414.4	456.5	508.4	561.8	608.7
47.5°	282.9	285.1	289.6	297.5	309.6	325.5	352.6	387.8	435.8	487.8	537.7
50°	259.4	261.3	264.8	271.9	281.2	295.4	317.6	350.5	388.1	440.4	489.4
52.5°	240.8	241.6	244.2	249.0	256.4	268.3	286.6	313.8	348.8	395.4	444.2
55°	212.1	213.0	215.4	218.9	225.3	232.9	246.8	267.2	297.7	338.2	380.6
57.5°	188.4	189.1	191.0	192.4	197.7	203.8	214.6	229.1	252.2	286.6	324.4
60°	173.2	172.8	175.1	176.3	179.9	185.1	193.4	207.3	227.4	255.1	289.9
62.5°	158.5	157.8	159.8	161.4	163.4	167.8	174.6	185.5	201.9	226.9	257.0
65°	136.3	135.4	136.6	138.5	140.3	142.7	147.7	157.4	170.4	188.4	211.3
67.5°	114.1	115.1	115.3	116.2	117.3	120.5	123.9	130.8	140.0	154.4	173.8
70°	100.8	101.1	102.0	102.0	102.7	105.6	108.4	112.4	121.4	134.7	150.5
72.5°	87.6	88.6	88.2	88.9	89.5	91.4	93.4	97.3	104.9	114.8	128.2
75°	68.2	68.9	68.9	69.1	69.8	70.5	72.2	75.0	80.5	87.8	97.0
77.5°	49.7	49.8	50.1	51.0	51.0	52.1	53.3	55.6	58.3	63.3	69.0
80°	38.3	38.8	38.6	39.1	39.1	40.0	40.5	43.3	44.5	47.8	52.3
82.5°	28.1	28.6	28.5	29.2	29.6	29.8	30.4	31.6	32.8	35.7	37.5
85°	14.2	14.7	14.2	14.7	15.4	15.6	16.3	16.6	17.5	18.2	19.9
87.5°	11.9	12.4	12.3	12.4	12.6	12.6	12.4	11.9	12.3	12.1	12.4
90°	38.9	38.3	37.8	37.2	36.6	35.4	33.7	32.0	30.3	28.5	26.2
92.5°	57.6	57.2	56.9	56.5	56.2	55.5	54.5	53.4	52.4	51.4	49.7
95°	102.5	102.5	102.5	102.5	102.5	102.0	101.2	100.3	99.4	98.6	96.5
97.5°	160.6	160.6	160.6	160.6	160.6	160.0	159.0	158.0	156.9	155.9	153.5
100°	201.0	201.0	201.0	201.0	201.0	200.7	200.2	199.6	199.0	198.4	195.8
102.5°	246.7	246.4	246.2	246.0	245.7	245.2	244.4	243.6	242.8	242.0	239.6
105°	316.4	315.6	314.7	313.8	313.0	312.1	311.3	310.4	309.5	308.7	307.5
107.5°	384.4	384.5	384.5	384.6	384.6	384.3	383.4	382.6	381.8	381.0	380.9
110°	433.2	432.3	431.4	430.6	429.7	429.6	430.1	430.7	431.3	431.9	432.2



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	482.8	482.6	482.4	482.3	482.2	482.4	482.5	482.6	482.7	483.2
115°	560.3	560.5	560.8	561.1	561.4	561.7	562.0	562.3	562.6	562.8	563.4
117.5°	633.9	634.5	635.1	635.6	636.2	637.0	638.0	639.0	639.9	640.9	641.3
120°	689.9	689.4	688.8	688.2	687.6	688.1	689.5	691.0	692.4	693.8	694.7
122.5°	736.6	737.7	738.7	739.7	740.8	741.8	742.8	743.7	744.7	745.7	746.1
125°	817.0	817.6	818.2	818.8	819.3	819.9	820.5	821.1	821.6	822.2	822.5
127.5°	891.5	891.9	892.4	892.9	893.3	893.8	894.4	895.0	895.6	896.1	896.6
130°	940.2	941.4	942.5	943.7	944.9	945.7	946.3	946.9	947.4	948.0	948.0
132.5°	992.1	992.6	993.0	993.5	994.0	994.5	995.1	995.6	996.2	996.8	997.0
135°	1063.4	1064.3	1065.2	1066.0	1066.9	1067.6	1068.2	1068.8	1069.4	1069.9	1069.9
137.5°	1138.4	1138.2	1138.1	1137.9	1137.7	1138.0	1138.8	1139.5	1140.2	1141.0	1140.5
140°	1184.1	1184.3	1184.6	1184.9	1185.2	1185.5	1185.8	1186.1	1186.4	1186.6	1186.6
142.5°	1229.7	1229.8	1229.8	1229.9	1229.9	1230.0	1230.1	1230.1	1230.2	1230.2	1230.5
145°	1291.7	1292.6	1293.4	1294.3	1295.2	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6
147.5°	1354.5	1354.8	1355.0	1355.3	1355.6	1355.9	1356.1	1356.3	1356.6	1356.8	1357.0
150°	1392.9	1393.1	1393.4	1393.7	1394.0	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1428.1	1428.9	1429.6	1430.4	1431.1	1431.2	1430.5	1429.8	1429.1	1428.4	1428.2
155°	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2	1477.4
157.5°	1521.0	1522.0	1522.9	1523.9	1524.9	1525.0	1524.1	1523.2	1522.4	1521.5	1521.6
160°	1545.9	1547.3	1548.8	1550.2	1551.6	1551.9	1551.1	1550.2	1549.3	1548.5	1548.8
162.5°	1571.8	1573.3	1574.7	1576.1	1577.6	1577.5	1576.0	1574.4	1572.9	1571.3	1571.6
165°	1605.5	1606.7	1607.8	1609.0	1610.2	1609.9	1608.1	1606.4	1604.7	1602.9	1603.5
167.5°	1629.7	1631.5	1633.2	1635.0	1636.8	1636.8	1635.1	1633.4	1631.7	1629.9	1629.9
170°	1643.2	1645.2	1647.2	1649.2	1651.2	1651.4	1649.6	1647.9	1646.2	1644.4	1644.2
172.5°	1654.6	1656.6	1658.6	1660.6	1662.6	1662.7	1660.7	1658.7	1656.8	1654.8	1654.8
175°	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5	1666.8
177.5°	1672.7	1674.6	1676.4	1678.3	1680.1	1680.2	1678.6	1677.0	1675.4	1673.8	1673.8
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	589.7	587.0	585.1	583.6	579.5	577.0	575.1	572.5	569.4	566.2	562.2
5°	623.1	615.1	609.2	600.2	591.7	584.6	577.2	570.6	562.6	553.8	547.4
7.5°	658.3	646.3	631.0	617.7	602.7	589.7	578.1	566.2	553.8	541.7	530.7
10°	680.7	665.3	648.2	628.1	609.2	592.4	576.8	561.6	546.9	532.3	519.7
12.5°	704.7	685.5	660.3	636.8	615.6	593.1	574.3	555.7	538.0	522.6	508.0
15°	737.0	709.3	680.2	648.7	620.8	594.5	568.7	545.3	525.4	505.0	490.8
17.5°	756.8	722.5	689.3	656.4	622.6	589.4	561.6	534.6	509.7	489.5	471.6
20°	769.9	735.8	694.4	661.5	621.3	587.2	555.0	524.9	498.9	477.4	458.9
22.5°	781.2	741.9	700.4	657.1	617.1	580.9	545.7	515.5	488.9	466.2	448.5
25°	787.4	742.2	697.2	654.1	608.7	565.9	533.9	498.4	470.0	446.1	427.2
27.5°	788.1	739.7	688.8	641.0	594.1	554.2	513.9	482.1	452.7	427.4	409.2
30°	786.0	735.6	680.9	629.1	582.0	538.7	503.6	469.1	439.0	413.9	395.0
32.5°	779.3	726.9	670.7	615.8	567.0	524.6	488.5	455.6	426.3	401.6	381.7
35°	760.2	708.3	648.5	591.4	541.5	498.7	466.0	432.6	403.3	379.9	360.7
37.5°	730.2	683.4	622.5	563.5	514.4	471.4	439.0	408.9	382.4	358.6	339.0
40°	704.1	662.9	601.8	544.3	491.3	450.4	420.1	392.4	366.1	343.6	324.9
42.5°	674.0	638.1	581.8	520.9	469.7	428.6	399.1	374.2	349.5	328.7	310.0
45°	620.3	596.6	543.6	487.3	434.0	395.2	367.1	345.3	324.5	304.1	288.5
47.5°	558.6	546.8	502.2	448.7	398.2	359.9	335.5	315.4	297.1	279.9	266.1
50°	517.1	511.4	472.9	421.3	373.0	337.0	312.4	295.1	279.5	264.4	251.3
52.5°	476.2	476.0	441.2	394.0	349.3	314.7	290.2	274.1	260.6	248.3	236.6
55°	413.7	420.3	393.1	351.0	311.0	279.7	257.7	243.3	233.8	223.7	214.9
57.5°	356.3	367.3	344.8	307.7	274.3	245.6	226.4	215.6	205.5	199.3	192.9
60°	318.8	329.2	311.7	280.5	249.0	224.4	206.1	196.4	187.7	183.4	178.9
62.5°	285.5	294.7	281.8	252.8	225.5	201.8	186.4	177.1	171.2	166.6	163.6
65°	237.9	245.7	234.5	213.5	190.0	171.1	158.6	151.2	145.6	143.7	140.3
67.5°	192.3	199.4	193.4	175.5	156.7	142.3	132.5	125.5	122.1	120.5	118.1
70°	165.2	172.3	165.9	150.3	135.8	123.8	114.5	110.5	107.0	106.3	103.0
72.5°	142.3	147.1	140.7	128.5	116.2	106.0	98.8	94.6	92.8	91.5	89.7
75°	106.7	111.0	106.7	97.3	88.5	81.4	75.3	73.6	71.5	70.8	69.6
77.5°	75.5	79.2	76.0	70.1	63.5	58.0	54.7	52.6	52.1	50.9	51.5
80°	57.7	60.1	57.0	53.0	47.8	44.0	41.7	40.5	39.1	38.6	39.5
82.5°	41.5	42.5	40.9	38.2	34.4	31.9	30.3	28.9	28.6	28.7	28.7
85°	21.5	21.3	21.1	18.7	17.5	15.9	14.9	14.7	14.4	14.9	15.4
87.5°	12.0	11.7	11.1	9.8	8.5	7.3	6.5	5.7	6.5	7.3	8.2
90°	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	48.1	46.5	44.9	42.3	38.6	35.0	31.4	27.8	31.4	35.0	38.6
95°	94.5	92.5	90.5	88.2	85.6	83.0	80.4	77.8	80.4	83.0	85.6
97.5°	151.2	148.8	146.4	144.2	142.1	140.1	138.0	135.9	138.0	140.1	142.1
100°	193.2	190.6	188.0	186.2	185.0	183.9	182.7	181.6	182.7	183.9	185.0
102.5°	237.3	234.9	232.5	231.1	230.7	230.2	229.8	229.3	229.8	230.2	230.7
105°	306.4	305.2	304.0	303.3	303.0	302.8	302.5	302.2	302.5	302.8	303.0
107.5°	380.7	380.5	380.3	380.1	379.7	379.4	379.0	378.7	379.0	379.4	379.7
110°	432.4	432.7	433.0	432.9	432.3	431.7	431.1	430.6	431.1	431.7	432.3



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	483.7	484.3	484.8	485.0	484.9	484.7	484.6	484.5	484.6	484.7	484.9
115°	564.0	564.6	565.2	565.4	565.4	565.4	565.4	565.4	565.4	565.4	565.4
117.5°	641.7	642.1	642.5	642.6	642.4	642.2	641.9	641.7	641.9	642.2	642.4
120°	695.6	696.4	697.3	697.1	696.0	694.8	693.7	692.5	693.7	694.8	696.0
122.5°	746.5	746.9	747.3	747.3	746.8	746.4	745.9	745.4	745.9	746.4	746.8
125°	822.8	823.1	823.4	823.5	823.5	823.5	823.5	823.5	823.5	823.5	823.5
127.5°	897.1	897.5	898.0	897.8	896.9	896.1	895.2	894.3	895.2	896.1	896.9
130°	948.0	948.0	948.0	947.6	946.7	945.9	945.0	944.1	945.0	945.9	946.7
132.5°	997.2	997.5	997.7	997.5	996.9	996.2	995.6	995.0	995.6	996.2	996.9
135°	1069.9	1069.9	1069.9	1069.1	1067.3	1065.6	1063.9	1062.1	1063.9	1065.6	1067.3
137.5°	1140.1	1139.6	1139.2	1138.5	1137.7	1136.9	1136.1	1135.3	1136.1	1136.9	1137.7
140°	1186.6	1186.6	1186.6	1186.4	1185.8	1185.2	1184.6	1184.1	1184.6	1185.2	1185.8
142.5°	1230.7	1230.9	1231.1	1231.0	1230.4	1229.8	1229.2	1228.7	1229.2	1229.8	1230.4
145°	1296.3	1296.0	1295.7	1295.0	1293.9	1292.7	1291.6	1290.4	1291.6	1292.7	1293.9
147.5°	1357.3	1357.5	1357.7	1357.1	1355.8	1354.4	1353.0	1351.6	1353.0	1354.4	1355.8
150°	1394.1	1394.1	1394.1	1393.6	1392.4	1391.3	1390.1	1389.0	1390.1	1391.3	1392.4
152.5°	1427.9	1427.7	1427.5	1427.0	1426.3	1425.6	1424.9	1424.2	1424.9	1425.6	1426.3
155°	1477.7	1478.0	1478.3	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4	1478.4
157.5°	1521.6	1521.7	1521.7	1522.0	1522.5	1523.1	1523.6	1524.1	1523.6	1523.1	1522.5
160°	1549.1	1549.3	1549.6	1549.9	1550.2	1550.5	1550.8	1551.1	1550.8	1550.5	1550.2
162.5°	1571.9	1572.2	1572.5	1573.0	1573.7	1574.5	1575.2	1576.0	1575.2	1574.5	1573.7
165°	1604.1	1604.7	1605.3	1606.0	1606.8	1607.7	1608.6	1609.4	1608.6	1607.7	1606.8
167.5°	1629.8	1629.8	1629.7	1630.3	1631.5	1632.7	1633.9	1635.1	1633.9	1632.7	1631.5
170°	1643.9	1643.6	1643.3	1643.9	1645.3	1646.8	1648.2	1649.6	1648.2	1646.8	1645.3
172.5°	1654.7	1654.7	1654.6	1655.2	1656.4	1657.6	1658.8	1660.0	1658.8	1657.6	1656.4
175°	1667.1	1667.4	1667.6	1668.5	1670.0	1671.4	1672.8	1674.3	1672.8	1671.4	1670.0
177.5°	1673.8	1673.8	1673.8	1674.3	1675.5	1676.6	1677.8	1678.9	1677.8	1676.6	1675.5
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	560.3	558.6	556.2	552.8	549.9	546.9	546.1	545.0	547.3	545.4	544.8
5°	542.0	537.0	530.6	523.3	519.0	512.9	511.7	509.3	506.9	506.7	504.3
7.5°	522.5	515.2	506.8	499.4	492.5	485.7	481.3	480.4	476.9	474.8	472.5
10°	510.0	501.0	491.3	484.2	476.2	469.1	464.1	461.3	458.9	456.3	453.9
12.5°	495.3	485.7	477.7	470.0	460.5	455.1	446.9	442.0	441.5	441.5	435.4
15°	478.1	468.6	456.3	445.4	440.2	429.8	425.3	419.6	416.1	412.5	409.7
17.5°	458.4	446.6	437.0	424.5	414.6	406.3	400.4	397.0	391.6	386.6	383.0
20°	446.1	433.6	423.4	410.1	399.3	389.1	384.1	379.4	375.4	371.1	367.1
22.5°	433.6	420.5	408.1	395.2	385.1	374.3	369.5	363.1	359.3	356.9	352.9
25°	413.9	399.7	385.5	373.2	362.8	353.3	347.0	342.0	337.7	335.8	333.2
27.5°	392.5	378.4	364.7	350.7	338.9	332.0	326.9	323.2	320.7	318.2	317.0
30°	378.9	364.2	349.6	336.5	325.7	318.8	314.1	311.5	309.6	308.4	307.2
32.5°	365.1	350.6	335.2	323.3	313.5	307.4	303.8	301.2	300.3	299.9	299.4
35°	342.9	328.3	314.1	303.4	294.2	291.8	288.7	287.3	286.8	288.5	289.2
37.5°	321.5	307.9	294.8	284.5	278.4	275.0	273.9	274.0	275.7	277.1	278.8
40°	307.7	294.4	282.1	273.1	267.4	265.3	264.8	266.0	267.9	269.6	271.5
42.5°	294.2	281.2	270.0	261.6	257.6	255.6	255.9	257.1	259.8	261.8	264.6
45°	273.4	262.5	251.6	244.7	241.4	241.9	241.9	244.0	246.6	249.7	252.8
47.5°	253.7	242.7	233.8	228.0	226.3	225.9	227.2	230.0	233.7	237.5	241.8
50°	240.5	230.0	222.2	217.0	215.1	215.8	217.7	220.3	224.8	229.6	234.1
52.5°	227.0	217.5	210.3	205.5	204.1	205.4	207.3	211.4	215.4	220.5	225.9
55°	206.1	198.1	192.4	188.9	188.4	189.1	191.2	195.7	201.4	207.8	213.0
57.5°	185.4	178.6	173.4	171.0	171.2	171.9	175.4	180.7	186.8	193.6	200.3
60°	171.3	165.2	160.9	159.0	159.3	160.7	165.0	169.9	177.5	184.1	191.2
62.5°	158.1	152.7	148.6	146.9	146.6	149.7	153.8	158.9	166.5	173.9	181.6
65°	136.8	132.5	129.2	128.3	129.0	131.4	136.6	143.4	149.8	157.6	165.7
67.5°	116.0	112.5	110.2	110.6	111.5	115.0	119.3	125.2	132.5	140.6	148.5
70°	102.7	99.4	97.5	97.7	99.2	103.4	107.2	113.1	120.9	129.2	135.8
72.5°	89.1	86.9	85.2	86.2	87.6	90.5	95.3	101.2	108.1	115.8	122.8
75°	68.4	68.4	67.5	68.2	70.3	73.1	76.7	82.8	89.7	95.9	101.5
77.5°	50.7	50.2	50.8	51.7	52.9	56.3	60.4	64.8	69.9	76.1	80.8
80°	38.8	39.1	40.2	41.7	42.1	44.7	49.0	53.0	57.0	62.2	66.7
82.5°	29.2	29.4	30.0	31.8	32.3	35.1	37.8	41.8	45.5	49.0	52.7
85°	15.9	15.9	17.0	17.8	18.9	20.8	22.5	24.9	28.2	30.5	34.1
87.5°	9.4	9.9	11.1	12.0	13.0	14.4	15.1	17.6	18.7	20.0	21.9
90°	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0	33.7	35.4	36.6
92.5°	42.3	44.9	46.5	48.1	49.7	51.4	52.4	53.4	54.5	55.5	56.2
95°	88.2	90.5	92.5	94.5	96.5	98.6	99.4	100.3	101.2	102.0	102.5
97.5°	144.2	146.4	148.8	151.2	153.5	155.9	156.9	158.0	159.0	160.0	160.6
100°	186.2	188.0	190.6	193.2	195.8	198.4	199.0	199.6	200.2	200.7	201.0
102.5°	231.1	232.5	234.9	237.3	239.6	242.0	242.8	243.6	244.4	245.2	245.7
105°	303.3	304.0	305.2	306.4	307.5	308.7	309.5	310.4	311.3	312.1	313.0
107.5°	380.1	380.3	380.5	380.7	380.9	381.0	381.8	382.6	383.4	384.3	384.6
110°	432.9	433.0	432.7	432.4	432.2	431.9	431.3	430.7	430.1	429.6	429.7



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	485.0	484.8	484.3	483.7	483.2	482.7	482.6	482.5	482.4	482.2	482.3
115°	565.4	565.2	564.6	564.0	563.4	562.8	562.6	562.3	562.0	561.7	561.4
117.5°	642.6	642.5	642.1	641.7	641.3	640.9	639.9	639.0	638.0	637.0	636.2
120°	697.1	697.3	696.4	695.6	694.7	693.8	692.4	691.0	689.5	688.1	687.6
122.5°	747.3	747.3	746.9	746.5	746.1	745.7	744.7	743.7	742.8	741.8	740.8
125°	823.5	823.4	823.1	822.8	822.5	822.2	821.6	821.1	820.5	819.9	819.3
127.5°	897.8	898.0	897.5	897.1	896.6	896.1	895.6	895.0	894.4	893.8	893.3
130°	947.6	948.0	948.0	948.0	948.0	948.0	947.4	946.9	946.3	945.7	944.9
132.5°	997.5	997.7	997.5	997.2	997.0	996.8	996.2	995.6	995.1	994.5	994.0
135°	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4	1068.8	1068.2	1067.6	1066.9
137.5°	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2	1139.5	1138.8	1138.0	1137.7
140°	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1186.1	1185.8	1185.5	1185.2
142.5°	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2	1230.1	1230.1	1230.0	1229.9
145°	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6	1296.3	1296.0	1295.7	1295.2
147.5°	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6	1356.3	1356.1	1355.9	1355.6
150°	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.0
152.5°	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1	1429.8	1430.5	1431.2	1431.1
155°	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8
157.5°	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4	1523.2	1524.1	1525.0	1524.9
160°	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3	1550.2	1551.1	1551.9	1551.6
162.5°	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9	1574.4	1576.0	1577.5	1577.6
165°	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7	1606.4	1608.1	1609.9	1610.2
167.5°	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7	1633.4	1635.1	1636.8	1636.8
170°	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2	1647.9	1649.6	1651.4	1651.2
172.5°	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8	1658.7	1660.7	1662.7	1662.6
175°	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6
177.5°	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4	1677.0	1678.6	1680.2	1680.1
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	544.4	544.1	542.7	542.5	542.7	544.1	544.4	544.8	545.4	547.3	545.0
5°	502.9	501.7	501.0	503.6	501.0	501.7	502.9	504.3	506.7	506.9	509.3
7.5°	471.6	470.7	468.6	467.9	468.6	470.7	471.6	472.5	474.8	476.9	480.4
10°	451.6	450.6	448.7	448.2	448.7	450.6	451.6	453.9	456.3	458.9	461.3
12.5°	432.2	430.4	430.0	430.5	430.0	430.4	432.2	435.4	441.5	441.5	442.0
15°	406.6	405.6	403.0	403.8	403.0	405.6	406.6	409.7	412.5	416.1	419.6
17.5°	381.3	380.2	377.0	379.8	377.0	380.2	381.3	383.0	386.6	391.6	397.0
20°	365.4	363.5	361.9	361.6	361.9	363.5	365.4	367.1	371.1	375.4	379.4
22.5°	350.3	348.6	348.4	346.9	348.4	348.6	350.3	352.9	356.9	359.3	363.1
25°	331.3	329.7	329.2	328.0	329.2	329.7	331.3	333.2	335.8	337.7	342.0
27.5°	316.8	316.0	315.1	315.5	315.1	316.0	316.8	317.0	318.2	320.7	323.2
30°	307.9	307.7	307.2	307.2	307.2	307.7	307.9	307.2	308.4	309.6	311.5
32.5°	300.5	300.5	300.8	300.8	300.8	300.5	300.5	299.4	299.9	300.3	301.2
35°	290.2	290.9	291.3	290.6	291.3	290.9	290.2	289.2	288.5	286.8	287.3
37.5°	280.8	281.5	282.2	283.0	282.2	281.5	280.8	278.8	277.1	275.7	274.0
40°	273.6	275.2	275.7	276.9	275.7	275.2	273.6	271.5	269.6	267.9	266.0
42.5°	266.8	268.6	269.8	270.1	269.8	268.6	266.8	264.6	261.8	259.8	257.1
45°	256.3	258.2	259.9	259.9	259.9	258.2	256.3	252.8	249.7	246.6	244.0
47.5°	245.5	248.2	249.9	250.3	249.9	248.2	245.5	241.8	237.5	233.7	230.0
50°	238.1	241.4	243.1	244.2	243.1	241.4	238.1	234.1	229.6	224.8	220.3
52.5°	230.9	234.2	236.4	237.0	236.4	234.2	230.9	225.9	220.5	215.4	211.4
55°	218.4	223.2	225.8	226.7	225.8	223.2	218.4	213.0	207.8	201.4	195.7
57.5°	206.7	211.1	214.1	214.8	214.1	211.1	206.7	200.3	193.6	186.8	180.7
60°	197.6	202.4	206.1	206.8	206.1	202.4	197.6	191.2	184.1	177.5	169.9
62.5°	188.3	193.3	196.7	198.5	196.7	193.3	188.3	181.6	173.9	166.5	158.9
65°	172.3	177.3	180.6	181.3	180.6	177.3	172.3	165.7	157.6	149.8	143.4
67.5°	154.8	159.8	161.9	163.3	161.9	159.8	154.8	148.5	140.6	132.5	125.2
70°	142.5	146.5	148.9	150.0	148.9	146.5	142.5	135.8	129.2	120.9	113.1
72.5°	128.5	132.7	135.4	135.7	135.4	132.7	128.5	122.8	115.8	108.1	101.2
75°	107.0	110.8	112.2	112.2	112.2	110.8	107.0	101.5	95.9	89.7	82.8
77.5°	84.7	86.6	88.4	88.8	88.4	86.6	84.7	80.8	76.1	69.9	64.8
80°	70.3	71.5	72.9	72.9	72.9	71.5	70.3	66.7	62.2	57.0	53.0
82.5°	55.5	56.5	57.9	57.7	57.9	56.5	55.5	52.7	49.0	45.5	41.8
85°	33.6	35.7	35.5	35.0	35.5	35.7	33.6	34.1	30.5	28.2	24.9
87.5°	22.6	22.9	23.6	24.1	23.6	22.9	22.6	21.9	20.0	18.7	17.6
90°	37.2	37.8	38.3	38.9	38.3	37.8	37.2	36.6	35.4	33.7	32.0
92.5°	56.5	56.9	57.2	57.6	57.2	56.9	56.5	56.2	55.5	54.5	53.4
95°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.0	101.2	100.3
97.5°	160.6	160.6	160.6	160.6	160.6	160.6	160.6	160.6	160.0	159.0	158.0
100°	201.0	201.0	201.0	201.0	201.0	201.0	201.0	201.0	200.7	200.2	199.6
102.5°	246.0	246.2	246.4	246.7	246.4	246.2	246.0	245.7	245.2	244.4	243.6
105°	313.8	314.7	315.6	316.4	315.6	314.7	313.8	313.0	312.1	311.3	310.4
107.5°	384.6	384.5	384.5	384.4	384.5	384.5	384.6	384.6	384.3	383.4	382.6
110°	430.6	431.4	432.3	433.2	432.3	431.4	430.6	429.7	429.6	430.1	430.7



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.4	482.6	482.8	483.0	482.8	482.6	482.4	482.3	482.2	482.4	482.5
115°	561.1	560.8	560.5	560.3	560.5	560.8	561.1	561.4	561.7	562.0	562.3
117.5°	635.6	635.1	634.5	633.9	634.5	635.1	635.6	636.2	637.0	638.0	639.0
120°	688.2	688.8	689.4	689.9	689.4	688.8	688.2	687.6	688.1	689.5	691.0
122.5°	739.7	738.7	737.7	736.6	737.7	738.7	739.7	740.8	741.8	742.8	743.7
125°	818.8	818.2	817.6	817.0	817.6	818.2	818.8	819.3	819.9	820.5	821.1
127.5°	892.9	892.4	891.9	891.5	891.9	892.4	892.9	893.3	893.8	894.4	895.0
130°	943.7	942.5	941.4	940.2	941.4	942.5	943.7	944.9	945.7	946.3	946.9
132.5°	993.5	993.0	992.6	992.1	992.6	993.0	993.5	994.0	994.5	995.1	995.6
135°	1066.0	1065.2	1064.3	1063.4	1064.3	1065.2	1066.0	1066.9	1067.6	1068.2	1068.8
137.5°	1137.9	1138.1	1138.2	1138.4	1138.2	1138.1	1137.9	1137.7	1138.0	1138.8	1139.5
140°	1184.9	1184.6	1184.3	1184.1	1184.3	1184.6	1184.9	1185.2	1185.5	1185.8	1186.1
142.5°	1229.9	1229.8	1229.8	1229.7	1229.8	1229.8	1229.9	1229.9	1230.0	1230.1	1230.1
145°	1294.3	1293.4	1292.6	1291.7	1292.6	1293.4	1294.3	1295.2	1295.7	1296.0	1296.3
147.5°	1355.3	1355.0	1354.8	1354.5	1354.8	1355.0	1355.3	1355.6	1355.9	1356.1	1356.3
150°	1393.7	1393.4	1393.1	1392.9	1393.1	1393.4	1393.7	1394.0	1394.1	1394.1	1394.1
152.5°	1430.4	1429.6	1428.9	1428.1	1428.9	1429.6	1430.4	1431.1	1431.2	1430.5	1429.8
155°	1480.6	1479.5	1478.3	1477.2	1478.3	1479.5	1480.6	1481.8	1481.8	1480.6	1479.5
157.5°	1523.9	1522.9	1522.0	1521.0	1522.0	1522.9	1523.9	1524.9	1525.0	1524.1	1523.2
160°	1550.2	1548.8	1547.3	1545.9	1547.3	1548.8	1550.2	1551.6	1551.9	1551.1	1550.2
162.5°	1576.1	1574.7	1573.3	1571.8	1573.3	1574.7	1576.1	1577.6	1577.5	1576.0	1574.4
165°	1609.0	1607.8	1606.7	1605.5	1606.7	1607.8	1609.0	1610.2	1609.9	1608.1	1606.4
167.5°	1635.0	1633.2	1631.5	1629.7	1631.5	1633.2	1635.0	1636.8	1636.8	1635.1	1633.4
170°	1649.2	1647.2	1645.2	1643.2	1645.2	1647.2	1649.2	1651.2	1651.4	1649.6	1647.9
172.5°	1660.6	1658.6	1656.6	1654.6	1656.6	1658.6	1660.6	1662.6	1662.7	1660.7	1658.7
175°	1672.5	1670.5	1668.5	1666.5	1668.5	1670.5	1672.5	1674.6	1674.6	1672.5	1670.5
177.5°	1678.3	1676.4	1674.6	1672.7	1674.6	1676.4	1678.3	1680.1	1680.2	1678.6	1677.0
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	546.1	546.9	549.9	552.8	556.2	558.6	560.3	562.2	566.2	569.4	572.5
5°	511.7	512.9	519.0	523.3	530.6	537.0	542.0	547.4	553.8	562.6	570.6
7.5°	481.3	485.7	492.5	499.4	506.8	515.2	522.5	530.7	541.7	553.8	566.2
10°	464.1	469.1	476.2	484.2	491.3	501.0	510.0	519.7	532.3	546.9	561.6
12.5°	446.9	455.1	460.5	470.0	477.7	485.7	495.3	508.0	522.6	538.0	555.7
15°	425.3	429.8	440.2	445.4	456.3	468.6	478.1	490.8	505.0	525.4	545.3
17.5°	400.4	406.3	414.6	424.5	437.0	446.6	458.4	471.6	489.5	509.7	534.6
20°	384.1	389.1	399.3	410.1	423.4	433.6	446.1	458.9	477.4	498.9	524.9
22.5°	369.5	374.3	385.1	395.2	408.1	420.5	433.6	448.5	466.2	488.9	515.5
25°	347.0	353.3	362.8	373.2	385.5	399.7	413.9	427.2	446.1	470.0	498.4
27.5°	326.9	332.0	338.9	350.7	364.7	378.4	392.5	409.2	427.4	452.7	482.1
30°	314.1	318.8	325.7	336.5	349.6	364.2	378.9	395.0	413.9	439.0	469.1
32.5°	303.8	307.4	313.5	323.3	335.2	350.6	365.1	381.7	401.6	426.3	455.6
35°	288.7	291.8	294.2	303.4	314.1	328.3	342.9	360.7	379.9	403.3	432.6
37.5°	273.9	275.0	278.4	284.5	294.8	307.9	321.5	339.0	358.6	382.4	408.9
40°	264.8	265.3	267.4	273.1	282.1	294.4	307.7	324.9	343.6	366.1	392.4
42.5°	255.9	255.6	257.6	261.6	270.0	281.2	294.2	310.0	328.7	349.5	374.2
45°	241.9	241.9	241.4	244.7	251.6	262.5	273.4	288.5	304.1	324.5	345.3
47.5°	227.2	225.9	226.3	228.0	233.8	242.7	253.7	266.1	279.9	297.1	315.4
50°	217.7	215.8	215.1	217.0	222.2	230.0	240.5	251.3	264.4	279.5	295.1
52.5°	207.3	205.4	204.1	205.5	210.3	217.5	227.0	236.6	248.3	260.6	274.1
55°	191.2	189.1	188.4	188.9	192.4	198.1	206.1	214.9	223.7	233.8	243.3
57.5°	175.4	171.9	171.2	171.0	173.4	178.6	185.4	192.9	199.3	205.5	215.6
60°	165.0	160.7	159.3	159.0	160.9	165.2	171.3	178.9	183.4	187.7	196.4
62.5°	153.8	149.7	146.6	146.9	148.6	152.7	158.1	163.6	166.6	171.2	177.1
65°	136.6	131.4	129.0	128.3	129.2	132.5	136.8	140.3	143.7	145.6	151.2
67.5°	119.3	115.0	111.5	110.6	110.2	112.5	116.0	118.1	120.5	122.1	125.5
70°	107.2	103.4	99.2	97.7	97.5	99.4	102.7	103.0	106.3	107.0	110.5
72.5°	95.3	90.5	87.6	86.2	85.2	86.9	89.1	89.7	91.5	92.8	94.6
75°	76.7	73.1	70.3	68.2	67.5	68.4	68.4	69.6	70.8	71.5	73.6
77.5°	60.4	56.3	52.9	51.7	50.8	50.2	50.7	51.5	50.9	52.1	52.6
80°	49.0	44.7	42.1	41.7	40.2	39.1	38.8	39.5	38.6	39.1	40.5
82.5°	37.8	35.1	32.3	31.8	30.0	29.4	29.2	28.7	28.7	28.6	28.9
85°	22.5	20.8	18.9	17.8	17.0	15.9	15.9	15.4	14.9	14.4	14.7
87.5°	15.1	14.4	13.0	12.0	11.1	9.9	9.4	8.2	7.3	6.5	5.7
90°	30.3	28.5	26.2	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9
92.5°	52.4	51.4	49.7	48.1	46.5	44.9	42.3	38.6	35.0	31.4	27.8
95°	99.4	98.6	96.5	94.5	92.5	90.5	88.2	85.6	83.0	80.4	77.8
97.5°	156.9	155.9	153.5	151.2	148.8	146.4	144.2	142.1	140.1	138.0	135.9
100°	199.0	198.4	195.8	193.2	190.6	188.0	186.2	185.0	183.9	182.7	181.6
102.5°	242.8	242.0	239.6	237.3	234.9	232.5	231.1	230.7	230.2	229.8	229.3
105°	309.5	308.7	307.5	306.4	305.2	304.0	303.3	303.0	302.8	302.5	302.2
107.5°	381.8	381.0	380.9	380.7	380.5	380.3	380.1	379.7	379.4	379.0	378.7
110°	431.3	431.9	432.2	432.4	432.7	433.0	432.9	432.3	431.7	431.1	430.6



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	482.6	482.7	483.2	483.7	484.3	484.8	485.0	484.9	484.7	484.6	484.5
115°	562.6	562.8	563.4	564.0	564.6	565.2	565.4	565.4	565.4	565.4	565.4
117.5°	639.9	640.9	641.3	641.7	642.1	642.5	642.6	642.4	642.2	641.9	641.7
120°	692.4	693.8	694.7	695.6	696.4	697.3	697.1	696.0	694.8	693.7	692.5
122.5°	744.7	745.7	746.1	746.5	746.9	747.3	747.3	746.8	746.4	745.9	745.4
125°	821.6	822.2	822.5	822.8	823.1	823.4	823.5	823.5	823.5	823.5	823.5
127.5°	895.6	896.1	896.6	897.1	897.5	898.0	897.8	896.9	896.1	895.2	894.3
130°	947.4	948.0	948.0	948.0	948.0	948.0	947.6	946.7	945.9	945.0	944.1
132.5°	996.2	996.8	997.0	997.2	997.5	997.7	997.5	996.9	996.2	995.6	995.0
135°	1069.4	1069.9	1069.9	1069.9	1069.9	1069.9	1069.1	1067.3	1065.6	1063.9	1062.1
137.5°	1140.2	1141.0	1140.5	1140.1	1139.6	1139.2	1138.5	1137.7	1136.9	1136.1	1135.3
140°	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1185.8	1185.2	1184.6	1184.1
142.5°	1230.2	1230.2	1230.5	1230.7	1230.9	1231.1	1231.0	1230.4	1229.8	1229.2	1228.7
145°	1296.6	1296.9	1296.6	1296.3	1296.0	1295.7	1295.0	1293.9	1292.7	1291.6	1290.4
147.5°	1356.6	1356.8	1357.0	1357.3	1357.5	1357.7	1357.1	1355.8	1354.4	1353.0	1351.6
150°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1393.6	1392.4	1391.3	1390.1	1389.0
152.5°	1429.1	1428.4	1428.2	1427.9	1427.7	1427.5	1427.0	1426.3	1425.6	1424.9	1424.2
155°	1478.3	1477.2	1477.4	1477.7	1478.0	1478.3	1478.4	1478.4	1478.4	1478.4	1478.4
157.5°	1522.4	1521.5	1521.6	1521.6	1521.7	1521.7	1522.0	1522.5	1523.1	1523.6	1524.1
160°	1549.3	1548.5	1548.8	1549.1	1549.3	1549.6	1549.9	1550.2	1550.5	1550.8	1551.1
162.5°	1572.9	1571.3	1571.6	1571.9	1572.2	1572.5	1573.0	1573.7	1574.5	1575.2	1576.0
165°	1604.7	1602.9	1603.5	1604.1	1604.7	1605.3	1606.0	1606.8	1607.7	1608.6	1609.4
167.5°	1631.7	1629.9	1629.9	1629.8	1629.8	1629.7	1630.3	1631.5	1632.7	1633.9	1635.1
170°	1646.2	1644.4	1644.2	1643.9	1643.6	1643.3	1643.9	1645.3	1646.8	1648.2	1649.6
172.5°	1656.8	1654.8	1654.8	1654.7	1654.7	1654.6	1655.2	1656.4	1657.6	1658.8	1660.0
175°	1668.5	1666.5	1666.8	1667.1	1667.4	1667.6	1668.5	1670.0	1671.4	1672.8	1674.3
177.5°	1675.4	1673.8	1673.8	1673.8	1673.8	1673.8	1674.3	1675.5	1676.6	1677.8	1678.9
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	575.1	577.0	579.5	583.6	585.1	587.0	589.7	589.5	590.2	593.1	599.1
5°	577.2	584.6	591.7	600.2	609.2	615.1	623.1	628.1	633.1	639.5	650.4
7.5°	578.1	589.7	602.7	617.7	631.0	646.3	658.3	669.6	679.8	693.2	706.2
10°	576.8	592.4	609.2	628.1	648.2	665.3	680.7	698.2	713.1	729.4	744.1
12.5°	574.3	593.1	615.6	636.8	660.3	685.5	704.7	722.4	742.2	761.0	783.7
15°	568.7	594.5	620.8	648.7	680.2	709.3	737.0	759.9	781.2	809.4	839.0
17.5°	561.6	589.4	622.6	656.4	689.3	722.5	756.8	791.3	818.2	853.2	876.3
20°	555.0	587.2	621.3	661.5	694.4	735.8	769.9	803.2	840.2	875.0	902.7
22.5°	545.7	580.9	617.1	657.1	700.4	741.9	781.2	817.4	854.4	892.2	925.7
25°	533.9	565.9	608.7	654.1	697.2	742.2	787.4	832.8	872.6	912.6	943.8
27.5°	513.9	554.2	594.1	641.0	688.8	739.7	788.1	835.6	877.3	910.2	929.5
30°	503.6	538.7	582.0	629.1	680.9	735.6	786.0	832.6	871.4	897.7	905.5
32.5°	488.5	524.6	567.0	615.8	670.7	726.9	779.3	823.3	855.7	869.5	860.1
35°	466.0	498.7	541.5	591.4	648.5	708.3	760.2	797.3	813.9	800.9	768.5
37.5°	439.0	471.4	514.4	563.5	622.5	683.4	730.2	757.0	751.5	719.1	670.8
40°	420.1	450.4	491.3	544.3	601.8	662.9	704.1	718.5	703.4	657.0	605.6
42.5°	399.1	428.6	469.7	520.9	581.8	638.1	674.0	675.2	649.8	594.3	542.8
45°	367.1	395.2	434.0	487.3	543.6	596.6	620.3	608.7	561.8	508.4	456.5
47.5°	335.5	359.9	398.2	448.7	502.2	546.8	558.6	537.7	487.8	435.8	387.8
50°	312.4	337.0	373.0	421.3	472.9	511.4	517.1	489.4	440.4	388.1	350.5
52.5°	290.2	314.7	349.3	394.0	441.2	476.0	476.2	444.2	395.4	348.8	313.8
55°	257.7	279.7	311.0	351.0	393.1	420.3	413.7	380.6	338.2	297.7	267.2
57.5°	226.4	245.6	274.3	307.7	344.8	367.3	356.3	324.4	286.6	252.2	229.1
60°	206.1	224.4	249.0	280.5	311.7	329.2	318.8	289.9	255.1	227.4	207.3
62.5°	186.4	201.8	225.5	252.8	281.8	294.7	285.5	257.0	226.9	201.9	185.5
65°	158.6	171.1	190.0	213.5	234.5	245.7	237.9	211.3	188.4	170.4	157.4
67.5°	132.5	142.3	156.7	175.5	193.4	199.4	192.3	173.8	154.4	140.0	130.8
70°	114.5	123.8	135.8	150.3	165.9	172.3	165.2	150.5	134.7	121.4	112.4
72.5°	98.8	106.0	116.2	128.5	140.7	147.1	142.3	128.2	114.8	104.9	97.3
75°	75.3	81.4	88.5	97.3	106.7	111.0	106.7	97.0	87.8	80.5	75.0
77.5°	54.7	58.0	63.5	70.1	76.0	79.2	75.5	69.0	63.3	58.3	55.6
80°	41.7	44.0	47.8	53.0	57.0	60.1	57.7	52.3	47.8	44.5	43.3
82.5°	30.3	31.9	34.4	38.2	40.9	42.5	41.5	37.5	35.7	32.8	31.6
85°	14.9	15.9	17.5	18.7	21.1	21.3	21.5	19.9	18.2	17.5	16.6
87.5°	6.5	7.3	8.5	9.8	11.1	11.7	12.0	12.4	12.1	12.3	11.9
90°	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0
92.5°	31.4	35.0	38.6	42.3	44.9	46.5	48.1	49.7	51.4	52.4	53.4
95°	80.4	83.0	85.6	88.2	90.5	92.5	94.5	96.5	98.6	99.4	100.3
97.5°	138.0	140.1	142.1	144.2	146.4	148.8	151.2	153.5	155.9	156.9	158.0
100°	182.7	183.9	185.0	186.2	188.0	190.6	193.2	195.8	198.4	199.0	199.6
102.5°	229.8	230.2	230.7	231.1	232.5	234.9	237.3	239.6	242.0	242.8	243.6
105°	302.5	302.8	303.0	303.3	304.0	305.2	306.4	307.5	308.7	309.5	310.4
107.5°	379.0	379.4	379.7	380.1	380.3	380.5	380.7	380.9	381.0	381.8	382.6
110°	431.1	431.7	432.3	432.9	433.0	432.7	432.4	432.2	431.9	431.3	430.7



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.6	484.7	484.9	485.0	484.8	484.3	483.7	483.2	482.7	482.6	482.5
115°	565.4	565.4	565.4	565.4	565.2	564.6	564.0	563.4	562.8	562.6	562.3
117.5°	641.9	642.2	642.4	642.6	642.5	642.1	641.7	641.3	640.9	639.9	639.0
120°	693.7	694.8	696.0	697.1	697.3	696.4	695.6	694.7	693.8	692.4	691.0
122.5°	745.9	746.4	746.8	747.3	747.3	746.9	746.5	746.1	745.7	744.7	743.7
125°	823.5	823.5	823.5	823.5	823.4	823.1	822.8	822.5	822.2	821.6	821.1
127.5°	895.2	896.1	896.9	897.8	898.0	897.5	897.1	896.6	896.1	895.6	895.0
130°	945.0	945.9	946.7	947.6	948.0	948.0	948.0	948.0	948.0	947.4	946.9
132.5°	995.6	996.2	996.9	997.5	997.7	997.5	997.2	997.0	996.8	996.2	995.6
135°	1063.9	1065.6	1067.3	1069.1	1069.9	1069.9	1069.9	1069.9	1069.9	1069.4	1068.8
137.5°	1136.1	1136.9	1137.7	1138.5	1139.2	1139.6	1140.1	1140.5	1141.0	1140.2	1139.5
140°	1184.6	1185.2	1185.8	1186.4	1186.6	1186.6	1186.6	1186.6	1186.6	1186.4	1186.1
142.5°	1229.2	1229.8	1230.4	1231.0	1231.1	1230.9	1230.7	1230.5	1230.2	1230.2	1230.1
145°	1291.6	1292.7	1293.9	1295.0	1295.7	1296.0	1296.3	1296.6	1296.9	1296.6	1296.3
147.5°	1353.0	1354.4	1355.8	1357.1	1357.7	1357.5	1357.3	1357.0	1356.8	1356.6	1356.3
150°	1390.1	1391.3	1392.4	1393.6	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1
152.5°	1424.9	1425.6	1426.3	1427.0	1427.5	1427.7	1427.9	1428.2	1428.4	1429.1	1429.8
155°	1478.4	1478.4	1478.4	1478.4	1478.3	1478.0	1477.7	1477.4	1477.2	1478.3	1479.5
157.5°	1523.6	1523.1	1522.5	1522.0	1521.7	1521.7	1521.6	1521.6	1521.5	1522.4	1523.2
160°	1550.8	1550.5	1550.2	1549.9	1549.6	1549.3	1549.1	1548.8	1548.5	1549.3	1550.2
162.5°	1575.2	1574.5	1573.7	1573.0	1572.5	1572.2	1571.9	1571.6	1571.3	1572.9	1574.4
165°	1608.6	1607.7	1606.8	1606.0	1605.3	1604.7	1604.1	1603.5	1602.9	1604.7	1606.4
167.5°	1633.9	1632.7	1631.5	1630.3	1629.7	1629.8	1629.8	1629.9	1629.9	1631.7	1633.4
170°	1648.2	1646.8	1645.3	1643.9	1643.3	1643.6	1643.9	1644.2	1644.4	1646.2	1647.9
172.5°	1658.8	1657.6	1656.4	1655.2	1654.6	1654.7	1654.7	1654.8	1654.8	1656.8	1658.7
175°	1672.8	1671.4	1670.0	1668.5	1667.6	1667.4	1667.1	1666.8	1666.5	1668.5	1670.5
177.5°	1677.8	1676.6	1675.5	1674.3	1673.8	1673.8	1673.8	1673.8	1673.8	1675.4	1677.0
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	602.2	602.6	604.3	605.6	606.0	607.9	608.0
5°	655.1	659.1	666.9	667.6	668.8	675.0	670.2
7.5°	717.1	727.3	734.1	740.2	742.3	745.0	744.5
10°	756.9	772.0	779.6	791.7	792.1	795.2	793.3
12.5°	796.8	814.4	828.2	830.5	840.6	842.2	844.8
15°	853.4	872.1	891.3	898.2	912.1	915.4	920.6
17.5°	906.6	925.7	939.2	956.9	962.7	970.3	965.1
20°	935.8	956.6	973.7	987.6	993.5	997.8	997.3
22.5°	953.4	974.4	988.2	998.8	1004.3	1006.1	1006.0
25°	964.4	976.5	980.8	984.8	978.6	976.5	977.4
27.5°	933.7	930.6	919.5	904.9	889.8	877.8	871.2
30°	891.5	873.1	856.3	826.9	811.8	802.8	794.7
32.5°	831.7	802.4	770.1	743.2	726.0	712.7	710.7
35°	729.2	685.2	645.6	612.7	595.7	581.3	577.9
37.5°	619.9	574.2	538.6	509.6	491.3	481.1	471.6
40°	547.4	508.1	473.1	448.5	434.5	427.2	421.3
42.5°	491.6	455.7	420.8	402.1	389.5	385.0	381.5
45°	414.4	381.0	356.9	342.7	335.4	327.8	324.2
47.5°	352.6	325.5	309.6	297.5	289.6	285.1	282.9
50°	317.6	295.4	281.2	271.9	264.8	261.3	259.4
52.5°	286.6	268.3	256.4	249.0	244.2	241.6	240.8
55°	246.8	232.9	225.3	218.9	215.4	213.0	212.1
57.5°	214.6	203.8	197.7	192.4	191.0	189.1	188.4
60°	193.4	185.1	179.9	176.3	175.1	172.8	173.2
62.5°	174.6	167.8	163.4	161.4	159.8	157.8	158.5
65°	147.7	142.7	140.3	138.5	136.6	135.4	136.3
67.5°	123.9	120.5	117.3	116.2	115.3	115.1	114.1
70°	108.4	105.6	102.7	102.0	102.0	101.1	100.8
72.5°	93.4	91.4	89.5	88.9	88.2	88.6	87.6
75°	72.2	70.5	69.8	69.1	68.9	68.9	68.2
77.5°	53.3	52.1	51.0	51.0	50.1	49.8	49.7
80°	40.5	40.0	39.1	39.1	38.6	38.8	38.3
82.5°	30.4	29.8	29.6	29.2	28.5	28.6	28.1
85°	16.3	15.6	15.4	14.7	14.2	14.7	14.2
87.5°	12.4	12.6	12.6	12.4	12.3	12.4	11.9
90°	33.7	35.4	36.6	37.2	37.8	38.3	38.9
92.5°	54.5	55.5	56.2	56.5	56.9	57.2	57.6
95°	101.2	102.0	102.5	102.5	102.5	102.5	102.5
97.5°	159.0	160.0	160.6	160.6	160.6	160.6	160.6
100°	200.2	200.7	201.0	201.0	201.0	201.0	201.0
102.5°	244.4	245.2	245.7	246.0	246.2	246.4	246.7
105°	311.3	312.1	313.0	313.8	314.7	315.6	316.4
107.5°	383.4	384.3	384.6	384.6	384.5	384.5	384.4
110°	430.1	429.6	429.7	430.6	431.4	432.3	433.2



TEST NUMBER: P332734

CATALOG NUMBER: S124DIW-S350D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	482.4	482.2	482.3	482.4	482.6	482.8	483.0
115°	562.0	561.7	561.4	561.1	560.8	560.5	560.3
117.5°	638.0	637.0	636.2	635.6	635.1	634.5	633.9
120°	689.5	688.1	687.6	688.2	688.8	689.4	689.9
122.5°	742.8	741.8	740.8	739.7	738.7	737.7	736.6
125°	820.5	819.9	819.3	818.8	818.2	817.6	817.0
127.5°	894.4	893.8	893.3	892.9	892.4	891.9	891.5
130°	946.3	945.7	944.9	943.7	942.5	941.4	940.2
132.5°	995.1	994.5	994.0	993.5	993.0	992.6	992.1
135°	1068.2	1067.6	1066.9	1066.0	1065.2	1064.3	1063.4
137.5°	1138.8	1138.0	1137.7	1137.9	1138.1	1138.2	1138.4
140°	1185.8	1185.5	1185.2	1184.9	1184.6	1184.3	1184.1
142.5°	1230.1	1230.0	1229.9	1229.9	1229.8	1229.8	1229.7
145°	1296.0	1295.7	1295.2	1294.3	1293.4	1292.6	1291.7
147.5°	1356.1	1355.9	1355.6	1355.3	1355.0	1354.8	1354.5
150°	1394.1	1394.1	1394.0	1393.7	1393.4	1393.1	1392.9
152.5°	1430.5	1431.2	1431.1	1430.4	1429.6	1428.9	1428.1
155°	1480.6	1481.8	1481.8	1480.6	1479.5	1478.3	1477.2
157.5°	1524.1	1525.0	1524.9	1523.9	1522.9	1522.0	1521.0
160°	1551.1	1551.9	1551.6	1550.2	1548.8	1547.3	1545.9
162.5°	1576.0	1577.5	1577.6	1576.1	1574.7	1573.3	1571.8
165°	1608.1	1609.9	1610.2	1609.0	1607.8	1606.7	1605.5
167.5°	1635.1	1636.8	1636.8	1635.0	1633.2	1631.5	1629.7
170°	1649.6	1651.4	1651.2	1649.2	1647.2	1645.2	1643.2
172.5°	1660.7	1662.7	1662.6	1660.6	1658.6	1656.6	1654.6
175°	1672.5	1674.6	1674.6	1672.5	1670.5	1668.5	1666.5
177.5°	1678.6	1680.2	1680.1	1678.3	1676.4	1674.6	1672.7
180°	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9	1676.9

(END OF REPORT)