

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332743

Luminaire Tested: **S124DIW-S350D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332743
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7758.6 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20																				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16																				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14																				
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12																				
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10																				
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9																				
6	58	46	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8																				
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7																				
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6																				
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5																				
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	0.7
10°-20°	156.7	2.0
20°-30°	230.7	3.0
30°-40°	268.2	3.5
40°-50°	268.2	3.5
50°-60°	234.6	3.0
60°-70°	174.2	2.2
70°-80°	99.0	1.3
80°-90°	34.4	0.4
90°-100°	69.0	0.9
100°-110°	439.7	5.7
110°-120°	841.1	10.8
120°-130°	1067.8	13.8
130°-140°	1142.4	14.7
140°-150°	1068.3	13.8
150°-160°	861.5	11.1
160°-170°	555.6	7.2
170°-180°	191.5	2.5
0°-30°	443.1	5.7
0°-40°	711.3	9.2
0°-60°	1214.1	15.6
0°-90°	1521.7	19.6
90°-120°	1349.8	17.4
90°-150°	4628.2	59.7
90°-180°	6237.0	80.4
0°-180°	7758.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	4	21	33	42	45	5
95°	83	35	33	42	44	107
105°	454	463	470	480	430	475
115°	848	852	850	853	854	834
125°	1191	1197	1194	1199	1200	1063
135°	1478	1477	1482	1485	1488	1138
145°	1704	1708	1709	1710	1713	1064
155°	1868	1870	1865	1871	1867	861
165°	1971	1964	1964	1974	1962	557
175°	2016	2008	2009	2021	2004	192
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.8	11.4	12.1	12.7	13.4	13.9	14.4	14.8	15.3	15.7	16.1
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	19.0	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0
95°	82.9	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2
97.5°	176.1	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0
100°	247.3	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7
102.5°	326.9	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2
105°	453.9	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5
107.5°	571.8	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1
110°	651.5	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	728.7	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9
115°	847.5	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2
117.5°	954.6	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8
120°	1027.0	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2
122.5°	1094.5	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7
125°	1191.4	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4
127.5°	1283.0	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3
130°	1342.2	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5
132.5°	1396.4	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2
135°	1477.9	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1
137.5°	1550.0	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9
140°	1597.0	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1
142.5°	1639.2	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2
145°	1704.1	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9
147.5°	1755.7	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9
150°	1793.1	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6
152.5°	1824.4	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1
155°	1868.5	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8
157.5°	1905.6	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3
160°	1927.3	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3
162.5°	1946.6	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3
165°	1971.0	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1
167.5°	1990.3	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5
170°	2001.2	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3
172.5°	2008.4	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5
175°	2016.2	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7
177.5°	2019.9	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	16.5	16.9	17.3	17.6	17.7	17.9	18.0	18.1
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	36.0	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	37.2	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.2	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	55.0	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	196.8	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	476.5	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	589.6	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	666.4	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P332743

CATALOG NUMBER: S124DIW-S350D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	740.8	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	851.9	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.7	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.1	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1196.4	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1291.1	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1348.9	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.6	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1483.7	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1558.7	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1605.1	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.0	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.3	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.1	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1827.6	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1868.1	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1943.4	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1968.8	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1987.5	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	1999.0	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2006.2	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2014.7	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2018.1	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)