

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333023-840

Luminaire Tested: **S124RDIW-S350D1050U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333023-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1050U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5735.0 lumens  
Efficiency: N/A  
Efficacy: 150.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	23				
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	9	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4789	4789	4789	4789
5°	5555	4803	4246	4803
10°	6571	4782	3789	4782
15°	7590	4738	3256	4738
20°	8451	4677	2944	4677
25°	8725	4618	2734	4618
30°	7637	4545	2606	4545
35°	5945	4438	2530	4438
40°	4458	4314	2488	4314
45°	3520	4117	2466	4117
50°	2972	3890	2396	3890
55°	2590	3640	2267	3640
60°	2330	3379	2007	3379
65°	2055	3100	1727	3100
70°	1851	2811	1555	2811
75°	1550	2489	1326	2489
80°	1311	2120	1246	2120
85°	1102	1667	1102	1667



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.5	1.0
10°-20°	173.4	3.0
20°-30°	271.2	4.7
30°-40°	301.5	5.3
40°-50°	267.5	4.7
50°-60°	208.4	3.6
60°-70°	136.5	2.4
70°-80°	67.1	1.2
80°-90°	20.5	0.4
90°-100°	46.8	0.8
100°-110°	298.3	5.2
110°-120°	570.7	10.0
120°-130°	724.4	12.6
130°-140°	775.1	13.5
140°-150°	724.8	12.6
150°-160°	584.5	10.2
160°-170°	377.0	6.6
170°-180°	129.9	2.3
0°-30°	502.0	8.8
0°-40°	803.5	14.0
0°-60°	1279.4	22.3
0°-90°	1503.4	26.2
90°-120°	915.8	16.0
90°-150°	3140.1	54.8
90°-180°	4232.0	73.8
0°-180°	5735.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	593	593	593	593	593	
5°	686	593	524	593	686	69
15°	908	567	390	567	908	258
25°	980	518	307	518	980	435
35°	603	450	257	450	603	378
45°	308	361	216	361	308	244
55°	184	259	161	259	184	167
65°	108	162	90	162	108	108
75°	50	80	42	80	50	55
85°	12	18	12	18	12	14
90°	31	3	31	3	31	14
95°	30	56	30	56	30	24
105°	292	308	292	308	292	254
115°	579	575	579	575	579	573
125°	814	808	814	808	814	725
135°	1010	1003	1010	1003	1010	777
145°	1162	1156	1162	1156	1162	726
155°	1267	1268	1267	1268	1267	584
165°	1331	1337	1331	1337	1331	376
175°	1360	1368	1360	1368	1360	129
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	625.7	627.4	625.7	625.5	623.6	623.0	622.3	619.8	615.2	612.5	613.1
5°	685.5	691.5	688.1	687.6	682.4	677.1	673.8	666.1	657.9	652.5	647.9
7.5°	754.6	758.0	755.9	752.6	744.1	739.2	731.4	721.4	706.8	695.7	685.5
10°	801.6	804.5	803.5	797.3	791.1	778.4	771.2	757.2	738.7	724.2	710.5
12.5°	847.9	850.9	842.5	842.8	831.0	821.0	809.7	791.9	770.7	751.9	734.9
15°	908.2	904.3	904.3	899.6	886.5	872.6	860.9	842.2	815.5	793.0	769.3
17.5°	955.4	956.7	954.8	943.5	933.2	918.9	897.4	875.7	850.8	820.6	796.5
20°	983.7	983.7	981.6	973.9	960.6	945.2	922.1	898.4	866.9	836.5	809.3
22.5°	995.2	995.9	993.4	987.1	975.1	960.2	940.4	916.4	883.8	849.7	816.0
25°	979.5	984.0	984.4	982.8	979.2	970.1	953.1	928.6	899.4	862.3	826.0
27.5°	899.2	904.9	910.0	918.3	929.3	934.9	935.7	923.2	897.8	862.1	825.6
30°	819.3	824.0	839.6	859.9	875.7	890.0	902.5	905.8	891.5	859.5	821.0
32.5°	730.5	737.1	752.7	774.5	800.7	825.1	852.9	867.2	866.8	847.6	812.0
35°	603.2	608.0	622.4	645.3	676.8	713.0	757.2	791.5	815.0	813.3	791.5
37.5°	486.6	491.9	506.3	525.4	556.0	600.7	643.5	690.9	734.2	758.5	751.2
40°	423.0	423.2	437.4	457.0	485.6	524.6	571.2	623.8	672.1	711.6	719.1
42.5°	372.9	372.9	382.3	403.4	424.0	460.7	505.2	557.4	614.0	659.5	679.7
45°	308.3	310.4	318.1	330.7	347.0	378.1	413.7	462.2	525.5	579.6	613.3
47.5°	261.1	264.3	269.1	279.4	292.4	313.1	342.5	386.2	437.7	497.1	545.0
50°	236.6	237.1	243.3	249.0	260.2	276.8	302.6	338.9	386.3	443.3	496.7
52.5°	215.6	215.5	219.2	226.5	235.6	248.4	269.3	302.4	344.4	395.6	450.6
55°	184.0	185.2	188.1	193.8	200.8	209.8	226.3	251.2	284.2	327.9	377.9
57.5°	160.1	160.7	162.9	165.3	171.7	178.3	190.7	207.9	235.7	271.6	318.1
60°	144.3	144.6	145.3	148.9	153.9	160.2	168.5	183.1	206.5	239.2	276.1
62.5°	129.1	129.5	130.6	133.2	137.1	141.4	150.2	161.9	181.3	209.2	242.4
65°	107.6	107.8	109.5	110.4	113.5	117.3	123.8	131.7	145.1	168.5	193.6
67.5°	89.9	89.9	90.0	91.3	93.4	95.9	99.8	106.1	116.2	130.6	152.7
70°	78.4	78.4	78.9	79.6	80.8	82.9	85.1	89.9	97.3	109.0	125.9
72.5°	67.7	67.9	68.4	68.5	69.1	70.9	72.5	75.5	81.0	89.9	103.6
75°	49.7	50.4	51.6	52.6	53.8	53.5	55.2	57.2	58.8	64.0	71.9
77.5°	37.0	36.7	36.8	37.6	37.7	38.0	39.2	40.6	41.9	44.3	47.2
80°	28.2	28.2	28.9	29.2	28.9	29.2	30.4	31.1	31.5	32.5	35.1
82.5°	21.3	21.7	21.5	21.7	21.8	22.1	23.1	23.2	23.7	24.1	25.1
85°	11.9	12.2	12.4	11.9	11.9	11.9	12.4	12.6	13.1	12.9	13.4
87.5°	10.3	10.1	10.2	10.1	10.2	9.8	9.7	9.8	9.2	9.1	8.7
90°	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2	23.8	22.5	20.7
92.5°	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4	23.0	21.7	19.9
95°	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2	23.8	22.5	22.3
97.5°	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3	27.2	27.0	52.4
100°	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3	41.2	45.0	76.4
102.5°	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5	175.2	216.9	221.0
105°	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4	321.2	319.2	318.1
107.5°	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0	399.0	398.0	396.5
110°	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1	451.7	451.2	449.9



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6	502.7	502.8	502.1
115°	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9	577.5	577.0	577.3
117.5°	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8	653.9	654.0	653.5
120°	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8	700.0
122.5°	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1	746.8	746.5	746.2
125°	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7	811.0	810.3	810.8
127.5°	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0	876.2	876.3	875.1
130°	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1	914.9	914.7	914.0
132.5°	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6	953.4	953.2	952.3
135°	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7	1006.2	1005.8	1004.9
137.5°	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5	1057.0	1056.5	1055.5
140°	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0	1088.3	1087.6	1087.2
142.5°	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1	1117.6	1117.1	1116.8
145°	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7	1159.5	1159.2	1159.2
147.5°	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3	1196.1	1195.9	1196.1
150°	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6	1219.6	1219.6	1219.8
152.5°	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0	1239.6	1239.3	1239.7
155°	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5	1266.6	1265.7	1266.4
157.5°	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8	1289.6
160°	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5	1303.7
162.5°	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5	1317.2	1315.8	1316.1
165°	1331.1	1333.2	1335.2	1337.3	1339.3	1339.3	1337.7	1335.8	1334.0	1332.2	1332.2
167.5°	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5	1346.5	1344.4	1344.6
170°	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2	1354.4	1352.6	1352.4
172.5°	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2	1359.4	1357.6	1357.4
175°	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0	1364.9	1362.9	1362.6
177.5°	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3	1367.8	1366.3	1365.9
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	611.2	608.5	607.1	604.1	600.5	598.5	596.8	594.3	591.1	587.6	585.2
5°	642.2	636.4	629.2	620.7	613.1	605.6	599.2	592.7	585.3	577.6	570.1
7.5°	674.0	662.8	650.6	636.4	622.8	610.3	598.7	587.8	575.4	564.2	554.1
10°	696.2	681.0	664.0	646.0	628.1	612.6	597.2	583.4	568.2	554.5	543.0
12.5°	714.2	696.2	675.8	653.5	631.9	613.1	595.5	577.4	560.1	545.3	530.0
15°	744.0	719.4	692.0	665.1	637.2	611.6	587.9	566.9	547.0	526.2	511.7
17.5°	764.6	735.3	701.9	669.7	636.7	606.5	579.3	554.2	531.3	510.1	492.7
20°	776.8	744.5	707.4	670.9	633.8	601.6	572.2	544.4	520.8	497.9	479.9
22.5°	783.7	747.9	707.4	669.1	630.8	595.8	563.6	534.7	509.0	485.9	466.2
25°	785.9	747.6	706.3	662.3	620.3	583.2	549.7	518.4	489.7	466.8	445.8
27.5°	782.7	737.7	695.4	650.3	606.8	567.8	532.7	499.8	471.1	446.5	424.9
30°	778.2	729.9	684.5	637.6	593.7	556.1	519.1	487.6	457.7	432.1	410.4
32.5°	768.2	720.3	671.5	623.5	579.0	540.3	505.1	473.4	444.1	418.0	394.9
35°	748.5	700.0	647.0	597.7	554.0	513.8	480.9	450.3	422.3	394.4	370.0
37.5°	722.6	673.1	620.3	566.3	522.5	484.6	454.4	425.7	398.4	372.8	345.9
40°	698.1	653.0	598.4	544.9	500.0	463.4	435.5	409.4	381.9	356.6	329.6
42.5°	668.5	630.1	574.9	521.2	476.9	441.6	415.6	390.1	365.1	340.5	312.4
45°	619.0	589.9	538.3	486.7	441.9	407.0	383.1	360.6	338.7	315.3	288.7
47.5°	562.3	542.6	498.1	445.1	403.8	372.4	349.3	330.9	312.4	288.9	265.7
50°	522.9	510.3	467.3	419.0	379.5	350.6	327.0	309.7	294.2	271.8	251.0
52.5°	480.9	474.1	437.8	391.6	353.6	325.2	305.0	289.5	273.8	255.1	235.7
55°	416.8	420.4	389.6	349.6	313.8	289.9	271.6	258.6	245.2	229.4	214.4
57.5°	351.3	364.5	343.8	308.7	275.1	253.0	239.1	228.3	217.0	204.0	191.1
60°	312.1	323.2	311.4	280.5	251.2	230.7	217.7	209.3	198.1	186.2	176.4
62.5°	273.9	285.7	278.7	253.8	226.5	208.8	197.4	189.7	181.3	170.9	160.7
65°	225.9	233.5	230.1	213.0	193.6	178.5	168.0	162.3	154.6	147.0	137.9
67.5°	173.0	187.7	185.8	176.6	160.0	148.1	141.3	136.2	129.3	123.6	117.4
70°	142.2	155.8	155.6	148.1	139.1	128.2	123.3	119.1	112.8	107.3	102.3
72.5°	116.4	128.9	130.8	125.0	118.9	110.5	105.9	103.0	96.9	93.2	89.1
75°	81.5	90.6	93.0	93.0	90.1	85.8	81.7	79.8	75.5	72.2	69.8
77.5°	53.4	59.2	62.9	63.7	64.2	62.7	59.4	58.1	54.7	53.6	51.3
80°	37.8	41.6	45.8	47.4	48.5	48.1	46.7	45.6	42.5	41.3	40.4
82.5°	26.1	28.2	31.7	34.9	34.5	35.9	34.5	33.8	31.4	31.0	30.1
85°	13.6	13.8	14.3	16.5	17.7	18.2	18.4	18.0	17.2	17.2	15.6
87.5°	8.4	7.8	7.9	7.4	7.1	7.4	7.5	7.1	7.1	7.0	6.9
90°	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0	5.6	8.1	10.6
92.5°	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9	13.0	13.1	13.3
95°	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2	48.6	40.8	33.1
97.5°	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5	124.3	129.2	134.0
100°	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8	171.9	176.0	180.1
102.5°	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9	224.8	227.8	230.9
105°	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0	309.3	310.7	312.0
107.5°	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0	388.7	389.3	390.0
110°	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0	442.7	443.3	444.0





TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4	495.6	496.9	498.1
115°	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0	575.7	576.4	577.0
117.5°	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6	648.5	649.4	650.4
120°	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8	697.7	698.6	699.5
122.5°	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7	743.2	743.7	744.3
125°	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3	809.2	810.1	811.0
127.5°	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5	870.7	871.0	871.2
130°	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6	910.9	911.1	911.3
132.5°	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5	947.9	948.3	948.7
135°	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7	1002.5	1002.3	1002.0
137.5°	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6	1051.7	1051.8	1051.9
140°	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6	1084.0	1084.5	1084.9
142.5°	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2	1113.0	1113.8	1114.7
145°	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2	1156.9	1157.5	1158.2
147.5°	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1	1192.4	1193.8	1195.0
150°	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6	1217.5	1218.4	1219.3
152.5°	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8	1238.6	1239.3	1240.0
155°	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7	1268.0	1268.2	1268.4
157.5°	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9	1292.7	1292.6	1292.4
160°	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6	1307.0	1306.3	1305.6
162.5°	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7	1319.9	1319.0	1318.1
165°	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3	1336.2	1335.0	1333.8
167.5°	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4	1349.2	1348.1	1346.9
170°	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8	1356.3	1355.0	1353.6
172.5°	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6	1361.3	1359.9	1358.6
175°	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0	1366.7	1365.2	1363.9
177.5°	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4	1369.2	1367.9	1366.7
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	582.5	580.6	578.1	575.2	571.8	568.8	567.3	568.6	569.2	567.5	567.3
5°	564.7	558.8	554.0	546.8	541.1	536.3	533.0	531.5	532.0	528.2	527.3
7.5°	544.8	537.8	529.9	521.4	513.5	506.4	502.8	500.8	496.7	494.9	492.0
10°	532.0	522.5	514.8	504.7	495.6	487.4	483.2	479.9	475.8	473.9	469.9
12.5°	518.9	507.8	499.3	488.9	479.6	469.6	465.6	459.5	453.1	449.1	443.8
15°	500.2	486.9	476.6	464.1	453.1	441.7	431.4	419.9	415.7	406.6	401.3
17.5°	478.5	464.9	452.2	435.6	418.6	404.2	393.3	382.3	375.8	370.0	367.3
20°	464.1	451.7	434.0	414.7	395.8	380.0	371.1	364.0	356.8	352.7	349.9
22.5°	450.6	434.6	414.1	393.2	374.4	362.0	354.6	347.2	341.3	337.5	333.7
25°	427.8	407.0	385.3	361.3	348.5	337.7	329.6	323.6	320.0	315.0	313.1
27.5°	404.5	379.2	355.3	339.2	325.8	315.9	308.8	304.4	299.8	296.6	294.1
30°	386.5	360.9	339.4	324.1	310.4	302.4	296.6	291.3	287.7	285.1	283.3
32.5°	368.7	343.2	325.1	308.6	297.8	289.9	283.8	279.8	277.0	273.7	272.5
35°	343.0	320.2	304.5	289.6	278.7	271.6	266.7	262.7	260.2	259.3	258.6
37.5°	318.2	299.6	282.7	270.5	260.7	255.1	249.4	247.4	245.8	244.1	244.9
40°	302.6	285.1	270.0	257.2	249.2	243.1	239.7	237.3	235.9	235.9	235.9
42.5°	289.0	272.0	257.2	245.7	237.8	232.6	228.8	226.8	226.3	226.1	227.3
45°	267.9	252.2	237.3	227.7	221.1	215.8	213.7	212.0	212.0	213.0	213.2
47.5°	247.0	232.3	220.4	209.6	203.5	200.3	198.3	197.5	197.6	198.5	199.7
50°	234.2	219.6	207.9	198.3	192.7	189.6	187.8	187.3	187.8	187.8	189.6
52.5°	220.3	207.2	195.7	187.6	181.2	178.2	177.3	176.6	176.9	177.7	178.4
55°	199.9	188.1	177.1	169.5	164.7	162.8	160.6	160.9	160.4	160.9	160.9
57.5°	179.3	168.7	158.5	152.5	148.2	145.5	143.2	143.8	143.1	143.0	142.6
60°	166.1	154.6	146.5	141.0	136.2	133.8	131.7	132.2	131.5	131.0	130.0
62.5°	151.8	142.2	134.4	129.2	125.3	122.6	120.4	120.0	118.3	116.6	114.5
65°	131.0	123.1	116.1	111.2	107.6	105.4	103.7	102.3	98.7	94.9	93.0
67.5°	110.8	105.0	98.6	94.3	91.4	88.7	85.4	83.0	79.7	77.6	76.3
70°	97.8	92.3	86.7	82.7	79.6	77.0	73.4	71.7	69.3	68.4	67.2
72.5°	85.3	80.2	75.1	71.4	68.2	66.0	63.2	61.6	60.5	60.1	59.0
75°	66.4	62.4	58.6	55.2	52.6	51.1	50.0	48.8	48.3	46.2	44.9
77.5°	48.5	45.7	43.4	41.0	39.2	38.2	35.9	34.5	33.7	32.7	32.4
80°	37.8	35.9	33.4	32.0	29.4	28.5	27.5	27.3	27.0	26.8	26.6
82.5°	28.4	26.5	24.1	23.2	22.5	21.9	21.4	21.1	20.9	21.0	21.0
85°	14.3	13.4	13.4	13.1	12.9	12.6	12.4	12.4	12.2	12.4	12.2
87.5°	7.4	7.7	8.0	8.0	8.6	8.9	9.0	9.3	9.7	9.6	9.8
90°	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2	26.6	28.0	28.9
92.5°	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4	25.8	27.2	27.9
95°	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2	26.6	28.0	28.8
97.5°	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3	27.5	27.6	27.8
100°	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3	33.4	29.6	27.8
102.5°	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5	91.8	50.1	29.3
105°	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4	325.4	327.4	324.4
107.5°	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0	401.0	402.0	402.9
110°	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1	452.6	453.0	453.6



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6	502.5	502.4	502.8
115°	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9	578.5	578.9	579.2
117.5°	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8	653.8	653.7	653.6
120°	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7	701.3	701.7	701.7
122.5°	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1	747.3	747.6	747.5
125°	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7	812.4	813.0	813.5
127.5°	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0	875.9	875.7	875.6
130°	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1	915.4	915.6	915.7
132.5°	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6	953.9	954.1	954.1
135°	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7	1007.1	1007.6	1008.0
137.5°	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5	1058.0	1058.5	1058.7
140°	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0	1089.6	1090.4	1090.9
142.5°	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1	1118.6	1119.1	1119.3
145°	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7	1159.9	1160.1	1160.5
147.5°	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3	1196.4	1196.6	1196.8
150°	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6	1219.6	1219.6	1219.7
152.5°	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0	1240.3	1240.7	1240.8
155°	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5	1268.4	1269.3	1269.4
157.5°	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5
160°	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0
162.5°	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5	1319.9	1321.2	1321.2
165°	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8	1337.7	1339.5	1339.3
167.5°	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5	1350.5	1352.4	1352.3
170°	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2	1358.1	1359.9	1359.7
172.5°	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2	1363.0	1364.8	1364.5
175°	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0	1369.0	1371.1	1370.7
177.5°	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3	1370.7	1372.2	1371.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	566.2	566.6	565.3	564.9	565.3	566.6	566.2	567.3	567.5	569.2	568.6
5°	525.3	524.8	523.6	523.9	523.6	524.8	525.3	527.3	528.2	532.0	531.5
7.5°	490.3	488.5	489.0	487.1	489.0	488.5	490.3	492.0	494.9	496.7	500.8
10°	468.9	466.3	464.1	462.2	464.1	466.3	468.9	469.9	473.9	475.8	479.9
12.5°	439.7	437.4	434.5	435.0	434.5	437.4	439.7	443.8	449.1	453.1	459.5
15°	398.2	394.6	388.9	389.6	388.9	394.6	398.2	401.3	406.6	415.7	419.9
17.5°	363.0	363.0	360.4	361.1	360.4	363.0	363.0	367.3	370.0	375.8	382.3
20°	344.9	343.3	343.5	342.7	343.5	343.3	344.9	349.9	352.7	356.8	364.0
22.5°	332.2	330.2	328.5	327.1	328.5	330.2	332.2	333.7	337.5	341.3	347.2
25°	310.9	309.5	307.4	306.9	307.4	309.5	310.9	313.1	315.0	320.0	323.6
27.5°	292.2	292.0	291.0	289.9	291.0	292.0	292.2	294.1	296.6	299.8	304.4
30°	281.3	280.8	280.3	279.6	280.3	280.8	281.3	283.3	285.1	287.7	291.3
32.5°	271.6	271.2	270.7	270.8	270.7	271.2	271.6	272.5	273.7	277.0	279.8
35°	257.6	257.4	256.9	256.7	256.9	257.4	257.6	258.6	259.3	260.2	262.7
37.5°	244.7	245.3	245.0	244.9	245.0	245.3	244.7	244.9	244.1	245.8	247.4
40°	235.7	235.9	236.4	236.1	236.4	235.9	235.7	235.9	235.9	235.9	237.3
42.5°	228.2	228.2	228.9	228.1	228.9	228.2	228.2	227.3	226.1	226.3	226.8
45°	214.9	216.3	216.0	216.0	216.0	216.3	214.9	213.2	213.0	212.0	212.0
47.5°	200.3	201.6	201.9	201.8	201.9	201.6	200.3	199.7	198.5	197.6	197.5
50°	190.8	190.3	191.0	190.8	191.0	190.3	190.8	189.6	187.8	187.8	187.3
52.5°	179.0	179.2	179.2	178.8	179.2	179.2	179.0	178.4	177.7	176.9	176.6
55°	161.1	161.4	160.9	161.1	160.9	161.4	161.1	160.9	160.9	160.4	160.9
57.5°	141.6	140.5	140.9	140.4	140.9	140.5	141.6	142.6	143.0	143.1	143.8
60°	127.6	125.7	125.2	124.3	125.2	125.7	127.6	130.0	131.0	131.5	132.2
62.5°	112.0	110.6	109.0	109.8	109.0	110.6	112.0	114.5	116.6	118.3	120.0
65°	91.1	90.1	89.4	90.4	89.4	90.1	91.1	93.0	94.9	98.7	102.3
67.5°	75.3	74.8	74.8	74.4	74.8	74.8	75.3	76.3	77.6	79.7	83.0
70°	67.2	66.4	66.4	65.9	66.4	66.4	67.2	67.2	68.4	69.3	71.7
72.5°	58.8	58.1	58.3	58.0	58.3	58.1	58.8	59.0	60.1	60.5	61.6
75°	43.5	42.3	42.3	42.5	42.3	42.3	43.5	44.9	46.2	48.3	48.8
77.5°	32.4	32.2	32.5	32.1	32.5	32.2	32.4	32.4	32.7	33.7	34.5
80°	26.6	26.3	26.1	26.8	26.1	26.3	26.6	26.6	26.8	27.0	27.3
82.5°	20.6	20.6	20.5	21.4	20.5	20.6	20.6	21.0	21.0	20.9	21.1
85°	12.4	11.9	12.4	11.9	12.4	11.9	12.4	12.2	12.4	12.2	12.4
87.5°	10.3	10.2	10.1	10.3	10.1	10.2	10.3	9.8	9.6	9.7	9.3
90°	29.3	29.8	30.2	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2
92.5°	28.0	28.1	28.2	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4
95°	29.0	29.2	29.5	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2
97.5°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3
100°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3
102.5°	29.3	29.4	29.4	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5
105°	316.2	308.0	299.8	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4
107.5°	403.8	404.7	405.6	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0
110°	454.3	454.9	455.7	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.7	504.5	505.4	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6
115°	579.2	579.2	579.2	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9
117.5°	653.5	653.4	653.3	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8
120°	701.3	700.7	700.3	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7
122.5°	747.1	746.6	746.2	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1
125°	813.7	814.0	814.3	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7
127.5°	875.4	875.1	874.9	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0
130°	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1
132.5°	953.9	953.7	953.6	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6
135°	1008.6	1009.0	1009.5	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7
137.5°	1058.5	1058.4	1058.3	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5
140°	1091.1	1091.3	1091.5	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0
142.5°	1119.4	1119.4	1119.5	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1
145°	1160.9	1161.4	1161.8	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7
147.5°	1197.1	1197.3	1197.5	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3
150°	1219.9	1220.2	1220.4	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6
152.5°	1240.7	1240.5	1240.4	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0
155°	1268.7	1268.1	1267.4	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5
157.5°	1292.3	1291.1	1290.0	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1
160°	1307.6	1306.3	1304.8	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3
162.5°	1319.6	1318.1	1316.6	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5
165°	1337.3	1335.2	1333.2	1331.1	1333.2	1335.2	1337.3	1339.3	1339.5	1337.7	1335.8
167.5°	1350.1	1347.8	1345.5	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5
170°	1357.4	1355.1	1352.8	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2
172.5°	1362.0	1359.6	1357.2	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2
175°	1368.0	1365.2	1362.5	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0
177.5°	1369.6	1367.5	1365.2	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	567.3	568.8	571.8	575.2	578.1	580.6	582.5	585.2	587.6	591.1	594.3
5°	533.0	536.3	541.1	546.8	554.0	558.8	564.7	570.1	577.6	585.3	592.7
7.5°	502.8	506.4	513.5	521.4	529.9	537.8	544.8	554.1	564.2	575.4	587.8
10°	483.2	487.4	495.6	504.7	514.8	522.5	532.0	543.0	554.5	568.2	583.4
12.5°	465.6	469.6	479.6	488.9	499.3	507.8	518.9	530.0	545.3	560.1	577.4
15°	431.4	441.7	453.1	464.1	476.6	486.9	500.2	511.7	526.2	547.0	566.9
17.5°	393.3	404.2	418.6	435.6	452.2	464.9	478.5	492.7	510.1	531.3	554.2
20°	371.1	380.0	395.8	414.7	434.0	451.7	464.1	479.9	497.9	520.8	544.4
22.5°	354.6	362.0	374.4	393.2	414.1	434.6	450.6	466.2	485.9	509.0	534.7
25°	329.6	337.7	348.5	361.3	385.3	407.0	427.8	445.8	466.8	489.7	518.4
27.5°	308.8	315.9	325.8	339.2	355.3	379.2	404.5	424.9	446.5	471.1	499.8
30°	296.6	302.4	310.4	324.1	339.4	360.9	386.5	410.4	432.1	457.7	487.6
32.5°	283.8	289.9	297.8	308.6	325.1	343.2	368.7	394.9	418.0	444.1	473.4
35°	266.7	271.6	278.7	289.6	304.5	320.2	343.0	370.0	394.4	422.3	450.3
37.5°	249.4	255.1	260.7	270.5	282.7	299.6	318.2	345.9	372.8	398.4	425.7
40°	239.7	243.1	249.2	257.2	270.0	285.1	302.6	329.6	356.6	381.9	409.4
42.5°	228.8	232.6	237.8	245.7	257.2	272.0	289.0	312.4	340.5	365.1	390.1
45°	213.7	215.8	221.1	227.7	237.3	252.2	267.9	288.7	315.3	338.7	360.6
47.5°	198.3	200.3	203.5	209.6	220.4	232.3	247.0	265.7	288.9	312.4	330.9
50°	187.8	189.6	192.7	198.3	207.9	219.6	234.2	251.0	271.8	294.2	309.7
52.5°	177.3	178.2	181.2	187.6	195.7	207.2	220.3	235.7	255.1	273.8	289.5
55°	160.6	162.8	164.7	169.5	177.1	188.1	199.9	214.4	229.4	245.2	258.6
57.5°	143.2	145.5	148.2	152.5	158.5	168.7	179.3	191.1	204.0	217.0	228.3
60°	131.7	133.8	136.2	141.0	146.5	154.6	166.1	176.4	186.2	198.1	209.3
62.5°	120.4	122.6	125.3	129.2	134.4	142.2	151.8	160.7	170.9	181.3	189.7
65°	103.7	105.4	107.6	111.2	116.1	123.1	131.0	137.9	147.0	154.6	162.3
67.5°	85.4	88.7	91.4	94.3	98.6	105.0	110.8	117.4	123.6	129.3	136.2
70°	73.4	77.0	79.6	82.7	86.7	92.3	97.8	102.3	107.3	112.8	119.1
72.5°	63.2	66.0	68.2	71.4	75.1	80.2	85.3	89.1	93.2	96.9	103.0
75°	50.0	51.1	52.6	55.2	58.6	62.4	66.4	69.8	72.2	75.5	79.8
77.5°	35.9	38.2	39.2	41.0	43.4	45.7	48.5	51.3	53.6	54.7	58.1
80°	27.5	28.5	29.4	32.0	33.4	35.9	37.8	40.4	41.3	42.5	45.6
82.5°	21.4	21.9	22.5	23.2	24.1	26.5	28.4	30.1	31.0	31.4	33.8
85°	12.4	12.6	12.9	13.1	13.4	13.4	14.3	15.6	17.2	17.2	18.0
87.5°	9.0	8.9	8.6	8.0	8.0	7.7	7.4	6.9	7.0	7.1	7.1
90°	23.8	22.5	20.7	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0
92.5°	23.0	21.7	19.9	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9
95°	23.8	22.5	22.3	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2
97.5°	27.2	27.0	52.4	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5
100°	41.2	45.0	76.4	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8
102.5°	175.2	216.9	221.0	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9
105°	321.2	319.2	318.1	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0
107.5°	399.0	398.0	396.5	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0
110°	451.7	451.2	449.9	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	502.7	502.8	502.1	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4
115°	577.5	577.0	577.3	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0
117.5°	653.9	654.0	653.5	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6
120°	700.3	699.8	700.0	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8
122.5°	746.8	746.5	746.2	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7
125°	811.0	810.3	810.8	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3
127.5°	876.2	876.3	875.1	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5
130°	914.9	914.7	914.0	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6
132.5°	953.4	953.2	952.3	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5
135°	1006.2	1005.8	1004.9	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7
137.5°	1057.0	1056.5	1055.5	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6
140°	1088.3	1087.6	1087.2	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6
142.5°	1117.6	1117.1	1116.8	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2
145°	1159.5	1159.2	1159.2	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2
147.5°	1196.1	1195.9	1196.1	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1
150°	1219.6	1219.6	1219.8	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6
152.5°	1239.6	1239.3	1239.7	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8
155°	1266.6	1265.7	1266.4	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7
157.5°	1290.0	1288.8	1289.6	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9
160°	1304.8	1303.5	1303.7	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6
162.5°	1317.2	1315.8	1316.1	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7
165°	1334.0	1332.2	1332.2	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3
167.5°	1346.5	1344.4	1344.6	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4
170°	1354.4	1352.6	1352.4	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8
172.5°	1359.4	1357.6	1357.4	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6
175°	1364.9	1362.9	1362.6	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0
177.5°	1367.8	1366.3	1365.9	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	596.8	598.5	600.5	604.1	607.1	608.5	611.2	613.1	612.5	615.2	619.8
5°	599.2	605.6	613.1	620.7	629.2	636.4	642.2	647.9	652.5	657.9	666.1
7.5°	598.7	610.3	622.8	636.4	650.6	662.8	674.0	685.5	695.7	706.8	721.4
10°	597.2	612.6	628.1	646.0	664.0	681.0	696.2	710.5	724.2	738.7	757.2
12.5°	595.5	613.1	631.9	653.5	675.8	696.2	714.2	734.9	751.9	770.7	791.9
15°	587.9	611.6	637.2	665.1	692.0	719.4	744.0	769.3	793.0	815.5	842.2
17.5°	579.3	606.5	636.7	669.7	701.9	735.3	764.6	796.5	820.6	850.8	875.7
20°	572.2	601.6	633.8	670.9	707.4	744.5	776.8	809.3	836.5	866.9	898.4
22.5°	563.6	595.8	630.8	669.1	707.4	747.9	783.7	816.0	849.7	883.8	916.4
25°	549.7	583.2	620.3	662.3	706.3	747.6	785.9	826.0	862.3	899.4	928.6
27.5°	532.7	567.8	606.8	650.3	695.4	737.7	782.7	825.6	862.1	897.8	923.2
30°	519.1	556.1	593.7	637.6	684.5	729.9	778.2	821.0	859.5	891.5	905.8
32.5°	505.1	540.3	579.0	623.5	671.5	720.3	768.2	812.0	847.6	866.8	867.2
35°	480.9	513.8	554.0	597.7	647.0	700.0	748.5	791.5	813.3	815.0	791.5
37.5°	454.4	484.6	522.5	566.3	620.3	673.1	722.6	751.2	758.5	734.2	690.9
40°	435.5	463.4	500.0	544.9	598.4	653.0	698.1	719.1	711.6	672.1	623.8
42.5°	415.6	441.6	476.9	521.2	574.9	630.1	668.5	679.7	659.5	614.0	557.4
45°	383.1	407.0	441.9	486.7	538.3	589.9	619.0	613.3	579.6	525.5	462.2
47.5°	349.3	372.4	403.8	445.1	498.1	542.6	562.3	545.0	497.1	437.7	386.2
50°	327.0	350.6	379.5	419.0	467.3	510.3	522.9	496.7	443.3	386.3	338.9
52.5°	305.0	325.2	353.6	391.6	437.8	474.1	480.9	450.6	395.6	344.4	302.4
55°	271.6	289.9	313.8	349.6	389.6	420.4	416.8	377.9	327.9	284.2	251.2
57.5°	239.1	253.0	275.1	308.7	343.8	364.5	351.3	318.1	271.6	235.7	207.9
60°	217.7	230.7	251.2	280.5	311.4	323.2	312.1	276.1	239.2	206.5	183.1
62.5°	197.4	208.8	226.5	253.8	278.7	285.7	273.9	242.4	209.2	181.3	161.9
65°	168.0	178.5	193.6	213.0	230.1	233.5	225.9	193.6	168.5	145.1	131.7
67.5°	141.3	148.1	160.0	176.6	185.8	187.7	173.0	152.7	130.6	116.2	106.1
70°	123.3	128.2	139.1	148.1	155.6	155.8	142.2	125.9	109.0	97.3	89.9
72.5°	105.9	110.5	118.9	125.0	130.8	128.9	116.4	103.6	89.9	81.0	75.5
75°	81.7	85.8	90.1	93.0	93.0	90.6	81.5	71.9	64.0	58.8	57.2
77.5°	59.4	62.7	64.2	63.7	62.9	59.2	53.4	47.2	44.3	41.9	40.6
80°	46.7	48.1	48.5	47.4	45.8	41.6	37.8	35.1	32.5	31.5	31.1
82.5°	34.5	35.9	34.5	34.9	31.7	28.2	26.1	25.1	24.1	23.7	23.2
85°	18.4	18.2	17.7	16.5	14.3	13.8	13.6	13.4	12.9	13.1	12.6
87.5°	7.5	7.4	7.1	7.4	7.9	7.8	8.4	8.7	9.1	9.2	9.8
90°	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2
92.5°	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4
95°	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2
97.5°	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3
100°	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3
102.5°	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5
105°	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4
107.5°	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0
110°	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1





TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6
115°	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9
117.5°	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8
120°	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7
122.5°	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1
125°	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7
127.5°	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0
130°	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1
132.5°	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6
135°	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7
137.5°	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5
140°	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0
142.5°	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1
145°	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7
147.5°	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3
150°	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6
152.5°	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0
155°	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5
157.5°	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1
160°	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3
162.5°	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5
165°	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8
167.5°	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5
170°	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2
172.5°	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2
175°	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0
177.5°	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	622.3	623.0	623.6	625.5	625.7	627.4	625.7
5°	673.8	677.1	682.4	687.6	688.1	691.5	685.5
7.5°	731.4	739.2	744.1	752.6	755.9	758.0	754.6
10°	771.2	778.4	791.1	797.3	803.5	804.5	801.6
12.5°	809.7	821.0	831.0	842.8	842.5	850.9	847.9
15°	860.9	872.6	886.5	899.6	904.3	904.3	908.2
17.5°	897.4	918.9	933.2	943.5	954.8	956.7	955.4
20°	922.1	945.2	960.6	973.9	981.6	983.7	983.7
22.5°	940.4	960.2	975.1	987.1	993.4	995.9	995.2
25°	953.1	970.1	979.2	982.8	984.4	984.0	979.5
27.5°	935.7	934.9	929.3	918.3	910.0	904.9	899.2
30°	902.5	890.0	875.7	859.9	839.6	824.0	819.3
32.5°	852.9	825.1	800.7	774.5	752.7	737.1	730.5
35°	757.2	713.0	676.8	645.3	622.4	608.0	603.2
37.5°	643.5	600.7	556.0	525.4	506.3	491.9	486.6
40°	571.2	524.6	485.6	457.0	437.4	423.2	423.0
42.5°	505.2	460.7	424.0	403.4	382.3	372.9	372.9
45°	413.7	378.1	347.0	330.7	318.1	310.4	308.3
47.5°	342.5	313.1	292.4	279.4	269.1	264.3	261.1
50°	302.6	276.8	260.2	249.0	243.3	237.1	236.6
52.5°	269.3	248.4	235.6	226.5	219.2	215.5	215.6
55°	226.3	209.8	200.8	193.8	188.1	185.2	184.0
57.5°	190.7	178.3	171.7	165.3	162.9	160.7	160.1
60°	168.5	160.2	153.9	148.9	145.3	144.6	144.3
62.5°	150.2	141.4	137.1	133.2	130.6	129.5	129.1
65°	123.8	117.3	113.5	110.4	109.5	107.8	107.6
67.5°	99.8	95.9	93.4	91.3	90.0	89.9	89.9
70°	85.1	82.9	80.8	79.6	78.9	78.4	78.4
72.5°	72.5	70.9	69.1	68.5	68.4	67.9	67.7
75°	55.2	53.5	53.8	52.6	51.6	50.4	49.7
77.5°	39.2	38.0	37.7	37.6	36.8	36.7	37.0
80°	30.4	29.2	28.9	29.2	28.9	28.2	28.2
82.5°	23.1	22.1	21.8	21.7	21.5	21.7	21.3
85°	12.4	11.9	11.9	11.9	12.4	12.2	11.9
87.5°	9.7	9.8	10.2	10.1	10.2	10.1	10.3
90°	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.6	453.0	453.6	454.3	454.9	455.7	456.4



TEST NUMBER: P333023-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)