

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332725

Luminaire Tested: **S124DIW-S350D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332725
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D770U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4588.7 lumens
Efficiency: N/A
Efficacy: 150.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	19	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.2
10°-20°	156.7	3.4
20°-30°	230.7	5.0
30°-40°	268.2	5.8
40°-50°	268.2	5.8
50°-60°	234.6	5.1
60°-70°	174.2	3.8
70°-80°	99.0	2.2
80°-90°	31.4	0.7
90°-100°	33.9	0.7
100°-110°	216.4	4.7
110°-120°	414.0	9.0
120°-130°	525.6	11.5
130°-140°	562.3	12.3
140°-150°	525.8	11.5
150°-160°	424.0	9.2
160°-170°	273.5	6.0
170°-180°	94.3	2.1
0°-30°	443.1	9.7
0°-40°	711.3	15.5
0°-60°	1214.1	26.5
0°-90°	1518.7	33.1
90°-120°	664.4	14.5
90°-150°	2278.1	49.6
90°-180°	3070.0	66.9
0°-180°	4588.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	2	10	16	21	22	3
95°	41	17	16	21	22	52
105°	223	228	232	236	212	234
115°	417	419	419	420	420	410
125°	586	589	588	590	591	523
135°	727	727	730	731	733	560
145°	839	841	841	842	843	524
155°	920	920	918	921	919	424
165°	970	967	966	972	966	274
175°	992	988	989	995	986	94
180°	992	992	992	992	992	



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.3	10.6	10.8	11.1	11.4	11.6	11.8	12.0	12.2	12.4	12.6
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	9.4	9.5	9.6	9.6	9.7	10.5	11.8	13.1	14.4	15.7	16.7
95°	40.8	35.2	29.6	24.0	18.4	15.7	15.8	16.0	16.2	16.3	17.3
97.5°	86.7	90.2	93.7	97.2	100.7	93.2	74.8	56.4	38.0	19.6	19.7
100°	121.7	124.7	127.7	130.6	133.6	123.7	101.0	78.2	55.4	32.7	29.9
102.5°	160.9	163.1	165.3	167.5	169.6	169.2	166.3	163.3	160.3	157.4	127.1
105°	223.4	224.4	225.4	226.4	227.4	228.3	229.1	229.9	230.8	231.6	233.1
107.5°	281.5	282.0	282.5	283.0	283.5	284.3	285.4	286.5	287.6	288.7	289.5
110°	320.7	321.2	321.7	322.2	322.6	323.4	324.4	325.4	326.4	327.3	327.7



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.6	360.5	361.3	362.2	362.9	363.4	363.8	364.3	364.8	364.7
115°	417.2	417.7	418.2	418.6	419.1	419.3	419.1	419.0	418.8	418.6	419.0
117.5°	469.9	470.5	471.2	471.8	472.5	473.0	473.4	473.7	474.1	474.5	474.4
120°	505.5	506.2	506.8	507.5	508.1	508.4	508.2	508.1	507.9	507.7	508.1
122.5°	538.8	539.1	539.5	539.9	540.3	540.6	540.9	541.1	541.3	541.6	541.8
125°	586.4	587.1	587.7	588.4	589.0	589.2	588.9	588.6	588.2	587.9	588.4
127.5°	631.5	631.7	631.9	632.0	632.2	632.7	633.4	634.2	634.9	635.7	635.6
130°	660.6	660.8	661.0	661.1	661.3	661.6	662.1	662.6	663.1	663.6	663.8
132.5°	687.4	687.7	688.0	688.2	688.5	689.0	689.6	690.3	690.9	691.5	691.7
135°	727.4	727.3	727.1	726.9	726.8	727.0	727.7	728.3	729.0	729.7	730.0
137.5°	762.9	763.0	763.1	763.1	763.2	763.6	764.3	765.0	765.8	766.5	766.8
140°	786.1	786.4	786.7	787.1	787.4	787.7	788.1	788.4	788.7	789.1	789.5
142.5°	806.9	807.5	808.1	808.6	809.2	809.6	809.8	810.0	810.2	810.4	810.8
145°	838.8	839.3	839.8	840.3	840.8	841.0	841.0	841.0	841.0	841.0	841.2
147.5°	864.2	865.1	866.0	866.9	867.9	868.2	868.1	867.9	867.7	867.6	867.7
150°	882.6	883.2	883.9	884.6	885.2	885.5	885.3	885.1	885.0	884.8	884.8
152.5°	898.0	898.5	899.1	899.6	900.1	900.2	899.9	899.7	899.4	899.1	899.3
155°	919.7	919.9	920.0	920.2	920.4	920.2	919.7	919.2	918.7	918.2	918.9
157.5°	938.0	937.9	937.8	937.7	937.6	937.2	936.7	936.1	935.5	935.0	935.8
160°	948.6	948.1	947.7	947.2	946.7	946.3	946.2	946.0	945.8	945.7	946.7
162.5°	958.1	957.5	956.9	956.3	955.6	955.2	955.1	954.9	954.7	954.6	955.6
165°	970.2	969.3	968.5	967.7	966.9	966.5	966.5	966.5	966.5	966.5	967.8
167.5°	979.7	978.8	978.0	977.1	976.2	975.8	975.7	975.6	975.5	975.4	976.8
170°	985.0	984.0	983.0	982.0	981.1	980.6	980.8	981.0	981.1	981.3	982.6
172.5°	988.6	987.6	986.6	985.6	984.6	984.2	984.4	984.5	984.7	984.9	986.2
175°	992.4	991.4	990.5	989.5	988.5	988.1	988.2	988.4	988.6	988.7	990.2
177.5°	994.2	993.3	992.4	991.4	990.5	990.2	990.5	990.7	991.0	991.2	992.3
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	12.7	12.9	13.1	13.3	13.3	13.4	13.5	13.5
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	17.7	18.7	19.7	20.2	20.3	20.4	20.4	20.5
95°	18.3	19.3	20.3	20.9	21.0	21.2	21.4	21.5
97.5°	19.8	19.9	20.0	20.1	20.3	20.5	20.6	20.8
100°	27.1	24.2	21.4	20.1	20.3	20.5	20.6	20.8
102.5°	96.9	66.6	36.4	21.2	21.3	21.3	21.3	21.4
105°	234.6	236.0	237.5	235.3	229.4	223.4	217.5	211.6
107.5°	290.2	290.9	291.7	292.3	293.0	293.6	294.2	294.8
110°	328.0	328.3	328.7	329.1	329.6	330.1	330.6	331.1



TEST NUMBER: P332725

CATALOG NUMBER: S124DIW-S350D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	364.6	364.6	364.5	364.8	365.4	366.0	366.7	367.3
115°	419.3	419.6	420.0	420.1	420.1	420.1	420.1	420.1
117.5°	474.3	474.3	474.2	474.1	474.1	474.0	473.9	473.9
120°	508.4	508.7	509.0	509.0	508.7	508.4	508.1	507.7
122.5°	542.0	542.2	542.4	542.3	542.0	541.6	541.3	541.0
125°	588.9	589.4	589.9	590.2	590.4	590.5	590.7	590.9
127.5°	635.5	635.4	635.3	635.2	635.1	634.9	634.8	634.7
130°	663.9	664.1	664.3	664.3	664.3	664.3	664.3	664.3
132.5°	691.8	692.0	692.2	692.2	692.1	691.9	691.8	691.7
135°	730.3	730.7	731.0	731.3	731.6	732.0	732.3	732.6
137.5°	767.2	767.6	767.9	768.1	768.0	767.9	767.8	767.7
140°	790.0	790.5	791.0	791.4	791.5	791.7	791.9	792.0
142.5°	811.2	811.5	811.9	812.1	812.1	812.1	812.2	812.2
145°	841.3	841.5	841.7	841.9	842.2	842.6	842.9	843.2
147.5°	867.8	868.0	868.1	868.3	868.4	868.6	868.8	868.9
150°	884.8	884.8	884.8	884.9	885.1	885.2	885.4	885.5
152.5°	899.6	899.8	900.1	900.2	900.1	900.0	899.9	899.8
155°	919.5	920.2	920.8	920.9	920.4	919.9	919.4	919.0
157.5°	936.7	937.6	938.4	938.4	937.6	936.7	935.8	935.0
160°	947.7	948.6	949.6	949.6	948.6	947.7	946.7	945.7
162.5°	956.6	957.5	958.5	958.5	957.4	956.2	955.1	954.0
165°	969.1	970.4	971.7	971.7	970.2	968.7	967.2	965.7
167.5°	978.3	979.7	981.2	981.1	979.4	977.8	976.1	974.5
170°	983.9	985.3	986.6	986.4	984.8	983.1	981.5	979.8
172.5°	987.5	988.8	990.1	989.9	988.1	986.4	984.6	982.8
175°	991.7	993.2	994.7	994.4	992.4	990.5	988.5	986.5
177.5°	993.4	994.4	995.5	995.2	993.6	992.0	990.5	988.9
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4

(END OF REPORT)