

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333025-840

Luminaire Tested: **S124RDIW-S350D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333025-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1050U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5677.9 lumens  
Efficiency: N/A  
Efficacy: 149.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14	10
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	1.0
10°-20°	163.5	2.9
20°-30°	236.1	4.2
30°-40°	267.7	4.7
40°-50°	258.5	4.6
50°-60°	214.9	3.8
60°-70°	148.4	2.6
70°-80°	75.2	1.3
80°-90°	23.2	0.4
90°-100°	46.8	0.8
100°-110°	298.3	5.3
110°-120°	570.7	10.1
120°-130°	724.4	12.8
130°-140°	775.1	13.7
140°-150°	724.8	12.8
150°-160°	584.5	10.3
160°-170°	377.0	6.6
170°-180°	129.9	2.3
0°-30°	458.3	8.1
0°-40°	726.0	12.8
0°-60°	1199.4	21.1
0°-90°	1446.3	25.5
90°-120°	915.8	16.1
90°-150°	3140.1	55.3
90°-180°	4232.0	74.5
0°-180°	5677.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	3	14	22	28	31	4
95°	56	23	22	28	30	72
105°	308	314	319	326	292	322
115°	575	578	577	579	579	566
125°	808	812	810	813	814	721
135°	1003	1002	1006	1008	1010	772
145°	1156	1159	1159	1160	1162	722
155°	1268	1268	1266	1269	1267	584
165°	1337	1332	1332	1339	1331	378
175°	1368	1362	1363	1371	1360	130
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.4	9.2	9.1	8.9	8.7	8.8	9.0	9.3	9.6	9.9	10.0
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	12.9	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0
95°	56.2	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8
97.5°	119.5	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2
100°	167.8	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2
102.5°	221.9	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2
105°	308.0	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2
107.5°	388.0	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0
110°	442.0	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7



TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	494.4	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7
115°	575.0	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5
117.5°	647.6	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9
120°	696.8	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3
122.5°	742.7	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8
125°	808.3	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0
127.5°	870.5	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2
130°	910.6	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9
132.5°	947.5	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4
135°	1002.7	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2
137.5°	1051.6	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0
140°	1083.6	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3
142.5°	1112.2	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6
145°	1156.2	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5
147.5°	1191.1	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1
150°	1216.6	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6
152.5°	1237.8	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6
155°	1267.7	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6
157.5°	1292.9	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0
160°	1307.6	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8
162.5°	1320.7	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2
165°	1337.3	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0
167.5°	1350.4	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5
170°	1357.8	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4
172.5°	1362.6	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4
175°	1368.0	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9
177.5°	1370.4	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	10.2	10.4	10.6	10.8	11.0	11.1	11.3	11.5
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	24.4	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	25.2	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.3	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	37.3	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	133.5	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	323.4	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	400.0	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.1	452.6	453.0	453.6	454.3	454.9	455.7	456.4





TEST NUMBER: P333025-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	502.6	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	577.9	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.1	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	811.7	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	876.0	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.1	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.6	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1006.7	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1057.5	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.0	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.1	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.7	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.3	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.0	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1267.5	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1318.5	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1335.8	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1348.5	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1356.2	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1361.2	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1367.0	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1369.3	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)