

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332757

Luminaire Tested: **S124DIW-S575D1050U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332757  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1050U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6785.6 lumens  
Efficiency: N/A  
Efficacy: 150.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	39	34	38	32	29	30	26	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7582	7582	7582	7582
5°	8930	7602	6710	7602
10°	10691	7569	6041	7569
15°	12649	7492	5548	7492
20°	14086	7414	5107	7414
25°	14313	7299	4804	7299
30°	12179	7189	4708	7189
35°	9363	7009	4709	7009
40°	7299	6798	4797	6798
45°	6085	6481	4877	6481
50°	5355	6094	5043	6094
55°	4906	5630	5246	5630
60°	4598	5214	5491	5214
65°	4281	4749	5692	4749
70°	3911	4289	5823	4289
75°	3497	3774	5752	3774
80°	2929	3092	5570	3092
85°	2158	2232	5335	2232



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	1.3
10°-20°	282.0	4.2
20°-30°	447.2	6.6
30°-40°	497.7	7.3
40°-50°	453.1	6.7
50°-60°	370.2	5.5
60°-70°	264.3	3.9
70°-80°	145.5	2.1
80°-90°	43.6	0.6
90°-100°	46.3	0.7
100°-110°	295.4	4.4
110°-120°	565.1	8.3
120°-130°	717.4	10.6
130°-140°	767.5	11.3
140°-150°	717.7	10.6
150°-160°	578.8	8.5
160°-170°	373.3	5.5
170°-180°	128.7	1.9
0°-30°	820.8	12.1
0°-40°	1318.5	19.4
0°-60°	2141.8	31.6
0°-90°	2595.3	38.2
90°-120°	906.8	13.4
90°-150°	3109.5	45.8
90°-180°	4190.0	61.7
0°-180°	6785.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	1102	938	828	938	1102	112
15°	1514	896	664	896	1514	428
25°	1607	819	539	819	1607	708
35°	950	711	478	711	950	603
45°	533	568	427	568	533	420
55°	349	400	373	400	349	315
65°	224	249	298	249	224	222
75°	112	121	184	121	112	119
85°	23	24	58	24	23	29
90°	30	3	30	3	30	14
95°	29	56	29	56	29	23
105°	289	305	289	305	289	252
115°	574	569	574	569	574	568
125°	806	800	806	800	806	718
135°	1000	993	1000	993	1000	770
145°	1151	1145	1151	1145	1151	719
155°	1254	1255	1254	1255	1254	578
165°	1318	1324	1318	1324	1318	372
175°	1346	1355	1346	1355	1346	128
180°	1355	1355	1355	1355	1355	



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	999.6	999.3	996.2	995.6	993.4	990.6	990.0	985.0	975.0	970.4	969.1
5°	1101.9	1109.7	1099.5	1097.6	1096.4	1083.6	1077.0	1069.2	1051.3	1040.8	1032.6
7.5°	1223.9	1224.8	1220.4	1216.8	1206.9	1195.7	1178.9	1161.0	1139.7	1117.5	1100.8
10°	1304.2	1307.3	1302.3	1301.5	1281.6	1269.2	1244.3	1223.3	1199.1	1172.3	1147.8
12.5°	1388.9	1384.5	1381.9	1365.3	1361.6	1338.9	1310.0	1288.3	1251.1	1220.2	1187.6
15°	1513.5	1505.0	1499.5	1476.6	1465.3	1433.8	1403.0	1379.3	1330.7	1284.4	1249.3
17.5°	1586.7	1595.2	1582.6	1573.2	1544.0	1521.9	1490.5	1440.7	1402.6	1345.1	1300.9
20°	1639.6	1640.4	1633.4	1623.6	1600.7	1572.7	1538.4	1484.0	1438.4	1381.2	1320.5
22.5°	1653.9	1654.1	1651.1	1642.0	1624.6	1601.9	1567.4	1521.9	1466.8	1404.6	1343.9
25°	1606.9	1605.4	1608.9	1619.0	1612.4	1605.4	1585.5	1551.7	1500.3	1434.5	1369.2
27.5°	1432.3	1443.0	1462.8	1487.7	1511.7	1529.9	1535.1	1528.2	1496.3	1442.2	1373.8
30°	1306.5	1319.8	1334.5	1359.5	1407.7	1435.3	1465.7	1488.6	1475.8	1432.6	1368.8
32.5°	1168.3	1171.6	1193.5	1221.9	1266.1	1319.2	1367.3	1413.9	1429.4	1406.8	1353.5
35°	950.1	955.6	979.3	1007.3	1061.4	1126.4	1198.8	1263.3	1316.7	1338.1	1310.8
37.5°	775.4	791.0	807.7	837.8	885.5	944.0	1019.2	1102.7	1182.2	1235.4	1244.4
40°	692.6	702.3	714.4	737.3	777.8	835.4	899.9	995.7	1080.1	1156.4	1181.3
42.5°	627.2	632.9	640.3	661.0	691.9	749.1	808.1	892.3	977.1	1068.3	1110.0
45°	533.0	538.9	551.3	563.4	586.7	626.4	681.3	750.5	835.7	923.7	1000.7
47.5°	465.0	468.8	476.2	489.1	508.9	535.1	579.7	637.5	716.5	801.9	884.0
50°	426.4	429.5	435.4	447.1	462.2	485.6	522.1	576.2	638.1	724.1	804.6
52.5°	395.9	397.2	401.5	409.4	421.5	441.1	471.1	515.8	573.4	650.0	730.2
55°	348.6	350.2	354.1	359.9	370.4	382.9	405.8	439.3	489.5	556.0	625.6
57.5°	309.7	310.8	314.1	316.3	325.0	335.1	352.7	376.6	414.7	471.1	533.3
60°	284.8	284.0	287.9	289.9	295.7	304.3	317.9	340.8	373.9	419.4	476.6
62.5°	260.5	259.4	262.7	265.3	268.6	275.9	287.1	305.0	331.9	373.1	422.5
65°	224.1	222.6	224.5	227.6	230.7	234.6	242.8	258.7	280.1	309.7	347.4
67.5°	187.5	189.2	189.5	191.0	192.8	198.1	203.7	215.0	230.1	253.8	285.7
70°	165.7	166.1	167.7	167.7	168.9	173.5	178.2	184.8	199.6	221.4	247.5
72.5°	144.0	145.6	145.0	146.2	147.1	150.2	153.6	159.9	172.5	188.7	210.7
75°	112.1	113.2	113.2	113.6	114.8	115.9	118.7	123.3	132.3	144.3	159.5
77.5°	81.7	81.9	82.4	83.8	83.8	85.7	87.7	91.4	95.9	104.1	113.4
80°	63.0	63.8	63.4	64.2	64.2	65.8	66.5	71.2	73.1	78.6	86.0
82.5°	46.2	47.0	46.9	48.0	48.6	48.9	50.0	51.9	53.8	58.7	61.7
85°	23.3	24.1	23.3	24.1	25.3	25.7	26.8	27.2	28.8	30.0	32.7
87.5°	12.9	13.8	13.7	13.9	14.4	14.6	14.6	14.0	15.0	15.0	15.9
90°	30.4	29.9	29.5	29.0	28.6	27.7	26.3	25.0	23.6	22.3	20.5
92.5°	28.0	27.9	27.8	27.7	27.6	26.9	25.5	24.2	22.8	21.5	19.7
95°	29.4	29.2	28.9	28.7	28.5	27.7	26.3	25.0	23.6	22.3	22.1
97.5°	28.4	28.1	27.9	27.7	27.5	27.3	27.2	27.0	26.9	26.7	51.9
100°	28.4	28.1	27.9	27.7	27.5	29.3	33.1	36.9	40.8	44.6	75.7
102.5°	29.2	29.1	29.1	29.0	29.0	49.6	90.9	132.2	173.5	214.8	218.8
105°	288.8	296.9	305.0	313.1	321.2	324.2	322.2	320.2	318.1	316.1	315.0
107.5°	402.4	401.6	400.7	399.9	399.0	398.1	397.1	396.1	395.1	394.1	392.6
110°	451.9	451.2	450.5	449.9	449.2	448.6	448.2	447.7	447.3	446.8	445.5



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	501.3	500.5	499.6	498.8	497.9	497.5	497.6	497.7	497.8	497.9	497.2
115°	573.5	573.5	573.5	573.5	573.5	573.2	572.8	572.3	571.9	571.4	571.7
117.5°	646.8	646.9	647.0	647.1	647.2	647.3	647.4	647.4	647.5	647.6	647.1
120°	693.0	693.5	693.9	694.4	694.8	694.8	694.4	693.9	693.5	693.0	693.2
122.5°	738.4	738.9	739.3	739.8	740.2	740.3	740.0	739.8	739.5	739.2	738.9
125°	806.5	806.3	806.0	805.8	805.6	805.1	804.5	803.8	803.1	802.4	802.9
127.5°	866.3	866.4	866.6	866.8	867.0	867.1	867.3	867.4	867.6	867.7	866.6
130°	906.8	906.8	906.8	906.8	906.8	906.7	906.5	906.2	906.0	905.8	905.1
132.5°	944.1	944.3	944.4	944.6	944.8	944.8	944.6	944.3	944.1	943.9	943.0
135°	1000.0	999.6	999.1	998.7	998.2	997.8	997.3	996.9	996.4	996.0	995.1
137.5°	1047.8	1048.0	1048.1	1048.2	1048.4	1048.2	1047.7	1047.2	1046.7	1046.2	1045.2
140°	1081.1	1080.8	1080.6	1080.4	1080.2	1079.7	1079.0	1078.4	1077.7	1077.0	1076.6
142.5°	1108.6	1108.6	1108.5	1108.5	1108.4	1108.2	1107.7	1107.2	1106.7	1106.2	1105.9
145°	1151.0	1150.5	1150.1	1149.6	1149.2	1148.8	1148.6	1148.4	1148.2	1147.9	1147.9
147.5°	1186.0	1185.8	1185.6	1185.4	1185.1	1184.9	1184.7	1184.6	1184.4	1184.2	1184.4
150°	1208.7	1208.5	1208.3	1208.0	1207.8	1207.7	1207.7	1207.7	1207.7	1207.7	1207.9
152.5°	1228.2	1228.3	1228.4	1228.6	1228.7	1228.6	1228.2	1227.9	1227.5	1227.2	1227.6
155°	1254.3	1255.0	1255.7	1256.3	1257.0	1256.9	1256.0	1255.1	1254.2	1253.3	1254.0
157.5°	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2	1277.0
160°	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8	1291.0
162.5°	1302.1	1303.7	1305.2	1306.7	1308.3	1308.3	1307.0	1305.6	1304.3	1302.9	1303.2
165°	1318.1	1320.2	1322.2	1324.2	1326.2	1326.4	1324.6	1322.8	1321.0	1319.2	1319.2
167.5°	1330.1	1332.4	1334.6	1336.9	1339.1	1339.2	1337.3	1335.3	1333.3	1331.3	1331.5
170°	1337.4	1339.6	1341.9	1344.1	1346.4	1346.6	1344.8	1343.0	1341.2	1339.4	1339.2
172.5°	1341.4	1343.9	1346.3	1348.7	1351.2	1351.5	1349.7	1347.9	1346.1	1344.3	1344.1
175°	1346.5	1349.2	1351.9	1354.6	1357.3	1357.7	1355.6	1353.6	1351.6	1349.6	1349.3
177.5°	1349.8	1351.9	1354.1	1356.2	1358.4	1358.8	1357.3	1355.9	1354.4	1353.0	1352.6
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	969.4	965.1	962.0	959.5	952.6	948.6	945.5	941.1	936.1	930.8	924.3
5°	1024.5	1011.2	1001.5	986.7	972.7	961.0	949.0	938.1	924.8	910.5	899.9
7.5°	1082.3	1062.6	1037.4	1015.5	990.9	969.5	950.4	930.8	910.4	890.6	872.5
10°	1119.0	1093.7	1065.7	1032.6	1001.5	973.9	948.2	923.3	899.2	875.0	854.4
12.5°	1158.5	1127.0	1085.6	1046.9	1012.1	975.1	944.1	913.6	884.5	859.2	835.1
15°	1211.6	1166.1	1118.2	1066.5	1020.6	977.4	935.0	896.4	863.8	830.3	807.0
17.5°	1244.2	1187.9	1133.2	1079.1	1023.5	969.0	923.3	878.9	837.9	804.7	775.3
20°	1265.7	1209.7	1141.6	1087.5	1021.3	965.3	912.4	863.0	820.2	784.8	754.4
22.5°	1284.4	1219.6	1151.5	1080.3	1014.5	955.0	897.1	847.4	803.7	766.4	737.3
25°	1294.5	1220.2	1146.2	1075.4	1000.7	930.3	877.8	819.4	772.7	733.4	702.3
27.5°	1295.6	1216.1	1132.5	1053.8	976.7	911.1	844.8	792.6	744.2	702.6	672.7
30°	1292.1	1209.3	1119.4	1034.2	956.8	885.5	828.0	771.2	721.7	680.5	649.4
32.5°	1281.2	1194.9	1102.6	1012.4	932.2	862.5	803.1	749.1	700.9	660.3	627.6
35°	1249.7	1164.5	1066.1	972.3	890.2	819.8	766.1	711.2	663.0	624.5	593.0
37.5°	1200.5	1123.4	1023.4	926.3	845.7	775.0	721.7	672.2	628.7	589.5	557.2
40°	1157.5	1089.8	989.4	894.9	807.7	740.4	690.6	645.1	601.9	564.9	534.2
42.5°	1108.0	1049.0	956.4	856.3	772.2	704.6	656.1	615.2	574.5	540.4	509.6
45°	1019.8	980.9	893.7	801.1	713.6	649.8	603.5	567.7	533.4	500.0	474.3
47.5°	918.3	899.0	825.6	737.7	654.6	591.7	551.6	518.5	488.5	460.1	437.5
50°	850.1	840.8	777.4	692.6	613.2	554.1	513.6	485.2	459.5	434.6	413.2
52.5°	782.9	782.6	725.4	647.7	574.3	517.3	477.2	450.6	428.4	408.1	388.9
55°	680.1	691.0	646.3	577.0	511.3	459.9	423.7	400.0	384.4	367.7	353.3
57.5°	585.7	603.8	566.9	505.9	451.0	403.7	372.2	354.4	337.8	327.7	317.2
60°	524.1	541.2	512.4	461.1	409.3	368.8	338.9	322.9	308.5	301.5	294.1
62.5°	469.3	484.6	463.2	415.6	370.7	331.8	306.5	291.2	281.5	273.8	268.9
65°	391.0	403.9	385.6	351.0	312.4	281.3	260.7	248.6	239.3	236.2	230.7
67.5°	316.1	327.8	317.9	288.5	257.6	234.0	217.9	206.3	200.8	198.0	194.2
70°	271.6	283.3	272.7	247.1	223.3	203.5	188.3	181.7	175.9	174.7	169.3
72.5°	233.9	241.9	231.3	211.3	191.0	174.2	162.5	155.6	152.5	150.4	147.5
75°	175.5	182.5	175.5	159.9	145.5	133.8	123.7	121.0	117.5	116.3	114.4
77.5°	124.2	130.3	124.9	115.2	104.4	95.4	90.0	86.5	85.7	83.7	84.6
80°	94.9	98.8	93.8	87.2	78.6	72.4	68.5	66.5	64.2	63.4	65.0
82.5°	68.2	69.9	67.3	62.9	56.5	52.4	49.8	47.5	47.1	47.2	47.2
85°	35.4	35.0	34.6	30.7	28.8	26.1	24.5	24.1	23.7	24.5	25.3
87.5°	15.6	15.5	14.8	13.2	11.7	10.3	9.5	8.7	9.5	10.3	11.1
90°	18.7	16.9	15.1	12.9	10.5	8.0	5.5	3.0	5.5	8.0	10.5
92.5°	17.9	16.1	14.3	13.3	13.2	13.0	12.9	12.8	12.9	13.0	13.2
95°	21.8	21.6	21.4	25.1	32.8	40.4	48.1	55.7	48.1	40.4	32.8
97.5°	77.0	102.1	127.3	137.4	132.7	127.9	123.1	118.3	123.1	127.9	132.7
100°	106.7	137.8	168.9	182.4	178.3	174.3	170.2	166.2	170.2	174.3	178.3
102.5°	222.9	227.0	231.0	231.5	228.6	225.6	222.6	219.7	222.6	225.6	228.6
105°	313.9	312.7	311.6	310.4	309.0	307.7	306.3	305.0	306.3	307.7	309.0
107.5°	391.1	389.5	388.0	386.9	386.2	385.5	384.9	384.2	384.9	385.5	386.2
110°	444.1	442.8	441.4	440.4	439.7	439.0	438.4	437.7	438.4	439.0	439.7





TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.6	496.0	495.4	494.4	493.2	492.0	490.8	489.6	490.8	492.0	493.2
115°	571.9	572.1	572.3	572.1	571.4	570.8	570.1	569.4	570.1	570.8	571.4
117.5°	646.6	646.1	645.6	644.9	644.0	643.1	642.2	641.3	642.2	643.1	644.0
120°	693.5	693.7	693.9	693.6	692.7	691.8	690.9	690.0	690.9	691.8	692.7
122.5°	738.6	738.3	738.0	737.5	737.0	736.4	735.9	735.4	735.9	736.4	737.0
125°	803.3	803.8	804.2	804.0	803.1	802.2	801.3	800.4	801.3	802.2	803.1
127.5°	865.6	864.6	863.5	862.9	862.7	862.5	862.2	862.0	862.2	862.5	862.7
130°	904.4	903.8	903.1	902.6	902.4	902.2	902.0	901.7	902.0	902.2	902.4
132.5°	942.2	941.3	940.5	939.8	939.4	939.0	938.6	938.2	938.6	939.0	939.4
135°	994.2	993.3	992.4	992.0	992.2	992.5	992.7	992.9	992.7	992.5	992.2
137.5°	1044.2	1043.2	1042.2	1041.7	1041.6	1041.5	1041.4	1041.3	1041.4	1041.5	1041.6
140°	1076.1	1075.7	1075.2	1074.8	1074.3	1073.9	1073.4	1073.0	1073.4	1073.9	1074.3
142.5°	1105.6	1105.4	1105.1	1104.6	1103.8	1102.9	1102.1	1101.3	1102.1	1102.9	1103.8
145°	1147.9	1147.9	1147.9	1147.6	1146.9	1146.2	1145.6	1144.9	1145.6	1146.2	1146.9
147.5°	1184.7	1184.9	1185.1	1184.6	1183.3	1182.1	1180.8	1179.5	1180.8	1182.1	1183.3
150°	1208.2	1208.4	1208.6	1208.3	1207.4	1206.5	1205.6	1204.7	1205.6	1206.5	1207.4
152.5°	1228.0	1228.4	1228.8	1228.6	1227.9	1227.2	1226.5	1225.7	1226.5	1227.2	1227.9
155°	1254.7	1255.3	1256.0	1256.2	1256.0	1255.8	1255.6	1255.3	1255.6	1255.8	1256.0
157.5°	1277.7	1278.5	1279.3	1279.7	1279.8	1280.0	1280.1	1280.3	1280.1	1280.0	1279.8
160°	1291.2	1291.5	1291.7	1292.1	1292.8	1293.5	1294.2	1294.8	1294.2	1293.5	1292.8
162.5°	1303.4	1303.6	1303.8	1304.4	1305.2	1306.1	1307.0	1307.8	1307.0	1306.1	1305.2
165°	1319.2	1319.2	1319.2	1319.7	1320.8	1322.0	1323.1	1324.2	1323.1	1322.0	1320.8
167.5°	1331.6	1331.7	1331.9	1332.5	1333.7	1334.9	1336.0	1337.2	1336.0	1334.9	1333.7
170°	1339.0	1338.7	1338.5	1339.1	1340.4	1341.8	1343.1	1344.5	1343.1	1341.8	1340.4
172.5°	1343.8	1343.6	1343.4	1343.9	1345.3	1346.6	1348.0	1349.3	1348.0	1346.6	1345.3
175°	1349.1	1348.9	1348.7	1349.2	1350.6	1351.9	1353.3	1354.6	1353.3	1351.9	1350.6
177.5°	1352.3	1351.9	1351.6	1352.0	1353.3	1354.5	1355.8	1357.0	1355.8	1354.5	1353.3
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	921.2	918.4	914.3	908.7	904.1	899.1	897.8	896.0	899.7	896.6	895.7
5°	891.0	882.8	872.3	860.3	853.3	843.1	841.2	837.3	833.4	833.0	829.1
7.5°	859.0	847.0	833.3	821.0	809.6	798.6	791.3	789.8	784.0	780.7	776.8
10°	838.5	823.7	807.7	796.1	782.8	771.2	763.0	758.3	754.4	750.1	746.3
12.5°	814.2	798.5	785.3	772.7	757.0	748.1	734.7	726.6	725.8	725.9	715.8
15°	785.9	770.4	750.1	732.3	723.7	706.6	699.2	689.8	684.0	678.2	673.5
17.5°	753.7	734.3	718.5	697.9	681.6	668.0	658.2	652.6	643.9	635.6	629.6
20°	733.4	712.8	696.1	674.3	656.4	639.7	631.5	623.7	617.1	610.1	603.5
22.5°	712.9	691.3	670.9	649.7	633.0	615.4	607.5	596.9	590.6	586.7	580.1
25°	680.5	657.2	633.8	613.6	596.5	580.9	570.4	562.2	555.2	552.1	547.8
27.5°	645.3	622.1	599.6	576.6	557.2	545.9	537.5	531.3	527.3	523.2	521.2
30°	622.9	598.8	574.7	553.3	535.4	524.1	516.3	512.0	508.9	507.0	505.0
32.5°	600.2	576.4	551.0	531.5	515.5	505.4	499.5	495.2	493.7	493.0	492.3
35°	563.8	539.7	516.3	498.8	483.6	479.7	474.7	472.3	471.6	474.3	475.5
37.5°	528.5	506.1	484.6	467.7	457.7	452.0	450.3	450.4	453.2	455.6	458.4
40°	505.8	484.0	463.8	449.0	439.7	436.2	435.4	437.3	440.4	443.2	446.3
42.5°	483.7	462.2	443.9	430.0	423.5	420.3	420.8	422.7	427.1	430.4	435.1
45°	449.4	431.5	413.6	402.3	396.9	397.6	397.6	401.1	405.4	410.5	415.5
47.5°	417.1	399.0	384.3	374.8	372.0	371.3	373.5	378.1	384.3	390.5	397.6
50°	395.3	378.2	365.3	356.8	353.7	354.8	358.0	362.2	369.6	377.4	384.8
52.5°	373.2	357.6	345.7	337.8	335.6	337.7	340.8	347.6	354.1	362.5	371.4
55°	338.9	325.7	316.3	310.5	309.7	310.9	314.4	321.8	331.1	341.6	350.2
57.5°	304.7	293.7	285.1	281.1	281.5	282.6	288.3	297.1	307.1	318.3	329.3
60°	281.7	271.6	264.6	261.5	261.9	264.2	271.2	279.4	291.8	302.7	314.4
62.5°	259.9	251.0	244.3	241.5	241.0	246.1	252.8	261.3	273.8	285.9	298.5
65°	224.9	217.9	212.4	210.9	212.0	215.9	224.5	235.8	246.3	259.1	272.4
67.5°	190.6	184.9	181.2	181.9	183.3	189.0	196.2	205.9	217.8	231.1	244.2
70°	168.9	163.4	160.3	160.7	163.0	170.0	176.3	186.0	198.8	212.4	223.3
72.5°	146.5	142.9	140.1	141.7	144.0	148.9	156.6	166.4	177.7	190.3	201.9
75°	112.4	112.4	110.9	112.1	115.6	120.2	126.1	136.2	147.5	157.6	166.9
77.5°	83.4	82.6	83.6	85.0	87.0	92.5	99.2	106.5	114.9	125.1	132.8
80°	63.8	64.2	66.1	68.5	69.3	73.5	80.5	87.2	93.8	102.3	109.7
82.5°	47.9	48.3	49.3	52.3	53.1	57.7	62.2	68.8	74.8	80.5	86.7
85°	26.1	26.1	28.0	29.2	31.1	34.2	37.0	40.9	46.3	50.2	56.0
87.5°	12.5	13.0	14.6	15.6	16.9	18.8	19.7	23.4	24.9	26.7	29.7
90°	12.9	15.1	16.9	18.7	20.5	22.3	23.6	25.0	26.3	27.7	28.6
92.5°	13.3	14.3	16.1	17.9	19.7	21.5	22.8	24.2	25.5	26.9	27.6
95°	25.1	21.4	21.6	21.8	22.1	22.3	23.6	25.0	26.3	27.7	28.5
97.5°	137.4	127.3	102.1	77.0	51.9	26.7	26.9	27.0	27.2	27.3	27.5
100°	182.4	168.9	137.8	106.7	75.7	44.6	40.8	36.9	33.1	29.3	27.5
102.5°	231.5	231.0	227.0	222.9	218.8	214.8	173.5	132.2	90.9	49.6	29.0
105°	310.4	311.6	312.7	313.9	315.0	316.1	318.1	320.2	322.2	324.2	321.2
107.5°	386.9	388.0	389.5	391.1	392.6	394.1	395.1	396.1	397.1	398.1	399.0
110°	440.4	441.4	442.8	444.1	445.5	446.8	447.3	447.7	448.2	448.6	449.2



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	494.4	495.4	496.0	496.6	497.2	497.9	497.8	497.7	497.6	497.5	497.9
115°	572.1	572.3	572.1	571.9	571.7	571.4	571.9	572.3	572.8	573.2	573.5
117.5°	644.9	645.6	646.1	646.6	647.1	647.6	647.5	647.4	647.4	647.3	647.2
120°	693.6	693.9	693.7	693.5	693.2	693.0	693.5	693.9	694.4	694.8	694.8
122.5°	737.5	738.0	738.3	738.6	738.9	739.2	739.5	739.8	740.0	740.3	740.2
125°	804.0	804.2	803.8	803.3	802.9	802.4	803.1	803.8	804.5	805.1	805.6
127.5°	862.9	863.5	864.6	865.6	866.6	867.7	867.6	867.4	867.3	867.1	867.0
130°	902.6	903.1	903.8	904.4	905.1	905.8	906.0	906.2	906.5	906.7	906.8
132.5°	939.8	940.5	941.3	942.2	943.0	943.9	944.1	944.3	944.6	944.8	944.8
135°	992.0	992.4	993.3	994.2	995.1	996.0	996.4	996.9	997.3	997.8	998.2
137.5°	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7	1047.2	1047.7	1048.2	1048.4
140°	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7	1078.4	1079.0	1079.7	1080.2
142.5°	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7	1107.2	1107.7	1108.2	1108.4
145°	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2	1148.4	1148.6	1148.8	1149.2
147.5°	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4	1184.6	1184.7	1184.9	1185.1
150°	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7	1207.7	1207.7	1207.7	1207.8
152.5°	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5	1227.9	1228.2	1228.6	1228.7
155°	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2	1255.1	1256.0	1256.9	1257.0
157.5°	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9
160°	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2
162.5°	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3	1305.6	1307.0	1308.3	1308.3
165°	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0	1322.8	1324.6	1326.4	1326.2
167.5°	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3	1335.3	1337.3	1339.2	1339.1
170°	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2	1343.0	1344.8	1346.6	1346.4
172.5°	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1	1347.9	1349.7	1351.5	1351.2
175°	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6	1353.6	1355.6	1357.7	1357.3
177.5°	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4	1355.9	1357.3	1358.8	1358.4
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	895.0	894.4	892.2	891.9	892.2	894.4	895.0	895.7	896.6	899.7	896.0
5°	826.8	824.9	823.7	828.0	823.7	824.9	826.8	829.1	833.0	833.4	837.3
7.5°	775.4	773.8	770.4	769.3	770.4	773.8	775.4	776.8	780.7	784.0	789.8
10°	742.4	740.8	737.7	736.9	737.7	740.8	742.4	746.3	750.1	754.4	758.3
12.5°	710.6	707.5	706.9	707.7	706.9	707.5	710.6	715.8	725.9	725.8	726.6
15°	668.4	666.9	662.6	663.8	662.6	666.9	668.4	673.5	678.2	684.0	689.8
17.5°	626.9	625.0	619.8	624.4	619.8	625.0	626.9	629.6	635.6	643.9	652.6
20°	600.7	597.6	594.9	594.5	594.9	597.6	600.7	603.5	610.1	617.1	623.7
22.5°	575.8	573.0	572.8	570.2	572.8	573.0	575.8	580.1	586.7	590.6	596.9
25°	544.7	542.0	541.2	539.3	541.2	542.0	544.7	547.8	552.1	555.2	562.2
27.5°	520.8	519.5	518.1	518.7	518.1	519.5	520.8	521.2	523.2	527.3	531.3
30°	506.2	505.8	505.0	505.0	505.0	505.8	506.2	505.0	507.0	508.9	512.0
32.5°	494.1	494.0	494.4	494.4	494.4	494.0	494.1	492.3	493.0	493.7	495.2
35°	477.0	478.2	479.0	477.8	479.0	478.2	477.0	475.5	474.3	471.6	472.3
37.5°	461.6	462.8	463.9	465.2	463.9	462.8	461.6	458.4	455.6	453.2	450.4
40°	449.8	452.5	453.3	455.2	453.3	452.5	449.8	446.3	443.2	440.4	437.3
42.5°	438.6	441.6	443.6	444.0	443.6	441.6	438.6	435.1	430.4	427.1	422.7
45°	421.4	424.5	427.2	427.2	427.2	424.5	421.4	415.5	410.5	405.4	401.1
47.5°	403.6	408.1	410.8	411.5	410.8	408.1	403.6	397.6	390.5	384.3	378.1
50°	391.4	396.9	399.6	401.5	399.6	396.9	391.4	384.8	377.4	369.6	362.2
52.5°	379.6	385.0	388.7	389.7	388.7	385.0	379.6	371.4	362.5	354.1	347.6
55°	359.1	366.9	371.2	372.7	371.2	366.9	359.1	350.2	341.6	331.1	321.8
57.5°	339.8	347.0	352.0	353.1	352.0	347.0	339.8	329.3	318.3	307.1	297.1
60°	324.9	332.7	338.9	340.1	338.9	332.7	324.9	314.4	302.7	291.8	279.4
62.5°	309.6	317.7	323.3	326.4	323.3	317.7	309.6	298.5	285.9	273.8	261.3
65°	283.3	291.4	296.9	298.0	296.9	291.4	283.3	272.4	259.1	246.3	235.8
67.5°	254.5	262.6	266.2	268.5	266.2	262.6	254.5	244.2	231.1	217.8	205.9
70°	234.2	240.8	244.7	246.7	244.7	240.8	234.2	223.3	212.4	198.8	186.0
72.5°	211.2	218.1	222.6	223.0	222.6	218.1	211.2	201.9	190.3	177.7	166.4
75°	175.9	182.1	184.4	184.4	184.4	182.1	175.9	166.9	157.6	147.5	136.2
77.5°	139.2	142.4	145.4	146.0	145.4	142.4	139.2	132.8	125.1	114.9	106.5
80°	115.6	117.5	119.8	119.8	119.8	117.5	115.6	109.7	102.3	93.8	87.2
82.5°	91.3	92.9	95.2	94.9	95.2	92.9	91.3	86.7	80.5	74.8	68.8
85°	55.2	58.8	58.4	57.6	58.4	58.8	55.2	56.0	50.2	46.3	40.9
87.5°	30.7	31.1	32.1	32.8	32.1	31.1	30.7	29.7	26.7	24.9	23.4
90°	29.0	29.5	29.9	30.4	29.9	29.5	29.0	28.6	27.7	26.3	25.0
92.5°	27.7	27.8	27.9	28.0	27.9	27.8	27.7	27.6	26.9	25.5	24.2
95°	28.7	28.9	29.2	29.4	29.2	28.9	28.7	28.5	27.7	26.3	25.0
97.5°	27.7	27.9	28.1	28.4	28.1	27.9	27.7	27.5	27.3	27.2	27.0
100°	27.7	27.9	28.1	28.4	28.1	27.9	27.7	27.5	29.3	33.1	36.9
102.5°	29.0	29.1	29.1	29.2	29.1	29.1	29.0	29.0	49.6	90.9	132.2
105°	313.1	305.0	296.9	288.8	296.9	305.0	313.1	321.2	324.2	322.2	320.2
107.5°	399.9	400.7	401.6	402.4	401.6	400.7	399.9	399.0	398.1	397.1	396.1
110°	449.9	450.5	451.2	451.9	451.2	450.5	449.9	449.2	448.6	448.2	447.7



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	498.8	499.6	500.5	501.3	500.5	499.6	498.8	497.9	497.5	497.6	497.7
115°	573.5	573.5	573.5	573.5	573.5	573.5	573.5	573.5	573.2	572.8	572.3
117.5°	647.1	647.0	646.9	646.8	646.9	647.0	647.1	647.2	647.3	647.4	647.4
120°	694.4	693.9	693.5	693.0	693.5	693.9	694.4	694.8	694.8	694.4	693.9
122.5°	739.8	739.3	738.9	738.4	738.9	739.3	739.8	740.2	740.3	740.0	739.8
125°	805.8	806.0	806.3	806.5	806.3	806.0	805.8	805.6	805.1	804.5	803.8
127.5°	866.8	866.6	866.4	866.3	866.4	866.6	866.8	867.0	867.1	867.3	867.4
130°	906.8	906.8	906.8	906.8	906.8	906.8	906.8	906.8	906.7	906.5	906.2
132.5°	944.6	944.4	944.3	944.1	944.3	944.4	944.6	944.8	944.8	944.6	944.3
135°	998.7	999.1	999.6	1000.0	999.6	999.1	998.7	998.2	997.8	997.3	996.9
137.5°	1048.2	1048.1	1048.0	1047.8	1048.0	1048.1	1048.2	1048.4	1048.2	1047.7	1047.2
140°	1080.4	1080.6	1080.8	1081.1	1080.8	1080.6	1080.4	1080.2	1079.7	1079.0	1078.4
142.5°	1108.5	1108.5	1108.6	1108.6	1108.6	1108.5	1108.5	1108.4	1108.2	1107.7	1107.2
145°	1149.6	1150.1	1150.5	1151.0	1150.5	1150.1	1149.6	1149.2	1148.8	1148.6	1148.4
147.5°	1185.4	1185.6	1185.8	1186.0	1185.8	1185.6	1185.4	1185.1	1184.9	1184.7	1184.6
150°	1208.0	1208.3	1208.5	1208.7	1208.5	1208.3	1208.0	1207.8	1207.7	1207.7	1207.7
152.5°	1228.6	1228.4	1228.3	1228.2	1228.3	1228.4	1228.6	1228.7	1228.6	1228.2	1227.9
155°	1256.3	1255.7	1255.0	1254.3	1255.0	1255.7	1256.3	1257.0	1256.9	1256.0	1255.1
157.5°	1279.7	1278.5	1277.4	1276.2	1277.4	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5
160°	1294.8	1293.5	1292.1	1290.8	1292.1	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5
162.5°	1306.7	1305.2	1303.7	1302.1	1303.7	1305.2	1306.7	1308.3	1308.3	1307.0	1305.6
165°	1324.2	1322.2	1320.2	1318.1	1320.2	1322.2	1324.2	1326.2	1326.4	1324.6	1322.8
167.5°	1336.9	1334.6	1332.4	1330.1	1332.4	1334.6	1336.9	1339.1	1339.2	1337.3	1335.3
170°	1344.1	1341.9	1339.6	1337.4	1339.6	1341.9	1344.1	1346.4	1346.6	1344.8	1343.0
172.5°	1348.7	1346.3	1343.9	1341.4	1343.9	1346.3	1348.7	1351.2	1351.5	1349.7	1347.9
175°	1354.6	1351.9	1349.2	1346.5	1349.2	1351.9	1354.6	1357.3	1357.7	1355.6	1353.6
177.5°	1356.2	1354.1	1351.9	1349.8	1351.9	1354.1	1356.2	1358.4	1358.8	1357.3	1355.9
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	897.8	899.1	904.1	908.7	914.3	918.4	921.2	924.3	930.8	936.1	941.1
5°	841.2	843.1	853.3	860.3	872.3	882.8	891.0	899.9	910.5	924.8	938.1
7.5°	791.3	798.6	809.6	821.0	833.3	847.0	859.0	872.5	890.6	910.4	930.8
10°	763.0	771.2	782.8	796.1	807.7	823.7	838.5	854.4	875.0	899.2	923.3
12.5°	734.7	748.1	757.0	772.7	785.3	798.5	814.2	835.1	859.2	884.5	913.6
15°	699.2	706.6	723.7	732.3	750.1	770.4	785.9	807.0	830.3	863.8	896.4
17.5°	658.2	668.0	681.6	697.9	718.5	734.3	753.7	775.3	804.7	837.9	878.9
20°	631.5	639.7	656.4	674.3	696.1	712.8	733.4	754.4	784.8	820.2	863.0
22.5°	607.5	615.4	633.0	649.7	670.9	691.3	712.9	737.3	766.4	803.7	847.4
25°	570.4	580.9	596.5	613.6	633.8	657.2	680.5	702.3	733.4	772.7	819.4
27.5°	537.5	545.9	557.2	576.6	599.6	622.1	645.3	672.7	702.6	744.2	792.6
30°	516.3	524.1	535.4	553.3	574.7	598.8	622.9	649.4	680.5	721.7	771.2
32.5°	499.5	505.4	515.5	531.5	551.0	576.4	600.2	627.6	660.3	700.9	749.1
35°	474.7	479.7	483.6	498.8	516.3	539.7	563.8	593.0	624.5	663.0	711.2
37.5°	450.3	452.0	457.7	467.7	484.6	506.1	528.5	557.2	589.5	628.7	672.2
40°	435.4	436.2	439.7	449.0	463.8	484.0	505.8	534.2	564.9	601.9	645.1
42.5°	420.8	420.3	423.5	430.0	443.9	462.2	483.7	509.6	540.4	574.5	615.2
45°	397.6	397.6	396.9	402.3	413.6	431.5	449.4	474.3	500.0	533.4	567.7
47.5°	373.5	371.3	372.0	374.8	384.3	399.0	417.1	437.5	460.1	488.5	518.5
50°	358.0	354.8	353.7	356.8	365.3	378.2	395.3	413.2	434.6	459.5	485.2
52.5°	340.8	337.7	335.6	337.8	345.7	357.6	373.2	388.9	408.1	428.4	450.6
55°	314.4	310.9	309.7	310.5	316.3	325.7	338.9	353.3	367.7	384.4	400.0
57.5°	288.3	282.6	281.5	281.1	285.1	293.7	304.7	317.2	327.7	337.8	354.4
60°	271.2	264.2	261.9	261.5	264.6	271.6	281.7	294.1	301.5	308.5	322.9
62.5°	252.8	246.1	241.0	241.5	244.3	251.0	259.9	268.9	273.8	281.5	291.2
65°	224.5	215.9	212.0	210.9	212.4	217.9	224.9	230.7	236.2	239.3	248.6
67.5°	196.2	189.0	183.3	181.9	181.2	184.9	190.6	194.2	198.0	200.8	206.3
70°	176.3	170.0	163.0	160.7	160.3	163.4	168.9	169.3	174.7	175.9	181.7
72.5°	156.6	148.9	144.0	141.7	140.1	142.9	146.5	147.5	150.4	152.5	155.6
75°	126.1	120.2	115.6	112.1	110.9	112.4	112.4	114.4	116.3	117.5	121.0
77.5°	99.2	92.5	87.0	85.0	83.6	82.6	83.4	84.6	83.7	85.7	86.5
80°	80.5	73.5	69.3	68.5	66.1	64.2	63.8	65.0	63.4	64.2	66.5
82.5°	62.2	57.7	53.1	52.3	49.3	48.3	47.9	47.2	47.2	47.1	47.5
85°	37.0	34.2	31.1	29.2	28.0	26.1	26.1	25.3	24.5	23.7	24.1
87.5°	19.7	18.8	16.9	15.6	14.6	13.0	12.5	11.1	10.3	9.5	8.7
90°	23.6	22.3	20.5	18.7	16.9	15.1	12.9	10.5	8.0	5.5	3.0
92.5°	22.8	21.5	19.7	17.9	16.1	14.3	13.3	13.2	13.0	12.9	12.8
95°	23.6	22.3	22.1	21.8	21.6	21.4	25.1	32.8	40.4	48.1	55.7
97.5°	26.9	26.7	51.9	77.0	102.1	127.3	137.4	132.7	127.9	123.1	118.3
100°	40.8	44.6	75.7	106.7	137.8	168.9	182.4	178.3	174.3	170.2	166.2
102.5°	173.5	214.8	218.8	222.9	227.0	231.0	231.5	228.6	225.6	222.6	219.7
105°	318.1	316.1	315.0	313.9	312.7	311.6	310.4	309.0	307.7	306.3	305.0
107.5°	395.1	394.1	392.6	391.1	389.5	388.0	386.9	386.2	385.5	384.9	384.2
110°	447.3	446.8	445.5	444.1	442.8	441.4	440.4	439.7	439.0	438.4	437.7



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	497.8	497.9	497.2	496.6	496.0	495.4	494.4	493.2	492.0	490.8	489.6
115°	571.9	571.4	571.7	571.9	572.1	572.3	572.1	571.4	570.8	570.1	569.4
117.5°	647.5	647.6	647.1	646.6	646.1	645.6	644.9	644.0	643.1	642.2	641.3
120°	693.5	693.0	693.2	693.5	693.7	693.9	693.6	692.7	691.8	690.9	690.0
122.5°	739.5	739.2	738.9	738.6	738.3	738.0	737.5	737.0	736.4	735.9	735.4
125°	803.1	802.4	802.9	803.3	803.8	804.2	804.0	803.1	802.2	801.3	800.4
127.5°	867.6	867.7	866.6	865.6	864.6	863.5	862.9	862.7	862.5	862.2	862.0
130°	906.0	905.8	905.1	904.4	903.8	903.1	902.6	902.4	902.2	902.0	901.7
132.5°	944.1	943.9	943.0	942.2	941.3	940.5	939.8	939.4	939.0	938.6	938.2
135°	996.4	996.0	995.1	994.2	993.3	992.4	992.0	992.2	992.5	992.7	992.9
137.5°	1046.7	1046.2	1045.2	1044.2	1043.2	1042.2	1041.7	1041.6	1041.5	1041.4	1041.3
140°	1077.7	1077.0	1076.6	1076.1	1075.7	1075.2	1074.8	1074.3	1073.9	1073.4	1073.0
142.5°	1106.7	1106.2	1105.9	1105.6	1105.4	1105.1	1104.6	1103.8	1102.9	1102.1	1101.3
145°	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1147.6	1146.9	1146.2	1145.6	1144.9
147.5°	1184.4	1184.2	1184.4	1184.7	1184.9	1185.1	1184.6	1183.3	1182.1	1180.8	1179.5
150°	1207.7	1207.7	1207.9	1208.2	1208.4	1208.6	1208.3	1207.4	1206.5	1205.6	1204.7
152.5°	1227.5	1227.2	1227.6	1228.0	1228.4	1228.8	1228.6	1227.9	1227.2	1226.5	1225.7
155°	1254.2	1253.3	1254.0	1254.7	1255.3	1256.0	1256.2	1256.0	1255.8	1255.6	1255.3
157.5°	1277.4	1276.2	1277.0	1277.7	1278.5	1279.3	1279.7	1279.8	1280.0	1280.1	1280.3
160°	1292.1	1290.8	1291.0	1291.2	1291.5	1291.7	1292.1	1292.8	1293.5	1294.2	1294.8
162.5°	1304.3	1302.9	1303.2	1303.4	1303.6	1303.8	1304.4	1305.2	1306.1	1307.0	1307.8
165°	1321.0	1319.2	1319.2	1319.2	1319.2	1319.2	1319.7	1320.8	1322.0	1323.1	1324.2
167.5°	1333.3	1331.3	1331.5	1331.6	1331.7	1331.9	1332.5	1333.7	1334.9	1336.0	1337.2
170°	1341.2	1339.4	1339.2	1339.0	1338.7	1338.5	1339.1	1340.4	1341.8	1343.1	1344.5
172.5°	1346.1	1344.3	1344.1	1343.8	1343.6	1343.4	1343.9	1345.3	1346.6	1348.0	1349.3
175°	1351.6	1349.6	1349.3	1349.1	1348.9	1348.7	1349.2	1350.6	1351.9	1353.3	1354.6
177.5°	1354.4	1353.0	1352.6	1352.3	1351.9	1351.6	1352.0	1353.3	1354.5	1355.8	1357.0
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	945.5	948.6	952.6	959.5	962.0	965.1	969.4	969.1	970.4	975.0	985.0
5°	949.0	961.0	972.7	986.7	1001.5	1011.2	1024.5	1032.6	1040.8	1051.3	1069.2
7.5°	950.4	969.5	990.9	1015.5	1037.4	1062.6	1082.3	1100.8	1117.5	1139.7	1161.0
10°	948.2	973.9	1001.5	1032.6	1065.7	1093.7	1119.0	1147.8	1172.3	1199.1	1223.3
12.5°	944.1	975.1	1012.1	1046.9	1085.6	1127.0	1158.5	1187.6	1220.2	1251.1	1288.3
15°	935.0	977.4	1020.6	1066.5	1118.2	1166.1	1211.6	1249.3	1284.4	1330.7	1379.3
17.5°	923.3	969.0	1023.5	1079.1	1133.2	1187.9	1244.2	1300.9	1345.1	1402.6	1440.7
20°	912.4	965.3	1021.3	1087.5	1141.6	1209.7	1265.7	1320.5	1381.2	1438.4	1484.0
22.5°	897.1	955.0	1014.5	1080.3	1151.5	1219.6	1284.4	1343.9	1404.6	1466.8	1521.9
25°	877.8	930.3	1000.7	1075.4	1146.2	1220.2	1294.5	1369.2	1434.5	1500.3	1551.7
27.5°	844.8	911.1	976.7	1053.8	1132.5	1216.1	1295.6	1373.8	1442.2	1496.3	1528.2
30°	828.0	885.5	956.8	1034.2	1119.4	1209.3	1292.1	1368.8	1432.6	1475.8	1488.6
32.5°	803.1	862.5	932.2	1012.4	1102.6	1194.9	1281.2	1353.5	1406.8	1429.4	1413.9
35°	766.1	819.8	890.2	972.3	1066.1	1164.5	1249.7	1310.8	1338.1	1316.7	1263.3
37.5°	721.7	775.0	845.7	926.3	1023.4	1123.4	1200.5	1244.4	1235.4	1182.2	1102.7
40°	690.6	740.4	807.7	894.9	989.4	1089.8	1157.5	1181.3	1156.4	1080.1	995.7
42.5°	656.1	704.6	772.2	856.3	956.4	1049.0	1108.0	1110.0	1068.3	977.1	892.3
45°	603.5	649.8	713.6	801.1	893.7	980.9	1019.8	1000.7	923.7	835.7	750.5
47.5°	551.6	591.7	654.6	737.7	825.6	899.0	918.3	884.0	801.9	716.5	637.5
50°	513.6	554.1	613.2	692.6	777.4	840.8	850.1	804.6	724.1	638.1	576.2
52.5°	477.2	517.3	574.3	647.7	725.4	782.6	782.9	730.2	650.0	573.4	515.8
55°	423.7	459.9	511.3	577.0	646.3	691.0	680.1	625.6	556.0	489.5	439.3
57.5°	372.2	403.7	451.0	505.9	566.9	603.8	585.7	533.3	471.1	414.7	376.6
60°	338.9	368.8	409.3	461.1	512.4	541.2	524.1	476.6	419.4	373.9	340.8
62.5°	306.5	331.8	370.7	415.6	463.2	484.6	469.3	422.5	373.1	331.9	305.0
65°	260.7	281.3	312.4	351.0	385.6	403.9	391.0	347.4	309.7	280.1	258.7
67.5°	217.9	234.0	257.6	288.5	317.9	327.8	316.1	285.7	253.8	230.1	215.0
70°	188.3	203.5	223.3	247.1	272.7	283.3	271.6	247.5	221.4	199.6	184.8
72.5°	162.5	174.2	191.0	211.3	231.3	241.9	233.9	210.7	188.7	172.5	159.9
75°	123.7	133.8	145.5	159.9	175.5	182.5	175.5	159.5	144.3	132.3	123.3
77.5°	90.0	95.4	104.4	115.2	124.9	130.3	124.2	113.4	104.1	95.9	91.4
80°	68.5	72.4	78.6	87.2	93.8	98.8	94.9	86.0	78.6	73.1	71.2
82.5°	49.8	52.4	56.5	62.9	67.3	69.9	68.2	61.7	58.7	53.8	51.9
85°	24.5	26.1	28.8	30.7	34.6	35.0	35.4	32.7	30.0	28.8	27.2
87.5°	9.5	10.3	11.7	13.2	14.8	15.5	15.6	15.9	15.0	15.0	14.0
90°	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6	25.0
92.5°	12.9	13.0	13.2	13.3	14.3	16.1	17.9	19.7	21.5	22.8	24.2
95°	48.1	40.4	32.8	25.1	21.4	21.6	21.8	22.1	22.3	23.6	25.0
97.5°	123.1	127.9	132.7	137.4	127.3	102.1	77.0	51.9	26.7	26.9	27.0
100°	170.2	174.3	178.3	182.4	168.9	137.8	106.7	75.7	44.6	40.8	36.9
102.5°	222.6	225.6	228.6	231.5	231.0	227.0	222.9	218.8	214.8	173.5	132.2
105°	306.3	307.7	309.0	310.4	311.6	312.7	313.9	315.0	316.1	318.1	320.2
107.5°	384.9	385.5	386.2	386.9	388.0	389.5	391.1	392.6	394.1	395.1	396.1
110°	438.4	439.0	439.7	440.4	441.4	442.8	444.1	445.5	446.8	447.3	447.7





TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	490.8	492.0	493.2	494.4	495.4	496.0	496.6	497.2	497.9	497.8	497.7
115°	570.1	570.8	571.4	572.1	572.3	572.1	571.9	571.7	571.4	571.9	572.3
117.5°	642.2	643.1	644.0	644.9	645.6	646.1	646.6	647.1	647.6	647.5	647.4
120°	690.9	691.8	692.7	693.6	693.9	693.7	693.5	693.2	693.0	693.5	693.9
122.5°	735.9	736.4	737.0	737.5	738.0	738.3	738.6	738.9	739.2	739.5	739.8
125°	801.3	802.2	803.1	804.0	804.2	803.8	803.3	802.9	802.4	803.1	803.8
127.5°	862.2	862.5	862.7	862.9	863.5	864.6	865.6	866.6	867.7	867.6	867.4
130°	902.0	902.2	902.4	902.6	903.1	903.8	904.4	905.1	905.8	906.0	906.2
132.5°	938.6	939.0	939.4	939.8	940.5	941.3	942.2	943.0	943.9	944.1	944.3
135°	992.7	992.5	992.2	992.0	992.4	993.3	994.2	995.1	996.0	996.4	996.9
137.5°	1041.4	1041.5	1041.6	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7	1047.2
140°	1073.4	1073.9	1074.3	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7	1078.4
142.5°	1102.1	1102.9	1103.8	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7	1107.2
145°	1145.6	1146.2	1146.9	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2	1148.4
147.5°	1180.8	1182.1	1183.3	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4	1184.6
150°	1205.6	1206.5	1207.4	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7	1207.7
152.5°	1226.5	1227.2	1227.9	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5	1227.9
155°	1255.6	1255.8	1256.0	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2	1255.1
157.5°	1280.1	1280.0	1279.8	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4	1278.5
160°	1294.2	1293.5	1292.8	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1	1293.5
162.5°	1307.0	1306.1	1305.2	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3	1305.6
165°	1323.1	1322.0	1320.8	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0	1322.8
167.5°	1336.0	1334.9	1333.7	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3	1335.3
170°	1343.1	1341.8	1340.4	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2	1343.0
172.5°	1348.0	1346.6	1345.3	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1	1347.9
175°	1353.3	1351.9	1350.6	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6	1353.6
177.5°	1355.8	1354.5	1353.3	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4	1355.9
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	990.0	990.6	993.4	995.6	996.2	999.3	999.6
5°	1077.0	1083.6	1096.4	1097.6	1099.5	1109.7	1101.9
7.5°	1178.9	1195.7	1206.9	1216.8	1220.4	1224.8	1223.9
10°	1244.3	1269.2	1281.6	1301.5	1302.3	1307.3	1304.2
12.5°	1310.0	1338.9	1361.6	1365.3	1381.9	1384.5	1388.9
15°	1403.0	1433.8	1465.3	1476.6	1499.5	1505.0	1513.5
17.5°	1490.5	1521.9	1544.0	1573.2	1582.6	1595.2	1586.7
20°	1538.4	1572.7	1600.7	1623.6	1633.4	1640.4	1639.6
22.5°	1567.4	1601.9	1624.6	1642.0	1651.1	1654.1	1653.9
25°	1585.5	1605.4	1612.4	1619.0	1608.9	1605.4	1606.9
27.5°	1535.1	1529.9	1511.7	1487.7	1462.8	1443.0	1432.3
30°	1465.7	1435.3	1407.7	1359.5	1334.5	1319.8	1306.5
32.5°	1367.3	1319.2	1266.1	1221.9	1193.5	1171.6	1168.3
35°	1198.8	1126.4	1061.4	1007.3	979.3	955.6	950.1
37.5°	1019.2	944.0	885.5	837.8	807.7	791.0	775.4
40°	899.9	835.4	777.8	737.3	714.4	702.3	692.6
42.5°	808.1	749.1	691.9	661.0	640.3	632.9	627.2
45°	681.3	626.4	586.7	563.4	551.3	538.9	533.0
47.5°	579.7	535.1	508.9	489.1	476.2	468.8	465.0
50°	522.1	485.6	462.2	447.1	435.4	429.5	426.4
52.5°	471.1	441.1	421.5	409.4	401.5	397.2	395.9
55°	405.8	382.9	370.4	359.9	354.1	350.2	348.6
57.5°	352.7	335.1	325.0	316.3	314.1	310.8	309.7
60°	317.9	304.3	295.7	289.9	287.9	284.0	284.8
62.5°	287.1	275.9	268.6	265.3	262.7	259.4	260.5
65°	242.8	234.6	230.7	227.6	224.5	222.6	224.1
67.5°	203.7	198.1	192.8	191.0	189.5	189.2	187.5
70°	178.2	173.5	168.9	167.7	167.7	166.1	165.7
72.5°	153.6	150.2	147.1	146.2	145.0	145.6	144.0
75°	118.7	115.9	114.8	113.6	113.2	113.2	112.1
77.5°	87.7	85.7	83.8	83.8	82.4	81.9	81.7
80°	66.5	65.8	64.2	64.2	63.4	63.8	63.0
82.5°	50.0	48.9	48.6	48.0	46.9	47.0	46.2
85°	26.8	25.7	25.3	24.1	23.3	24.1	23.3
87.5°	14.6	14.6	14.4	13.9	13.7	13.8	12.9
90°	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	25.5	26.9	27.6	27.7	27.8	27.9	28.0
95°	26.3	27.7	28.5	28.7	28.9	29.2	29.4
97.5°	27.2	27.3	27.5	27.7	27.9	28.1	28.4
100°	33.1	29.3	27.5	27.7	27.9	28.1	28.4
102.5°	90.9	49.6	29.0	29.0	29.1	29.1	29.2
105°	322.2	324.2	321.2	313.1	305.0	296.9	288.8
107.5°	397.1	398.1	399.0	399.9	400.7	401.6	402.4
110°	448.2	448.6	449.2	449.9	450.5	451.2	451.9



TEST NUMBER: P332757

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	497.6	497.5	497.9	498.8	499.6	500.5	501.3
115°	572.8	573.2	573.5	573.5	573.5	573.5	573.5
117.5°	647.4	647.3	647.2	647.1	647.0	646.9	646.8
120°	694.4	694.8	694.8	694.4	693.9	693.5	693.0
122.5°	740.0	740.3	740.2	739.8	739.3	738.9	738.4
125°	804.5	805.1	805.6	805.8	806.0	806.3	806.5
127.5°	867.3	867.1	867.0	866.8	866.6	866.4	866.3
130°	906.5	906.7	906.8	906.8	906.8	906.8	906.8
132.5°	944.6	944.8	944.8	944.6	944.4	944.3	944.1
135°	997.3	997.8	998.2	998.7	999.1	999.6	1000.0
137.5°	1047.7	1048.2	1048.4	1048.2	1048.1	1048.0	1047.8
140°	1079.0	1079.7	1080.2	1080.4	1080.6	1080.8	1081.1
142.5°	1107.7	1108.2	1108.4	1108.5	1108.5	1108.6	1108.6
145°	1148.6	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1184.7	1184.9	1185.1	1185.4	1185.6	1185.8	1186.0
150°	1207.7	1207.7	1207.8	1208.0	1208.3	1208.5	1208.7
152.5°	1228.2	1228.6	1228.7	1228.6	1228.4	1228.3	1228.2
155°	1256.0	1256.9	1257.0	1256.3	1255.7	1255.0	1254.3
157.5°	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2
160°	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8
162.5°	1307.0	1308.3	1308.3	1306.7	1305.2	1303.7	1302.1
165°	1324.6	1326.4	1326.2	1324.2	1322.2	1320.2	1318.1
167.5°	1337.3	1339.2	1339.1	1336.9	1334.6	1332.4	1330.1
170°	1344.8	1346.6	1346.4	1344.1	1341.9	1339.6	1337.4
172.5°	1349.7	1351.5	1351.2	1348.7	1346.3	1343.9	1341.4
175°	1355.6	1357.7	1357.3	1354.6	1351.9	1349.2	1346.5
177.5°	1357.3	1358.8	1358.4	1356.2	1354.1	1351.9	1349.8
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6

(END OF REPORT)