

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333026-840

Luminaire Tested: **S124RDIW-S350D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333026-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1050U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5116.2 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	60	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26
3	77	68	61	56	69	62	56	51	49	44	41	36	34	32	25	24	22
4	71	61	53	47	63	54	48	43	43	39	35	33	29	27	23	21	19
5	65	54	46	40	58	49	42	37	39	34	30	29	26	23	20	18	17
6	60	48	40	35	53	44	37	32	35	30	26	26	23	20	19	17	15
7	55	43	36	30	49	39	33	28	31	26	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	16	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	1.1
10°-20°	163.5	3.2
20°-30°	236.1	4.6
30°-40°	267.7	5.2
40°-50°	258.5	5.1
50°-60°	214.9	4.2
60°-70°	148.4	2.9
70°-80°	75.2	1.5
80°-90°	23.2	0.5
90°-100°	87.2	1.7
100°-110°	258.4	5.1
110°-120°	438.7	8.6
120°-130°	578.4	11.3
130°-140°	649.6	12.7
140°-150°	638.4	12.5
150°-160°	536.9	10.5
160°-170°	357.2	7.0
170°-180°	125.1	2.4
0°-30°	458.3	9.0
0°-40°	726.0	14.2
0°-60°	1199.4	23.4
0°-90°	1446.3	28.3
90°-120°	784.3	15.3
90°-150°	2650.7	51.8
90°-180°	3670.0	71.7
0°-180°	5116.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	3	14	22	28	31	5
95°	61	70	78	81	81	68
105°	238	240	244	247	250	253
115°	446	446	444	443	442	440
125°	650	650	649	647	644	579
135°	838	844	844	842	839	648
145°	1018	1022	1023	1022	1019	637
155°	1166	1166	1165	1169	1165	536
165°	1270	1267	1264	1270	1266	358
175°	1321	1316	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.4	9.2	9.1	8.9	8.7	8.8	9.0	9.3	9.6	9.9	10.0
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	21.9	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3
95°	61.4	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5
97.5°	107.2	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8
100°	143.2	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9
102.5°	180.9	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6
105°	238.3	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2
107.5°	298.7	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2
110°	339.6	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.2	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7
115°	446.1	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7
117.5°	506.2	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8
120°	546.3	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2
122.5°	588.0	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4
125°	649.6	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1
127.5°	705.5	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5
130°	744.8	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4
132.5°	784.9	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9
135°	837.9	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5
137.5°	895.5	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5
140°	934.0	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8
142.5°	969.3	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4
145°	1017.9	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1066.2	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2
150°	1095.7	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1123.5	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3
155°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2
157.5°	1202.2	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9
160°	1223.6	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1
162.5°	1243.1	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7
165°	1269.6	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9
167.5°	1289.8	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1
170°	1301.3	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6
172.5°	1309.5	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0
175°	1320.7	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2
177.5°	1324.4	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	10.2	10.4	10.6	10.8	11.0	11.1	11.3	11.5
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.1	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.1	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	124.6	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.4	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.2	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	244.9	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	301.8	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.7	339.3	338.8	339.0	339.6	340.3	341.0	341.7



TEST NUMBER: P333026-840

CATALOG NUMBER: S124RDIW-S350D1050U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.6	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.5	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	504.0	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	545.0	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	586.7	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.7	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	706.0	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.9	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.4	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	843.1	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.9	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.6	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.4	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.6	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1070.0	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1127.8	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1201.6	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1222.8	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1241.9	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1267.2	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1288.5	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1299.9	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1308.5	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1322.9	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)