

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332761

Luminaire Tested: **S124DIW-S575D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332761
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1050U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6686.3 lumens
Efficiency: N/A
Efficacy: 147.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.4
10°-20°	257.7	3.9
20°-30°	379.3	5.7
30°-40°	440.9	6.6
40°-50°	440.9	6.6
50°-60°	385.7	5.8
60°-70°	286.4	4.3
70°-80°	162.7	2.4
80°-90°	50.9	0.8
90°-100°	46.3	0.7
100°-110°	295.4	4.4
110°-120°	565.1	8.5
120°-130°	717.4	10.7
130°-140°	767.5	11.5
140°-150°	717.7	10.7
150°-160°	578.8	8.7
160°-170°	373.3	5.6
170°-180°	128.7	1.9
0°-30°	728.4	10.9
0°-40°	1169.3	17.5
0°-60°	1996.0	29.9
0°-90°	2496.0	37.3
90°-120°	906.8	13.6
90°-150°	3109.5	46.5
90°-180°	4190.0	62.7
0°-180°	6686.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	3	14	22	28	30	5
95°	56	23	22	28	29	72
105°	305	311	316	323	289	319
115°	569	572	571	573	574	560
125°	800	804	802	805	806	714
135°	993	992	996	998	1000	765
145°	1145	1148	1148	1149	1151	715
155°	1255	1256	1253	1257	1254	579
165°	1324	1319	1319	1326	1318	374
175°	1355	1349	1350	1358	1346	129
180°	1355	1355	1355	1355	1355	



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.8	17.2	17.5	17.9	18.2	18.5	18.7	19.0	19.2	19.4	19.7
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	12.8	12.9	13.0	13.2	13.3	14.3	16.1	17.9	19.7	21.5	22.8
95°	55.7	48.1	40.4	32.8	25.1	21.4	21.6	21.8	22.1	22.3	23.6
97.5°	118.3	123.1	127.9	132.7	137.4	127.3	102.1	77.0	51.9	26.7	26.9
100°	166.2	170.2	174.3	178.3	182.4	168.9	137.8	106.7	75.7	44.6	40.8
102.5°	219.7	222.6	225.6	228.6	231.5	231.0	227.0	222.9	218.8	214.8	173.5
105°	305.0	306.3	307.7	309.0	310.4	311.6	312.7	313.9	315.0	316.1	318.1
107.5°	384.2	384.9	385.5	386.2	386.9	388.0	389.5	391.1	392.6	394.1	395.1
110°	437.7	438.4	439.0	439.7	440.4	441.4	442.8	444.1	445.5	446.8	447.3



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.6	490.8	492.0	493.2	494.4	495.4	496.0	496.6	497.2	497.9	497.8
115°	569.4	570.1	570.8	571.4	572.1	572.3	572.1	571.9	571.7	571.4	571.9
117.5°	641.3	642.2	643.1	644.0	644.9	645.6	646.1	646.6	647.1	647.6	647.5
120°	690.0	690.9	691.8	692.7	693.6	693.9	693.7	693.5	693.2	693.0	693.5
122.5°	735.4	735.9	736.4	737.0	737.5	738.0	738.3	738.6	738.9	739.2	739.5
125°	800.4	801.3	802.2	803.1	804.0	804.2	803.8	803.3	802.9	802.4	803.1
127.5°	862.0	862.2	862.5	862.7	862.9	863.5	864.6	865.6	866.6	867.7	867.6
130°	901.7	902.0	902.2	902.4	902.6	903.1	903.8	904.4	905.1	905.8	906.0
132.5°	938.2	938.6	939.0	939.4	939.8	940.5	941.3	942.2	943.0	943.9	944.1
135°	992.9	992.7	992.5	992.2	992.0	992.4	993.3	994.2	995.1	996.0	996.4
137.5°	1041.3	1041.4	1041.5	1041.6	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7
140°	1073.0	1073.4	1073.9	1074.3	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7
142.5°	1101.3	1102.1	1102.9	1103.8	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7
145°	1144.9	1145.6	1146.2	1146.9	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2
147.5°	1179.5	1180.8	1182.1	1183.3	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4
150°	1204.7	1205.6	1206.5	1207.4	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7
152.5°	1225.7	1226.5	1227.2	1227.9	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5
155°	1255.3	1255.6	1255.8	1256.0	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2
157.5°	1280.3	1280.1	1280.0	1279.8	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4
160°	1294.8	1294.2	1293.5	1292.8	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1
162.5°	1307.8	1307.0	1306.1	1305.2	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3
165°	1324.2	1323.1	1322.0	1320.8	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0
167.5°	1337.2	1336.0	1334.9	1333.7	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3
170°	1344.5	1343.1	1341.8	1340.4	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2
172.5°	1349.3	1348.0	1346.6	1345.3	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1
175°	1354.6	1353.3	1351.9	1350.6	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6
177.5°	1357.0	1355.8	1354.5	1353.3	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	19.9	20.2	20.5	20.7	20.7	20.8	20.9	21.0
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	24.2	25.5	26.9	27.6	27.7	27.8	27.9	28.0
95°	25.0	26.3	27.7	28.5	28.7	28.9	29.2	29.4
97.5°	27.0	27.2	27.3	27.5	27.7	27.9	28.1	28.4
100°	36.9	33.1	29.3	27.5	27.7	27.9	28.1	28.4
102.5°	132.2	90.9	49.6	29.0	29.0	29.1	29.1	29.2
105°	320.2	322.2	324.2	321.2	313.1	305.0	296.9	288.8
107.5°	396.1	397.1	398.1	399.0	399.9	400.7	401.6	402.4
110°	447.7	448.2	448.6	449.2	449.9	450.5	451.2	451.9



TEST NUMBER: P332761

CATALOG NUMBER: S124DIW-S575D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.7	497.6	497.5	497.9	498.8	499.6	500.5	501.3
115°	572.3	572.8	573.2	573.5	573.5	573.5	573.5	573.5
117.5°	647.4	647.4	647.3	647.2	647.1	647.0	646.9	646.8
120°	693.9	694.4	694.8	694.8	694.4	693.9	693.5	693.0
122.5°	739.8	740.0	740.3	740.2	739.8	739.3	738.9	738.4
125°	803.8	804.5	805.1	805.6	805.8	806.0	806.3	806.5
127.5°	867.4	867.3	867.1	867.0	866.8	866.6	866.4	866.3
130°	906.2	906.5	906.7	906.8	906.8	906.8	906.8	906.8
132.5°	944.3	944.6	944.8	944.8	944.6	944.4	944.3	944.1
135°	996.9	997.3	997.8	998.2	998.7	999.1	999.6	1000.0
137.5°	1047.2	1047.7	1048.2	1048.4	1048.2	1048.1	1048.0	1047.8
140°	1078.4	1079.0	1079.7	1080.2	1080.4	1080.6	1080.8	1081.1
142.5°	1107.2	1107.7	1108.2	1108.4	1108.5	1108.5	1108.6	1108.6
145°	1148.4	1148.6	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1184.6	1184.7	1184.9	1185.1	1185.4	1185.6	1185.8	1186.0
150°	1207.7	1207.7	1207.7	1207.8	1208.0	1208.3	1208.5	1208.7
152.5°	1227.9	1228.2	1228.6	1228.7	1228.6	1228.4	1228.3	1228.2
155°	1255.1	1256.0	1256.9	1257.0	1256.3	1255.7	1255.0	1254.3
157.5°	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2
160°	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8
162.5°	1305.6	1307.0	1308.3	1308.3	1306.7	1305.2	1303.7	1302.1
165°	1322.8	1324.6	1326.4	1326.2	1324.2	1322.2	1320.2	1318.1
167.5°	1335.3	1337.3	1339.2	1339.1	1336.9	1334.6	1332.4	1330.1
170°	1343.0	1344.8	1346.6	1346.4	1344.1	1341.9	1339.6	1337.4
172.5°	1347.9	1349.7	1351.5	1351.2	1348.7	1346.3	1343.9	1341.4
175°	1353.6	1355.6	1357.7	1357.3	1354.6	1351.9	1349.2	1346.5
177.5°	1355.9	1357.3	1358.8	1358.4	1356.2	1354.1	1351.9	1349.8
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6

(END OF REPORT)