

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-840

Luminaire Tested: **S124RDIW-S350D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333017-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3336.9 lumens
Efficiency: N/A
Efficacy: 145.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	1.8
10°-20°	163.5	4.9
20°-30°	236.1	7.1
30°-40°	267.7	8.0
40°-50°	258.5	7.7
50°-60°	214.9	6.4
60°-70°	148.4	4.4
70°-80°	75.2	2.3
80°-90°	21.1	0.6
90°-100°	20.9	0.6
100°-110°	133.4	4.0
110°-120°	255.3	7.6
120°-130°	324.0	9.7
130°-140°	346.7	10.4
140°-150°	324.2	9.7
150°-160°	261.4	7.8
160°-170°	168.6	5.1
170°-180°	58.1	1.7
0°-30°	458.3	13.7
0°-40°	726.0	21.8
0°-60°	1199.4	35.9
0°-90°	1444.1	43.3
90°-120°	409.6	12.3
90°-150°	1404.6	42.1
90°-180°	1893.0	56.7
0°-180°	3336.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	1	6	10	13	14	2
95°	25	10	10	13	13	32
105°	138	140	143	146	130	144
115°	257	258	258	259	259	253
125°	362	363	362	364	364	323
135°	448	448	450	451	452	345
145°	517	518	519	519	520	323
155°	567	567	566	568	567	261
165°	598	596	596	599	595	169
175°	612	609	610	613	608	58
180°	612	612	612	612	612	



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.1	8.6	8.2	7.7	7.3	7.1	7.2	7.2	7.3	7.4	7.4
90°	1.4	2.5	3.6	4.7	5.9	6.8	7.7	8.5	9.3	10.1	10.7
92.5°	5.8	5.9	5.9	6.0	6.1	6.5	7.3	8.1	8.9	9.7	10.3
95°	25.1	21.7	18.3	14.8	11.3	9.7	9.8	9.9	10.0	10.1	10.7
97.5°	53.4	55.6	57.8	59.9	62.1	57.5	46.2	34.7	23.4	12.1	12.1
100°	75.0	76.9	78.8	80.6	82.4	76.2	62.2	48.2	34.1	20.1	18.4
102.5°	99.3	100.6	101.9	103.2	104.6	104.3	102.5	100.7	98.9	97.0	78.4
105°	137.7	138.4	139.0	139.6	140.2	140.8	141.3	141.8	142.3	142.8	143.7
107.5°	173.6	173.9	174.2	174.5	174.8	175.3	175.9	176.6	177.3	178.0	178.4
110°	197.7	198.0	198.3	198.6	198.9	199.3	200.0	200.7	201.3	201.9	202.1



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	221.2	221.7	222.3	222.8	223.4	223.8	224.1	224.3	224.6	224.9	224.9
115°	257.2	257.5	257.8	258.1	258.4	258.5	258.4	258.3	258.2	258.1	258.3
117.5°	289.7	290.1	290.5	290.9	291.3	291.6	291.9	292.1	292.4	292.6	292.5
120°	311.6	312.0	312.5	312.9	313.3	313.5	313.4	313.3	313.2	313.1	313.3
122.5°	332.1	332.4	332.6	333.0	333.2	333.4	333.5	333.7	333.8	334.0	334.1
125°	361.5	361.9	362.3	362.7	363.1	363.2	363.0	362.8	362.6	362.4	362.7
127.5°	389.4	389.5	389.6	389.7	389.8	390.1	390.5	391.0	391.5	391.9	391.9
130°	407.3	407.4	407.6	407.7	407.8	408.0	408.3	408.6	408.9	409.2	409.3
132.5°	423.8	423.9	424.1	424.3	424.5	424.9	425.3	425.6	426.0	426.4	426.5
135°	448.5	448.4	448.3	448.2	448.1	448.3	448.7	449.1	449.5	449.9	450.1
137.5°	470.4	470.4	470.5	470.5	470.6	470.8	471.2	471.7	472.1	472.6	472.8
140°	484.6	484.8	485.0	485.2	485.4	485.6	485.8	486.1	486.4	486.6	486.9
142.5°	497.5	497.9	498.3	498.6	499.0	499.2	499.3	499.5	499.6	499.7	499.9
145°	517.2	517.5	517.8	518.1	518.4	518.6	518.6	518.6	518.6	518.6	518.7
147.5°	532.8	533.4	533.9	534.5	535.1	535.3	535.2	535.1	535.0	534.9	535.0
150°	544.2	544.6	545.0	545.4	545.8	545.9	545.8	545.7	545.6	545.5	545.5
152.5°	553.7	554.0	554.3	554.6	555.0	555.0	554.9	554.7	554.5	554.3	554.5
155°	567.0	567.1	567.2	567.3	567.4	567.3	567.0	566.7	566.4	566.1	566.5
157.5°	578.3	578.2	578.1	578.1	578.0	577.8	577.5	577.1	576.8	576.5	577.0
160°	584.9	584.6	584.3	584.0	583.7	583.5	583.4	583.3	583.2	583.1	583.7
162.5°	590.8	590.4	590.0	589.6	589.3	589.0	588.9	588.8	588.7	588.5	589.2
165°	598.1	597.6	597.1	596.6	596.1	595.9	595.9	595.9	595.9	595.9	596.7
167.5°	604.0	603.5	603.0	602.5	601.9	601.6	601.6	601.5	601.5	601.4	602.3
170°	607.3	606.7	606.1	605.5	604.9	604.6	604.7	604.8	604.9	605.0	605.8
172.5°	609.6	608.9	608.3	607.7	607.1	606.8	606.9	607.0	607.1	607.2	608.0
175°	611.9	611.3	610.7	610.1	609.5	609.3	609.4	609.5	609.6	609.7	610.6
177.5°	613.0	612.5	611.9	611.3	610.8	610.6	610.7	610.9	611.0	611.2	611.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	7.5	7.5	7.5	7.6	7.7	7.9	8.0	8.1
90°	11.3	11.9	12.5	12.9	13.1	13.3	13.5	13.7
92.5°	10.9	11.5	12.1	12.4	12.5	12.5	12.6	12.6
95°	11.3	11.9	12.5	12.8	12.9	13.0	13.1	13.2
97.5°	12.2	12.2	12.3	12.4	12.5	12.6	12.7	12.8
100°	16.7	14.9	13.2	12.4	12.5	12.6	12.7	12.8
102.5°	59.7	41.1	22.4	13.1	13.1	13.1	13.1	13.2
105°	144.6	145.5	146.4	145.1	141.4	137.7	134.1	130.5
107.5°	178.9	179.4	179.9	180.3	180.7	181.0	181.4	181.8
110°	202.3	202.5	202.7	202.9	203.2	203.5	203.8	204.1



TEST NUMBER: P333017-840

CATALOG NUMBER: S124RDIW-S350D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	224.8	224.8	224.7	224.9	225.3	225.7	226.1	226.4
115°	258.5	258.7	258.9	259.0	259.0	259.0	259.0	259.0
117.5°	292.5	292.5	292.4	292.4	292.3	292.3	292.3	292.2
120°	313.5	313.7	313.9	313.9	313.7	313.5	313.3	313.1
122.5°	334.2	334.3	334.4	334.4	334.2	334.0	333.8	333.6
125°	363.0	363.3	363.7	363.9	364.0	364.1	364.2	364.3
127.5°	391.8	391.7	391.7	391.6	391.5	391.4	391.4	391.3
130°	409.4	409.5	409.6	409.6	409.6	409.6	409.6	409.6
132.5°	426.6	426.7	426.8	426.8	426.7	426.7	426.6	426.5
135°	450.3	450.5	450.7	450.9	451.1	451.3	451.5	451.7
137.5°	473.0	473.2	473.5	473.5	473.5	473.4	473.4	473.3
140°	487.2	487.5	487.8	488.0	488.1	488.2	488.3	488.4
142.5°	500.1	500.4	500.6	500.7	500.7	500.8	500.8	500.8
145°	518.8	518.9	519.0	519.1	519.3	519.5	519.7	519.9
147.5°	535.1	535.1	535.2	535.3	535.4	535.5	535.6	535.7
150°	545.5	545.5	545.5	545.6	545.7	545.8	545.9	546.0
152.5°	554.6	554.8	555.0	555.0	555.0	554.9	554.8	554.8
155°	566.9	567.3	567.7	567.8	567.5	567.2	566.9	566.6
157.5°	577.5	578.0	578.6	578.6	578.0	577.5	577.0	576.5
160°	584.3	584.9	585.5	585.5	584.9	584.3	583.7	583.1
162.5°	589.8	590.4	591.0	591.0	590.3	589.6	588.9	588.2
165°	597.5	598.3	599.2	599.1	598.1	597.2	596.3	595.4
167.5°	603.2	604.1	605.0	604.9	603.9	602.9	601.9	600.9
170°	606.6	607.4	608.3	608.2	607.1	606.1	605.1	604.1
172.5°	608.8	609.7	610.5	610.4	609.3	608.1	607.0	605.9
175°	611.5	612.4	613.3	613.1	611.9	610.7	609.5	608.2
177.5°	612.5	613.1	613.8	613.6	612.7	611.7	610.7	609.8
180°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9

(END OF REPORT)